



-1. Lindström Precision Tools

-1.1. ELECTRONICS AND FINE MECHANICAL PLIERS

- Material: High performance alloy steel
- Black finish
- Numerically controlled machine grinding guarantees edge angle accuracy and contact, increasing the tools reliability and consistency
- Precision induction hardened edges 63-65 HRC
- Screw joint that minimizes friction and maximizes alignment of cutting edges
- ESD safe handles in synthetic material with return spring
- Ideal for use in confined spaces and for rework
- The cutting capacity that is given is for copper wire
- "CO" standard handle shape in conductive material

80-Series Diagonal cutters Tapered and relieved head

8146-8158

			A mm	B mm	C mm	D mm	F mm			
8146	7314150051076	10	110.0	10.0	10.0	6	0.8	0.2-1.0	Micro	46
8147	7314150051083	10	110.0	10.0	10.0	6	0.8	0.1-1.0	Flush	46
8148	7314150051090	10	110.0	10.0	10.0	6	0.8	0.1-0.8	Ultra	45
8148 CO	7314150051656	10	110.0	10.0	10.0	6	0.8	0.1-0.8	Ultra	45
8156	7314150051212	10	112.5	12.5	12.5	6	1.0	0.3-1.25	Micro	49
8157	7314150052127	10	112.5	12.5	12.5	6	1.0	0.2-1.25	Flush	49
8158	7314150052134	10	112.5	12.5	12.5	6	1.0	0.2-1.0	Ultra	49

