

8146-8158

ELECTRONICS AND FINE MECHANICAL PLIERS


80-Series Diagonal cutters Tapered and relieved head



These cutters are made from high performance ball bearing steel, black oxidised. Numerically controlled machine grinding guarantees edge angle accuracy and contact which increases the tools reliability and consistency.

Precision induction hardened edges, 63-65 HRC. Handles in synthetic material and come with return spring.

The cutting capacity that is given is for copper wire!

These Tapered and Relieved Head cutters are ideal for use in confined spaces and for rework.



Product	EAN-code		A	B	C	D	F	Capacity	Bevel	 g
code	731415+		mm	mm	mm	mm	mm	mm		
8146	0051076	1	110	10	10	6	0,8	0,2-1,0	Micro	46
8147	0051083	1	110	10	10	6	0,8	0,1-1,0	Flush	46
8148	0051090	1	110	10	10	6	0,8	0,1-0,8	Ultra	45
8156	0051212	1	112,5	12,5	12,5	6	1,0	0,3-1,25	Micro	49
8157	0052127	1	112,5	12,5	12,5	6	1,0	0,2-1,25	Flush	49
8158	0052134	1	112,5	12,5	12,5	6	1,0	0,2-1,0	Ultra	49