

# I<sup>2</sup>C-Compatible 256-Position Digital Potentiometers

### **FEATURES**

- 256 positions
- 10 kΩ, 100 kΩ, 1 MΩ
- ▶ Low temperature coefficient: 30 ppm/°C
- Internal power on midscale preset
- Single-supply 2.7 V to 5.5 V or dual-supply ±2.7 V for ac or bipolar operation
- I<sup>2</sup>C-compatible interface with readback capability
- Extra programmable logic outputs
- Self contained shutdown feature
- ▶ Extended temperature range: -40°C to +105°C

### **APPLICATIONS**

- Multimedia, video, and audio
- Communications
- Mechanical potentiometer replacement
- Instrumentation: gain, offset adjustment
- Programmable voltage-to-current conversion
- ► Line impedance matching

### **GENERAL DESCRIPTION**

The AD5241/AD5242<sup>1</sup> provide a single-/dual-channel, 256-position, digitally controlled variable resistor (VR) device. These devices perform the same electronic adjustment function as a potentiometer, trimmer, or variable resistor. Each VR offers a completely programmable value of resistance between the A terminal and the wiper, or the B terminal and the wiper. For the AD5242, the fixed A-to-B terminal resistance of 10 k $\Omega$ , 100 k $\Omega$ , or 1 M $\Omega$  has a 1% channel-to-channel matching tolerance. The nominal temperature coefficient of both parts is 30 ppm/°C.

Wiper position programming defaults to midscale at system power on. When powered, the VR wiper position is programmed by an I<sup>2</sup>C-compatible, 2-wire serial data interface. Both parts have two extra programmable logic outputs available that enable users to drive digital loads, logic gates, LED drivers, and analog switches in their system.

The AD5241/AD5242 are available in surface-mount, 14-lead SO-IC and 16-lead SOIC packages and, for ultracompact solutions, 14-lead TSSOP and 16-lead TSSOP packages. All parts are guaranteed to operate over the extended temperature range of  $-40^{\circ}$ C to +105°C.

### FUNCTIONAL BLOCK DIAGRAM




Figure 1. AD5241 Functional Block Diagram





Figure 2. AD5242 Functional Block Diagram

<sup>1</sup> Patent Number 5,495,245 applies.

Rev. E



Information furnished by Analog Devices is believed to be accurate and reliable "as is". However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

### TABLE OF CONTENTS

Features	1
Applications	1
Functional Block Diagram	1
General Description	1
Specifications	3
10 kΩ, 100 kΩ, 1 MΩ Version	
Timing Specifications	4
Timing Diagrams	5
Absolute Maximum Ratings	6
ESD Caution	6
Pin Configurations and Function Descriptions	7
Typical Performance Characteristics	8
Test Circuits	11

Theory of Operation	12
Programming the Variable Resistor	
Programming the Potentiometer Divider	
Digital Interface	13
Readback RDAC Value	
Multiple Devices on One Bus	14
Level-Shift for Bidirectional Interface	14
Additional Programmable Logic Output	14
Shutdown Function	15
Outline Dimensions	16
Ordering Guide	17
Evaluation Boards	17

## **REVISION HISTORY**

### 1/2022—Rev. D to Rev. E

Deleted Interface Timing Characteristics Parameter, Table 1	3
Changes to Power Single-Supply Range Parameter and Power Dual-Supply Range Parameter, Table 1	3
Added Timing Specifications Section and Table 2; Renumbered Sequentially	4
Moved Figure 32	14
Changes to Ordering Guide	17

### **SPECIFICATIONS**

## 10 KΩ, 100 KΩ, 1 MΩ VERSION

 $V_{DD}$  = 2.7 V to 5.5 V,  $V_A$  =  $V_{DD},$   $V_B$  = 0 V, –40°C <  $T_A$  < +105°C, unless otherwise noted.

### Table 1.

Parameter	Symbol	Conditions	Min	Typ <sup>1</sup>	Мах	Unit	
DC CHARACTERISTICS, RHEOSTAT MODE (SPECIFICATIONS APPLY TO ALL VRs)							
Resolution	Ν		8			Bits	
Resistor Differential Nonlinearity <sup>2</sup>	R-DNL	R <sub>WB</sub> , V <sub>A</sub> = no connect	-1	±0.4	+1	LSB	
Resistor Integral Nonlinearity <sup>2</sup>	R-INL	$R_{WB}$ , $V_A$ = no connect	-2	±0.5	+2	LSB	
Nominal Resistor Tolerance	$\Delta R_{AB}/R_{AB}$	T <sub>A</sub> = 25°C, R <sub>AB</sub> = 10 kΩ	-30		+30	%	
		T <sub>A</sub> = 25°C, R <sub>AB</sub> = 100 kΩ/1 MΩ	-30		+50	%	
Resistance Temperature Coefficient	$(\Delta R_{AB}/R_{AB})/\Delta T \times 10^6$	V <sub>AB</sub> = V <sub>DD</sub> , wiper = no connect		30		ppm/°C	
Wiper Resistance	R <sub>W</sub>	$I_W = V_{DD}/R$		60	120	Ω	
DC CHARACTERISTICS, POTENTIOMETER DIVIDER MODE (SPECIFICATIONS APPLY TO ALL VRs)							
Resolution	Ν		8			Bits	
Differential Nonlinearity <sup>3</sup>	DNL		-1	±0.4	+1	LSB	
Integral Nonlinearity <sup>3</sup>	INL		-2	±0.5	+2	LSB	
Voltage Divider Temperature Coefficient	$(\Delta V_W/V_W)/\Delta T \times 10^6$	Code = 0x80		5		ppm/°C	
Full-Scale Error	V <sub>WFSE</sub>	Code = 0xFF	-1	-0.5	0	LSB	
Zero-Scale Error	V <sub>WZSE</sub>	Code = 0x00	0	0.5	1	LSB	
RESISTOR TERMINALS							
Voltage Range <sup>4</sup>	V <sub>A</sub> , V <sub>B</sub> , V <sub>W</sub>		V <sub>SS</sub>		V <sub>DD</sub>	V	
Capacitance (A, B) <sup>5</sup>	C <sub>A</sub> , C <sub>B</sub>	f = 1 MHz, measured to GND, code = 0x80		45		pF	
Capacitance (W) <sup>5</sup>	C <sub>W</sub>	f = 1 MHz, measured to GND, code = 0x80		60		pF	
Common-Mode Leakage	I <sub>CM</sub>	$V_A = V_B = V_W$		1		nA	
DIGITAL INPUTS							
Input Logic High (SDA and SCL)	VIH		0.7 × V <sub>DD</sub>		V <sub>DD</sub> + 0.5 V	V	
Input Logic Low (SDA and SCL)	V <sub>IL</sub>		-0.5		+0.3 × V <sub>DD</sub>	V	
Input Logic High (AD0 and AD1)	V <sub>IH</sub>	V <sub>DD</sub> = 5 V	2.4		V <sub>DD</sub>	V	
Input Logic Low (AD0 and AD1)	V <sub>IL</sub>	$V_{DD} = 5 V$	0		0.8	V	
Input Logic High	V <sub>IH</sub>	V <sub>DD</sub> = 3 V	2.1		V <sub>DD</sub>	V	
Input Logic Low	V <sub>IL</sub>	V <sub>DD</sub> = 3 V	0		0.6	V	
Input Current	IL	$V_{IH}$ = 5 V or $V_{IL}$ = GND			1	μA	
Input Capacitance <sup>5</sup>	C <sub>IL</sub>			3		pF	
DIGITAL OUTPUT	V <sub>OL</sub>	I <sub>OL</sub> = 3 mA			0.4	V	
Output Logic Low (SDA)	V <sub>OL</sub>	I <sub>OL</sub> = 6 mA			0.6	V	
Output Logic Low (O <sub>1</sub> and O <sub>2</sub> )	V <sub>OL</sub>	I <sub>SINK</sub> = 1.6 mA			0.4	V	
Output Logic High (O <sub>1</sub> and O <sub>2</sub> )	V <sub>OH</sub>	I <sub>SOURCE</sub> = 40 μA	4			V	
Three-State Leakage Current (SDA)	I <sub>OZ</sub>	$V_{IH}$ = 5 V or $V_{IL}$ = GND			±1	μA	
Output Capacitance <sup>5</sup>	C <sub>OZ</sub>			3	8	pF	
POWER SUPPLIES							
Power Single-Supply Range	V <sub>DD</sub>	V <sub>SS</sub> = 0 V	2.7		5.5	V	
Power Dual-Supply Range	V <sub>DD</sub> /V <sub>SS</sub>		±2.3		±2.7	V	
Positive Supply Current	I <sub>DD</sub>	$V_{IH}$ = 5 V or $V_{IL}$ = GND		0.1	50	μA	
Negative Supply Current	I <sub>SS</sub>	V <sub>SS</sub> = -2.5 V, V <sub>DD</sub> = +2.5 V		+0.1	-50	μA	

### **SPECIFICATIONS**

#### Table 1.

Parameter	Symbol	Conditions	Min	Typ <sup>1</sup>	Max	Unit
Power Dissipation <sup>6</sup>	P <sub>DISS</sub>	$V_{IH}$ = 5 V or $V_{IL}$ = GND, $V_{DD}$ = 5 V		0.5	250	μW
Power Supply Sensitivity	PSS		-0.01	+0.002	+0.01	%/%
DYNAMIC CHARACTERISTICS <sup>5, 7, 8</sup>						
−3 dB Bandwidth	BW_10 kΩ	$R_{AB} = 10 \text{ k}\Omega$ , code = 0x80		650		kHz
	BW_100 kΩ	$R_{AB}$ = 100 k $\Omega$ , code = 0x80		69		kHz
	BW_1 MΩ	$R_{AB} = 1 M\Omega$ , code = 0x80		6		kHz
Total Harmonic Distortion	THD <sub>w</sub>	$V_A$ = 1 V rms + 2 V dc, $V_B$ = 2 V dc, f = 1 kHz		0.005		%
V <sub>W</sub> Settling Time	t <sub>S</sub>	$V_A = V_{DD}, V_B = 0 V, \pm 1 LSB$ error band, $R_{AB} = 10 k\Omega$		2		μs
Resistor Noise Voltage	e <sub>N WB</sub>	R <sub>WB</sub> = 5 kΩ, f = 1 kHz		14		nV√Hz

<sup>1</sup> Typicals represent average readings at 25°C, V<sub>DD</sub> = 5 V.

<sup>2</sup> Resistor position nonlinearity error R-INL is the deviation from an ideal value measured between the maximum resistance and the minimum resistance wiper positions. R-DNL measures the relative step change from ideal between successive tap positions. Parts are guaranteed monotonic. See Test Circuits.

<sup>3</sup> INL and DNL are measured at V<sub>W</sub> with the RDAC configured as a potentiometer divider similar to a voltage output D/A converter. V<sub>A</sub> = V<sub>DD</sub> and V<sub>B</sub> = 0 V. DNL specification limits of ±1 LSB maximum are guaranteed monotonic operating conditions. See Figure 37.

<sup>4</sup> Resistor Terminal A, Resistor Terminal B, and Resistor Terminal W have no limitations on polarity with respect to each other.

<sup>5</sup> Guaranteed by design, not subject to production test.

<sup>6</sup> P<sub>DISS</sub> is calculated from (I<sub>DD</sub> × V<sub>DD</sub>). CMOS logic level inputs result in minimum power dissipation.

<sup>7</sup> Bandwidth, noise, and settling time are dependent on the terminal resistance value chosen. The lowest R value results in the fastest settling time and highest bandwidth. The highest R value results in the minimum overall power consumption.

<sup>8</sup> All dynamic characteristics use V<sub>DD</sub> = 5 V.

### TIMING SPECIFICATIONS

### Table 2.

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
INTERFACE TIMING CHARACTERISTICS (APPLIES TO ALL PARTS <sup>1, 2</sup> )						
SCL Clock Frequency	f <sub>SCL</sub>		0		400	kHz
Bus Free Time Between Stop and Start, $\mathrm{t}_{\mathrm{BUF}}$	t <sub>1</sub>		1.3			μs
Hold Time (Repeated Start), $t_{\text{HD};\;\text{STA}}$	t <sub>2</sub>	After this period, the first clock pulse is generated	600			ns
Low Period of SCL Clock, t <sub>LOW</sub>	t <sub>3</sub>		1.3			μs
High Period of SCL Clock, t <sub>HIGH</sub>	t <sub>4</sub>		0.6		50	μs
Setup Time for Repeated Start Condition, $t_{SU; STA}$	t <sub>5</sub>		600			ns
Data Hold Time, t <sub>HD; DAT</sub>	t <sub>6</sub>				900	ns
Data Setup Time, t <sub>SU; DAT</sub>	t <sub>7</sub>		100			ns
Rise Time of Both SDA and SCL Signals, $\mathrm{t}_{\mathrm{R}}$	t <sub>8</sub>				300	ns
Fall Time of Both SDA and SCL Signals, ${\rm t}_{\rm F}$	t <sub>9</sub>				300	ns
Setup Time for Stop Condition, t <sub>SU; STO</sub>	t <sub>10</sub>		0.6			μs

<sup>1</sup> Guaranteed by design, not subject to production test.

<sup>2</sup> See timing diagram in Figure 3 for location of measured values.

### **SPECIFICATIONS**

### **TIMING DIAGRAMS**




Figure 3. Detail Timing Diagram

Data of AD5241/AD5242 is accepted from the I<sup>2</sup>C bus in the following serial format.

able 3.										R																	
0	1	0	1	1	AD1	AD0	R/W	Α	Ā/B	S	SD	<b>0</b> 1	02	X	Х	X	A	D7	D6	D5	D4	D3	D2	D1	D0	Α	Ρ
			Slav	e Ac	dress	Byte					Inst	ructio	on Byte	9							Dat	a Byte					
2/W = R 5/B = R[ 2S = Mic 5D = Sh 0 <sub>1</sub> , O <sub>2</sub> =	cor now t ca 00 = Reac DAC dsc utd	ndit ledo re Pa l en C su ale owr itpu	ion ge ckaq able ibad rese i in a t log	e at l dres activ jic p , D2	high a ss sele ctive h ve high in latc 2, D1,	nd outp ect; 0 fo igh. . Same hed va	able add out to SI or RDAC e as exc lues ata bits.	DA. V C1 an cept ii	Vrite er Id 1 for	nable RD/	e at lo AC2.	atche w.	ed wit	h tho	e log	ic st	tates	at P	'in AE	)1 and	d Pin /	AD0.					
			s		CL		0 1	E1 —						2 —			□  BY 241 ■	 X®X	 FI		⊥⊤⊔ ₂χ₀₁χ 		Y 1 TOP BY MASTER	900			
									Fig	ure 4.	Writii	ng to t	the RD	ACS	Serial	Reg	ister										
						STAI MA	SCL SDA RT BY I	⊔^⊥ •∕				AD0/R/W	ACK BY AD5241			ROM P	AME 2 REVIOU			9 CK BY STER STOP B MASTE	- Y X 200						

Figure 5. Reading Data from a Previously Selected RDAC Register in Write Mode

### **ABSOLUTE MAXIMUM RATINGS**

 $T_A = 25^{\circ}C$ , unless otherwise noted.

#### Table 4.

Parameter	Rating
V <sub>DD</sub> to GND	-0.3 V to +7 V
V <sub>SS</sub> to GND	0 V to -7 V
V <sub>DD</sub> to V <sub>SS</sub>	7 V
$V_A$ , $V_B$ , $V_W$ to GND	$V_{SS}$ to $V_{DD}$
I <sub>A</sub> , I <sub>B</sub> , I <sub>W</sub>	
$R_{AB} = 10 \text{ k}\Omega$ in TSSOP-14	5.0 mA <sup>1</sup>
R <sub>AB</sub> = 100 kΩ in TSSOP-14	1.5 mA <sup>1</sup>
$R_{AB} = 1 M\Omega$ in TSSOP-14	0.5 mA <sup>1</sup>
Digital Input Voltage to GND	0 V to V <sub>DD</sub> + 0.3 V
Operating Temperature Range	-40°C to +105°C
Thermal Resistance θ <sub>JA</sub>	
14-Lead SOIC	158°C/W
16-Lead SOIC	73°C/W
14-Lead TSSOP	206°C/W
16-Lead TSSOP	180°C/W
Maximum Junction Temperature (T <sub>J</sub> max)	150°C
Package Power Dissipation	$P_D = (T_J max - T_A)/\theta_{JA}$
Storage Temperature Range	-65°C to +150°C
Lead Temperature	
Vapor Phase, 60 sec	215°C
Infrared, 15 sec	220°C

<sup>1</sup> Maximum current increases at lower resistance and different packages.

Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

### ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

### PIN CONFIGURATIONS AND FUNCTION DESCRIPTIONS




Figure 6. AD5241 Pin Configuration


Pin No.	Mnemonic	Description							
1	A <sub>1</sub>	Resistor Terminal A <sub>1</sub> .							
2	W <sub>1</sub>	Wiper Terminal W <sub>1</sub> .							
3	B <sub>1</sub>	Resistor Terminal B <sub>1</sub> .							
4	V <sub>DD</sub>	Positive Power Supply, Specified for Operation from 2.2 V to 5.5 V.							
5	SHDN	Active low, asynchronous connection of Wiper W to Terminal B, and open circuit of Terminal A. RDAC register contents unchanged. SHDN should tie to V <sub>DD</sub> if not used.							
6	SCL	Serial Clock Input.							
7	SDA	Serial Data Input/Output.							
8	AD0	Programmable Address Bit for Multiple Package Decoding. Bit AD0 and Bit AD1 provide four possible addresses.							
9	AD1	Programmable Address Bit for Multiple Package Decoding. Bit AD0 and Bit AD1 provide four possible addresses.							
10	DGND	Common Ground.							
11	V <sub>SS</sub>	Negative Power Supply, Specified for Operation from 0 V to -2.7 V.							
12	O <sub>2</sub>	Logic Output Terminal O <sub>2</sub> .							
13	NC	No Connect.							
14	01	Logic Output Terminal O <sub>1</sub> .							




Figure 7. AD5242 Pin Configuration


Pin No.	Mnemonic	Description						
1	0 <sub>1</sub>	Logic Output Terminal O <sub>1</sub> .						
2	A <sub>1</sub>	Resistor Terminal A <sub>1</sub> .						
3	W <sub>1</sub>	Wiper Terminal W <sub>1</sub> .						
4	B <sub>1</sub>	Resistor Terminal B <sub>1</sub> .						
5	V <sub>DD</sub>	Positive Power Supply, Specified for Operation from 2.2 V to 5.5 V.						
6	SHDN	Active Low, Asynchronous Connection of Wiper W to Terminal B, and Open Circuit of Terminal A. RDAC register contents unchanged. SHDN should tie to V <sub>DD</sub> , if not used.						
7	SCL	Serial Clock Input.						
8	SDA	Serial Data Input/Output.						
9	AD0	Programmable Address Bit for Multiple Package Decoding. Bit AD0 and Bit AD1 provide four possible addresses.						
10	AD1	Programmable Address Bit for Multiple Package Decoding. Bit AD0 and Bit AD1 provide four possible addresses.						
11	DGND	Common Ground.						
12	V <sub>SS</sub>	Negative Power Supply, Specified for Operation from 0 V to -2.7 V.						
13	O <sub>2</sub>	Logic Output Terminal O <sub>2</sub> .						
14	B <sub>2</sub>	Resistor Terminal B <sub>2</sub> .						
15	W <sub>2</sub>	Wiper Terminal W <sub>2</sub> .						
16	A <sub>2</sub>	Resistor Terminal A <sub>2</sub> .						

### **TYPICAL PERFORMANCE CHARACTERISTICS**












Figure 11. INL vs. Code




Figure 12. Nominal Resistance vs. Temperature






Figure 13. Supply Current vs. Input Logic Voltage

### **TYPICAL PERFORMANCE CHARACTERISTICS**








Figure 15.  $\Delta V_{WB}/\Delta T$  Potentiometer Mode Temperature Coefficient




Figure 16. ΔR<sub>WB</sub>/ΔT Rheostat Mode Temperature Coefficient




Figure 17. Incremental Wiper Contact vs. V<sub>DD</sub>/V<sub>SS</sub>




Figure 18. Supply Current vs. Frequency




Figure 19. AD5242 10 k  $\Omega$  Gain vs. Frequency vs. Code

### **TYPICAL PERFORMANCE CHARACTERISTICS**




Figure 20. AD5242 100 k $\Omega$  Gain vs. Frequency vs. Code







Figure 21. AD5242 1 M $\Omega$  Gain vs. Frequency vs. Code


## **TEST CIRCUITS**

Figure 22 to Figure 30 define the test conditions used in the product specifications table.












Figure 24. Wiper Resistance




Figure 25. Power Supply Sensitivity (PSS, PSRR)




Figure 26. Inverting Gain




Figure 27. Noninverting Gain




Figure 28. Gain vs. Frequency




Figure 29. Incremental On Resistance




Figure 30. Common-Mode Leakage Current

The AD5241/AD5242 provide a single-/dual-channel, 256-position digitally controlled variable resistor (VR) device. The terms VR, RDAC, and programmable resistor are commonly used inter-changeably to refer to digital potentiometer.

To program the VR settings, refer to the Digital Interface section. Both parts have an internal power-on preset that places the wiper in midscale during power-on that simplifies the fault condition recovery at power-up. In addition, the shutdown pin (SHDN) of AD5241/ AD5242 places the RDAC in an almost zero power consumption state where Terminal A is open circuited and Wiper W is connected to Terminal B, resulting in only leakage current being consumed in the VR structure. During shutdown, the VR latch contents are maintained when the RDAC is inactive. When the part returns from shutdown, the stored VR setting is applied to the RDAC.




Figure 31. Equivalent RDAC Circuit

### **PROGRAMMING THE VARIABLE RESISTOR**

### **Rheostat Operation**

The nominal resistance of the RDAC between Terminal A and Terminal B is available in 10 k $\Omega$ , 100 k $\Omega$ , and 1 M $\Omega$ . The final two or three digits of the part number determine the nominal resistance value, for example, 10 k $\Omega$  = 10, 100 k $\Omega$  = 100, and 1 M $\Omega$  = 1 M. The nominal resistance (R<sub>AB</sub>) of the VR has 256 contact points accessed by the wiper terminal, plus the B terminal contact. The 8-bit data in the RDAC latch is decoded to select one of the 256 possible settings. Assume a 10 k $\Omega$  part is used; the first connection of the wiper starts at the B terminal for Data 0x00. Because there is a 60  $\Omega$  wiper contact resistance, such connection yields a minimum of 60  $\Omega$  resistance between Terminal W and Terminal B. The second connection is the first tap point that corresponds to 99  $\Omega$  (R<sub>WB</sub> = R<sub>AB</sub>/256 + R<sub>W</sub> = 39 + 60) for Data 0x01. The third connection is the next tap point representing 138  $\Omega$  (39 × 2 + 60) for Data 0x02, and so on. Each LSB data value increase moves the wiper up the resistor ladder until the last tap point is reached at 10,021 Ω [R<sub>AB</sub> – 1 LSB + R<sub>W</sub>].

Figure 31 shows a simplified diagram of the equivalent RDAC circuit where the last resistor string is not accessed; therefore, there is 1 LSB less of the nominal resistance at full scale in addition to the wiper resistance.

The general equation determining the digitally programmed resistance between W and B is

$$R_{WB}(D) = \frac{D}{256} \times R_{AB} + R_W \tag{1}$$

where:

*D* is the decimal equivalent of the binary code between 0 and 255, which is loaded in the 8-bit RDAC register.

 $R_{AB}$  is the nominal end-to-end resistance.

 $R_W$  is the wiper resistance contributed by the on resistance of the internal switch.

Again, if  $R_{AB} = 10 \text{ k}\Omega$ , Terminal A can be either open circuit or tied to W. Table 7 shows the  $R_{WB}$  resistance based on the code set in the RDAC latch.

Table 7. R <sub>WB</sub> (D) at Selecte	d Codes for $R_{AB}$ = 10 k $\Omega$
---	--------------------------------------

D (DEC)	R <sub>WB</sub> (Ω)	Output State						
255	10,021	Full-scale (R <sub>WB</sub> – 1 LSB + R <sub>W</sub> )						
128	5060	Midscale						
1	99	1 LSB						
0	60	Zero-scale (wiper contact resistance)						

Note that in the zero-scale condition, a finite wiper resistance of 60  $\Omega$  is present. Care should be taken to limit the current flow between W and B in this state to a maximum current of no more than 20 mA. Otherwise, degradation or possible destruction of the internal switch contact can occur.

Similar to the mechanical potentiometer, the resistance of the RDAC between Wiper W and Terminal A also produces a digitally controlled resistance,  $R_{WA}$ . When these terminals are used, Terminal B can be opened or tied to the wiper terminal. The minimum  $R_{WA}$  resistance is for Data 0xFF and increases as the data loaded in the latch decreases in value. The general equation for this operation is

$$R_{WA}(D) = \frac{256 - D}{256} \times R_{AB} + R_W \tag{2}$$

For  $R_{AB}$  = 10 k $\Omega$ , Terminal B can be either open circuit or tied to W. Table 8 shows the  $R_{WA}$  resistance based on the code set in the RDAC latch.

|--|

Table 6. NWA (D) at Selected Codes for NAB - 10 KM2				
D (DEC)	R <sub>WA</sub> (Ω)	Output State		
255	99	Full-scale		
128	5060	Midscale		
1	10,021	1 LSB		
0	10,060	Zero-scale		

The typical distribution of the nominal resistance  $R_{AB}$  from channel to channel matches within ±1% for AD5242. Device-to-device matching is process lot dependent, and it is possible to have ±30% variation. Because the resistance element is processed in thin film

technology, the change in  $R_{AB}$  with temperature has no more than a 30 ppm/°C temperature coefficient.

# PROGRAMMING THE POTENTIOMETER DIVIDER

### Voltage Output Operation

The digital potentiometer easily generates output voltages at wiperto-B and wiper-to-A to be proportional to the input voltage at A-to-B. Unlike the polarity of  $V_{DD}$  / $V_{SS}$ , which must be positive, voltage across terminal A to terminal B, terminal W to terminal A, and terminal W to terminal B can be at either polarity provided that  $V_{SS}$ is powered by a negative supply.

If ignoring the effect of the wiper resistance for approximation, connecting Terminal A to 5 V and Terminal B to ground produces an output voltage at the wiper-to-B starting at 0 V up to 1 LSB less than 5 V. Each LSB of voltage is equal to the voltage applied across Terminal AB divided by the 256 positions of the potentiometer divider. Because AD5241/AD5242 can be supplied by dual supplies, the general equation defining the output voltage at V<sub>W</sub> with respect to ground for any valid input voltage applied to Terminal A and Terminal B is

$$V_W(D) = \frac{D}{256}V_A + \frac{256 - D}{256}V_B \tag{3}$$

which can be simplified to

$$V_W(D) = \frac{D}{256} V_{AB} + V_B$$
(4)

where *D* is the decimal equivalent of the binary code between 0 to 255 that is loaded in the 8-bit RDAC register.

For a more accurate calculation, including the effects of wiper resistance,  $V_W$  can be found as

$$V_W(D) = \frac{R_{WB}(D)}{R_{AB}} V_A + \frac{R_{WA}(D)}{R_{AB}} V_B$$
(5)

where  $R_{WB}(D)$  and  $R_{WA}(D)$  can be obtained from Equation 1 and Equation 2.

Operation of the digital potentiometer in divider mode results in a more accurate operation over temperature. Unlike rheostat mode, the output voltage is dependent on the ratio of the internal resistors,  $R_{WA}$  and  $R_{WB}$ , and not the absolute values; therefore, the temperature drift reduces to 5 ppm/°C.

### DIGITAL INTERFACE

### 2-Wire Serial Bus

The AD5241/AD5242 are controlled via an I<sup>2</sup>C-compatible serial bus. The RDACs are connected to this bus as slave devices.

Referring to Figure 3 and Figure 4, the first byte of AD5241/AD5242 is a slave address byte. It has a 7-bit slave address and an R/ bit. The five MSBs are 01011 and the following two bits are determined

by the state of the AD0 and AD1 pins of the device. AD0 and AD1 allow users to use up to four of these devices on one bus.

The 2-wire, I<sup>2</sup>C serial bus protocol operates as follows:

- The master initiates a data transfer by establishing a start condition, which is when a high-to-low transition on the SDA line occurs while SCL is high (see Figure 4). The following byte is the Frame 1, slave address byte, which consists of the 7-bit slave address followed by an R/W bit (this bit determines whether data is read from or written to the slave device).
- 2. The slave whose address corresponds to the transmitted address responds by pulling the SDA line low during the ninth clock pulse (this is the acknowledge bit). At this stage, all other devices on the bus remain idle while the selected device waits for data to be written to or read from its serial register. If the R/W bit is high, the master reads from the slave device. If the R/W bit is low, the master writes to the slave device.
- 3. A write operation contains an extra instruction byte more than the read operation. The Frame 2 instruction byte in write mode follows the slave address byte. The MSB of the instruction byte labeled A/B is the RDAC subaddress select. A low selects RDAC1 and a high selects RDAC2 for the dual-channel AD5242. Set  $\overline{A}/B$  to low for the AD5241. The second MSB, RS, is the midscale reset. A logic high of this bit moves the wiper of a selected RDAC to the center tap where  $R_{WA} = R_{WB}$ . The third MSB, SD, is a shutdown bit. A logic high on SD causes the RDAC to open circuit at Terminal A while shorting the wiper to Terminal B. This operation yields almost a 0  $\Omega$  rheostat mode or 0 V in potentiometer mode. This SD bit serves the same function as the SHDN pin except that the SHDN pin reacts to active low. The following two bits are  $O_2$  and  $O_1$ . They are extra programmable logic outputs that users can use to drive other digital loads, logic gates, LED drivers, analog switches, and the like. The three LSBs are don't care (see Figure 4).
- 4. After acknowledging the instruction byte, the last byte in write mode is the, Frame 3 data byte. Data is transmitted over the serial bus in sequences of nine clock pulses (eight data bits followed by an acknowledge bit). The transitions on the SDA line must occur during the low period of SCL and remain stable during the high period of SCL (see Figure 4).
- 5. Unlike the write mode, the data byte follows immediately after the acknowledgment of the slave address byte in Frame 2 read mode. Data is transmitted over the serial bus in sequences of nine clock pulses (slightly different from the write mode, there are eight data bits followed by a no acknowledge Logic 1 bit in read mode). Similarly, the transitions on the SDA line must occur during the low period of SCL and remain stable during the high period of SCL (see Figure 5).
- 6. When all data bits have been read or written, a stop condition is established by the master. A stop condition is defined as a low-to-high transition on the SDA line while SCL is high. In write mode, the master pulls the SDA line high during the tenth clock pulse to establish a stop condition (see Figure 4). In read mode,

the master issues a no acknowledge for the ninth clock pulse (that is, the SDA line remains high). The master then brings the SDA line low before the tenth clock pulse, which goes high to establish a stop condition (see Figure 5).

A repeated write function gives the user flexibility to update the RDAC output a number of times after addressing and instructing the part only once. During the write cycle, each data byte updates the RDAC output. For example, after the RDAC has acknowledged its slave address and instruction bytes, the RDAC output is updated. If another byte is written to the RDAC while it is still addressed to a specific slave device with the same instruction, this byte updates the output of the selected slave device. If different instructions are needed, the write mode has to start a completely new sequence with a new slave address, instruction, and data bytes transferred again. Similarly, a repeated read function of the RDAC is also allowed.

### READBACK RDAC VALUE

Specific to the AD5242 dual-channel device, the channel of interest is the one that was previously selected in the write mode. In addition, to read both RDAC values consecutively, users have to perform two write-read cycles. For example, users may first specify the RDAC1 subaddress in write mode (it is not necessary to issue the data byte and stop condition), and then change to read mode to read the RDAC1 value. To continue reading the RDAC2 value, users have to switch back to write mode, specify the subaddress, and then switch once again to read mode to read the RDAC2 value. It is not necessary to issue the write mode data byte or the first stop condition for this operation. Users should refer to Figure 4 and Figure 5 for the programming format.

### **MULTIPLE DEVICES ON ONE BUS**

Figure 32 shows four AD5242 devices on the same serial bus. Each has a different slave address because the state of their AD0 and AD1 pins are different. This allows each RDAC within each device to be written to or read from independently. The master device output bus line drivers are open-drain pull-downs in a fully I<sup>2</sup>C-compatible interface. Note, a device is addressed properly only if the bit information of AD0 and AD1 in the slave address byte matches with the logic inputs at the AD0 and AD1 pins of that particular device.




Figure 32. Multiple AD5242 Devices on One Bus

### LEVEL-SHIFT FOR BIDIRECTIONAL INTERFACE

While most old systems can operate at one voltage, a new component may be optimized at another. When they operate the same signal at two different voltages, a proper method of level-shifting is needed. For instance, a 3.3 V E<sup>2</sup>PROM can be used to interface with a 5 V digital potentiometer. A level-shift scheme is needed to enable a bidirectional communication so that the setting of the digital potentiometer can be stored to and retrieved from the E<sup>2</sup>PROM. Figure 33 shows one of the techniques. M1 and M2 can be N-channel FETs (2N7002) or low threshold FDV301N if V<sub>DD</sub> falls below 2.5 V.




Figure 33. Level-Shift for Different Voltage Devices Operation

### ADDITIONAL PROGRAMMABLE LOGIC OUTPUT

The AD5241/AD5242 feature additional programmable logic outputs,  $O_1$  and  $O_2$ , that can be used to drive digital load, analog switches, and logic gates. They can also be used as a self-contained shutdown preset to Logic 0 that is further explained in the Shutdown Function section.  $O_1$  and  $O_2$  default to Logic 0 during power-up. The logic states of  $O_1$  and  $O_2$  can be programmed in Frame 2 under the write mode (see Figure 4). Figure 34 shows the output stage of  $O_1$ , which employs large P-channel and N-channel MOSFETs in push-pull configuration. As shown in Figure 34, the output is equal to  $V_{DD}$  or  $V_{SS}$ , and these logic outputs have adequate current driving capability to drive milliamperes of load.




Figure 34. Output Stage of Logic Output, O1

Users can also activate  $O_1$  and  $O_2$  in the following three different ways without affecting the wiper settings:

- Start, slave address byte, acknowledge, instruction byte with O<sub>1</sub> and O<sub>2</sub> specified, acknowledge, stop.
- Complete the write cycle with stop, then start, slave address byte, acknowledge, instruction byte with O<sub>1</sub> and O<sub>2</sub> specified, acknowledge, stop.
- Do not complete the write cycle by not issuing the stop, then start, slave address byte, acknowledge, instruction byte with O<sub>1</sub> and O<sub>2</sub> specified, acknowledge, stop.

All digital inputs are protected with a series input resistor and the parallel Zener ESD structures shown in Figure 36. This applies to the digital input pins, SDA, SCL, and SHDN.

### SHUTDOWN FUNCTION

Shutdown can be activated by strobing the SHDN pin or programming the SD bit in the write mode instruction byte (see Table 3). If the RDAC Register 1 or RDAC Register 2 (AD5242 only) is placed in shutdown mode by the software, SD bit, the part returns the wiper to its prior position when a new command is received.

In addition, shutdown can be implemented with the device digital output, as shown in Figure 35. In this configuration, the device is shutdown during power-up but users are allowed to program the device. Thus, when  $O_1$  is programmed high, the device exits shutdown mode and responds to the new setting. This self-contained shutdown function allows absolute shutdown during power-up, which is crucial in hazardous environments, and it does not add extra components.



Figure 35. Shutdown by Internal Logic Output, O1




Figure 36. ESD Protection of Digital Pins




Figure 37. ESD Protection of Resistor Terminals

### **OUTLINE DIMENSIONS**



(RU-16) Dimensions shown in millimeters

### **OUTLINE DIMENSIONS**



Dimensions shown in millimeters and inches

Updated: October 05, 2021

### **ORDERING GUIDE**

Model <sup>1</sup>	Temperature Range	Package Description	Packing Quantity	Package Option
AD5241BRUZ10	-40°C to +105°C	14-Lead TSSOP	Tube, 96	RU-14
AD5241BRUZ100	-40°C to +105°C	14-Lead TSSOP	Tube, 96	RU-14
AD5241BRUZ100-R7	-40°C to +105°C	14-Lead TSSOP	Reel, 1000	RU-14
AD5241BRUZ10-R7	-40°C to +105°C	14-Lead TSSOP	Reel, 1000	RU-14
AD5241BRZ10	-40°C to +105°C	14-Lead SOIC	Tube, 56	R-14
AD5241BRZ100	-40°C to +105°C	14-Lead SOIC	Tube, 56	R-14
AD5241BRZ10-RL7	-40°C to +105°C	14-Lead SOIC	Reel, 1000	R-14
AD5241BRZ1M	-40°C to +105°C	14-Lead SOIC	Tube, 56	R-14
AD5241BRZ1M-REEL	-40°C to +105°C	14-Lead SOIC	Reel, 2500	R-14
AD5242BRUZ10	-40°C to +105°C	16-Lead TSSOP	Tube, 96	RU-16
AD5242BRUZ100	-40°C to +105°C	16-Lead TSSOP	Tube, 96	RU-16
AD5242BRUZ100-RL7	-40°C to +105°C	16-Lead TSSOP	Reel, 1000	RU-16
AD5242BRUZ10-RL7	-40°C to +105°C	16-Lead TSSOP	Reel, 1000	RU-16
AD5242BRUZ1M	-40°C to +105°C	16-Lead TSSOP	Tube, 96	RU-16
AD5242BRUZ1M-REEL7	-40°C to +105°C	16-Lead TSSOP	Reel, 1000	RU-16
AD5242BRZ10	-40°C to +105°C	16-Lead SOIC	Tube, 48	R-16
AD5242BRZ100	-40°C to +105°C	16-Lead SOIC	Tube, 48	R-16
AD5242BRZ100-REEL7	-40°C to +105°C	16-Lead SOIC	Reel, 1000	R-16
AD5242BRZ10-REEL7	-40°C to +105°C	16-Lead SOIC	Reel, 1000	R-16
AD5242BRZ1M	-40°C to +105°C	16-Lead SOIC	Tube, 48	R-16

<sup>1</sup> Z = RoHS Compliant Part.

### **EVALUATION BOARDS**

Model <sup>1</sup>	Package Description	
EVAL-AD5242DBZ	Evaluation Board	

<sup>1</sup> Z = RoHS Compliant Part.

I<sup>2</sup>C refers to a communications protocol originally developed by Philips Semiconductors (now NXP Semiconductors).



# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Analog Devices Inc.:

AD5242BRZ1M AD5242BRUZ100 AD5242BRZ100 AD5242BRUZ1M AD5242BRUZ10 AD5242BRZ10 AD5242BRUZ100-RL7 AD5242BRUZ10-RL7 AD5242BRUZ1M-REEL7 AD5242BRZ100-REEL7 AD5242BRZ10-REEL7 EVAL-AD5242DBZ