

D-ST 6 - End cover

3030433

<https://www.phoenixcontact.com/us/products/3030433>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 36 mm, width: 2.2 mm, height: 69.5 mm, color: gray



Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 3030433 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE29 |
| Product key | BE2Z1X |
| Catalog page | Page 237 (C-1-2019) |
| GTIN | 4017918188023 |
| Weight per piece (including packing) | 3.398 g |
| Weight per piece (excluding packing) | 3.398 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

D-ST 6 - End cover



3030433

<https://www.phoenixcontact.com/us/products/3030433>

Technical data

Product properties

| | |
|--------------|-----------|
| Product type | End cover |
|--------------|-----------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Material specifications

| | |
|--|-------------|
| Color | gray |
| Material | PA |
| Flammability rating according to UL 94 | V0 |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Dimensions

| | |
|--------|---------|
| Width | 2.2 mm |
| Height | 69.5 mm |
| Depth | 36 mm |

D-ST 6 - End cover



3030433

<https://www.phoenixcontact.com/us/products/3030433>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27141133 |
| ECLASS-12.0 | 27141133 |
| ECLASS-13.0 | 27250301 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000886 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

D-ST 6 - End cover



3030433

<https://www.phoenixcontact.com/us/products/3030433>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com