

15mmx15mm LIGHT BAR

Part Number: DE/4ID

HIGH EFFICIENCY RED


Features

- •UNIFORM LIGHT EMITTING AREA.
- •EASILY MOUNTED ON P.C. BOARDS OR INDUSTRY STANDARD SOCKETS.
- •FLUSH MOUNTABLE.
- ●EXCELLENT ON/OFF CONTRAST.
- •CAN BE USED WITH PANELS AND LEGEND MOUNTS.
- •MECHANICALLY RUGGED.
- ●I.C. COMPATIBLE.
- ●RoHS COMPLIANT.

Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

Package Dimensions & Internal Circuit Diagram



Notes:

1. All dimensions are in millimeters (inches), Tolerance is ±0.25(0.01")unless otherwise noted.

2. Specifications are subject to change without notice.





SPEC NO: DSAB7832 REV NO: V.7 DATE: JUL/16/2007 PAGE: 1 OF 3

APPROVED: WYNEC CHECKED: Joe Lee DRAWN: S.J.LIU ERP: 1334000027

Kingbright

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 10mA		Viewing Angle [1]
			Min.	Тур.	2 θ 1/2
DE/4ID	HIGH EFFICIENCY RED (GaAsP/GaP)	RED DIFFUSED	8	31	120°

 $1.\,\theta1/2$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value. 2.Luminous Intensity / Luminous Flux: +/-15%.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627		nm	IF=20mA
λD [1]	Dominant Wavelength	High Efficiency Red	625		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45		nm	IF=20mA
С	Capacitance	High Efficiency Red	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	High Efficiency Red	2.0	2.5	V	IF=20mA
lr	Reverse Current	High Efficiency Red		10	uA	VR = 5V

Notes:

- Wavelength: +/-1nm.
 Forward Voltage: +/-0.1V.

Absolute Maximum Ratings at Ta=25°C


Parameter	High Efficiency Red		
Power dissipation	75	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	160	mA	
Reverse Voltage	5	V	
Operating/Storage Temperature	-40°C To +85°C		
Lead Solder Temperature [2]	260°C For 3~5 Seconds		

Notes:

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.

SPEC NO: DSAB7832 **REV NO: V.7** DATE: JUL/16/2007 PAGE: 2 OF 3 APPROVED: WYNEC **CHECKED:** Joe Lee **DRAWN: S.J.LIU** ERP: 1334000027


Kingbright





RELATIVE INTENSITY Vs. WAVELENGTH


High Efficiency Red


DE/4ID











SPEC NO: DSAB7832 **REV NO: V.7** DATE: JUL/16/2007 PAGE: 3 OF 3 APPROVED: WYNEC **CHECKED:** Joe Lee **DRAWN: S.J.LIU** ERP: 1334000027