Kingbright

4.8mm BI-LEVEL LED INDICATOR

Part Number: L-73EB/2GDA Green


Features

- PRE-TRIMMED LEADS FOR PC BOARD MOUNTING.
- COLORS CAN BE MIXED IN A SINGLE HOUSING.
- I.C. COMPATIBLE.
- BLACK CASE ENHANCES CONTRAST RATIO.
- WIDE VIEWING ANGLE.
- HIGH RELIABILITY LIFE MEASURED IN YEARS.
- UL RATING : 94V-0.
- HOUSING MATERIAL: TYPE 66 NYLON.
- RoHS COMPLIANT.

Description

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions





1. All dimensions are in millimeters (inches).

2. Tolerance is ±0.25(0.01") unless otherwise noted.

Lead spacing is measured where the leads emerge from the package.
Specifications are subject to change without notice.

DATE: JUL/13/2007 **DRAWN: Y.H.CHEN**



Kingbright

Selection Guide

| Part No. | Dice Lens Type | Dice Lens Type [2] | | / | Viewing Angle [1] | | | |
|-------------|----------------|--------------------|------|------|----------------------|--|--|--|
| | | | Min. | Тур. | 201/2 | | | |
| L-73EB/2GDA | Green (GaP) | GREEN DIFFUSED | 8 | 20 | 60° | | | |

Notes:

θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.
Luminous intensity/ luminous Flux: +/-15%.

Electrical / Optical Characteristics at TA=25°C

| Symbol | Parameter | Device | Тур. | Max. | Units | Test Conditions |
|--------|--------------------------|--------|------|------|-------|-----------------|
| λpeak | Peak Wavelength | Green | 565 | | nm | IF=20mA |
| λD [1] | Dominant Wavelength | Green | 568 | | nm | IF=20mA |
| Δλ1/2 | Spectral Line Half-width | Green | 30 | | nm | IF=20mA |
| С | Capacitance | Green | 15 | | pF | VF=0V;f=1MHz |
| VF [2] | Forward Voltage | Green | 2.2 | 2.5 | V | I⊧=20mA |
| lr | Reverse Current | Green | | 10 | uA | VR = 5V |

Notes:

1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.


Absolute Maximum Ratings at TA=25°C

| Green | Units | |
|---------------------|---|--|
| 62.5 | mW | |
| 25 | mA | |
| 140 | mA | |
| 5 | V | |
| -40°C To +85°C | | |
| 260°C For 3 Seconds | | |
| 260°C For 5 Seconds | | |
| | 62.5 25 140 5 -40°C To +85°C 260°C For 3 Seconds | |

Notes:

1.1/10 Duty Cycle, 0.1ms Pulse Width.
2.2mm below package base.
3.5mm below package base.

Kingbright



REV NO: V.7 CHECKED: Allen Liu DATE: JUL/13/2007 DRAWN: Y.H.CHEN