

12SEGMENT BAR GRAPH ARRAY

Part Number: DD-12HWB

BRIGHT RED


Features


- •SUITABLE FOR LEVEL INDICATORS.
- •LOW CURRENT OPERATION.
- •WIDE VIEWING ANGLE.
- •MECHANICALLY RUGGED.
- •DIFFERENT COLORS IN ONE UNIT AVAILABLE.
- •STANDARD: BLACK FACE, WHITE SEGMENT.
- •RoHS COMPLIANT.


Description

The Bright Red source color devices are made with Gallium Phosphide Red Light Emitting Diode.

Package Dimensions & Internal Circuit Diagram







12 NO PIN

Notes:

- 1. All dimensions are in millimeters (inches), Tolerance is $\pm 0.25 (0.01")$ unless otherwise noted.
- 2. Specifications are subject to change without notice.



7.0(0.275)



SPEC NO: DSAA4271 REV NO: V.11 DATE: JUN/07/2007 PAGE: 1 OF 3
APPROVED: WYNEC CHECKED: Joe Lee DRAWN: W.J.HUA

Kingbright

Selection Guide

Part No.	Dice	Lens Type	lv (ucd) [1] @ 10mA		Description
			Min.	Тур.	
DD-12HWB	BRIGHT RED (GaP)	WHITE DIFFUSED	300	1400	12 Segments Bar- graph-Display

Note:

Electrical / Optical Characteristics at Ta=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Bright Red	700		nm	IF=20mA
λD [1]	Dominant Wavelength	Bright Red	660		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Bright Red	45		nm	IF=20mA
С	Capacitance	Bright Red	40		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage (Per Segment)	Bright Red	2.25	2.5	V	Ir=20mA
lr	Reverse Current (Per Segment)	Bright Red		10	uA	VR = 5V

Notes:

Absolute Maximum Ratings at Ta=25°C

Parameter	Bright Red	Units		
Power dissipation (Per Segment)	62.5	mW		
DC Forward Current (Per Segment)	25	mA		
Peak Forward Current [1] (Per Segment)	130	mA		
Reverse Voltage (Per Segment)	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	260°C For 3~5 Seconds			

Notes

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.


SPEC NO: DSAA4271 REV NO: V.11 DATE: JUN/07/2007 PAGE: 2 OF 3
APPROVED: WYNEC CHECKED: Joe Lee DRAWN: W.J.HUA

^{1.} Luminous intensity/ luminous Flux: +/-15%.

^{1.}Wavelength: +/-1nm.

^{2.} Forward Voltage: +/-0.1V.

Kingbright



Bright Red

DD-12HWB

