











TPS65000, TPS65001, TPS650001 TPS650003, TPS650006, TPS650061

SLVS810C -JUNE 2009-REVISED SEPTEMBER 2015

TPS6500xx 2.25-MHz Step-Down Converter With Dual Low Dropouts and Supply Voltage **Supervisor**

Features

- Step-Down Converters:
 - V_{IN} Range From 2.3 V to 6 V
 - Spread Spectrum Clock (SSC) Generation for Reduced EMI
 - 2.25-MHz Fixed Frequency Operation
 - 600-mA or 1-A (TPS650061) Output Current
- Low Dropouts (LDOs):
 - V_{IN} Range From 1.6 V to 6 V
 - Adjustable Output Voltage
 - Up to 300-mA Output Current
 - Separate Power Inputs and Enables
- Supply Voltage Supervisor (TPS65001)
 - Manual Reset Input for Push Button
 - Adjustable Reset Time
 - Adjustable Reset Voltage
- 3-mm × 3-mm 16-Pin WQFN (TPS65000)
- 3-mm × 3-mm 20-Pin WQFN (TPS65001)

Applications

- Points-of-Load
- **Embedded Processor Power**
- Cell Phones
- **Smart Phones**
- **PDAs**
- Pocket PCs
- Portable Media Players

3 Description

The TPS6500xx devices are single-chip power management (PWM) ICs for portable applications. Both devices combine a single step-down converter with two low-dropout (LDO) regulators. The stepdown converter enters a low-power mode at light load for maximum efficiency across the widest possible range of load currents. For low-noise applications, the devices can be forced into fixed-frequency PWM through a pin. The step-down converter is small because of its small inductor and capacitors. The step-down converter has power good status output for sequencing. The LDOs can supply 300 mA and operate with an input voltage range from 1.6 V to 6 V. A step-down converter or main battery can power the LDOs directly. The step-down converter and the LDOs have separate voltage inputs that enable maximum design and sequencing flexibility.

Device Information⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) |
|--|-----------|-------------------|
| TPS65000, TPS650001, TPS650003, TPS650006 | WQFN (16) | 3.00 mm × 3.00 mm |
| TPS65001, TPS650061 | WQFN (20) | 3.00 mm × 3.00 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Application Circuit






Table of Contents

| 1 | Features 1 | | 9.3 Feature Description | 13 |
|---|--------------------------------------|----|--|-----------------|
| 2 | Applications 1 | | 9.4 Device Functional Modes | 19 |
| 3 | Description 1 | 10 | Application and Implementation | 20 |
| 4 | Revision History2 | | 10.1 Application Information | 20 |
| 5 | Description (continued)3 | | 10.2 Typical Application | 20 |
| 6 | Device Options | 11 | Power Supply Recommendations | 26 |
| 7 | Pin Configuration and Functions | 12 | Layout | 27 |
| 8 | _ | | 12.1 Layout Guidelines | |
| 0 | Specifications | | 12.2 Layout Example | <mark>27</mark> |
| | 8.1 Absolute Maximum Ratings | 13 | Device and Documentation Support | 28 |
| | 8.3 Recommended Operating Conditions | | 13.1 Device Support | |
| | 8.4 Thermal Information | | 13.2 Documentation Support | 28 |
| | 8.5 Electrical Characteristics | | 13.3 Related Links | 28 |
| | 8.6 Switching Characteristics | | 13.4 Community Resources | 28 |
| | 8.7 Dissipation Ratings | | 13.5 Trademarks | 28 |
| | 8.8 Typical Characteristics | | 13.6 Electrostatic Discharge Caution | 28 |
| 9 | Detailed Description | | 13.7 Glossary | 29 |
| 3 | 9.1 Overview | | Mechanical, Packaging, and Orderable Information | 29 |
| | 9.2 Functional Block Diagram | | | |

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision B (August 2010) to Revision C

Page

Added ESD Ratings table, Feature Description section, Device Functional Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and Mechanical, Packaging, and Orderable Information section

Changes from Revision A (October 2009) to Revision B

Page

Changes from Original (June 2009) to Revision A

Page

| • | Changed the PG pin connection From: VDCDC To: V _{IN} in the application circuit | 1 |
|---|--|------|
| • | Changed resistor values for VLDO1 and VLDO2 in the application circuit | 1 |
| • | Changed the configuration of the PG and RST pins in the application circuit | 1 |
| • | Added Note 2: to the Electrical Characteristics table. | 6 |
| • | Changed Figure 1 title From: EFFICIENCY (DCDC PFM Mode) To: EFFICIENCY (DCDC 600mA PFM Mode) | 9 |
| • | Changed Figure 2 title From: EFFICIENCY (DCDC PFM Mode) To: EFFICIENCY (DCDC 600mA PFM Mode) | 9 |
| • | Added Figure 3, EFFICIENCY (DCDC PWM Mode) | 9 |
| • | Added Figure 4, EFFICIENCY (DCDC PWM Mode) | 9 |
| • | Changed the configuration of the PG pin in Figure 24 | . 20 |
| • | Changed the \overline{PG} pin connection From: VDCDC To: V _{IN} in Figure 31 | . 24 |
| • | Changed the configuration of the \overline{PG} and \overline{RST} pins in Figure 31 | . 24 |

Submit Documentation Feedback

Copyright © 2009–2015, Texas Instruments Incorporated



5 Description (continued)

The TPS65001 extends functionality by adding a supply voltage supervisor (SVS). To maximize the flexibility of the SVS, the reset voltage is set with two external resistors and the reset time is set by a small external capacitor. For external control, the SVS can use its active-low manual reset input to connect to a push button.

The TPS65000 is available in a 16-pin leadless package (3 mm \times 3 mm QFN). The TPS65001 is available in a 20-pin leadless package (3 mm \times 3 mm QFN).

6 Device Options


| PART NUMBER (1)(2) | OPTIONS | SVS | SSC |
|--------------------|---|----------|----------|
| TPS65000 | LDO voltages externally adjustable DC-DC | N/A | Included |
| TPS65001 | LDO voltages externally adjustable DC-DC converters 600 mA, V _{OUT} externally adjustable Included LDO1 = 1.8 V fixed, LDO2 = 2.8 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.2 V fixed LDO1 = 3.3 V fixed, LDO2 = 1.8 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.5 V fixed LDO1 = 1.8 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.5 V fixed LDO1 = 3.3 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.2 V fixed LDO1 = 3.3 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.2 V fixed LDO1 = 3.3 V fixed, LDO2 = 1.8 V fixed, LDO3 Included | Included | |
| TPS650001 | LDO2 = 2.8 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.2 V | N/A | Included |
| TPS650003 | LDO2 = 1.8 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.5 V | N/A | Included |
| TPS650006 | LDO2 = 3.3 V fixed, DC-DC Converter 600 MA, DCDC VOUT = 1.2 V | N/A | Included |
| TPS650061 | | Included | Included |

⁽¹⁾ TPS650001, TPS650003, and TPS650006 are spin versions of TPS65000. TPS650061 is a spin version of TPS65001. Different DC-DC current limits and fixed voltage outputs of the DC-DC and LDOs are available. Please contact your TI sales representative for further information.

⁽²⁾ For the most current package and ordering information, see the *Mechanical, Packaging, and Orderable Information* at the end of this document, or see the TI website at www.ti.com.



7 Pin Configuration and Functions



Pin Functions

| | PIN | | I/O | DESCRIPTION |
|---------|------------|------------|-----|--|
| NAME | 16-PIN RTE | 20-PIN RUK | 10 | DESCRIPTION |
| AGND | 10 | 12 | | Analog ground - Start back to PGND as close to the IC as possible. |
| EN_DCDC | 8 | 10 | 1 | Enable DC-DC converter |
| EN_LDO1 | 1 | 3 | 1 | Enable LDO1 |
| EN_LDO2 | 2 | 4 | 1 | Enable LDO2 |
| FB_DCDC | 9 | 11 | 1 | Voltage to DC-DC error amplifier |
| FB_LDO1 | 11 | 13 | 1 | Voltage to LDO1 error amplifier |
| FB_LDO2 | 14 | 16 | 1 | Voltage to LDO2 error amplifier |
| MODE | 7 | 9 | I | Selects force PWM or PWM/PFM automatic-transition mode |
| MR | | 1 | _ | Active-low input to force a reset. (1) |
| PG | 3 | 5 | 0 | Open-drain active low power good output. |
| PGND | 4 | 6 | | Power ground – Connected to the thermal pad |
| RST | _ | 20 | 0 | Open-drain active low reset output |
| RSTSNS | _ | 19 | I | Voltage for RST generation |
| SW | 5 | 7 | 0 | Switch pin – connect inductor here |
| TRST | | 2 | 1/0 | Capacitor connection for setting reset time |
| VINDCDC | 6 | 8 | I | Input voltage to DC-DC converter and all other control blocks |
| VINLDO1 | 13 | 15 | 1 | Input voltage to LDO1 |
| VINLDO2 | 16 | 18 | Ι | Input voltage to LDO2 |
| VLDO1 | 12 | 14 | 0 | LDO1 output voltage |
| VLDO2 | 15 | 17 | 0 | LDO2 output voltage |

(1) External pull up on MR is required.



8 Specifications

8.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

| | | MIN | MAX | UNIT |
|--|---|-------------------------------|----------------|-------|
| Input voltage range | On all pins except AGND, PGND, EN_DCDC, VLDO1, VLDO2, FB_LDO1, FB_LDO2, FB_DCDC pins with respect to AGND | -0.3 | 7 | V |
| Input voltage range | On all pins except AGND, PGND, EN_DCDC, VLDO1, VLDO2, FB_LDO1, FB_LDO2, FB_DCDC pins with respect to AGND On EN_DCDC with respect to AGND On VLDO1, VLDO2, FB_LDO1, FB_LDO2, FB_DCDC On VLDO1, VLDO2, FB_LDO1, FB_LDO2, FB_DCDC VINDCDC, SW, PGND, 1800 VINLDO1/2, VLDO1/2, AGND At all other pins otal power dissipation See Dissipation re-air temperature, T_A -40 85 notion temperature, T_J 125 | V _{IN} + 0.3, ≤ 7 | V | |
| Output voltage range | On VLDO1, VLDO2, FB_LDO1, FB_LDO2, FB_DCDC | -0.3 | 3.6 | V |
| | VINDCDC, SW, PGND, | | 1800 | mA |
| Current | VINLDO1/2, VLDO1/2, AGND | | 800 | mA |
| | At all other pins | | 1 | mA |
| Continuous total power | dissipation | See | Dissipation Ra | tings |
| Operating free-air temperature, T _A —40 | | 85 | °C | |
| Maximum junction temperature, T _J | | | 125 | °C |
| Storage temperature, T | stg | -65 | 150 | °C |

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

8.2 ESD Ratings

| | | | VALUE | UNIT |
|--|---|--------------------|-------|------|
| V _(ESD) Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾ | ±2500 | | |
| | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins (2) | ±2000 | V | |
| | | Machine model (MM) | ±750 | |

⁽¹⁾ JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

8.3 Recommended Operating Conditions

| | | MIN | NOM | MAX | UNIT |
|----------------|---|-----|-----|------|------|
| L1 | SW pin inductor | 1.5 | 2.2 | 3.3 | μΗ |
| 0 | Input capacitor at VINDCDC | 10 | | | μF |
| C _I | Input capacitor at VINLDO1/2 | 2.2 | | | μF |
| C | Output capacitor for DCDC | 10 | | 22 | μF |
| Co | Output capacitor for LDO1/2 | 2.2 | | | μF |
| | DC-DC converter output current | | | 600 | mA |
| | DC-DC converter output current (TPS650061 ONLY) | | | 1000 | mA |
| IO | LDO1 output current | | | 300 | mA |
| | LDO2 output current | | | 300 | mA |
| T _A | Operating ambient temperature | -40 | | 85 | °C |

⁽²⁾ JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



8.4 Thermal Information

| | | TPS | | |
|----------------------|--|------------|------------|------|
| | THERMAL METRIC ⁽¹⁾ | RTE (WQFN) | RUK (WQFN) | UNIT |
| | | 16 PINS | 20 PINS | |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance | 44.7 | 46.2 | °C/W |
| $R_{\theta JC(top)}$ | Junction-to-case (top) thermal resistance | 41.7 | 51 | °C/W |
| $R_{\theta JB}$ | Junction-to-board thermal resistance | 16 | 17.8 | °C/W |
| ΨЈТ | Junction-to-top characterization parameter | 0.4 | 0.7 | °C/W |
| Ψ_{JB} | Junction-to-board characterization parameter | 16 | 17.8 | °C/W |
| $R_{\theta JC(bot)}$ | Junction-to-case (bottom) thermal resistance | 4.4 | 4.5 | °C/W |

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

8.5 Electrical Characteristics

Over full operating ambient temperature range, typical values are at T_A = 25°C. Unless otherwise noted, specifications apply for condition V_{IN} = EN_LDOx = EN_DCDC = 3.6 V. External components L = 2.2 μ H, C_{OUT} = 10 μ F, C_{IN} = 4.7 μ F, (see the *Typical Application* section).

| | PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-----------------|--|--|------|------|------|------|
| OPERAT | ING VOLTAGE | | | | | |
| | Input voltage for VINDCDC of DC-DC converter | | 2.3 | | 6 | |
| V_{IN} | Input voltage for LDO1 (VINLDO1) | See ⁽¹⁾ | 1.6 | | 6 | V |
| | Input voltage for LDO2 (VINLDO2) | See ⁽¹⁾ | 1.6 | | 6 | |
| UVLO | Internal undervoltage lockout threshold | V _{CC} falling | 1.72 | 1.77 | 1.82 | V |
| UVLO | Internal undervoltage lockout hysteresis | | | 160 | | mV |
| SUPPLY | CURRENT TPS65000 | | | | | |
| | Operating quiescent current | MODE low, EN_DCDC high, EN_LDO1/2 low, I _{OUT} = 0 mA and no switching | | 23 | 32 | μA |
| I_Q | | MODE low, EN_DCDC low, EN_LDO1/2 high, I _{OUT} = 0 mA I _{OUT} = 0 mA and no switching ⁽²⁾ | | 50 | 57 | μΑ |
| | | EN_DCDC high, MODE high, EN_LDO1/2 low, I _{OUT} = 0 mA | | 4 | | mA |
| I _{SD} | Shutdown Current | EN_DCDC low EN_LDO1 and EN_LDO2 low | | 0.16 | 2.2 | μΑ |
| SUPPLY | CURRENT TPS65001 | | | | | |
| | | MODE low, EN_DCDC high, EN_LDO1/2 low, I _{OUT} = 0 mA and no switching | | 24 | 37 | μΑ |
| l _Q | Operating quiescent current | MODE low, EN_DCDC low, EN_LDO1/2 high, I _{OUT} = 0 mA I _{OUT} = 0 mA and no switching ⁽²⁾ | | 55 | 62 | μΑ |
| | | EN_DCDC high, MODE high, EN_LDO1/2 low, I _{OUT} = 0 mA | | 4 | | mA |
| I _{SD} | Shutdown Current | EN_DCDC low EN_LDO1 and EN_LDO2 low | | 11 | 17 | μΑ |

⁽¹⁾ The design principle lets only VINDCDC be the highest supply in the system if different voltage input supplies separately to DC-DC converter and LDOs, meaning VINDCDC ≥ VINLDO1, VINDCDC ≥ VINLDO2.

⁽²⁾ The max quiescent current of enabling LDOs is 8 μA higher for TPS650001, TPS650003, TPS650006, and TPS650061.



Electrical Characteristics (continued)

Over full operating ambient temperature range, typical values are at T_A = 25°C. Unless otherwise noted, specifications apply for condition V_{IN} = EN_LDOx = EN_DCDC = 3.6 V. External components L = 2.2 μ H, C_{OUT} = 10 μ F, C_{IN} = 4.7 μ F, (see the *Typical Application* section).

| | PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|---------------------|--|---|------------|------------|-------------------|-----------|
| DIGITAL P | PINS (EN_DCDC, EN_LDO1, EN_LDO2 | 2, MODE, PG, MR, RST) | | | | |
| V _{IH} | High-level input voltage | | 1.2 | | | V |
| V _{IL} | Low-level input voltage | | | | 0.4 | V |
| V _{OL} | Low-level output voltage | \overline{PG} and \overline{RST} pins only, $I_O = -100 \mu A$ | | | 0.4 | V |
| I _{lkg} | Input leakage current | MODE, EN_DCDC, EN_LDO1, EN_LDO2 tied to GND or VINDCDC | | 0.01 | 0.1 | μΑ |
| OSCILLAT | OR | | | | • | |
| f_{SW} | Oscillator frequency | | 1.722 | 2.25 | 2.847 | MHz |
| STEP DOV | VN CONVERTER POWER SWITCH | | | | • | |
| R _{DS(on)} | High-side MOSFET ON-resistance Low-side MOSFET ON-resistance | VINDCDC = V _{GS} = 3.6 V | | 240 185 | 480 380 | mΩ |
| | Low side in Col L1 On Tesistand | 2.3 V ≤ VINDCDC ≤ 2.5 V | | 100 | 300 | |
| I_O | DC-output current | 2.5 V ≤ VINDCDC ≤ 6 V | | | 600 | mA |
| Io | DC-output current (TPS650061 ONLY) | 2.7 V ≤ VINDCDC ≤ 6 V | | | 1000 | mA |
| I _{LIMF} | Forward current limit PMOS and NMOS | 2.3 V ≤ VINDCDC ≤ 6 V | 800 | 1000 | 1400 | mA |
| I _{LIMF} | Forward current limit PMOS and NMOS (TPS650061 ONLY) | 2.7 V ≤ VINDCDC ≤ 6 V | 1200 | 1500 | 1680 | mA |
| - | Thermal shutdown | Increasing junction temperature | | 150 | | 00 |
| T_{SD} | Thermal shutdown hysteresis | Decreasing junction temperature | | 30 | | °C |
| STEP DOV | VN CONVERTER OUTPUT VOLTAGE | | | | | |
| VDCDC | Adjustable output voltage range, DCDC | | 0.6 | VIN | IDCDC | V |
| | FB_DCDC pin current | | | | 0.1 | μΑ |
| V _{ref} | Internal reference voltage | | 0.594 | 0.6 | 0.606 | V |
| \/D0D0 | Output Voltage Accuracy (PWM Mode) ⁽³⁾ | MODE = high, 2.3 ≤ VINDCDC ≤ 6 V | -1.5% | 0% | 1.5% | |
| VDCDC | Output Voltage Accuracy (PFM mode) (4) | MODE low 1% voltage positioning active | | 1% | | |
| | Load regulation (PWM mode) | MODE high | | 0.5% | | Α |
| R _{DIS} | Internal discharge resistance at SW | EN_DCDC low | | 450 | | Ω |
| LOW DRO | P OUT REGULATORS | | | | | |
| VI | Input voltage for LDOx (VINLDOx) | | 1.6 | | 6 | V |
| Vo | Adjustable output voltage, LDOx (VLDOx) ⁽⁵⁾ | | 0.73 | VINLDOX | - V _{DO} | V |
| Io | Continuous Pass FET Current | | | | 300 | mA |
| I _{SC} | Short circuit current limit | 2.3 V ≤ VINLDOx VINLDOx < 2.3V | 340 210 | | 700 700 | mA |
| | FB_LDOx pin current | VIII LOGA \ Z.GV | 210 | | 0.1 | μA |
| | FB_LDOx pin current FB_LDOx voltage | Adjustable V _{OUT} mode only | | 0.5 | 0.1 | μA V |
| | | | | 0.5 | 270 | • |
| V_{DO} | Dropout Voltage (6) | VINLDOx ≥ 2.3 V, I _{OUT} = 250 mA | | | 370 | mV m\/ |
| | | $VINLDOx < 2.3V I_{OUT} = 175 mA$ | | 37 | 3/0 | mV |

⁽³⁾ For VINDCDC = VDCDC + 1 V

⁽⁴⁾ In PFM Mode, the internal reference voltage is typ 1.01 \times V_{REF}.

⁽⁵⁾ Maximum output voltage VLDOx = 3.6 V.

⁽⁶⁾ $V_{DO} = VINLDOx - VLDOx where VINLDOx = VLDOx (nominal) - 100 mV$



Electrical Characteristics (continued)

Over full operating ambient temperature range, typical values are at T_A = 25°C. Unless otherwise noted, specifications apply for condition V_{IN} = EN_LDOx = EN_DCDC = 3.6 V. External components L = 2.2 μ H, C_{OUT} = 10 μ F, C_{IN} = 4.7 μ F, (see the *Typical Application* section).

| | PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-------------------|--|--|-------|------|------|------|
| LOW DROP | OUT REGULATORS (continued) | | | | | |
| | Output Voltage Accuracy (7) | I _O = 1 mA to 300 mA, VINLDOx = 2.3 V - 6 V, VLDOx = 1.2 V | -3.5% | | 3.5% | |
| | Output Voltage Accuracy V | I_O = 1mA to 175 mA VINLDOx = 1.6 V - 6 V, VLDOx = 1.2 V | -3.5% | | 3.5% | |
| | Load regulation | I _O = 1mA to 300 mA VINLDOx = 3.6 V VLDOx = 1.2 V | -1.5% | | 1.5% | |
| | Line regulation | VINLDOx = 1.6 V $-$ 6 V VLDOx = 1.2 V at $I_0 = 1$ mA | -0.5% | | 0.5% | |
| PSRR | Power Supply Rejection Ratio | $f_{NOISE} \le 10 \text{ kHz}, C_{OUT} \ge 2.2 \mu\text{F}, V_{IN} = 2.3 \text{ V}, V_{OUT} = 1.3 \text{ V} I_{OUT} = 10 \text{ mA}$ | | 40 | | dB |
| R _{DIS} | Internal discharge resistance at VLDOx | EN_LDOx low | | 450 | | Ω |
| T_{SD} | Thermal shutdown | Increasing temperature | | 150 | | °C |
| | Thermal shutdown hysteresis | Decreasing temperature | | 30 | | °C |
| SUPPLY VO | LTAGE SUPERVISOR | | · | | | |
| V_{IN} | Input voltage for RSTSNS pin | | 0 | | 6 | V |
| t MRDEGLITCH | MR Deglitch time | | | 1 | | ms |
| V _{IH} | Input high voltage | MR pin only | 1.2 | | 6 | V |
| V_{IL} | Input low voltage | MR pin only | 0 | | 0.4 | V |
| I _{lkg} | High-input leakage current | RST pin | | 0.01 | 0.1 | μΑ |
| V _{OL} | Output low voltage | \overline{RST} pin only, $I_O = -100 \mu A$ | | | 0.4 | V |
| I _{TRST} | Reset timer capacitor current | | 1.6 | 2 | 2.2 | μΑ |
| | Reset voltage trip voltage | Voltage rising (Reset time begins) | 0.58 | 0.6 | 0.63 | V |
| | Reset voltage trip hysteresis | Voltage falling (RST pulled low) | | -5% | | |

⁽⁷⁾ Output voltage specification does not include tolerance of external programming resistors.

8.6 Switching Characteristics

over operating free-air temperature range (unless otherwise noted)

| | PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT | | | | |
|------------------------------------|--------------------|-------------------------------------|-----|-----|-----|------|--|--|--|--|
| STEP DOWN CONVERTER OUTPUT VOLTAGE | | | | | | | | | | |
| t _{Start} Start-up time | | EN_DCDC to start of switching (10%) | | 250 | | μs | | | | |
| t _{Ramp} | VDCDC ramp-up time | VDCDC ramp from 10% to 90% | | 250 | | μs | | | | |
| LOW DROP OUT REGULATORS | | | | | | | | | | |
| t _{RAMP} | VLDOx Ramp Time | VLDOx ramp from 10% to 90% | | 200 | | μs | | | | |

8.7 Dissipation Ratings


| DEVICE | PACKAGE | $R_{\theta JA}$ | R _{0JB} | T _A ≤ 25°C POWER RATING | T _A = 70°C POWER RATING | T _A = 85°C POWER RATING |
|----------------------------|---------|-----------------|------------------|---------------------------------------|---------------------------------------|---------------------------------------|
| TPS65000/01 (1) | RTE/RUK | 270°C/W | 14°C/W | 370 mW | 204 mW | 148 mW |
| TPS65000/01 ⁽²⁾ | | 48.7°C/W | 14°C/W | 2.05 W | 1.13 W | 821 mW |

⁽¹⁾ The JEDEC low-K (1s) board used to derive this data was a 3 in × 3 in, two-layer board with 2-oz copper traces on top of the board.

⁽²⁾ The JEDEC high-K (2s2p) board used to derive this data was a 3 in x 3 in, multilayer board with 1-oz internal power and ground.




8.8 Typical Characteristics






Typical Characteristics (continued)





Typical Characteristics (continued)






Figure 14. Power Supply Rejection Ratio (LDOx) vs Frequency



9 Detailed Description

9.1 Overview

The TPS6500x provides one step-down converter, two low dropout regulators, spread spectrum clock generation, and a supply voltage supervisor for the TPS65001 only. The device has an input voltage range of 2.3 V to 6 V and is characterized across a -40°C to 85°C range. This device is intended, but not limited, to powering smart phones, embedded processors, and point-of-load devices.

The output voltage of the step-down converter can be selected through resistor networks on the output. To maximize efficiency, there are two modes of operation based on load conditions: PWM or PFM. By pulling the MODE pin high, forced PWM can be achieved. Pulling this pin low results in an automatic adjustment between PFM and PWM modes.

The two general purpose low drop-out regulators each have their own separate enables and voltage inputs. The inputs can be tied to the output of the step-down converter or to a separate voltage source. Resistor networks are required on the output of the regulator to set the output voltage. Their wide voltage range lets them handle direct connections to a battery.


The switching frequency of the step-down converter is handled by the oscillator, with a typical frequency of 2.25 MHz. The spread spectrum clock (SSC) modulates this frequency when the device is in PWM mode. This additional circuit in the oscillator block reduces power that may cause EMI.

The TPS6500x devices also provide a power good signal to monitor the condition of the DC-DC and both LDOs. The DC-DC and LDOs are only monitored if their enable signal is high. If all enabled resources are in regulation, the pin is pulled low. If one or more of the enabled resources are out of regulation, the pin is pulled in Hi-Z.

The supply voltage supervisor is only available for the TPS65001 and TPS650061 devices. This circuit monitors the supply voltage to the device that the TPS65001 and TPS650061 is powering for under voltage conditions. The circuit can connect to a button for manual resets. Reset-recovery time can also be set. Four different scenarios can trigger the circuit to cause a rest.



9.2 Functional Block Diagram



9.3 Feature Description

9.3.1 Step-Down Converter

TI intends the step-down converter to maximize the flexibility in the equipment. The output voltage is selectable with a resistor network on the output. Figure 15 shows the required connections.




Figure 15. DCDC Block Diagram and Output Voltage Setting



The output voltage of the DC-DC converter is set by Equation 1:

$$V_{DCDC} = V_{FB_DCDC} \times \frac{(R_{DC1} + R_{DC2})}{R_{DC2}}$$

$$V_{DCDC} = 0.6V \times \frac{(R_{DC1} + R_{DC2})}{R_{DC2}}$$
 (1)

The combined resistance of R_{DC1} and R_{DC2} should be less than 1 M Ω .

Fixed output voltages and additional current limit options are also possible. Contact TI for further information.

The step-down converter has two modes of operation to maximize efficiency at different load conditions. At moderate to heavy load currents, the device operates in a fixed-frequency pulse width modulation (PWM) mode that results in small output ripple and high efficiency. Pulling the MODE pin to a DC-high level results in PWM mode over the load range.

At light-load currents, the device operates in a pulsed-frequency modulation (PFM) mode to improve efficiency. The transition to this mode occurs when the inductor current through the low-side FET becomes zero, indicating discontinuous conduction. PFM mode also results in the output voltage increasing by 1% from its nominally set value. TI intends this voltage positioning to minimize the voltage undershoot of a load step from light to heavy loads, as when a processor moves from sleep to active modes, and the voltage overshoot at load throw-off. Figure 16 shows the voltage positioning behavior for a light to heavy load step.




Figure 16. PFM Voltage Positioning

Pulling the MODE pin to DC ground results in an automatic transition between PFM and PWM modes to maximize efficiency.

The DC-DC converter output automatically discharges to ground through an internal 450- Ω load when EN_DCDC goes low or when the UVLO condition is met.

9.3.2 Soft Start

The step-down converter has an internal soft start circuit that limits the inrush current during start-up. During a soft start, the output voltage ramp up is controlled as Figure 17 shows.






Figure 17. Soft Start

9.3.3 Linear Regulators

TI designed the two linear drop-out regulators (LDOs) in the TPS65000 and TPS65001 to provide flexibility in system design. Each LDO has a separate voltage input and enable signal. The input can be tied to the output of the step-down converter or the output of another voltage source. Each LDO output discharge to ground automatically when EN_LDOx goes low.

A resistor network is required to set the output voltage of the LDOs. Fixed-voltage output versions are also available. Contact TI sales representative for more information.

The LDOs are general-purpose devices that can handle inputs from 6 V to 1.6 V, making them suitable for directly connecting to the battery. Figure 18 illustrates the connections for LDO1. The same architecture applies to LDO2.




Figure 18. LDO Block Diagram and Output Voltage Setting

The output voltages of the LDOs are set by Equation 2:

$$V_{LDO1} = V_{FB_LDO1} x \frac{\left(R_{LDO1_1} + R_{LDO1_2}\right)}{R_{LDO1_2}}$$

$$V_{LDO1} = 0.5V \times \frac{\left(R_{LDO1_{1}} + R_{LDO1_{2}}\right)}{R_{LDO1_{2}}}$$
(2)

The combined resistance of R_{LDO1 1} and R_{LDO1 2} should be less than 1 M Ω .

9.3.4 Oscillator and Spread Spectrum Clock Generation

The TPS6500x contains an internal oscillator running at a typical frequency of 2.25 MHz. This frequency is the fundamental switching frequency of the step-down converter when running in PWM mode. An additional circuit in the oscillator block implements spread spectrum clocking, which modulates the main-switching frequency when the device is in PWM mode. This spread spectrum oscillation reduces the power that may cause EMI. When viewed in the frequency domain, the SSC spreads out the frequency that may introduce interference while simultaneously reducing the power. Because the frequency is continually shifting, the amount of time the switcher spends at any single frequency is reduced. This reduction in time indicates that the receiver that may sense the interference has less time to integrate the interference.

Different spin versions of SSC settings are also feasible. Contact a TI sales representative for more information.




Figure 19 to Figure 20 shows the advantage of SSC with the frequency spectrum centering on the nominal frequency 2.25 MHz. The blue spectrum is the result of the spread change. The figures show the harmonic spectrum is attenuated 10 dB comparing to the same device without SSC.

9.3.5 Power Good

The open drain \overline{PG} output indicates the condition of the step-down converter and each LDO. This output is combined, with the outputs being compared when the appropriate enable signal is high. The pin is pulled low when all enabled outputs are greater than 90% of the target voltage and Hi-Z when an enabled output is less than 90% of its intended value or when all the enable signals are pulled low.






Figure 21. Power Good Functionality

9.3.6 Supply Voltage Supervisor (SVS) [TPS65001 and TPS650061 Only]

The SVS has fourinputs and one output. The $\overline{\text{RST}}$ pin is an active-low high-impedance output. The $\overline{\text{MR}}$ pin is an active-low input that suitable for connecting to a push-button circuit for manual reset generation. The RSTSNS pin is an analog-input pin for voltage comparison. The TRST pin is connected to an external capacitor, allowing the reset timing to be set in the application. The VINDCDC pin is the main-supply input for the control circuits and the switch-mode converter.




Figure 22. SVS Block Diagram

Each input can individually trigger RST to go active. Table 1 outlines the paths to activate the reset.



Table 1. RST Generation Table

| | OUTPUTS | | |
|----------------|-----------------------|---------------------|--------|
| VINDCDC | MR | V _{RSTSNS} | RST |
| 0.4 < V < UVLO | X | X | Low |
| > UVLO | ≥ V _{IH(MR)} | ≤ 0.6 V | Low |
| > UVLO | ≥ V _{IH(MR)} | > 0.6 V | High-Z |
| > UVLO | < V _{IL(MR)} | X | Low |

The RSTSNS pin must be tied to VINDCDC if the reset functionality is not required from this pin. This action causes the reset to activate only when VINDCDC is rising from 0 V or when VINDCDC drops below UVLO. The RSTSNS pin must connect to an external RC network to set the deglitch timing for triggering a reset when VINDCDC is below the UVLO threshold. The reset threshold voltage is given by Equation 3:

$$V_{RST} = 0.6V \times \frac{(R_{S2} + R_{S1})}{R_{S2}}$$
(3)

The \overline{RST} recovery timing is set by the capacitor on the TRST pin. A 2- μ A current is enabled when the reset condition is met, charging the capacitor. The TRST voltage is monitored internally and the reset ends when the voltage reaches 0.6 V. The capacitor value to reset time can be computed with Equation 4:

$$t_{RST} = 0.6V \times \frac{C}{2 \times 10^{-6} A}$$
 (4)

The value t_{RST} is the time from the end of condition that activated \overline{RST} until \overline{RST} returns to its Hi-Z state. The TRST pin would be internally discharged to ground when the reset condition is true or after t_{RST} .




Figure 23. RST Recovery Timing



9.4 Device Functional Modes

The step-down converter has two modes of operation to maximize efficiency:

PFM

- For light loads
- For automatic transition to between this mode and PWM mode automatically when MODE pin is pulled low over all load ranges
- To increase in output voltage setting by 1%
- For better accuracy

PWM

- For moderate to heavy loads
- For a small output ripple
- For pulling MODE pin high to result in PWM mode over all load range



10 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI-component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

10.1 Application Information

The TPS65000 device is designed to pair with various applications, such as embedded processor power and portable media players. For detailed information on using the TPS65000 with TMS32C2834x, see *Related Documentation*.

TI designed the TPS65001 device to pair with various applications, such as PDAs and pocket PCs. For detailed information on using the TPS65001 with TMS320C5504/05, see *Related Documentation*.

TI designed the TPS650001 and TPS650061 devices to pair with various applications, such as cell and smart phones, as well as point-of-load. For detailed information on using the TPS650001 and TPS650061 with OMAP-L13x, see *Related Documentation*.

10.2 Typical Application

10.2.1 Typical TPS65000 Application




Figure 24. Typical TPS65000 Application Schematic

10.2.1.1 Design Requirements

For this design example, use the parameters listed in Table 2.

Table 2. Design Parameters

| RESOURCES | VOLTAGE |
|-----------|---------|
| SW | 3.3 V |
| VLDO1 | 1.8 V |
| VLDO2 | 2.8 V |



10.2.1.2 Detailed Design Procedure

10.2.1.2.1 Output Filter Design (Inductor and Output Capacitor)

10.2.1.2.1.1 Inductor Selection

The typical value for the converter inductor is 2.2- μ H output inductor. Larger or smaller inductor values in the range of $1.5~\mu$ H to $3.3~\mu$ H can optimize the performance of the device for specific operation conditions. The selected inductor has to be rated for its DC resistance and saturation current. The DC resistance of the inductance influences the efficiency of the converter directly. An inductor with lowest DC resistance must be selected for highest efficiency. See SLVA157 for more information on inductor selection.

Equation 5 calculates the maximum inductor current under static load conditions. The saturation current of the inductor should be rated higher than the maximum inductor current as calculated with Equation 6. The recommends this because during heavy load transient the inductor current rises above the calculated value.

$$\Delta I_L = V_{OUT} \times \frac{1 - \frac{V_{OUT}}{V_{IN}}}{L \times f}$$

where

- f = Switching Frequency (2.25 MHz typical)
- L = Inductor Value

$$I_{Lmax} = I_{OUTmax} + \frac{\Delta I_{L}}{2}$$

where

The highest inductor current occurs at maximum V_{IN}.

Open-core inductors have a soft saturation characteristic and can usually handle higher inductor currents versus a comparable shielded inductor.

A more conservative approach is to select the inductor current rating just for the maximum switch current of the corresponding converter. Consider that the core material from inductor to inductor differs and impacts the efficiency especially at high-switching frequencies.

The step down converter has internal loop compensation. TI designed the internal loop compensation to work with a certain output filter corner frequency calculated as follows:

$$f_{\rm C} = \frac{1}{2\pi \sqrt{L \times C_{\rm OUT}}}$$
 with L = 2.2 μ H, $C_{\rm OUT} = 10\mu$ F (7)

The selection of external L-C filter must be coped with Equation 7. The product of L \times C_{OUT} must be constant while selecting smaller inductor or increasing output capacitor value.

See Table 3 and the typical applications for possible inductors.

Table 3. Inductors

| INDUCTOR TYPE | INDUCTANCE (µH) | SUPPLIER | MAX DIMENSIONS (mm) |
|------------------|-----------------|---------------|-----------------------------|
| MIPS2520D2R2 | 2.0 | FDK | $2.5 \times 2.0 \times 1.0$ |
| MIPSA2520D2R2 | 2.0 | FDK | $2.5 \times 2.0 \times 1.2$ |
| KSLI-252010AG2R2 | 2.2 | Htachi Metals | $2.5 \times 2.0 \times 1.0$ |
| LQM2HPN2R2MJ0L | 2.2 | Murata | $2.5 \times 2.0 \times 1.2$ |
| LPS15222 | 2.2 | Coilcraft | $3.0 \times 3.0 \times 1.5$ |

(5)



10.2.1.2.1.2 Output Capacitor Selection

The advanced fast response voltage mode control scheme of the converter allows the use of small ceramic capacitors with a typical value of 22 μ F, without having large output voltage under and overshoots during heavy load transients. TI recommends ceramic capacitors with low ESR values because they result in lowest output voltage ripple. See the TI-recommended components.

If ceramic output capacitors are used, the capacitor RMS ripple current rating always meets the application requirements. The RMS ripple current is calculated as the following:

$$I_{RMSCout} = V_{OUT} \times \frac{1 - \frac{V_{OUT}}{V_{IN}}}{L \times f} \times \frac{1}{2 \times \sqrt{3}}$$
(8)

At nominal load current, the device operates in PWM mode and the overall output voltage ripple is the sum of the voltage spike caused by the output capacitor ESR plus the voltage ripple caused by charging and discharging the output capacitor:

$$\Delta V_{OUT} = V_{OUT} \times \frac{1 - \frac{V_{OUT}}{V_{IN}}}{L \times f} \times \left(\frac{1}{8 \times C_{OUT} \times f} + ESR\right)$$
(9)

Where the highest output voltage ripple occurs at the highest input voltage V_{IN}.

At light load currents, the converter operates in power save mode and the output voltage ripple is dependent on the output capacitor value. The output voltage ripple is set by the internal comparator delay and the external capacitor. The typical output voltage ripple is less than 1% of the nominal output voltage.

The adjustable output voltage of the DC-DC converter is calculated by Equation 1 in the Step-Down Converter. To keep the external resistor divider network robust against noise, an external feed forward capacitor is required for optimum load transient response. The value of feed forward capacitor must be in the range between 22 pF and 33 pF provided the equivalent resistance of RDC1 || RDC2 in Equation 1 is approximately 300 k Ω . Scale change on RDC1||RDC2 would apply a scale change to the feed forward capacitor to keep the RC product a constant.

10.2.1.2.1.3 Input Capacitor Selection


Due to the DC-DC converter having a pulsating input current, a low-ESR input capacitor is required for best input voltage filtering, and minimizing the interference with other circuits caused by high-input voltage spikes. Put the input capacitor as close to the VINDCDC pin as close as possible with the clean GND connection. Do the same for the output capacitor and the inductor. The converters require a ceramic input capacitor of 10 μ F. The input capacitor can increase without any limit for better input voltage filtering.

Table 4. Capacitors

| CAPACITANCE | SUPPLIER | TYPE |
|-------------|---------------------------|---------|
| 22 μF | TDK C2012X5R0J226MT | Ceramic |
| 22 μF | Taiyo Yuden JMK212BJ226MG | Ceramic |
| 10 μF | Taiyo Yuden JMK212BJ106M | Ceramic |
| 10 μF | TDK C2012X5R0J106M | Ceramic |
| 10 μF | Murata GRM188R60J106M69D | Ceramic |



10.2.1.3 Application Curves



10.2.2 Typical TPS65001 Application




Figure 31. Typical TPS65001 Application Schematic

10.2.2.1 Design Requirements

For this design example, use the parameters listed in Table 5.

Table 5. Design Parameters

| RESOURCES | VOLTAGE |
|-----------|---------|
| SW | 1.2 V |
| VLDO1 | 1.8 V |
| VLDO2 | 2.8 V |



10.2.3 Typical TPS650001 Application




Figure 32. Typical TPS650001 Application Schematic

Table 6. Design Parameters

| RESOURCES | VOLTAGE | | | | |
|-----------|---------|--|--|--|--|
| SW | 1.2 V | | | | |
| VLDO1 | 3.3 V | | | | |
| VLDO2 | 1.8 V | | | | |



10.2.4 Typical TPS650061 Application




Figure 33. Typical TPS650061 Application Schematic

10.2.4.1 Design Requirements

For this design example, use the parameters listed in Table 7.

VLDO1

VLDO2

RESOURCES VOLTAGE
SW 1.2 V

3.3 V

1.8 V

Table 7. Design Parameters

11 Power Supply Recommendations

The device is designed to operate with an input voltage supply range from 1.6 V to 6 V. This input supply can be from a DC supply, or other externally regulated supply. If the input supply is located more than a few inches from the TPS65000, additional bulk capacitance may be required in addition to the ceramic bypass capacitors. An electrolytic capacitor with a value of 10 μ F is a typical choice.



12 Layout

12.1 Layout Guidelines

- The VINDCDC and VINLDOx pins must be bypassed to ground with a low-ESR ceramic bypass capacitor. TI recommends the typical bypass capacitance is 10 μF and 2.2 μF with a X5R dielectric.
- The optimum placement is closest to the VINDCDCx and VINLDOx pins of the device. Minimize the loop area formed by the bypass capacitor connection, the VINDCDC and VINLDO pins, and the thermal pad of the device.
- The thermal pad must be tied to the PCB ground plane with multiple vias.
- The VLDOx and VDCDCx pins (feedback pins) traces must be routed away from any potential noise source to avoid coupling.
- VODC output capacitance must be placed immediately at the VODC pin. Excessive distance between the capacitance and DCDCx pin may cause poor converter performance.
- AGND star back to PGND as close to IC as possible.
- · DGND connect to thermal pad.

12.2 Layout Example




Figure 34. Layout Recommendation




Figure 35. Bypass Capacitor and Via Placement Recommendation



13 Device and Documentation Support

13.1 Device Support

13.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

13.2 Documentation Support

13.2.1 Related Documentation

For related documentation see the following:

- Choosing Inductors and Capacitors for DC/DC Converters, SLVA157
- High Efficiency Power Solution for TMS32C2834x MCU, SLDA039
- Power for TMS320C5504/05, SLVA401
- Power for OMAP-L13x, SLYT405

13.3 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

Table 8. Related Links

| PARTS | PRODUCT FOLDER SAMPLE & BUY | | TECHNICAL DOCUMENTS | TOOLS & SOFTWARE | SUPPORT & COMMUNITY |
|-----------|-----------------------------|------------|---------------------|---------------------|---------------------|
| TPS65000 | Click here | Click here | Click here | Click here | Click here |
| TPS65001 | Click here | Click here | Click here | Click here | Click here |
| TPS650001 | Click here | Click here | Click here | Click here | Click here |
| TPS650003 | Click here | Click here | Click here | Click here | Click here |
| TPS650006 | Click here | Click here | Click here | Click here | Click here |
| TPS650061 | Click here | Click here | Click here | Click here | Click here |

13.4 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

13.5 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

13.6 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.



www.ti.com

13.7 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.





10-Dec-2020

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|------------|--------------|--------------------|------|----------------|--------------|-------------------------------|---------------------|--------------|-------------------------|---------|
| TPS650001RTER | ACTIVE | WQFN | RTE | 16 | 3000 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | DAG | Samples |
| TPS650001RTET | ACTIVE | WQFN | RTE | 16 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | DAG | Samples |
| TPS650003RTER | ACTIVE | WQFN | RTE | 16 | 3000 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | DAH | Samples |
| TPS650003RTET | ACTIVE | WQFN | RTE | 16 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | DAH | Samples |
| TPS650006RTER | ACTIVE | WQFN | RTE | 16 | 3000 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -55 to 125 | DAI | Samples |
| TPS650006RTET | ACTIVE | WQFN | RTE | 16 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | DAI | Samples |
| TPS65000RTER | ACTIVE | WQFN | RTE | 16 | 3000 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | CFO | Samples |
| TPS65000RTET | ACTIVE | WQFN | RTE | 16 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | CFO | Samples |
| TPS65001RUKR | ACTIVE | WQFN | RUK | 20 | 3000 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | CFQ | Samples |
| TPS65001RUKT | ACTIVE | WQFN | RUK | 20 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | CFQ | Samples |
| TPS650061RUKR | ACTIVE | WQFN | RUK | 20 | 3000 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | DAJ | Samples |
| TPS650061RUKT | ACTIVE | WQFN | RUK | 20 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 85 | DAJ | Samples |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.



PACKAGE OPTION ADDENDUM

10-Dec-2020

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TPS65000:

Automotive: TPS65000-Q1

NOTE: Qualified Version Definitions:


Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

PACKAGE MATERIALS INFORMATION

www.ti.com 16-Oct-2020

TAPE AND REEL INFORMATION





| | Dimension designed to accommodate the component width |
|----|---|
| | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




*All dimensions are nominal

| All dimensions are nominal | | | | | | | | | | | | |
|----------------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
| TPS650001RTER | WQFN | RTE | 16 | 3000 | 330.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS650001RTET | WQFN | RTE | 16 | 250 | 180.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS650003RTER | WQFN | RTE | 16 | 3000 | 330.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS650003RTET | WQFN | RTE | 16 | 250 | 180.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS650006RTER | WQFN | RTE | 16 | 3000 | 330.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS650006RTET | WQFN | RTE | 16 | 250 | 180.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS65000RTER | WQFN | RTE | 16 | 3000 | 330.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS65000RTET | WQFN | RTE | 16 | 250 | 180.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS65001RUKR | WQFN | RUK | 20 | 3000 | 330.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS65001RUKT | WQFN | RUK | 20 | 250 | 180.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS650061RUKR | WQFN | RUK | 20 | 3000 | 330.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS650061RUKT | WQFN | RUK | 20 | 250 | 180.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |

PACKAGE MATERIALS INFORMATION

www.ti.com 16-Oct-2020



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS650001RTER | WQFN | RTE | 16 | 3000 | 853.0 | 449.0 | 35.0 |
| TPS650001RTET | WQFN | RTE | 16 | 250 | 210.0 | 185.0 | 35.0 |
| TPS650003RTER | WQFN | RTE | 16 | 3000 | 853.0 | 449.0 | 35.0 |
| TPS650003RTET | WQFN | RTE | 16 | 250 | 210.0 | 185.0 | 35.0 |
| TPS650006RTER | WQFN | RTE | 16 | 3000 | 853.0 | 449.0 | 35.0 |
| TPS650006RTET | WQFN | RTE | 16 | 250 | 210.0 | 185.0 | 35.0 |
| TPS65000RTER | WQFN | RTE | 16 | 3000 | 853.0 | 449.0 | 35.0 |
| TPS65000RTET | WQFN | RTE | 16 | 250 | 210.0 | 185.0 | 35.0 |
| TPS65001RUKR | WQFN | RUK | 20 | 3000 | 853.0 | 449.0 | 35.0 |
| TPS65001RUKT | WQFN | RUK | 20 | 250 | 210.0 | 185.0 | 35.0 |
| TPS650061RUKR | WQFN | RUK | 20 | 3000 | 853.0 | 449.0 | 35.0 |
| TPS650061RUKT | WQFN | RUK | 20 | 250 | 210.0 | 185.0 | 35.0 |

RTE (S-PWQFN-N16)

PLASTIC QUAD FLATPACK NO-LEAD



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M—1994.

- B. This drawing is subject to change without notice.
- C. Quad Flatpack, No-leads (QFN) package configuration.
- The package thermal pad must be soldered to the board for thermal and mechanical performance. See the Product Data Sheet for details regarding the exposed thermal pad dimensions.
- E. Falls within JEDEC MO-220.



RTE (S-PWQFN-N16)


PLASTIC QUAD FLATPACK NO-LEAD

THERMAL INFORMATION

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No—Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



Bottom View

Exposed Thermal Pad Dimensions


4206446-8/U 08/15

NOTE: A. All linear dimensions are in millimeters



RTE (S-PWQFN-N16)

PLASTIC QUAD FLATPACK NO-LEAD




NOTES: A. All I

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Application Note, Quad Flat—Pack Packages, Texas Instruments Literature No. SLUA271, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com http://www.ti.com>.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- F. Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.



RUK (S-PWQFN-N20)

PLASTIC QUAD FLATPACK NO-LEAD



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. Quad Flatpack, No-leads (QFN) package configuration.
- D. The package thermal pad must be soldered to the board for thermal and mechanical performance.
- E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- F. Falls within JEDEC MO-220.



RUK (S-PWQFN-N20)


PLASTIC QUAD FLATPACK NO-LEAD

THERMAL INFORMATION

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No—Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



Bottom View

Exposed Thermal Pad Dimensions


4209762/1 05/15

NOTE: All linear dimensions are in millimeters



RUK (S-PWQFN-N20)

PLASTIC QUAD FLATPACK NO-LEAD



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Application Note, Quad Flat—Pack Packages, Texas Instruments Literature No. SLUA271, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com http://www.ti.com.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- F. Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

Tl's products are provided subject to Tl's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such Tl products. Tl's provision of these resources does not expand or otherwise alter Tl's applicable warranties or warranty disclaimers for Tl products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated