



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2016-12-21	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	826467-3	Amount	502.09377	Version	-	Identity			
Manufacturer Item Name	3P MOD II SHROUDED HEADER, ST	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	50P MOD2 ST-WANNGEH				0.06	5590.0	mg	
Material	2	PCT-GF20				0.06	5590.0	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.318	0.06	17.7762	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	0.06	111.8	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.212	0.06	11.8508	mg	
Substance	3	2,4,8,10-Tetraoxa-3,9-diphosphaspiro [5.5]undecane, 3,9-bis[2,4-bis(1,1-dimethylethyl)p henoxyl]-	Supplier	26741-53-7	0.3	0.06	16.77	mg	
Substance	3	Poly(oxy-1,2-ethanediyl),a-(1-oxododecyl)-w-[(1-oxododecyl)oxy]-	Supplier	9005-02-1	4.3	0.06	240.37	mg	
Substance	3	Ethene, homopolymer, oxidized	Supplier	68441-17-8	0.5	0.06	27.95	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	0.06	55.9	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	19.0	0.06	1062.1	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	18.0	0.06	1006.2	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	4.5	0.06	251.55	mg	

Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2-[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-2-(hydroxymethyl)-1,3-propanediyl] ester	Supplier	84633-54-5	0.0030	0.06	0.1677	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	49.0	0.06	2739.1	mg	
Substance	3	Formaldehyde, polymer with 2-(chloromethyl)oxirane and 2-methylphenol	Supplier	29690-82-2	0.57	0.06	31.863	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.297	0.06	16.6023	mg	
Sub-Item	1	MOD II, DIA0.63 MM PIN, BANDLR, PDNI				3.0	55.56459	mg	
Material	2	Nickel Plate				3.0	0.37	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	7.4E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	3.7E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.36889	mg	
Material	2	Gold Plate				3.0	0.01559	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	3.0	0.01554323	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	3.0	4.677E-5	mg	
Material	2	Tin Plate				3.0	0.21	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	4.2E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	0.20943	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	1.47E-4	mg	
Material	2	Brass				3.0	54.9	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	3.0	0.0549	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	3.0	35.136	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.02745	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	5.49E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00549	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.0549	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	3.0	0.0549	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	3.0	19.32947	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00549	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	3.0	0.00549	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	3.0	0.02745	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	3.0	0.1647	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.00549	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.745E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.02745	mg	

Material	2	Palladium-Nickel Plate				3.0	0.069	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	3.0	0.0552	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	3.0	0.0138	mg	