

Product data sheet

Specifications



Easy UPS On-Line SRVS 1000VA 230V with Extended Runtime Battery Pack

SRVS1KIL

Overview

Presentation	For small to medium businesses, Easy UPS 1 Ph On-Line provides essential power protection for unstable power conditions, ensuring consistent and reliable connectivity at the most critical moments.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	800 W
Rated power in VA	1000 VA
Plug standard	IEC 60320 C14
Nb of power socket outlets	3 IEC 60320 C13
Cable length	1.52 m
Number of cables	1
Provided equipment	Basic UPS signalling RS-232 cable CD with software Country-specific detachable power cord 1 x DC cable User manual USB cable

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

Colour	Black
Height	23.8 cm
Width	29 cm

Depth	40 cm
Net weight	24 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	Yes
Mounting position	Vertical

Input

Input voltage limits	110...285 V half load 160...280 V full load
Input protection type	Circuit breaker and fuse
Network frequency	40...70 Hz auto sensing

Output

Maximum configurable power in VA	1000 VA
Maximum configurable power in W	800 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Transfer time	4 ms typical
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	88 % (full load)
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

Conformance

Product certifications	CE
Standards	EN/IEC 62040-1 EN/IEC 62040-2

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...15000 m
Acoustic level	50 dBA
IP degree of protection	IP20

Batteries & Runtime

Battery type	Lead-acid battery
--------------	-------------------

Battery voltage	36 V
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 h
Battery life	3...5 year(s)
Battery charger power	129 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	Multifunction LCD status and control console
Free slots	1

Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	26.7 kg
Package 1 Height	35.5 cm
Package 1 width	47 cm
Package 1 Length	52.5 cm

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------