



# LUMAWISE ALR AA SERIES

## Electronic Version

TE Connectivity's (TE) LUMAWISE ALR AA 2000EL is an electronic version of TE's popular AA series button photocell. The button cell, wired in design, is a photocontrol solution for multiple luminaire form factors.

The compact form is designed to be internally hardwired in the luminaire. The polycarbonate lens gives a discrete appearance as well as a tough construction.

The device gives dusk and dawn control of incandescent and LED light sources. Via an electromagnetic relay rated for greater than 20k operating cycles.

### APPLICATIONS

- Street lighting
- Area lighting
- Signage
- Group switching
- Flood lighting
- Wall lighting

# LUMAWISE ALR AA SERIES

## BENEFITS

- Standalone device which will monitor ambient light levels and accurately switch a light source ON/OFF at fixed levels
- Ambient light levels detected by silicon photoelectric sensor
- In built delay will prevent false switching due to light pollution
- Designed for a 10-year life or 20k switching cycles
- Standard ANSI switch levels
- Designed to meet the requirements of UL773A

## MECHANICAL

- **Total height:** 52.1mm
- **Width:** 58.5mm
- **Depth:** 33mm
- **Thread:** 3/8"
- **Lead Wire Type:** 16AWG (105°C), 168mm length, other lengths upon request

## ELECTRICAL

- 105-305Vac Input and switching voltage
- **Power consumption:** <0.5W max

## MATERIALS

- **Housing:** Polycarbonate
- **Lens:** UV stabilized

## FEATURES

- **Voltage Rating:** 120/208/240/277Vac
- **Operating Voltage Range:** 105-305Vac
  - At 50/60Hz
- **Switching Levels:** 1.5Fc ON, 2.0Fc OFF
- **Switching Ratio:** 1.3:1 OFF/ON
- **Rated Switching Current:**
  - **Ballast:** 1800VA
  - **Tungsten:** 1000W
  - **Electronic:** 5A at 120/277Vac
- **Switching Delay:** Instant ON, 2-5s OFF
- **Failure Mode:** On
- **Surge Protection:** 445J, 10kA
- **Operating Temperature Range:** -40°C to +65°C
- **Relative Humidity:** 96%

## STANDARDS

- Meets the requirements of UL773A
- Meets the requirements of ANSI C136.24

## SPECIFICATIONS

- **Application Specification:** 114-160404

Description	Part Number
LUMAWISE ALR AA-2000EL Button Photocontrol	<a href="#"><u>2393866-1</u></a>

## te.com

© 2022 TE Connectivity. All Rights Reserved.

LUMAWISE, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by TE Connectivity. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

09/22 MU

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2393866-1](#)