



Part Number: 70030

AUDIO ANALOG 1 PAIR, 24AWG, ISTP, LSZH

Product Description

ANALOG AUDIO 1 PAIR, 24AWG/0.22mm², ISTP, LSZH

Technical Specifications

Product Overview

Environmental Space:	Indoor - Euroclass Dca
Suitable Applications:	Single pair 24 AWG halogen free screened pair cable for analog audio; For analogue audio

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Construction n x D	No. of Pairs
24	7x32	BOFC - Bare Oxygen free Copper	7x0.20 mm	1

Conductor Count:	2
Total Number of Pairs:	1
Conductor Size:	24 AWG

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Insulation	Polyethylene	1.02 mm	0.05 mm

Color Chart

Number	Color
Pair 1	Red & Black

Outer Shield Material

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D	Drainwire Position
Foil	Aluminum/Polyester	100 %	Stranded tinned copper	24	7x0.20 mm	Under shielding foil

Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH / FRNC	3.1 mm	0.1 mm

Construction and Dimensions

Cabling

Description
1 Pair + Stranded tinned copper drainwire (AWG 24)(7x0.20)

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
88.5 Ohm/km	52 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
92 pF/m	180 pF/m

Inductance

Nominal Inductance
0.75 μ H/m

Temperature Range

Other Temp Range:	-30-+70 °C
-------------------	------------

Mechanical Characteristics

Max Recommended Pulling Tension:	70 N
Min Bend Radius During Installation:	31 mm
Min Setting Radius:	15.5 mm

Standards

CPR Euroclass:	Dca-s2,d1,a1
----------------	--------------

Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2013-07-05
---------------------------------------	------------

Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2
LOI of Jacket:	34 %
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

Part Number

Variants

Item #	Color	Length
70030.01100	Black	100 m
70030.01500	Black	500 m
70030.00100	Gray	100 m
70030.00500	Gray	500 m

History

Revision Number:	1
------------------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.