



NOTES:

1. Electrical Specifications:

- Meets USB 2.0 specifications
- Low level Contact Resistance: 30 mOhm max.
- Insulation Resistance 1000 MOhm min.
- Currant Rating: 1.5 A max. @ 25°C
- DWV: 500 VAC/60s at sea level
- Operating Temperature: -40°C to +80°C

2. Material and Finish:

- Coupling Ring: Brass, Nickel Plated
- Plug Housing: ABS, UL94 V-0, Nickel Plated
- Interfacial Seal: Silicone, Color: White
- Cable Gland: Brass, Nickel Plated
- Cable Gland Seal: NBR, Color: Black
- USB Insulator: PBT, UL 94V-0, Color: White
- USB Overmold: PVC, UL 94V-0, Color: Black
- USB Metal Shell: SPCC, Nickel plated
- USB Contact: Copper Alloy, 30 u" min. Au over 40 u" min. Nickel Plated

3. Shielded USB Cable Configuration

AWM 2725 AWG28/1p + AWG24/2c, OD: 4.5 mm Color: black

4. RoHS compliant

Directive 2002/95/EC
"RoHS"
Compliant

Cable Length L	Part Number
2 m	17-200341
3 m	17-200351
4.5 m	17-200361

THIS DRAWING MAY NOT BE COPIED, OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:		Tolerance Unless otherwise specified			Scale: 1.5:1	Dim. in m	
	Name	Title	Approval Date	0 PLC ±0.30 1 PLC ±0.20 2 PLC ±0.10 3 PLC ±0.05 ANGLES ±1°		Material: See Notes		
				2008	Date	Name	USB Patch Cord (Metal Version) USB 2.0 Type A Plug (Industrial) to USB 2.0 Type B Plug (Standrad)	
				Draw.	Oct 31	Vincent Ke		
			Appd.	Oct 31	J. chaudry	Title:		
				Norm		Drawing No.: 17K1A116		
				D-old		Part No.: SEE P/N ABOVE		
	b	Jan/19/2009	Vincent ke			DIN A3		
	a	original				Sheet 1/1		
	Rev.	Changes	Date	Name	CONEC			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-200341](#) [17-200351](#) [17-200361](#)