

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Flat-type fuse terminal block, cross section: 0.2 - 6 mm², AWG: 26 - 8, width: 8.2 mm, color: black, with light indicator, voltage light indicator: 12 V DC, current light indicator: 2 mA

Your advantages

- Can be bridged with FBI ... fixed bridge
- For the use of KFZ flat-type fuses from the FSI/C series

Fuse modular terminal block - UK 6-FSI/C-LED12



3001925

<https://www.phoenixcontact.com/in/products/3001925>

Commercial Data

Order Key	3001925
Packing unit	50 pc
Minimum order quantity	1 pc
Sales Key	BE1
Catalog Page	Page 499 (C-1-2019)
GTIN	4017918100964
Weight per Piece (including packing)	21.1 GRM
Weight per Piece (excluding packing)	21.1 GRM
Customs tariff number	85369010
Country of origin	TR

Technical Data

Product properties

Number of positions	1
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Fuse type	Flat
Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	1.31 W
Fuse	C
Voltage LED	12 V DC (LED red)
Current LED	2 mA DC (LED red)
Maximum current with single arrangement	30 A (special arrangements on request)

Input data

Voltage LED	12 V DC (LED red)
-------------	-------------------

Connection data

Grounding foot	No
Number of connections per level	2
Nominal cross section	6 mm ²

1 level

Designation	Level 1 above 1 below 1
Connection labeling	1 level
Screw thread	M4
Tightening torque	1.5 ... 1.8 Nm
Stripping length	10 mm
Internal cylindrical gage	A5
Connection in acc. with standard	IEC 60947-7-3
Conductor cross section solid	0.2 mm ² ... 10 mm ²
Cross section AWG	24 ... 8
Conductor cross section flexible	0.2 mm ² ... 6 mm ²
Conductor cross section, flexible [AWG]	24 ... 10
Flexible conductor cross section flexible (ferrule, w/o plastic sleeve)	0.25 mm ² ... 6 mm ²
Flexible conductor cross section (ferrule with plastic sleeve)	0.25 mm ² ... 4 mm ²
2 conductors with same cross section, solid	0.2 mm ² ... 2.5 mm ²

Fuse modular terminal block - UK 6-FSI/C-LED12



3001925

<https://www.phoenixcontact.com/in/products/3001925>

2 conductors with same cross section, flexible	0.2 mm ² ... 2.5 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm ² ... 2.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 4 mm ²
Nominal current	30 A
Maximum load current	30 A
Nominal voltage	250 V
Nominal cross section	4 mm ²

Dimensions

Width	8.2 mm
Height NS 35/15	59.5 mm
Height NS 35/7,5	52 mm
Height	2.047 "
Height NS 32	57 mm
Length	64 mm

Material specifications

Color	black
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
---------------------------------	---

Fuse modular terminal block - UK 6-FSI/C-LED12



3001925

<https://www.phoenixcontact.com/in/products/3001925>

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-3
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

Fuse modular terminal block - UK 6-FSI/C-LED12


3001925

<https://www.phoenixcontact.com/in/products/3001925>



Drawings

Circuit diagram




Fuse modular terminal block - UK 6-FSI/C-LED12




3001925

<https://www.phoenixcontact.com/in/products/3001925>

Approvals

CSA 	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
	12 V	30 A	26 - 8	-

EAC

cULus Recognized 	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
Use group B	300 V	30 A	26 - 8	-
Use group C	300 V	30 A	26 - 8	-
Use group F	250 V	30 A	26 - 8	-
Use group D	600 V	5 A	26 - 8	-

Fuse modular terminal block - UK 6-FSI/C-LED12



3001925

<https://www.phoenixcontact.com/in/products/3001925>

Classifications

ECLASS

ECLASS-9.0	27141116
ECLASS-10.0.1	27141116
ECLASS-11.0	27141116

ETIM

ETIM 6.0	EC000899
----------	----------

UNSPSC

UNSPSC 19.0	39121410
UNSPSC 20.0	39121410
UNSPSC 21.0	39121410

Fuse modular terminal block - UK 6-FSI/C-LED12



3001925

<https://www.phoenixcontact.com/in/products/3001925>

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	--

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Accessories

 Note: Applying some accessories below might limit this product.

Fuse

Fuse - SI FORM C 15 A DIN 72581 - 0913676



Flat-type plug-in fuse, type C, color code: light blue, nominal current: 15 A

Fuse

Fuse - SI FORM C 7,5 A DIN 72581 - 0913702



Flat-type plug-in fuse, type C, color code: brown, nominal current: 7.5 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Fuse

Fuse - SI FORM C 10 A DIN 72581 - 0913715



Flat-type plug-in fuse, type C, color code: red, nominal current: 10 A

Fuse

Fuse - SI FORM C 25 A DIN 72581 - 0913757



Flat-type plug-in fuse, type C, color code: white, nominal current: 25 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Fuse

Fuse - SI FORM C 20 A DIN 72581 - 0913744



Flat-type plug-in fuse, type C, color code: yellow, nominal current: 20 A

Fuse

Fuse - SI FORM C 4 A DIN 72581 - 0913731



Flat-type plug-in fuse, type C, color code: pink, nominal current: 4 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Fuse

Fuse - SI FORM C 3 A DIN 72581 - 0913773



Flat-type plug-in fuse, type C, color code: violet, nominal current: 3 A

Fuse

Fuse - SI FORM C 30 A DIN 72581 - 0913760



Flat-type plug-in fuse, type C, color code: light green, nominal current: 30 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Fuse

Fuse - SI FORM C 2 A - 0913689



Flat-type plug-in fuse, type C, color code: gray, nominal current: 2 A

Fuse

Fuse - SI FORM C 5 A DIN 72581 - 0913692



Flat-type plug-in fuse, type C, color code: light brown, nominal current: 5 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

End clamp

End clamp - CLIPFIX 35 - 3022218

Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, width: 9.5 mm, color: gray



End clamp

End clamp - CLIPFIX 35-5 - 3022276

Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, with parking option for FBS...5, FBS...6, KSS 5, KSS 6, width: 5.15 mm, color: gray



Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

End clamp

End clamp - E/NS 35 N - 0800886

End clamp, width: 9.5 mm, color: gray



End clamp

End clamp - E/UK - 1201442

End clamp, Mounting on a DIN rail NS 32 or NS 35, material: PA, color: gray



Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

End clamp

End clamp - E/UK 1 - 1201413



End clamps, for supporting the ends of double-level and three-level terminal blocks, width: 10 mm, color: gray

Separating plate

Separating plate - TS-KK 3 - 2770215



Separating plate, length: 14 mm, width: 0.5 mm, height: 16 mm, color: gray

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

End cap

End cap - NS 35/ 7,5 CAP - 1206560


DIN rail end piece, for DIN rail NS 35/7.5



End cap

End cap - NS 35/15 CAP - 1206573

DIN rail end piece, for DIN rail NS 35/15



Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 0,1A - 0712107



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Thermal device circuit breaker

Thermal device circuit breaker - TCP 0,25A - 0712123



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 0,5A - 0712152



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Thermal device circuit breaker

Thermal device circuit breaker - TCP 1A - 0712194



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 2A - 0712217



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Thermal device circuit breaker

Thermal device circuit breaker - TCP 3A - 0712233



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 4A - 0712259



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Thermal device circuit breaker

Thermal device circuit breaker - TCP 6A - 0712275



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 8A - 0712291



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Thermal device circuit breaker

Thermal device circuit breaker - TCP 10A - 0712314



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 5/DC32V - 0700005



Thermal device circuit breaker, number of positions: 1, nominal current: 5 A, nom. voltage: 32 V, width: 6 mm, fuse type: Slow-blow, fuse type: Automatic device, mounting type: on base element, Color: light brown

Thermal device circuit breaker

Thermal device circuit breaker - TCP 7,5/DC32V - 0700007



Thermal device circuit breaker, number of positions: 1, nominal current: 7.5 A, nom. voltage: 32 V, width: 6 mm, fuse type: Slow-blow, fuse type: Automatic device, mounting type: on base element, Color: brown

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 10/DC32V - 0700010



Thermal device circuit breaker, number of positions: 1, nominal current: 10 A, nom. voltage: 32 V, width: 6 mm, fuse type: Slow-blow, fuse type: Automatic device, mounting type: on base element, Color: red

Thermal device circuit breaker

Thermal device circuit breaker - TCP 15/DC32V - 0700015



Thermal device circuit breaker, number of positions: 1, nominal current: 15 A, nom. voltage: 32 V, width: 6 mm, fuse type: Slow-blow, fuse type: Automatic device, mounting type: on base element, Color: blue

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 20/DC32V - 0700020



Thermal device circuit breaker, number of positions: 1, nominal current: 20 A, nom. voltage: 32 V, width: 6 mm, fuse type: Slow-blow, fuse type: Automatic device, mounting type: on base element, Color: yellow

Thermal device circuit breaker

Thermal device circuit breaker - TCP 25/DC32V - 0700025



Thermal device circuit breaker, number of positions: 1, nominal current: 25 A, nom. voltage: 32 V, width: 6 mm, fuse type: Slow-blow, fuse type: Automatic device, mounting type: on base element, Color: white

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Thermal device circuit breaker

Thermal device circuit breaker - TCP 30/DC32V - 0700030



Thermal device circuit breaker, number of positions: 1, nominal current: 30 A, nom. voltage: 32 V, width: 6 mm, fuse type: Slow-blow, fuse type: Automatic device, mounting type: on base element, Color: light green

DIN rail, unperforated

DIN rail, unperforated - NS 32 UNPERF 2000MM - 1201015



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, G profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 UNPERF 2000MM - 0801681



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 WH UNPERF 2000MM - 1204122



DIN rail, unperforated, acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 AL UNPERF 2000MM - 0801704



DIN rail, unperforated, acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 CU UNPERF 2000MM - 0801762



DIN rail, unperforated, acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

DIN rail, unperforated

DIN rail, unperforated - NS 35/15 UNPERF 2000MM - 1201714



DIN rail, unperforated, similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail, unperforated

DIN rail, unperforated - NS 35/15 WH UNPERF 2000MM - 1204135



DIN rail, unperforated, similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

DIN rail, unperforated

DIN rail, unperforated - NS 35/15 AL UNPERF 2000MM - 1201756



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail, unperforated

DIN rail, unperforated - NS 35/15 ZN UNPERF 2000MM - 1206586



DIN rail, unperforated, similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

DIN rail, unperforated

DIN rail, unperforated - NS 35/15 CU UNPERF 2000MM - 1201895



DIN rail, unperforated, similar to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail, unperforated

DIN rail, unperforated - NS 35/15-2,3 UNPERF 2000MM - 1201798



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile 2.3 mm, color: silver

Fixed bridge

Fixed bridge - FBI 2- 8 - 0200020



Fixed bridge, pitch: 8 mm, color: silver

 Max. current carrying capacity: 34 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Fixed bridge

Fixed bridge - FBI 3- 8 - 0200059



Fixed bridge, pitch: 8 mm, color: silver

 Max. current carrying capacity: 34 A

Fixed bridge

Fixed bridge - FBI 4- 8 - 0200046



Fixed bridge, pitch: 8 mm, color: silver

 Max. current carrying capacity: 34 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925


<https://www.phoenixcontact.com/in/products/3001925>

Fixed bridge

Fixed bridge - FBI 10- 8 - 0203263




Fixed bridge, pitch: 8 mm, color: silver

 Max. current carrying capacity: 34 A

Zack marker strip

Zack marker strip - ZB 8:UNBEDRUCKT - 1052002




Zack marker strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Zack marker strip


Zack marker strip - ZB 8 CUS - 0825011



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

Zack marker strip

Zack marker strip - ZB 8,LGS:FORTL.ZAHLEN - 1052015



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10


Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Zack marker strip

Zack marker strip - ZB 8,QR:FORTL.ZAHLEN - 1052028



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

DIN rail perforated

DIN rail perforated - NS 32 PERF 2000MM - 1201002



DIN rail perforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, G profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail perforated

DIN rail perforated - NS 35/ 7,5 PERF 2000MM - 0801733



DIN rail perforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

DIN rail perforated

DIN rail perforated - NS 35/ 7,5 WH PERF 2000MM - 1204119



DIN rail perforated, acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail perforated

DIN rail perforated - NS 35/ 7,5 ZN PERF 2000MM - 1206421



DIN rail perforated, acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

DIN rail perforated

DIN rail perforated - NS 35/15 PERF 2000MM - 1201730



DIN rail perforated, similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

DIN rail perforated

DIN rail perforated - NS 35/15 WH PERF 2000MM - 0806602



DIN rail perforated, similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

DIN rail perforated

DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599



DIN rail perforated, similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

Fuse modular terminal block - UK 6-FSI/C-LED12



3001925

<https://www.phoenixcontact.com/in/products/3001925>

Marker for terminal blocks

Marker for terminal blocks - UC-TM 8 - 0818072



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 56

Marker for terminal blocks

Marker for terminal blocks - UC-TM 8 CUS - 0824597



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 56

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Marker for terminal blocks

Marker for terminal blocks - UCT-TM 8 - 0828740



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 42

Marker for terminal blocks

Marker for terminal blocks - UCT-TM 8 CUS - 0829616



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 42


Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Marker for terminal blocks

Marker for terminal blocks - ZB 8,LGS:L1-N,PE - 1052413



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

Insertion bridge

Insertion bridge - EB 2- 8 - 0202154



Insertion bridge, pitch: 8 mm, color: gray

 Max. current carrying capacity: 57 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Insertion bridge

Insertion bridge - EB 3- 8 - 0202141



Insertion bridge, pitch: 8 mm, color: gray

 Max. current carrying capacity: 57 A

Insertion bridge

Insertion bridge - EB 10- 8 - 0202138



Insertion bridge, pitch: 8 mm, color: gray

 Max. current carrying capacity: 57 A

Fuse modular terminal block - UK 6-FSI/C-LED12

3001925

<https://www.phoenixcontact.com/in/products/3001925>

Insertion bridge

Insertion bridge - EB 4- 8 - 0202142

Insertion bridge, pitch: 8 mm, color: gray




 Max. current carrying capacity: 57 A

Insertion bridge

Insertion bridge - EB 1/3/5/7-8 - 3072340

Insertion bridge, pitch: 16.4 mm, pin assignment: 1, 3, 5, 7, color: gray



 Max. current carrying capacity: 57 A

Fuse modular terminal block - UK 6-FSI/C-LED12



3001925


<https://www.phoenixcontact.com/in/products/3001925>

Insertion bridge

Insertion bridge - EB 1/3/5-8 - 3072341

Insertion bridge, pitch: 16.4 mm, pin assignment: 1,3,5, color: gray




 Max. current carrying capacity: 57 A

Bridge

Bridge - ISSBI 10- 8 - 0301534

Bridge, pitch: 8 mm, color: silver



 Max. current carrying capacity: 38 A

Phoenix Contact 2021 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in