Vishay General Semiconductor


Surface Mount Schottky Barrier Rectifier



www.vishay.com

GL41 (DO-213AB)

DESIGN SUPPORT TOOLS





PRIMARY CHARACTERISTICS						
I _{F(AV)}	1.0 A					
V _{RRM}	20 V to 60 V					
I _{FSM}	30 A					
V _F	0.50 V, 0.70 V					
T _J max.	125 °C, 150 °C					
Package	GL41 (DO-213AB)					
Circuit configuration	Single					

FEATURES

- MELF Schottky rectifier
- · Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- Low forward voltage drop
- · High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 250 °C
- AEC-Q101 gualified
- · Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications

MECHANICAL DATA

Case: GL41 (DO-213AB) Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/NHE3 - RoHS-compliant, AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: two bands indicate cathode end 1st band denotes device type 2nd band denotes voltage type

MAXIMUM RATINGS ($T_A = 25 \text{ °C}$ unless otherwise noted)							
PARAMETER	SYMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT
DENOTES SCHOTTKY DEVICES: 1 st BAND IS ORANGE		SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	
Polarity color bands (2 nd band) voltage type		Gray	Red	Orange	Yellow	Green	
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	V
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	V
Maximum average forward rectified current (fig. 1)	I _{F(AV)}	1.0				А	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	30					А
Voltage rate of change (rated V _R)	dV/dt	10 000				V/µs	
Operating junction temperature range	TJ	-55 to +125 -55 to +150				°C	
Storage temperature range	T _{STG}	-55 to +150				°C	

Reivision: 19-Feb-18





Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)									
	TEST CONDITIONS		SYMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT
PARAMETER TEST COND		ONDITIONS		SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	
Maximum instantaneous forward voltage ⁽¹⁾	1.0 A		V _F	0.50	0.50	0.50	0.70	0.70	V
Maximum reverse	T _A = 25 °C			0.5					
current at rated DC blocking voltage ⁽¹⁾		T _A = 100 °C	I _R		10		5	.0	mA
Typical junction capacitance	4.0 V, 1.0 MHz C _J		CJ	110		80		pF	

Note

⁽¹⁾ Pulse test: 300 µs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)							
PARAMETER	SAMBUI	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT
PARAMETER		SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	
Maximum thermal resistance ⁽¹⁾	$R_{\theta JA}$	75					°C/W
Maximum thermal resistance (*)	$R_{\theta JT}$	30				C/W	

Note


⁽¹⁾ Thermal resistance junction to terminal, 0.24" x 0.24" (6.0 mm x 6.0 mm) copper pads to each terminal

ORDERING INFORMATION (Example)								
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE				
SGL41-40-E3/96	0.137	96	1500	7" diameter plastic tape and reel				
SGL41-40-E3/97	0.137	97	5000	13" diameter plastic tape and reel				
BYM13-40-E3/96	0.137	96	1500	7" diameter plastic tape and reel				
BYM13-40-E3/97	0.137	97	5000	13" diameter plastic tape and reel				
SGL41-40HE3/96 (1)	0.137	96	1500	7" diameter plastic tape and reel				
SGL41-40HE3/97 (1)	0.137	97	5000	13" diameter plastic tape and reel				
BYM13-40HE3/96 (1)	0.137	96	1500	7" diameter plastic tape and reel				
BYM13-40HE3/97 (1)	0.137	97	5000	13" diameter plastic tape and reel				

Note

(1) AEC-Q101 qualified

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)






Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current

Reivision: 19-Feb-18

2

Document Number: 88548

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics





Fig. 4 - Typical Reverse Characteristics





1st band denotes type and positive end (cathode)




Fig. 5 - Typical Junction Capacitance



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

SGL41-20/46 SGL41-20-E3/25 SGL41-20-E3/26 SGL41-20-E3/46 SGL41-20-E3/51 SGL41-20-E3/75 SGL41-20-E3/76 SGL41-20-E3/96 SGL41-20HE3/75 SGL41-20HE3/76 SGL41-20HE3/96 SGL41-30/46 SGL41-30-E3/25 SGL41-30-E3/26 SGL41-30-E3/46 SGL41-30-E3/51 SGL41-30-E3/75 SGL41-30-E3/76 SGL41-30-E3/96 SGL41-30HE3/75 SGL41-30HE3/76 SGL41-30HE3/96 SGL41-40/46 SGL41-40-E3/25 SGL41-40-E3/26 SGL41-40-E3/46 SGL41-40-E3/51 SGL41-40-E3/75 SGL41-40-E3/76 SGL41-40-E3/96 SGL41-40HE3/75 SGL41-40HE3/76 SGL41-40HE3/96 SGL41-50/46 SGL41-50-E3/46 SGL41-50-E3/96 SGL41-50HE3/96 SGL41-60/46 SGL41-60-E3/25 SGL41-60-E3/26 SGL41-60-E3/46 SGL41-60-E3/51 SGL41-60-E3/75 SGL41-60-E3/76 SGL41-60-E3/96 SGL41-60HE3/75 SGL41-60HE3/76 SGL41-60HE3/96 BYM13-20/25 BYM13-20/26 BYM13-20/51 BYM13-20/75 BYM13-20/76 BYM13-20/96 BYM13-20-E3/25 BYM13-20-E3/26 BYM13-20-E3/46 BYM13-20-E3/51 BYM13-20-E3/75 BYM13-20-E3/76 BYM13-20-E3/96 BYM13-20HE3/75 BYM13-20HE3/76 BYM13-20HE3/96 BYM13-30/25 BYM13-30/26 BYM13-30/46 BYM13-30/51 BYM13-30/75 BYM13-30/76 BYM13-30/96 BYM13-30-E3/25 BYM13-30-E3/26 BYM13-30-E3/46 BYM13-30-E3/51 BYM13-30-E3/75 BYM13-30-E3/76 BYM13-30-E3/96 BYM13-30HE3/75 BYM13-30HE3/76 BYM13-30HE3/96 BYM13-40/25 BYM13-40/26 BYM13-40/46 BYM13-40/51 BYM13-40/75 BYM13-40/76 BYM13-40/96 BYM13-40-E3/25 BYM13-40-E3/26 BYM13-40-E3/46 BYM13-40-E3/51 BYM13-40-E3/75 BYM13-40-E3/76 BYM13-40-E3/96 BYM13-40HE3/75 BYM13-40HE3/76 BYM13-40HE3/96 BYM13-50/25 BYM13-50/26