



## VOIDLESS HERMETICALLY SEALED STANDARD RECOVERY GLASS RECTIFIERS

Qualified to MIL-PRF-19500/420

Qualified Levels:  
JAN, JANTX, JANTXV  
and JANS

### DESCRIPTION

This “standard recovery” rectifier diode series is military qualified and is ideal for high-reliability applications where a failure cannot be tolerated. These industry-recognized 5.0 amp rated rectifiers for working peak reverse voltages from 200 to 1000 volts are hermetically sealed with voidless-glass construction using an internal “Category 1” metallurgical bond. These devices are also available in surface mount MELF package configurations. Microsemi also offers numerous other rectifier products to meet higher and lower current ratings with various recovery time speed requirements including fast and ultrafast device types in both through-hole and surface mount packages.

**Important:** For the latest information, visit our website <http://www.microsemi.com>.

### FEATURES

- JEDEC registered 1N5550 thru 1N5554 series.
- Voidless hermetically sealed glass package.
- Extremely robust construction.
- Quadruple-layer passivation.
- Internal “Category 1” metallurgical bonds.
- JAN, JANTX, JANTXV and JANS qualified versions available per MIL-PRF-19500/420.
- RoHS compliant versions available (commercial grade only).


### APPLICATIONS / BENEFITS

- Standard recovery 5 amp 200 to 1000 volts rectifier series.
- Military and other high-reliability applications.
- General rectifier applications including bridges, half-bridges, catch diodes, etc.
- High forward surge current capability.
- Low thermal resistance.
- Controlled avalanche with peak reverse power capability.
- Extremely robust construction.
- Inherently radiation hard as described in Microsemi “[MicroNote 050](#)”.

### MAXIMUM RATINGS @ T<sub>A</sub> = 25 °C unless otherwise noted.

Parameters/Test Conditions	Symbol	Value	Unit
Junction and Storage Temperature	T <sub>J</sub> and T <sub>STG</sub>	-65 to +175	°C
Thermal Resistance Junction-to-Lead <sup>(1)</sup>	R <sub>θJL</sub>	22	°C/W
Thermal Impedance @ 10 ms heating time	Z <sub>θJX</sub>	1.5	°C/W
Maximum Forward Surge Current (8.3 ms half sine)	I <sub>FSM</sub>	100	A
Average Rectified Forward Current <sup>(1)</sup> @ T <sub>L</sub> = 30 °C	I <sub>O(L)</sub>	5	A
Average Rectified Forward Current <sup>(3)</sup> @ T <sub>A</sub> = 55 °C	I <sub>O2</sub> <sup>(2)</sup>	3	A
@ T <sub>A</sub> = 100 °C	I <sub>O3</sub> <sup>(4)</sup>	2	A
Working Peak Reverse Voltage	V <sub>RWM</sub>	200 400 600 800 1000	V
Solder Temperature @ 10 s	T <sub>SP</sub>	260	°C

See notes on next page.




“B” Package

Also available in:

“B” SQ-MELF  
(D-5B) Package

(surface mount)

 [1N5550US – 1N5554US](#)

#### MSC – Lawrence

6 Lake Street,  
Lawrence, MA 01841  
Tel: 1-800-446-1158 or  
(978) 620-2600  
Fax: (978) 689-0803

#### MSC – Ireland

Gort Road Business Park,  
Ennis, Co. Clare, Ireland  
Tel: +353 (0) 65 6840044  
Fax: +353 (0) 65 6822298

Website:

[www.microsemi.com](http://www.microsemi.com)

**MAXIMUM RATINGS**

- Notes:**
1. At .375 inch (9.52 mm) lead length from body.
  2. Derate linearly at 22.2 mA/°C from +55 °C to +100 °C.
  3. These  $I_O$  ratings are for a thermally (PC boards or other) mounting methods where the lead or end-cap temperatures cannot be maintained and where thermal resistance from mounting point to ambient is still sufficiently controlled where  $T_{J(MAX)}$  does not exceed 175 °C. This equates to  $R_{\theta,JX} \leq 47$  °C/W.
  4. Derate linearly at 26.7 mA/°C above  $T_A = +100$  °C to +175 °C ambient.

**MECHANICAL and PACKAGING**

- CASE: Hermetically sealed voidless hard glass with tungsten slugs.
- TERMINALS: Axial-leads are tin/lead (Sn/Pb) over copper. RoHS compliant matte-tin is available for commercial only.
- MARKING: Body paint and part number.
- POLARITY: Cathode band.
- TAPE & REEL option: Standard per EIA-296. Consult factory for quantities.
- WEIGHT: 750 milligrams.
- See [Package Dimensions](#) on last page.

**PART NOMENCLATURE**

**JAN 1N5550 (e3)**

**Reliability Level**

JAN = JAN Level  
 JANTX = JANTX Level  
 JANTXV = JANTXV Level  
 JANS = JANS Level  
 Blank = commercial

**JEDEC type number**

See [Electrical Characteristics](#) table

**RoHS Compliance**

e3 = RoHS compliant (available on commercial grade only)  
 Blank = non-RoHS compliant

**SYMBOLS & DEFINITIONS**


Symbol	Definition
$V_{BR}$	Minimum Breakdown Voltage: The minimum voltage the device will exhibit at a specified current.
$V_{RWM}$	Working Peak Reverse Voltage: The maximum peak voltage that can be applied over the operating temperature range excluding all transient voltages (ref JESD282-B).
$I_O$	Average Rectified Output Current: The Output Current averaged over a full cycle with a 50 Hz or 60 Hz sine-wave input and a 180 degree conduction angle.
$V_F$	Maximum Forward Voltage: The maximum forward voltage the device will exhibit at a specified current.
$I_R$	Maximum Reverse Current: The maximum reverse (leakage) current that will flow at the specified voltage and temperature.
$t_{rr}$	Reverse Recovery Time: The time interval between the instant the current passes through zero when changing from the forward direction to the reverse direction and a specified decay point after a peak reverse current occurs.

**ELECTRICAL CHARACTERISTICS @  $T_A = 25^\circ\text{C}$  unless otherwise noted.**


TYPE	MINIMUM BREAKDOWN VOLTAGE $V_{BR}$ $I_R @ 50 \mu\text{A}$ Volts	FORWARD VOLTAGE $V_F @ I_F = 9 \text{ A (pk)}$		MAXIMUM REVERSE CURRENT $I_R @ V_{RWM}$ $\mu\text{A}$	REVERSE RECOVERY $t_{rr}$ (Note 1) $\mu\text{s}$
		MIN. Volts	MAX. Volts		
1N5550	220	0.6 V (pk)	1.2 V (pk)	1.0	2.0
1N5551	440	0.6 V (pk)	1.2 V (pk)	1.0	2.0
1N5552	660	0.6 V (pk)	1.2 V (pk)	1.0	2.0
1N5553	880	0.6 V (pk)	1.3 V (pk)	1.0	2.0
1N5554	1100	0.6 V (pk)	1.3 V (pk)	1.0	2.0

**NOTE 1:**  $I_F = 0.5 \text{ A}$ ,  $I_{RM} = 1.0 \text{ A}$ ,  $I_{R(REC)} = .250 \text{ A}$ .

GRAPHS




**FIGURE 1**  
Maximum Thermal Impedance




**FIGURE 2**  
Maximum Current vs. Lead Temperature

- NOTES:** 1. Dimensions are in inches.  
2. Metric equivalents (to the nearest .01 mm) are given for general information only and are based upon 1 inch = 25.4 mm.

GRAPHS (continued)



**FIGURE 3**  
Typical Forward Voltage vs. Forward Current

**PACKAGE DIMENSIONS**


Ltr	Dimensions				Notes
	Inch		Millimeters		
	Min	Max	Min	Max	
<b>BD</b>	0.115	0.180	2.92	4.57	3, 4
<b>BL</b>	0.130	0.300	3.30	7.62	4
<b>LD</b>	0.036	0.042	0.92	1.07	
<b>LL</b>	0.900	1.300	22.86	33.02	

**NOTES:**

1. Dimensions are in inches.
2. Millimeter equivalents are given for general information only.
3. The BL dimension shall include the entire body including slugs and sections of the lead over which the diameter is uncontrolled. This uncontrolled area is defined as the zone between the edge of the diode body and extending .050 inch (1.27 mm) onto the leads.
4. Dimension BD shall be measured at the largest diameter.
5. In accordance with ASME Y14.5M, diameters are equivalent to  $\Phi$ x symbology.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Microsemi:

[JANTXV1N5552](#) [JANTXV1N5551](#) [JAN1N5552](#) [JAN1N5553](#) [JAN1N5550](#) [1N5551](#) [1N5552](#) [JAN1N5551](#)  
[JANTX1N5551](#) [JANTX1N5553](#) [JANTX1N5552](#) [JANTX1N5554](#) [JANTX1N5550](#) [1N5554](#) [1N5553](#) [1N5550](#)  
[1N5552/TR](#) [JAN1N5554/TR](#) [JANS1N5552/TR](#) [JANS1N5554/TR](#) [JAN1N5553/TR](#) [JANTX1N5554/TR](#) [JAN1N5551/TR](#)  
[JANTXV1N5554/TR](#) [JANTX1N5550/TR](#) [JANTX1N5551/TR](#) [JANTXV1N5550/TR](#) [JANTX1N5552/TR](#)  
[JANS1N5551/TR](#) [JAN1N5552/TR](#) [JANTXV1N5552/TR](#) [JANTX1N5553/TR](#) [JANS1N5553/TR](#) [JANTXV1N5553/TR](#)  
[JANTXV1N5551/TR](#) [JAN1N5550/TR](#) [1N5551/TR](#) [1N5553/TR](#) [1N5554/TR](#) [1N5550/TR](#)