
# anasonīc

# **Automation Controls Catalog**

## 







```
RoHS compliant
```

low-level analog signals without distortion.

3. Low-level off state leakage current of max. 1  $\mu$ A

Photo MOS<sup>®</sup> GU SOP 2 Form A (AQW21OS)

## TYPICAL APPLICATIONS

- Measuring instruments
- Data communications
- Computers
- Industrial robots

TYPES										
	Output rating*				Part No.	Packing quantity				
	Load Load voltage current	Load Package		Tape and reel	packing style					
			l'uonago	Tube packing style	Picked from the 1/2/3/4-pin side	Picked from the 5/6/7/8-pin side	Tube	Tape and reel		
	60V	400mA	SOP8-pin	AQW212S	AQW212SX	AQW212SZ	1 tube contains:			
AC/DC dual use	350V	100mA		AQW210S	AQW210SX	AQW210SZ	50 pcs. 1 batch contains: 1,000 pcs.	1,000 pcs.		
	400V	80mA		AQW214S	AQW214SX	AQW214SZ				

\* Indicate the peak AC and DC values.

Note: The packing style indicator "X" or "Z" are not marked on the device.

## RATING


1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)

	Symbol	AQW212S	AQW210S	AQW214S	Remarks		
Input	LED forward current	١۶	50 mA				
	LED reverse voltage	VR	5 V				
	Peak forward current	IFP	IFP 1 A			f = 100 Hz, Duty factor = 0.1%	
	Power dissipation	Pin	75 mW				
	Load voltage (peak AC)	VL	60 V	350 V	400 V		
Output	Continuous load current	l.	0.4 A (0.5 A)	0.1 A (0.13 A)	0.08 A (0.1 A)	Peak AC, DC (): in case of using only 1 channel	
	Peak load current	Ipeak	1.5 A	0.3 A	0.24 A	A connection: 100 ms (1 shot), V <sub>L</sub> = D	
	Power dissipation	Pout	600 mW				
Total power dissipation		Ρτ	650 mW				
I/O isolation voltage		Viso	1,500 Vrms				
Ambient temperature	Operating	Topr	<b>−40 to +85°C</b> −40 to +185°F			(Non-icing at low temperatures)	
Ambient temperature	Storage	Tstg	-40 to +100°C -40 to +212°F				

# GU SOP 2 Form A (AQW21OS)

	Item	Symbol	AQW212S	AQW210S	AQW214S	Condition		
		Typical		0.9 mA			— I∟ = Max.	
	LED operate current	Maximum	Fon	3 mA				
Innut	LED turn off current	Minimum	l= n	0.4 mA			l∟ = Max.	
Input	LED turn on current	Typical	Foff	0.8 mA				
	LED dropout voltage	Typical	Ve –	1.25 V (1.14 V at I⊧ = 5 mA)			— I⊧ = 50 mA	
	LED dropout voltage	Maximum	VF	1.5 V				
Output	On resistance	Typical	- Ron -	0.83 Ω	16 Ω	30 Ω	l⊧ = 5 mA I∟ = Max. Within 1 s	
		Maximum	- Ron	2.5 Ω	35 Ω	50 Ω		
	Off state leakage current	Maximum	ILeak	1 μΑ		l⊧ = 0 mA V∟ = Max.		
Transfer characteristics	Turn on time*	Typical	- Ton -	0.65 ms	0.23 ms	0.21 ms	l⊧ = 5 mA	
		Maximum	Ion	2 ms	0.5	ms	I∟ = Max.	
	Turn off time*	Typical	- Toff -	0.08 ms	0.04 ms		I⊧ = 5 mA	
		Maximum	Lott	0.2 ms			I∟ = Max.	
	I/O consolitance	Typical	- Ciso -	0.8 pF			f = 1 MHz V <sub>B</sub> = 0 V	
	I/O capacitance	Maximum	UISO	1.5 pF				
	Initial I/O isolation resistance	Minimum	Riso	1,000 MΩ		500 V DC		

\*Turn on/Turn off time



3. Recommended operating conditions (Ambient temperature: 25°C 77°F)
Please use under recommended operating conditions to obtain expected characteristics.


	Item	Symbol	Number of used channels	Min.	Max.	Unit
LED current		IF		5	30	mA
	Load voltage (Peak AC)	VL		_	48	V
AQW212S	Continuous load current	l.	1ch 2ch	_	0.5 0.4	А
AQW210S	Load voltage (Peak AC)	VL		—	280	V
	Continuous load current	lı.	1ch 2ch	—	0.13 0.1	А
AQW214S	Load voltage (Peak AC)	VL		—	320	V
	Continuous load current	lı.	1ch 2ch	_	0.1 0.08	А

#### ■ These products are not designed for automotive use.


If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

### **REFERENCE DATA**

1.-(1) Load current vs. ambient temperature characteristics




1.-(2) Load current vs. ambient temperature characteristics



2.-(1) On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8; LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)




Panasonic Corporation Electromechanical Control Business Division industrial panasonic.com/ac/e/


## GU SOP 2 Form A (AQW21OS)

2.-(2) On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8; LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)




5. LED operate current vs. ambient temperature characteristics Sample: All types; Load voltage: Max. (DC); Continuous load current: Max. (DC)




#### 8.-(1) Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F



10. Turn on time vs. LED forward current characteristics


Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 7




3. Turn on time vs. ambient temperature characteristics

LED current: 5 mA; Load voltage: Max. (DC);

Continuous load current: Max. (DC)




6. LED turn off current vs. ambient temperature characteristics




8.-(2) Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F




#### 11. Turn off time vs. LED forward current characteristics


Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77




4. Turn off time vs. ambient temperature characteristics LED current: 5 mA;

Load voltage: Max. (DC);






7. LED dropout voltage vs. ambient temperature characteristics Sample: All types;



#### 9. Off state leakage current vs. load voltage characteristics


Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F



12. Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8; Frequency: 1 MHz;

Ambient temperature: 25°C 77°F



Panasonic Corporation Electromechanical Control Business Division industrial.panasonic.com/ac/e/

"PhotoMOS", "PhotoMOS" and "PHOTOMOS" are registered trademarks of Panasonic Corporation. \*Recognized in Japan, the United States, all member states of European Union and other countries.

Please contact .....

## Panasonic Corporation Electromechanical Control Business Division

Electromechanical Control Business Division ■ 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan industrial.panasonic.com/ac/e/



©Panasonic Corporation 2017

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

AQW210SX AQW210S AQW212S AQW210SZ AQY212SD09 AQW414SZ AQW212SX