





| Rev | AWO # | Description | Date | Appr |
|-----|-------|-------------|----------|------|
| - | 7553 | RELEASED | 02/23/07 | |

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:
 Material:
 Insulator: Hi-temp thermoplastic, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass

A=.049 [1.25] X No. of Spaces
 B=.049 [1.25] X No. of Spaces + .070 [1.80]
 C=.049 [1.25] X No. of Spaces +.118 [3.00]
 D=.049 [1.25] X No. of Spaces + .251 [6.40]

Plating:
 Tin over Nickel underplate overall
Electrical:
 Operating voltage: 250 VAC max
 Current rating: 1 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 100 Mohms min
 Dielectric withstanding voltage: 250 VAC for 1 minute
Temperature Rating:
 Operating temperature: -40°C to +85°C
 Environmental:
 Lead free, RoHS compliant.

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710
 TITLE: MX 1.25mm WAFER SMT STRAIGHT

| | |
|--|--------------|
| UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] | |
| TOLERANCES: EXCEPT AS NOTED | |
| INCHES | HOLES |
| .X ± .10 | ØXX ± .10 |
| .XX ± .020 | ØXXX ± .015 |
| .XXX ± .015 | ØXXXX ± .010 |
| APPROVALS | DATE |
| DRAWN | BW |
| CHECKED | |
| APPROVED | |

| | | |
|------|-------------------|--------------|
| SIZE | PART NO. | REV. |
| X | 125SH+A-XX-TS-SMT | - |
| REF: | SCALE: NTS | SHEET 1 OF 1 |