

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese

FAIRCHILD

SEMICONDUCTOR

74LCXH162244

Low Voltage 16-Bit Buffer/Line Driver with Bushold and 26 Ω Series Resistors in Outputs

General Description

The LCXH162244 contains sixteen non-inverting buffers with 3-STATE outputs designed to be employed as a memory and address driver, clock driver, or bus oriented transmitter/receiver. The device is nibble controlled. Each nibble has separate 3-STATE control inputs which can be shorted together for full 16-bit operation.

The LCXH162244 data inputs include active bushold circuitry, eliminating the need for external pull-up resistors to hold unused or floating data inputs at a valid logic level.

In addition, the outputs include equivalent 26Ω (nominal) series resistors to reduce overshoot and undershoot and are designed to sink/source up to 12 mA at V_{CC} = 3.0V.

The LCXH162244 is designed for low voltage (2.5V or 3.3V) $\rm V_{CC}$ applications with capability of interfacing to a 5V signal environment.

The LCXH162244 is fabricated with an advanced CMOS technology to achieve high speed operation while maintaining CMOS low power dissipation.

Features

- 5V tolerant control inputs and outputs
- 2.3V–3.6V V_{CC} specifications provided
- Outputs include equivalent series resistance of 26Ω to make external termination resistors unnecessary and reduce overshoot and undershoot

September 2000

Revised May 2005

- Bushold on data inputs eliminates the need for external pull-up/pull-down resistors
- \blacksquare 5.3 ns t_{PD} max (V_{CC} = 3.0V), 20 μA I_{CC} max
- Power down high impedance inputs and outputs
- ±12 mA output drive (V_{CC} = 3.0V)
- Implements proprietary noise/EMI reduction circuitry
- Latch-up performance exceeds 500 mA
 ESD performance:
 - Human body model > 2000V Machine model > 200V


Ordering Co	de:	
Order Number	Package Number	Package Description
74LCXH162244MEA	MS48A	48-Lead Small Shrink Outline Package (SSOP), JEDEC MO-118, 0.300" Wide [RAIL]
74LCXH162244MEX	MS48A	48-Lead Small Shrink Outline Package (SSOP), JEDEC MO-118, 0.300" Wide [TAPE and REEL]
74LCXH162244MTD	MTD48	48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide [RAIL]
74LCXH162244MTX	MTD48	48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide [TAPE and REEL]

© 2005 Fairchild Semiconductor Corporation DS500249

74LCXH162244

Connection D	iagram	
Connection D	1 2 3 4 5 5 6 7 8 9 10 11 11 12 13 14 15 16 17 18	48 OE2 47 Ig 46 Ig 45 GND 44 I2 43 I3 44 I5 38 I6 37 I7 35 I8 34 GND 332 I10 31 VCc 30 I12
	19 20 21 22 23	00

Logic Symbol



Pin Descriptions

Pin Names	Description
OE _n	Output Enable Input (Active LOW)
I ₀ -I ₁₅	Bushold Inputs
O ₀ -O ₁₅	Outputs

Truth Tables

Inp	Inputs		
OE ₁	OE ₁ I ₀ -I ₃		
L	L	L	
L	н	н	
Н	Х	Z	

Inp	uts	Outputs
OE ₂	I ₄ —I ₇	0 ₄ –0 ₇
L	L	L
L	н	н
н	Х	Z

Inp	uts	Outputs
\overline{OE}_3	I ₈ –I ₁₁	0 ₈ –0 ₁₁
L	L	L
L	н	н
Н	Х	Z

In	puts	Outputs
OE ₄	I ₁₂ –I ₁₅	O ₁₂ -O ₁₅
L	L	L
L	н	н
н	х	Z
X = Immaterial		•

H = HIGH Voltage Level L = LOW Voltage Level


Functional Description

The LCXH162244 contains sixteen non-inverting buffers with 3-STATE standard outputs. The LCXH162244 data inputs include active bushold circuitry eliminating the need for pull-up resistors to hold unused or floating data inputs at a valid logic level. The devise is also designed with 26Ω series resistors in the outputs. This design reduces line noise in applications such as memory address drivers, clock drivers and bus transceiver/transmitters. The device is nibble (4 bits) controlled with each nibble functioning

Z = High Impedance

identically, but independent of the other. The control pins can be shorted together to obtain full 16-bit operation. The 3-STATE outputs are controlled by an Output Enable (\overline{OE}_n) input for each nibble. When \overline{OE}_n is LOW, the outputs are in 2-state mode. When \overline{OE}_n is HIGH, the outputs are in the high impedance mode, but this does not interfere with entering new data into the inputs.

Logic Diagram



3

74LCXH162244

Absolute Maximum Ratings(Note 1)

Symbol	Parameter Value			Conditions	Units	
V _{CC}	Supply Voltage		Supply Voltage -0.5 to +7.0		V	
VI	DC Input Voltage OE		-0.5 to +7.0		V	
		I ₀ - I ₁₅	-0.5 to V _{CC} + 0.5		v	
Vo	DC Output Voltage		-0.5 to +7.0	Output in 3-STATE	V	
			–0.5 to V_{CC} + 0.5	Output in HIGH or LOW State (Note 2)	v	
I _{IK}	DC Input Diode Current		-50	V _I < GND	mA	
I _{OK}	DC Output Diode Current DC Output Source/Sink Current		-50	V _O < GND	mA	
			+50	$V_{O} > V_{CC}$	ШA	
I _O			±50		mA	
I _{CC}	DC Supply Current per Supply Pin		±100		mA	
I _{GND}	DC Ground Current per Ground Pin		±100		mA	
T _{STG}	Storage Temperature		-65 to +150		°C	

Recommended Operating Conditions (Note 3)

Symbol	Parameter		Min	Max	Units	
V _{CC}	Supply Voltage	2.0	3.6	V		
		Data Retention	1.5	3.6	v	
VI	Input Voltage		0	V _{CC}	V	
Vo	Output Voltage	HIGH or LOW State	0	V _{CC}	V	
		3-STATE	0	5.5	v	
I _{OH} /I _{OL}	Output Current	V _{CC} = 3.0V – 3.6V		±12		
		$V_{CC} = 3.0V - 3.6V$ $V_{CC} = 2.7V - 3.0V$ $V_{CC} = 2.3V - 2.7V$		±8	mA	
		$V_{CC} = 2.3V - 2.7V$		±4		
T _A	Free-Air Operating Temperature		-40	85	°C	
$\Delta t / \Delta V$	Input Edge Rate, V _{IN} = 0.8V–2.0V, V _{CC} = 3.0V		0	10	ns/V	

Note 1: The Absolute Maximum Ratings are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the Absolute Maximum Ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 2: I_O Absolute Maximum Rating must be observed.

Note 3: Unused control inputs must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

Symbol	Parameter	Conditions	V _{cc}	$T_A = -40$ °C to +85 °C		Units
Symbol	Falameter	Conditions	(V)	Min	Max	Units
VIH	HIGH Level Input Voltage		2.3 – 2.7	1.7		V
			2.7 – 3.6	2.0		v
V _{IL}	LOW Level Input Voltage		2.3 – 2.7		0.7	V
			2.7 – 3.6		0.8	v
V _{OH} HIGH L	HIGH Level Output Voltage	I _{OH} = -100 μA	2.3 - 3.6	V _{CC} - 0.2		
		I _{OH} = -4 mA	2.3	1.8		V
		$I_{OH} = -4 \text{ mA}$	2.7	2.2		
		I _{OH} = -6 mA	3.0	2.4		
		I _{OH} = -8 mA	2.7	2.0		
		I _{OH} = -12 mA	3.0	2.0		
V _{OL}	LOW Level Output Voltage	I _{OL} = 100 μA	2.3 - 3.6		0.2	
		I _{OL} = 4 mA	2.3		0.6	
		I _{OL} = 4 mA	2.7		0.4	v
		I _{OL} = 6 mA	3.0		0.55	v
		I _{OL} = 8 mA	2.7		0.6	
		I _{OL} = 12 mA	3.0		0.8	

Symbol	Parameter		Conditions	V _{CC}	T _A = -40°0	C to +85°C	Units
	Parameter		Conditions	(V)	Min	Max	Unite
I _I	Input Leakage Current	Data	$V_I = V_{CC}$ or GND	2.3 - 3.6		±5.0	μA
		Control	$0 \le V_I \le 5.5$	2.3 - 3.6		±5.0	μΑ
I _{I(HOLD)}	Bushold Input Minimum		$V_{IN} = 0.7V$	2.3 45			
Drive	Drive Hold Current		$V_{IN} = 1.7V$	2.3	-45		цА
			$V_{IN} = 0.8V$	3.0	75		μα
			$V_{IN} = 2.0V$	3.0	-75		
I _{I(OD)}	Bushold Input Over-Drive		(Note 4)	2.7	300		
Current to Change State			(Note 5)	2.1	-300		μA
			(Note 4)	3.6	450		
			(Note 5)	3.0	-450		
l _{oz}	3-STATE Output Leakage		$0 \le V_O \le 5.5V$	2.3 - 3.6		±5.0	
			$V_I = V_{IH} \text{ or } V_{IL}$	2.3 - 3.0		± 3 .0	μA
IOFF	Power-Off Leakage Current		$V_0 = 5.5V$	0		10	μA
I _{CC}	Quiescent Supply Current		V _I = V _{CC} or GND	2.3 - 3.6		20	μA
Δl _{CC}	Increase in I _{CC} per Input		$V_{IH} = V_{CC} - 0.6V$	2.3 - 3.6		500	μA

Note 4: An external driver must source at least the specified current to switch from LOW-to-HIGH.

Note 5: An external driver must sink at least the specified current to switch from HIGH-to-LOW.

AC Electrical Characteristics

			$T_A = -40^{\circ}C \text{ to } +85^{\circ}C, R_L = 500 \Omega$					
Symbol	Parameter	$V_{CC}=3.3V\pm0.3V$		$V_{CC} = 2.7V$		$V_{CC}=2.5V\pm0.2V$		Units
		C _L =	C _L = 50 pF		C _L = 50 pF		C _L = 30 pF	
		Min	Max	Min	Max	Min	Max	
t _{PHL}	Propagation Delay	1.0	5.3	1.0	6.0	1.0	6.4	
t _{PLH}	Data to Output	1.0	5.3	1.0	6.0	1.0	6.4	ns
t _{PZL}	Output Enable Time	1.0	6.3	1.0	7.1	1.0	8.2	
t _{PZH}		1.0	6.3	1.0	7.1	1.0	8.2	ns
t _{PLZ}	Output Disable Time	1.0	5.4	1.0	5.7	1.0	6.5	-
t _{PHZ}		1.0	5.4	1.0	5.7	1.0	6.5	ns
t _{OSHL}	Output to Output Skew (Note 6)		1.0					ns
tOSLH			1.0					ns


Note 6: Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW (t_{OSHL}) or LOW-to-HIGH (t_{OSLH}). Parameter guaranteed by design.


Dynamic Switching Characteristics

Symbol	Parameter	Conditions	V _{cc}	$T_A = 25^{\circ}C$	Units
			(V)	Typical	
V _{OLP}	Quiet Output Dynamic Peak V _{OL}	$C_L = 50 \text{ pF}, V_{IH} = 3.3 \text{V}, V_{IL} = 0 \text{V}$	3.3	0.35	V
		$C_L = 30 \text{ pF}, V_{IH} = 2.5 \text{V}, V_{IL} = 0 \text{V}$	2.5	0.25	v
V _{OLV}	Quiet Output Dynamic Valley V _{OL}	$C_{L} = 50 \text{ pF}, V_{IH} = 3.3 \text{V}, V_{IL} = 0 \text{V}$	3.3	-0.35	M
		$C_L=30 \text{ pF, } V_{IH}=2.5 \text{V} \text{, } V_{IL}=0 \text{V}$	2.5	-0.25	v


Capacitance


Symbol	Parameter	Conditions	Typical	Units
C _{IN}	Input Capacitance	$V_{CC} = Open, V_I = 0V \text{ or } V_{CC}$	7	pF
C _{OUT}	Output Capacitance	$V_{CC} = 3.3V$, $V_I = 0V$ or V_{CC}	8	pF
C _{PD}	Power Dissipation Capacitance	$V_{CC} = 3.3V$, $V_I = 0V$ or V_{CC} , f = 10 MHz	20	pF





74LCXH162244





www.fairchildsemi.com

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly ori indirectly, any claim of personal injury or death

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: 74LCXH162244MTD 74LCXH162244MTX 74LCXH162244MEA