16 1613 21


# Power supply connectors





Power supply chassis socket, angular version, with break contact, for printed circuit boards


State: Active

1 of 3 01/2018














\*a printed circuit board layout, solder side view

#### **Environmental conditions**

Temperature range -20 °C/+70 °C

#### Materials

Insulating body PBT GF, V-0 according to UL94

Contact pin CuZn, nickel-plated Contact Cu alloy, tin-plated

### Mechanical data

Diameter opening 6,0 mm
Diameter center pin 2,35 mm
Mating cycles ≥ 5000¹

Insertion force 5–20 N (initial value) Withdrawal force 4–15 N (initial value)

<sup>1</sup> measured with a gauge plug

## Electrical data (at Tamb 20 °C)

 $\begin{array}{ll} \mbox{Contact resistance} & \leq 30 \ \mbox{m}\Omega \\ \mbox{Rated current} & 2 \ \mbox{A} \\ \mbox{Rated voltage} & 24 \ \mbox{V DC} \\ \mbox{Rated impulse voltage} & 500 \ \mbox{V/60 s} \\ \mbox{Insulation resistance} & \geq 100 \ \mbox{M}\Omega \\ \end{array}$ 

# Associated products

Counterparts

 © 1633 04
 © 1634 02
 © NES/J 25

☑ NES/J 250 ☑ XNES/J 250



1613 21 16

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
1613 21	2	250	500

**Packaging:** in bulk, in a cardboard box or a plastic bag

3 of 3 01/2018