

# <sup>OGY</sup> Low Noise, 8th Order, Clock Sweepable Elliptic Lowpass Filter

### **FEATURES**

- 8th Order Filter in a 14-Pin Package
- No External Components
- 100:1 Clock to Center Ratio
- 150µV<sub>RMS</sub> Total Wideband Noise
- 0.03% THD or Better
- 50kHz Maximum Corner Frequency
- Operates from ±2.37V to ±8V Power Supplies
- Passband Ripple Guaranteed Over Full Military Temperature Range

### **APPLICATIONS**

- Antialiasing Filters
- Telecom PCM Filters

### DESCRIPTION

The LTC $^{\circ}$ 1064-1 is an 8th order, clock sweepable elliptic (Cauer) lowpass switched capacitor filter. The passband ripple is typically  $\pm 0.15$ dB, and the stopband attenuation at 1.5 times the cutoff frequency is 68dB or more.

An external TTL or CMOS clock programs the value of the filter's cutoff frequency. The clock to cutoff frequency ratio is 100:1.

No external components are needed for cutoff frequencies up to 20kHz. For cutoff frequencies over 20kHz two low value capacitors are required to maintain passband flatness. The LTC1064-1 features low wideband noise and low harmonic distortion even for input voltages up to  $3V_{RMS}$ . In fact the LTC1064-1 overall performance completes with equivalent multiple op amp RC active realizations.


The LTC1064-1 is available in a 14-pin DIP or 16-pin surface mounted SW package.

The LTC1064-1 is pin compatible with the LTC1064-2.

17, LTC and LT are registered trademarks of Linear Technology Corporation.

## TYPICAL APPLICATION


### 8th Order Clock Sweepable Lowpass Elliptic Antialiasing Filter



NOTE: THE POWER SUPPLIES SHOULD BE BYPASSED BY A  $0.1\mu\text{F}$  CAPACITOR CLOSE TO THE PACKAGE.

FOR SERVO OFFSET NULLING APPLICATIONS, PIN 1 IS THE 2ND STAGE SUMMING JUNCTION.

\*FOR CUTOFF FREQUENCY ABOVE 20kHz, USE COMPENSATION CAPACITORS (5pF TO 56pF) BETWEEN PIN 13 AND PIN 1 AND PIN 6 AND PIN 7.




8th Order Clock sweepable Lowpass elliptic antialiasing filter maintains, for 0.1Hz  $\leq f_{CUTOFF} \leq$  10kHz, A  $\pm 0.15$ db Passband Ripple and 72db stopband attenuation at 1.5  $\times$   $f_{CUTOFF}$ . Total wideband noise = 150µV<sub>RMS</sub>, thd = 0.03% for V<sub>IN</sub> = 1V<sub>RMS</sub>



## **ABSOLUTE MAXIMUM RATINGS** (Note 1)

Total Supply Voltage (V <sup>+</sup> to V <sup>-</sup> )	Operating Temperature Range
Power Dissipation	LTC1064-1M ( <b>OBSOLETE</b> )55°C to 125°C
Storage Temperature Range65°C to 150°C	LTC1064-1C/AC40°C to 85°C
Lead Temperature (Soldering, 10 sec)300°C	

## PACKAGE/ORDER INFORMATION



Consult LTC Marketing for parts specified with wider operating temperature ranges.

**ELECTRICAL CHARACTERISTICS** The  $\bullet$  denotes the specifications which apply over the full operating temperature range, otherwise specifications are at  $T_A = 25^{\circ}$ C.  $V_S = \pm 7.5$ V,  $f_{CLK} = 1$ MHz, R1 = 10k, C1 = 10pF, TTL or CMOS clock input level unless otherwise specified.

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
Passband Gain, LTC1064-1, 1A	Referenced to OdB, 1Hz to 0.1f <sub>C</sub>	•		±0.1	±0.35	dB
Gain TempCo				0.0002		dB/°C
Passband Edge Frequency, f <sub>C</sub>				10 ± 1%		kHz
Gain at f <sub>C</sub> LTC1064-1 LTC1064-1A	Referenced to Passband Gain	•	-1.25 -0.75		0.85 0.65	dB dB
-3dB Frequency				10.7		kHz
Passband Ripple (Note 1) LTC1064-1 LTC1064-1A	0.1f <sub>C</sub> to 0.85f <sub>C</sub> Referenced to Passband Gain, Measured at 6.25kHz and 8.5kHz	•		±0.15 ±0.1	±0.32 ±0.19	dB dB
Ripple TempCo				0.0004		dB/°C
Stopband Attenuation LTC1064-1 LTC1064-1A	At 1.5f <sub>C</sub> Referenced to 0dB	•	66 68	72 72		dB dB
Stopband Attenuation LTC1064-1 LTC1064-1A	At 2f <sub>C</sub> Referenced to 0dB	•	67 68	72 72		dB dB




**ELECTRICAL CHARACTERISTICS** The  $\bullet$  denotes the specifications which apply over the full operating temperature range, otherwise specifications are at  $T_A = 25^{\circ}C$ .  $V_S = \pm 7.5V$ ,  $f_{CLK} = 1$ MHz, R1 = 10k, C1 = 10pF, TTL or CMOS clock input level unless otherwise specified.


PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
Input Frequency Range			0		f <sub>CLK</sub> /2	kHz
Output Voltage Swing and Operating Input Voltage Range	$V_S = \pm 2.37V$ $V_S = \pm 5V$ $V_S = \pm 7.5V$	•	±1 ±3 ±5			V V V
Total Harmonic Distortion	$V_S = \pm 5V$ , Input = $1V_{RMS}$ at 1kHz $V_S = \pm 7.5V$ , Input = $3V_{RMS}$ at 1kHz			0.015 0.03		% %
Wideband Noise	$V_S = \pm 5V$ , Input = GND 1Hz to 999kHz $V_S = \pm 7.5V$ , Input = GND 1Hz to 999kHz			150 165		μV <sub>RMS</sub> μV <sub>RMS</sub>
Output DC Offset LTC1064-1 LTC1064-1A Output DC Offset TempCo	$V_S = \pm 7.5V$ , Pin 2 Grounded $V_S = \pm 5V$			50 50 –100	175 125	mV mV μV/°C
Input Impedance			10	20		kΩ
Output Impedance	f <sub>OUT</sub> = 10kHz			2		Ω
Output Short-Circuit Current	Source/Sink			3/1		mA
Clock Feedthrough				200		μV <sub>RMS</sub>
Maximum Clock Frequency	50% Duty Cycle, V <sub>S</sub> = ±7.5V				5	MHz
Power Supply Current	$V_S = \pm 2.37V$	•		10	22	mA
	$V_S = \pm 5V$	•		12	23 26	mA mA
	$V_S = \pm 7.5V$ , $f_{CLK} = 1MHz$	•		16	28 32	mA mA
Power Supply Voltage Range		•	±2.37		±8	V


**Note 1:** Absolute Maximum Ratings are those values beyond which the life of a device may be impaired.

**Note 2:** For tighter specifications please contact LTC Marketing.

## TYPICAL PERFORMANCE CHARACTERISTICS













### TYPICAL PERFORMANCE CHARACTERISTICS









Typical Wideband Noise (151 $\mu$ V<sub>RMS</sub>) V<sub>S</sub> =  $\pm$ 5V, T<sub>A</sub> = 25°C f<sub>CLK</sub> = 1MHz, f<sub>C</sub> = 10kHz Input Grounded



Total Harmonic Distortion (0.025%)  $V_S = \pm 7.5 V$ ,  $T_A = 25^{\circ}C$   $f_{CLK} = 1 MHz$ ,  $f_C = 1 0 kHz$  Input = 1 kHz at  $3 V_{RMS}$ 



Power Supply Current vs Power Supply Voltage



# PIN FUNCTIONS (Pin Numbers Refer to the 14-Pin Package)

**COMP1, INV A, COMP2, INV C (Pins 1,6,7, and 13):** For filter cutoff frequencies higher than 20kHz, in order to minimize the passband ripple, compensation capacitors should be added between Pin 6 and Pin 7 (COMP1) and Pin 1 and Pin 13 (COMP2). For COMP1 (COMP2), add 1pF (1.5pF) mica capacitor for each kHz increase in cutoff frequency above 20kHz. For more detail refer to Gain vs Frequency graphs.

**V<sub>IN</sub>**, **V<sub>OUT</sub>** (**Pins 2**, **9**): The input Pin 2 is connected to an 18k resistor tied to the inverting input of an op amp. Pin 2

is protected against static discharge. The device's output, Pin 9, is the output of an op amp which can typically source/sink 3mA/1mA. Although the internal op amps are unity gain stable, driving long coax cables is not recommended.

When testing the device for noise and distortion, the output, Pin 9, should be buffered (Figure 4). The op amp power supply wire (or trace) should be connected directly to the power source.

**AGND (Pins 3, 5):** For dual supply operation these pins should be connected to a ground plane. For single supply



# **PIN FUNCTIONS** (Pin Numbers Refer to the 14-Pin Package)

operation both pins should be tied to one half supply (Figure 2). Also Pin 8 and Pin 10, although they are not internally connected should be tied to analog ground or system ground. This improves the clock feedthrough performance.

**V**<sup>+</sup>, **V**<sup>-</sup> (**Pins 4, 12**): The V<sup>+</sup> and V<sup>-</sup> pins should be bypassed with a  $0.1\mu$ F capacitor to an adequate analog ground. Low noise, nonswitching power supplies are recommended. *To avoid latchup when the power supplies exhibit high turn-on transients, a 1N5817 Schottky diode should be added from the V<sup>+</sup> and V<sup>-</sup> pins to ground (Figure 1).* 

**INV A, R(h, I) (Pins 7, 14):** A very short connection between Pin 14 and Pin 7 is recommended. This connection should be preferably done under the IC package. In a

breadboard, use a one inch, or less, shielded coaxial cable; the shield should be grounded. In a PC board, use a one inch trace or less; surround the trace by a ground plane.

**NC (Pins 8, 10):** The "no connection" pins preferably should be grounded.

f<sub>CLK</sub> (Pin 11): For ±5V supplies the logic threshold level is 1.4V. For ±8V and 0V to 5V supplies the logic threshold levels are 2.2V and 3V respectively. The logic threshold levels vary ±100mV over the full military temperature range. The recommended duty cycle of the input clock is 50% although for clock frequencies below 500kHz the clock "on" time can be as low as 200ns. The maximum clock frequency for ±5V supplies is 4MHz. For ±7V supplies and above, the maximum clock frequency is 5MHz. Do not allow the clock levels to exceed the power supplies. For clock level shifting (see Figure 3).

## TYPICAL APPLICATIONS




Figure 1. Using Schottky Diodes to Protect the IC from Power Supply Spikes




Figure 3. Level Shifting the Input  $T^2L$  Clock for Single Supply Operation, V+>6V.




Figure 2. Single Supply Operation. If Fast Power Up or Down Transients are Expected, Use a 1N5817 Schottky Diode Between Pin 4 and Pin 5.






Figure 4. Buffering the Filter Output. The Buffer Op Amp Should Not Share the LTC1064-1 Power Lines.




## TYPICAL APPLICATIONS

### Transitional Elliptic-Bessel Dual 5th Order Lowpass Filter







# Transient Response to a 2V Step Input $V_{OUT2}$



# Transient Response to a 2V Step Input $V_{OUT1}$



# Adding an Output Buffer-Filter to Eliminate Any Clock Feedthrough Over a 10:1 Clock Range, for $f_{CLK} = 2kHz$ to 20kHz



/ LINEAR

.045 - .065

(1.143 - 1.651)

 $\frac{.005}{(0.125)}$ 

MIN (2.54) BSC

100

.065


(1.651) TYP

N14 1002

.018 ± .003


 $(0.457 \pm 0.076)$ 

### PACKAGE DESCRIPTION



### N Package 14-Lead PDIP (Narrow 0.300)

(LTC DWG # 05-08-1510)




\*THESE DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS.

MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED .010 INCH (0.254mm)


### SW Package 16-Lead Plastic Small Outline (Wide .300 Inch)

(Reference LTC DWG # 05-08-1620)




## TYPICAL APPLICATION


#### Transitional Elliptic-Bessel 10th Order Lowpass Filter



### **Amplitude Response**



#### Transient Response to a 2V Step Input



# **RELATED PARTS**

PART NUMBER	DESCRIPTION	COMMENTS
LTC1069-1	8th Order Elliptic Lowpass	S0-8 Package, Low Power
LTC1069-6	Single Supply, 8th Order Elliptic Lowpass	S0-8 Package, Very Low Power
LTC1569-6	DC Accurate, 10th Order, Lowpass	Internal Precision Clock, Low Power
LTC1569-7	DC Accurate, 10th Order, Lowpass	Internal Precision Clock, S0-8 Package

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Analog Devices Inc.:

LTC1064-1CSW#PBF LTC1064-1CN#PBF LTC1064-1CSW#TRPBF LTC1064-1ACN#PBF