

PRODUCT FAMILY DATASHEET BROOKE

BROOKE

Ø45 mm LEDiL System Reflectors ideal for compact trackand downlight fixtures

BROOKE-family is a series of compact (Ø45 mm, H 19.7 mm) reflectors making it possible to construct compact luminaires with modern high density COBs that have smaller LES`s. In addition LEDiL`s patented BARBARA-RZ colour mixing sublens can be used for multi-colour or tunable white light applications. The lens can also be used to smoothen out and remove any unwanted colour-over-angle artefacts from the beam. Spot, medium and wide beams available.

BROOKE


Variant with a tape mounting for up to 18 mm LES size COBs



PRODUCTS:

C12119_BROOKE-M

C12083_BROOKE-SCR-M



Dimensions: 45.0 mm x 45.0 mm Height: 20.20 mm

~30° medium beam and screw installation.

C12120_BROOKE-W

SetPlotAreaWorld(): X range error - min >= m

Dimensions: 45.0 mm x 45.0 mm Height: 20.10 mm

~40° wide beam

Height: 20.10 mm ~30° medium beam

Dimensions: 45.0 mm x 45.0 mm



PRODUCT FAMILY DATASHEET BROOKE

PRODUCTS:


C12084_BROOKE-SCR-W

Dimensions: 45.0 mm x 45.0 mm

~40° wide beam and screw installation.

Height: 20.20 mm


CA11182_BROOKE-M



Dimensions: 45.0 mm x 45.0 mm Height: 21.10 mm

~30° medium beam. Assembly with installation tape.


CA11183_BROOKE-W



Dimensions: 45.0 mm x 45.0 mm Height: 21.10 mm

~40° wide beam. Assembly with installation tape.

CA11181_BROOKE-S




Dimensions: 45.0 mm x 45.0 mm

Height: 20.10 mm

 $\sim\!\!25^{\circ}$ spot beam. Assembly with installation tape.

CA14591_BROOKE-XW



Dimensions: 45.0 mm x 45.0 mm

Height: 20.00 mm

~85° wide beam. Assembly with installation tape.



PRODUCT FAMILY DATASHEET BROOKE

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy