

5-V Low Drop Fixed Voltage Regulator

TLE 4275




Features


- Output voltage 5 V \pm 2%
- Very low current consumption
- Power-on and undervoltage reset
- Reset low down to V_Q = 1 V
- Very low-drop voltage
- Short-circuit-proof
- Reverse polarity proof
- Suitable for use in automotive electronics
- ESD protection > 4 kV
- Green Product (RoHS compliant) version of TLE 4275
- AEC qualified

Functional Description

The TLE 4275 is a monolithic integrated low-drop voltage regulator in a 5-pin TO-package. An input voltage up to 45 V is regulated to $V_{Q,nom} = 5.0$ V. The IC is able to drive loads up to 450 mA and is short-circuit proof. At overtemperature the TLE 4275 is turned off by the incorporated temperature protection. A reset signal is generated for an output voltage $V_{Q,rt}$ of typ. 4.65 V. The delay time can be programmed by the external delay capacitor.







Туре	Package
TLE 4275	PG-TO220-5-11 (RoHS compliant)
TLE 4275 D	PG-TO252-5-11 (RoHS compliant)
TLE 4275 G	PG-TO263-5-1 (RoHS compliant)
TLE 4275 S	PG-TO220-5-12 (RoHS compliant)



Dimensioning Information on External Components

The input capacitor $C_{\rm I}$ is necessary for compensation of line influences. Using a resistor of approx. 1 Ω in series with $C_{\rm I}$, the oscillating of input inductivity and input capacitance can be damped. The output capacitor $C_{\rm Q}$ is necessary for the stability of the regulation circuit. Stability is guaranteed at values $C_{\rm Q} \ge 22 \ \mu\text{F}$ and an ESR of $\le 5 \ \Omega$ within the operating temperature range.

Circuit Description

The control amplifier compares a reference voltage to a voltage that is proportional to the output voltage and drives the base of the series transistor via a buffer. Saturation control as a function of the load current prevents any oversaturation of the power element. The IC also incorporates a number of internal circuits for protection against:

- Overload
- Overtemperature
- Reverse polarity






Figure 1 Pin Configuration (top view)

Pin No.	Symbol	Function
1	1	Input; block to ground directly at the IC by a ceramic capacitor.
2	RO	Reset Output; open collector output
3	GND	Ground; Pin 3 internally connected to heatsink
4	D	Reset Delay; connect capacitor to GND for setting delay time
5	Q	Output; block to ground with a $\ge 22 \ \mu$ F capacitor, ESR < 5 Ω at 10 kHz.






Figure 2 **Block Diagram**



Parameter	Symbol	Lim	it Values	Unit	Test Condition	
		Min.	Max.			
Input		•				
Voltage	V ₁	-42	45	V	-	
Current	I	-	-	_	Internally limited	
Output		·				
Voltage	V _Q	-1.0	16	V	-	
Current	IQ	-	_	_	Internally limited	
Reset Output		·				
Voltage	V _{RO}	-0.3	25	V	-	
Current	I _{RO}	- 5	5	mA	-	
Reset Delay						
Voltage	V _D	-0.3	7	V	-	
Current	ID	-2	2	mA	-	
Temperature						
Junction temperature	Tj	-40	150	°C	-	
Storage temperature	$T_{\rm stg}$	-50	150	°C	-	

Table 2Absolute Maximum Ratings

Note: Maximum ratings are absolute ratings; exceeding any one of these values may cause irreversible damage to the integrated circuit.

Table 3Operating Range

Parameter	Symbol	Lim	it Values	Unit	Remarks
		Min.	Max.		
Input voltage	V ₁	5.5	42	V	-
Junction temperature	Tj	-40	150	°C	_
Thermal Resistance					
Junction case	$R_{ m thjc}$	_	4	K/W	_
Junction ambient	$R_{\mathrm{thj-a}}$	-	53	K/W	TO263 ¹⁾
Junction ambient	R _{thj-a}	-	78	K/W	TO252 ¹⁾
Junction ambient	R _{thj-a}	_	65	K/W	TO220

1) Worst case, regarding peak temperature; zero airflow; mounted on a PCB FR4, $80 \times 80 \times 1.5 \text{ mm}^3$, heat sink area 300 mm²



Table 4Characteristics

 $V_{\rm I}$ = 13.5 V; -40 °C < $T_{\rm j}$ < 150 °C (unless otherwise specified)

Parameter	Symbol	Limit Values			Unit	Measuring		
		Min.	Тур.	Max.		Condition		
Output								
Output voltage	V _Q	4.9	5.0	5.1	V	$5 \text{ mA} < I_Q < 400 \text{ mA}$ $6 \text{ V} < V_1 < 28 \text{ V}$		
Output voltage	V _Q	4.9	5.0	5.1	V	5 mA < I_Q < 200 mA 6 V < V_1 < 40 V		
Output current limitation ¹⁾	I _Q	450	700	-	mA	_		
$\overline{\text{Current consumption;}} \\ I_{q} = I_{I} - I_{Q}$	Iq	_	150	200	μA	I_Q = 1 mA; T_j = 25 °C		
Current consumption; $I_q = I_1 - I_Q$	Iq	-	150	220	μA	$I_{\rm Q}$ = 1 mA; $T_{\rm j}$ \leq 85 °C		
$\overline{\text{Current consumption;}} \\ I_{q} = I_{I} - I_{Q}$	Iq	_	5	10	mA	I _Q = 250 mA		
Current consumption; $I_q = I_1 - I_Q$	Iq	_	12	22	mA	<i>I</i> _Q = 400 mA		
Drop voltage ¹⁾	V_{dr}	-	250	500	mV	$I_{\rm Q}$ = 300 mA; $V_{\rm dr}$ = $V_{\rm I}$ - $V_{\rm Q}$		
Load regulation	ΔV_{Q}	-	15	30	mV	$I_{\rm Q}$ = 5 mA to 400 mA		
Line regulation	ΔV_{Q}	-15	5	15	mV	ΔV_1 = 8 V to 32 V I_Q = 5 mA		
Power supply ripple rejection	PSRR	_	60	-	dB	$f_{\rm r}$ = 100 Hz; $V_{\rm r}$ = 0.5 Vpp		
Temperature output voltage drift	dV_Q/dT	-	0.5	-	mV/K	-		




Table 4Characteristics (cont'd)

$V_{\rm I}$ = 13.5 V; -40 °C < $T_{\rm j}$ < 150 °C (unless otherwise specified)


Parameter	Symbol	Limit Values			Unit	Measuring
		Min.	Тур.	Max.		Condition
Reset Timing D and Ou	tput RO					
Reset switching threshold	V _{Q,rt}	4.5	4.65	4.8	V	-
Reset output low voltage	V _{ROL}	_	0.2	0.4	V	$R_{\text{ext}} \ge 5 \text{ k}\Omega;$ $V_{\text{Q}} > 1 \text{ V}$
Reset output leakage current	I _{ROH}	-	0	10	μA	V _{ROH} = 5 V
Reset charging current	I _{D,c}	3.0	5.5	9.0	μA	<i>V</i> _D = 1 V
Jpper timing threshold	V_{DU}	1.5	1.8	2.2	V	-
ower timing threshold	V_{DRL}	0.2	0.4	0.7	V	-
Reset delay time	t _{rd}	10	16	22	ms	C _D = 47 nF
Reset reaction time	t _{rr}	-	0.5	2	μs	<i>C</i> _D = 47 nF

1) Measured when the output voltage $V_{\rm Q}$ has dropped 100 mV from the nominal value obtained at $V_{\rm I}$ = 13.5 V.
















Output Voltage $V_{\rm Q}$ versus Temperature $T_{\rm i}$




Output Voltage $V_{\rm Q}$ versus Temperature $T_{\rm i}$



Output Current $I_{\rm Q}$ versus Temperature $T_{\rm i}$




Output Voltage V_{Q} versus Input Voltage V_{I}







Output Current $I_{\rm Q}$ versus Input Voltage $V_{\rm I}$




Current Consumption I_q versus Output Current I_o






Drop Voltage $V_{\rm dr}$ versus Output Current $I_{\rm O}$






Charge Current $I_{\rm D,c}$ versus Temperature $T_{\rm j}$



Delay Switching Threshold $V_{\rm DU,}$ $V_{\rm DRL}$ versus Temperature $T_{\rm j}$





Package Outlines




Figure 5 PG-TO220-5-11 (Plastic Transistor Single Outline)

Green Product (RoHS compliant)

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).

You can find all of our packages, sorts of packing and others in our Infineon Internet Page "Products": http://www.infineon.com/products.

SMD = Surface Mounted Device






Figure 6 PG-TO252-5-11 (Plastic Transistor Single Outline)

Green Product (RoHS compliant)

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).

You can find all of our packages, sorts of packing and others in our Infineon Internet Page "Products": http://www.infineon.com/products.

SMD = Surface Mounted Device






Figure 7 PG-TO263-5-1 (Plastic Transistor Single Outline)

Green Product (RoHS compliant)

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).

You can find all of our packages, sorts of packing and others in our Infineon Internet Page "Products": http://www.infineon.com/products.

SMD = Surface Mounted Device






Figure 8 PG-TO220-5-12 (Plastic Transistor Single Outline)

Green Product (RoHS compliant)

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).

You can find all of our packages, sorts of packing and others in our Infineon Internet Page "Products": http://www.infineon.com/products.

SMD = Surface Mounted Device



TLE 4275

Revision Hist	ory: 2007-02-19	Rev. 1.7				
Previous Version: 1.6						
Page Subjects (major changes since last revision)						
general	Removed all information related to the TL (See separate datasheet for the TLE427	•				
general	Updated Infineon logo					
#1	Added "AEC" and "Green" logo					
#1	Added "Green Product" and "AEC qualifi	ed" to the feature list				
#1	Updated Package Names to "PG-xxx"					
general	Removed leadframe variant "P-TO-252-7	1"				
#12 to #15	Added "Green Product" remark					
#17	Disclaimer Update					

Edition 2007-02-19 Published by Infineon Technologies AG 81726 München, Germany © Infineon Technologies AG 2007. All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infineon:

TLE42754D TLE4275 TLE4275D TLE4275G TLE4275S TLE4275DXT