## Field Wiring with Solder Pin Female Connector


**Specifications:** 


## multicomp PRO



Mating Style Contact Gender Material Contact Material Connector Body Cable OD Contact Resistance Insulation Resistance Durability Breakdown Voltage Corrosion Temperature Range Waterproof Rate

- : Lock Type
- : Female pin
- : Copper Alloy, Gold Plated
- : Nylon+GF, PBT
- : 4mm to 6.5mm
- : ≤30mΩ (without cable)
- : ≥100MΩ at DC 500V
- : 500 cycles Min.
- : ≥AC 500V/1 minute
- : 48 hours salt spray contact
- : -40°C to +100°C
- : IP67 (IP67: Immersed in 1m water for 30 minutes)





**Dimensions : Millimetres** 

No.	Description	Material	Plating & Colour	Qty
Α	Sealing Nut	PC		1
В	Seal	EPDM		
С	Clamp Ring	PC	Black	
D	Gasket	Silicone	DIACK	
E	Body	Nylon+GF		
F	Lock Nut	Nylon+GF		
G	Female Pin	Phosphor Bronze	6µ" Gold Plated Over Nickel Plating	-
Н	Liquid Glue	NA	Black	1
I	O-Ring	EPDM	DIACK	

Part Number	Pin Assignments Front View	Current Rating	Recommended Cable AWG
2CT3032-W02400		10A	18AWG to 20AWG
2CT3032-W03400		10A	18AWG to 20AWG

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



## multicomp PRO

Part Number	Pin Assignments Front View	Current Rating	Recommended Cable AWG
2CT3032-W04400		10A	18AWG to 20AWG
2CT3032-W04300		5A	22AWG to 24AWG
2CT3032-W05300		5A	22AWG to 24AWG
2CT3032-W06300		5A	22AWG to 24AWG
2CT3032-W07300		5A	22AWG to 24AWG
2CT3032-W08300		5A	22AWG to 24AWG
2CT3032-W10200		2A	24AWG to 26AWG
2CT3032-W12200		2A	24AWG to 26AWG

## Part Number Table

Description	Part Number	
Plug, In-Line, 10A, 2 Way, SKT	2CT3032-W02400	
Plug, In-Line, 10A, 3 Way, SKT	2CT3032-W03400	
Plug, In-Line, 10A, 4 Way, SKT	2CT3032-W04400	
Plug, In-Line, 5A, 4 Way, SKT	2CT3032-W04300	
Plug, In-Line, 5A, 5 Way, SKT	2CT3032-W05300	
Plug, In-Line, 5A, 6 Way, SKT	2CT3032-W06300	
Plug, In-Line, 5A, 7 Way, SKT	2CT3032-W07300	
Plug, In-Line, 5A, 8 Way, SKT	2CT3032-W08300	
Plug, In-Line, 2A, 10 Way, SKT	2CT3032-W10200	
Plug, In-Line, 2A, 12 Way, SKT	2CT3032-W12200	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

