



Part Number: 4100UE
AUDIO 2x14AWG LSZH

Product Description

AUDIO 2x14AWG LSZH

Technical Specifications

Product Overview

Environmental Space:	Indoor - Euroclass Eca
Suitable Applications:	Commercial applications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
14	19x27	BC - Bare Copper	1.8 mm	2

Conductor Count:	2
Conductor Size:	14 AWG

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
Insulation	PP - Polypropylene	2.34 mm	0.05 mm	0.28 mm

Color Chart

Number	Color
Wire 1	Black
Wire 2	White

Outer Jacket Material

Material	Color	Nominal Diameter	Nominal Wall Thickness	Ripcord
LSZH / FRNC	Gray	5.55 mm	0.4 mm	Provided under the sheath

Construction and Dimensions

Cabling

Description
2 wires twisted

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
8.3 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor
270 pF/m

Current

Max. Recommended Current [A]

8 A

Voltage**Voltage Rating [V]**

300 V

Temperature Range

Installation Temp Range:	-20°C To +70°C
Storage Temp Range:	-30°C To +70°C
Operating Temp Range:	-20°C To +70°C

Mechanical Characteristics

Max Recommended Pulling Tension:	60 N
Min Bend Radius During Installation:	55.5 mm
Min Setting Radius:	27.75 mm

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	1998-01-01
---------------------------------------	------------

Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

Part Number**Variants**

Item #	Color
4100UE.00100	Gray, RAL 7032
4100UE.00500	Gray, RAL 7032
4100UE.01500	White

History

Revision Number:	5
------------------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.