

# GRM31A7U3A100JW31#

“#” indicates a package specification code.



< List of part numbers with package codes >

GRM31A7U3A100JW31J      GRM31A7U3A100JW31D

## Appearance & Shape



## References

Packaging	Specifications	Minimum Order Quantity
J	330mm Paper Tape	10000
D	180mm Paper Tape	4000

Mass (typ.)	
1 piece	27.0mg

### Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM31A7U3A100JW31#

“#” indicates a package specification code.



## Specifications

Length	3.2±0.2mm
Width	1.6±0.2mm
Thickness	1.0+0/-0.3mm
Capacitance	10pF ±5%
Distance between external terminals g	1.5mm min.
External terminal size e	0.3mm min.
Operating Temperature Range	-55°C to 125°C
Rated Voltage	1000Vdc
Size code in inch(mm)	1206 (3216M)
TC	-750±120ppm/°C
Temperature characteristics (complied standard)	U2J(EIA)
Temperature range of temperature characteristics	25°C to 125°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM31A7U3A100JW31#


“#” indicates a package specification code.

## Characteristic Data


The charts below may show another part number which shares its characteristics.




■ GRM31A7U3A100JW31 |Z| DC0V, 25degC



■ GRM31A7U3A100JW31 R DC0V, 25degC



■ GRM31A7U3A100JW31 C-DC bias capchange, 25.0degC, AC1V




■ GRM31A7U3A100JW31 C-AC Voltage capchange, DC0V, 25.0d

**Attention**


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM31A7U3A100JW31#

“#” indicates a package specification code.



■ GRM31A7U3A100JW31 C-Temp. capchange, DCOV, AC1Vrms



■ GRM31A7U3A100JW31 S21 DCOV, 25degC

**Attention**

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.