



Series 80 Mighty Mouse Standard Series Discrete Connector Offerings

The Series 80 Mighty Mouse Connector is designed for high-reliability commercial and aerospace/defense interconnect applications that require both robust environmental/EMI performance and reduced size and weight. The Series 80 Mighty Mouse Connector offers comparable performance to MIL-DTL-38999 Series interconnects with up to 71% weight and 52% size savings for similar contact layouts. The six versions of the product offer a variety of styles and features to suit just about any application.

Series 800



Series 801



Description

Original Mighty Mouse with UNF Threads

Double-Start ACME Thread

Notes

A general purpose connector for high-speed Ethernet switches, tactical equipment and instrumentation.

More rugged keys and threads compared to Series 800. Faster mating, slightly larger than Series 800.

Number of Contacts

1 to 37

1 to 130

Coupling

Threaded Coupling with 4 ½ Turns to Full Mate

Threaded Coupling with 1 ½ Turns to Full Mate

Water Immersion, Mated

MIL-STD-810 Method 512
1 Meter for 1 Hour

MIL-STD-810 Method 512
1 Meter for 1 Hour

EMI Shielding

Good

Good

Vibration and Shock

37 g's Random Vibration;
300 g's Shock

37 g's Random Vibration;
300 g's Shock

Mating Cycles

2000 Cycles

2000 Cycles

Electrical Performance

#12: 23 Amp, 1800 VAC
#16: 13 Amp, 1800 VAC
#20HD: 7.5 Amp, 1000 VAC
#23: 5 Amp, 750 VAC

#12: 23 Amp, 1800 VAC
#16: 13 Amp, 1800 VAC
#20HD: 7.5 Amp, 1000 VAC
#23: 5 Amp, 750 VAC





Proven Performance Applications

Commercial air frame sensors;
UAV telemetry; Tactical computers; field radios

Military air frame;
Dismounted soldier; Tactical ground weaponry; Avionic (FLIR) systems

**Series 80 Mighty Mouse
Standard Series
Discrete Connector Offerings**



Series 802	Series 803	Series 804	Series 805
			
AquaMouse™ 3500 PSI	Bayonet	Push-Pull	Triple-Start ACME Thread
<p>Rugged stainless steel, resists chemicals. For geophysical and underwater applications.</p>	<p>Quick-mating, light duty, general purpose. Not rated for immersion. 50 milliohms shell-to-shell resistance.</p>	<p>Breakaway connector for headsets and tactical equipment. Gold-plated spring for long mating life and superior EMI shielding.</p>	<p>“Clicker” ratchet mechanism and ground spring for military airframes and avionics boxes. Fast-mating, D38999 equivalent.</p>
1 to 130	1 to 55	1 to 55	1 to 130
Threaded Coupling with UN Threads	Push-to-Mate, ¼ Turn to Lock	Quick-Disconnect	One Full Turn for Full Mate
1000 Feet Immersion in Salt Water	Splashproof	MIL-STD-810 Method 512 1 Meter for 1 Hour	MIL-STD-810 Method 512 1 Meter for 1 Hour
Good	Fair	Very Good	Excellent
37 g's Random Vibration; 300 g's Shock	37 g's Random Vibration; 300 g's Shock	37 g's Random Vibration; 300 g's Shock	37 g's Random Vibration; 300 g's Shock
2000 Cycles	250 Cycles Aluminum 2000 Cycles SST	2000 Cycles Aluminum 2000 Cycles SST	500 Cycles
#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC	#12: 23 Amp, 1800 VAC #16: 13 Amp, 1800 VAC #20HD: 7.5 Amp, 1000 VAC #23: 5 Amp, 750 VAC
Pipe line inspection equipment; Well logging; Amphibious vehicles; Unmanned submersibles	Soldier system radios; Autosport diagnostics; Airborne surveillance; Communication systems	Helmet breakaway connector; QDC battery; Missile applications; Weapon interconnects	Military air frame; Joint Strike Fighter

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[805-011-07M8-4PA](#) [805-011-07M11-19SB](#) [805-011-07M11-19SA](#) [801-023-07M6-7PB](#) [805-017-07M11-19SA](#) [805-017-07M11-201SB](#) [801-017M13-37PA](#) [805-005-07M12-26SA](#) [805-005-07ZN19-85SA](#) [801-023-07M6-4PA](#) [801-023-07ZNU5-3PB](#) [803-003-07ZNU10-26PN](#) [805-005-02M11-19SA](#) [805-005-02M12-26PA](#) [805-005-02M12-26SA](#) [805-005-02M15-37PA](#) [805-005-02M19-85PA](#) [805-005-02M8-4SA](#) [805-005-02M8-7PA](#) [805-005-02M8-7SA](#) [805-005-02M9-10SA](#) [805-005-07M10-13SA](#) [805-005-07M15-37PA](#) [805-005-07M15-37SB](#) [805-005-07M15-7PA](#) [805-005-07M18-55PA](#) [805-005-07M18-55SA](#) [805-005-07M19-85PA](#) [805-005-07M19-85SA](#) [805-005-07M8-4PA](#) [805-005-07M8-7PA](#) [805-005-07M9-10SA](#) [805-005-07NF11-4EA](#) [805-005-07NF8-7EA](#) [805-005-07NF8-7SB](#) [805-005-07Z111-19PA](#) [805-006-02Z111-19PA](#) [805-006-07Z19-10CB](#) [805-011-07MT10-13PA](#) [801-02307ZNU7-10SA](#) [801-023-07M6-4SA-501](#) [801-023-07M6-4PB](#) [801-023-07Z16-7PA-518](#) [801-023-07M5-3PA-501](#) [801-023-07M5-3SA-501](#) [801-023-07M6-7PA-501](#) [801-023-07M6-7SA-501](#) [801-023-07M9-19PB](#) [801-017M16-55SA](#) [801-017Z19-19SA](#) [801-017ZW13-37SA](#) [805-005-07MT12-26PA](#) [805-005-07Z111-210SA](#) [805-005-07NF8-6PA](#) [805-005-07NF10-2SA](#) [805-017-07ZR9-10FA](#) [805-017-02ZNU8-4EA](#) [805-005-07NF12-5PA](#) [805-005-07NF8-4SC](#) [805-005-02M19-241SA](#) [805-017-07NF10-13SA](#) [805-005-07M18-55SB](#) [805-005-02M23-130PA](#) [805-005-07ZN11-19PA](#) [805-005-07NF18-55PB](#) [805-017-07NF9-10SA](#) [805-005-07M9-10SD](#) [805-005-07M8-6EA](#) [805-005-07NF11-19SB](#) [805-005-07NF10-28SA](#) [805-005-07M9-10SC](#) [805-005-07NF15-37SA](#) [805-005-07NF15-37PC](#) [805-005-07ZNU8-7SA](#) [805-005-07M12-26SC](#) [805-005-07NF10-13PA](#) [805-005-07NF9-10PB](#) [805-005-02M12-26PB](#) [805-005-07Z115-37PA](#) [805-005-07Z119-85PA-501](#) [805-005-07Z19-10PA-501](#) [805-005-07M12-26PC](#) [805-005-07Z19-10PB-501](#) [805-005-07M11-200SA](#) [805-017-07M11-19SC](#) [805-011-07MT8-7PA](#) [805-011-07M11-19PA](#) [805-011-07MT10-13SA](#) [805-011-07NF11-19PA-518](#) [805-011-07M8-7PA](#) [805-006-07Z115-37CA](#) [805-006-07ZL9-10PA](#) [801-008-26NF10-26SB](#) [801-007-16NF8-28SA](#) [801-007-26NF6-23PA](#) [801-007-26M6-7PB](#) [801-008-16M6-6PA](#) [801-007-26NF7-10PB](#) [801-007-16ZNU8-28SA](#) [801-008-26NF5-3SA](#)