


DESCRIPTION


This monolithic integrated circuit is an adjustable 3-terminal positive voltage regulator designed to supply more than 1.5A of load current with an output voltage adjustable over a 1.2 to 37V. It employs internal current limiting , thermal shut-down and safe area compensation.

FEATURE

- Internal thermal overload protection
- Internal short circuit current limiting
- Output transistor safe operating area compensation



Internal Block Diagram



Absolute Maximum Ratings

Symbol	Parameter		Value	Unit
V _I -V _O	Input-Output Voltage Differential		40	V
T _{LEAD}	Lead Temperature		230	°C
P _D	Power Dissipation	TO-220	Internally limited	W
		TO-252	2	
		SOT-223	1	
T _J	Operating Junction Temperature Range		-40~105	°C
T _{stg}	Storage Temperature Range		-55~125	
ΔV _O /ΔT	Temperature Coefficient of Output Voltage		±0.02	%/°C

ELECTRICAL CHARACTERISTICS


(V_I-V_O=5V, I_O=0.5A, 0°C≤T_J≤+125°C , I_{MAX}=1.5A, P_{DMAX}=20W, unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Line Regulation(note1)	R _{line}	T _A =25°C 3V≤V _I -V _O ≤40V		0.01	0.04	%/V
		3V≤V _I -V _O ≤40V		0.02	0.07	
Load Regulation(note1)	R _{load}	T _A =25°C , 10mA≤I _O ≤I _{MAX} V _O <5V V _O ≥5V		18 0.4	25 0.5	mV
		10mA≤I _O ≤I _{MAX} V _O <5V V _O ≥5V		40 0.8	70 1.5	
Adjustable Pin Current	I _{ADJ}	-		46	100	μA
Adjustable Pin Current Change	ΔI _{ADJ}	3V≤V _I -V _O ≤40V 10mA≤I _O ≤I _{MAX} , P _D ≤P _{MAX}		2.0	5	
Reference Voltage	V _{REF}	3V≤V _{IN} -V _O ≤40V 10mA≤I _O ≤I _{MAX} , P _D ≤P _{MAX}	1.20	1.25	1.30	V
Temperature Stability	S _T	-		0.7		%/ V _O
Minimum Load Current to Maintain Regulation	I _{L(MIN)}	V _I -V _O =40V		3.5	12	mA
Maximum Output Current	I _{O(MAX)}	V _I -V _O ≤15V, P _D ≤P _{MAX} V _I -V _O ≤40V, P _D ≤P _{MAX} T _A = 25 °C	1.0	2.2 0.3		A
RMS Noise,% of V _{OUT}	e _N	T _A =25°C , 10Hz≤f≤10KHz		0.003	0.01	%/ V _O
Ripple Rejection	RR	V _O =10V, f=120Hz without C _{ADJ} C _{ADJ} = 10 μF (note2)	66	60 75		dB
Long-Term Stability,T _J =T _{HIGH}	ST	T _A = 25 °C for end point measurements, 1 0 0 0 HR		0.3	1	%
Thermal Resistance Junction to case	R _{θJC}	-		5		°C/W

Notes:

- Load and line regulation are specified at constant junction temperature. Change in V_D due to heating effects must be taken into account separately. Pulse testing with low duty is used.(P_{MAX}=20W)
- C_{ADJ} . when used, is connected between the adjustment pin and ground.

Typical Application




C_i is required when regulator is located an appreciable distance from power supply filter.

C_o is not needed for stability , however, it does improve transient response.

Since I_{ADJ} is controlled to less than 100μA, the error associated with this term is negligible in most applications.


TO-220

DIM.	mm.			inch		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A	4.40		4.60	0.173		0.181
b	0.61		0.88	0.024		0.034
b1	1.15		1.70	0.045		0.067
c	0.49		0.70	0.019		0.027
D	15.25		15.75	0.600		0.620
E	10.0		10.40	0.393		0.409
e	2.4		2.7	0.094		0.106
e1	4.95		5.15	0.194		0.203
F	1.23		1.32	0.048		0.051
H1	6.2		6.6	0.244		0.260
J1	2.40		2.72	0.094		0.107
L	13.0		14.0	0.511		0.551
L1	3.5		3.93	0.137		0.154
L20		16.4			0.645	
L30		28.9			1.138	
φP	3.75		3.85	0.147		0.151
Q	2.65		2.95	0.104		0.116



0015988/N


SOT-223



S Y M B O L	SOT-223	
	MILLIMETERS	
	MIN.	MAX.
A		1.80
A1	0.02	0.10
A2	1.55	1.65
b	0.66	0.84
b2	2.90	3.10
c	0.23	0.33
D	6.30	6.70
E	6.70	7.30
E1	3.30	3.70
e	2.30 BSC	
e1	4.60 BSC	
L	0.90	
θ	0°	8°

Note:
 1. Refer to JEDEC TO-261AA.
 2. Dimension D and E1 are determined at the outermost extremes of the plastic body exclusive of mold flash, tie bar burrs, gate burrs, and interlead flash, but including any mismatch between the top and bottom of the plastic body.
 3. Controlling dimension is millimeter, converted inch dimensions are not necessarily exact.

TO-252



Unit: mm

Item	Min	Max
A	6.40	6.70
B	5.20	5.40
C	6.00	6.30
D	6.55	6.85
E	0.45	0.60
F	3.07	3.35
G	0.85	1.05
H	0.75	0.95
I	0.55	0.75
J	2.20	2.40
K	0.43	0.58
L	0.43	0.58
M	0.90	1.10
N	0.90	1.10
O	2.20	2.40

Ordering information

Order code	Package	Baseqty	Delivery mode
UMW LM217DCYR	SOT-223	2500	Tape and reel
UMW LM217T	TO-220	1000	Tube and box
UMW LM217MDT	TO-252	2500	Tape and reel