General purpose small signal amplifier (50V, 0.15A)

2SC4081UB Data Sheet

Applications

General purpose small signal amplifier


Features

- 1) Low Cob. Cob=2.0pF (Typ.)
- 2) Complements the 2SA1576UB.

Structure

NPN silicon epitaxial planar transistor

●Dimensions (Unit: mm)



●Absolute maximum (Ta=25°C)

Parameter	Symbol	Limits	Unit
Collector-base voltage	Vсво	60	V
Collector-emitter voltage	Vceo	50	V
Emitter-base voltage	VEBO	7	V
Collector current	Ic	150	mA
	Icp *1	200	mA
Power dissipation	P _D *2	200	mW
Junction temperature	Tj	150	°C
Range of storage temperature	Tstg	-55 to +150	°C

^{*1} Pw=1ms Single pulse

●Electrical characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Collector-emitter breakdown voltage	BVceo	50	_	_	V	Ic=1mA
Collector-base breakdown voltage	ВУсво	60	_	_	V	Ic=50μA
Emitter-base breakdown voltage	ВУево	7	_	_	V	Iε=50μA
Collector cutoff current	Ісво	_	_	100	nA	Vcb=60V
Emitter cutoff current	ІЕВО	_	_	100	nA	V _{EB} =7V
Collector-emitter saturation voltage	VCE(sat)	_	_	400	mV	Ic/I _B =50mA/5mA
DC current gain	hfe	120	_	560	_	VcE=6V, Ic=1mA
Transition frequency	f⊤	_	180	_	MHz	Vce=12V, Ie=-2mA, f=100MHz
Output capacitance	Cob	_	2.0	3.5	pF	Vcb=12V, Ie=0A, f=1MHz

h_{FE} rank categories

Rank	Q	R	S
hfe	120 to 270	180 to 390	270 to 560

^{*2} Each terminal mounted on a recommended land

•Electrical characteristic curves




Fig.1 Grounded emitter propagation characteristics




Fig.2 Grounded emitter output characteristics (I)




Fig.3 Grounded emitter output characteristics (II)




Fig.4 DC current gain vs. collector current (I)




Fig.5 DC current gain vs. collector current (II)




Fig. 6 Collector-emitter saturation voltage vs. collector current




Fig.7 Collector-emitter saturation voltage vs. collector current (I)




Fig.8 Collector-emitter saturation voltage vs. collector current (II)




Fig.9 Gain bandwidth product vs. emitter current

Data Sheet




Fig.10 Collector output capacitance vs. collector-base voltage Emitter input capacitance vs. emitter-base voltage




Fig.11 Base-collector time constant vs. emitter current

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications:
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensur the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor: 2SC4081UBTLR