

QTP-OPTIMAL 1X54...58

QUICKTRONIC PROFESSIONAL OPTIMAL | ECG for FL and CFL, not dimmable



Areas of application

- Emergency lighting systems acc. to EN 50172 / DIN VDE 0108-100
- Industry
- Open-plan offices, corridors and storage rooms
- Public buildings
- Sports halls and factories
- Strip lighting
- Suitable for emergency lighting (DC operation)
- Modernization of existing systems

Product benefits

- Long lamp life
- No adverse effect from frequent on/off switching
- Automatic restart after lamp replacement
- Perfect lamp start for applications with motion sensors
- VDE/VDE EMC certified system
- Very high energy efficiency due to cut-off technology

Product features

- Supply voltage: 220...240 V
- Line voltage: 198...264 V
- Line frequency: 0 Hz | 50 Hz | 60 Hz
- Lamp start with optimum filament preheating
- Lifetime: up to 100,000 h (temperature at $T_c = 65$ °C, max. 10 % failure rate)
- Energy Efficiency Index EEI: A2 BAT
- Automatic shutdown of defective lamps and at end of life (EoL T.2)
- Safety: to EN 61347-2-3
- Lamp operation: to EN 60929

Technical data

Electrical data

Input voltage AC	198...264 V
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Input voltage DC	176...276 V
Operating frequency	40...50 kHz
Max. no. of ECGs on circuit breaker 10 A	12 ¹⁾
Max. no. of ECGs on circuit breaker 16 A	19 ¹⁾


¹⁾ Type B

Light technical data

Starting time	1.5 s ¹⁾
----------------------	---------------------

¹⁾ If there is a temporary interruption in the power supply (< 0.5 s), the lamp will start within 0.3 s

Dimensions & weight



Length	280.0 mm
Width	30.0 mm
Height	21.0 mm
Mounting hole spacing, length	270.0 mm
Product weight	180.00 g

Temperatures

Ambient temperature range	-20...+50 °C
----------------------------------	--------------

Lifespan

ECG lifetime	100000 h ¹⁾
---------------------	------------------------

¹⁾ At tcase = 65°C at tc point / 10 % failure rate

Product datasheet

Expected Lifetime

Product name	Lamp group				
QTP-OPTIMAL 1x54-58	L 58 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	55	60	70
		Lifetime [h]	100000	100000	80000










Capabilities

Suitable for fixtures with prot. class	I / II
End of lamp life safety shutdown	EOL T.2

Certificates & standards

Approval marks – approval	EL / VDE / ENEC 10 / VDE-EMC
EEI – Energy Label	A2 BAT
Standards	Acc. to IEC 61347-2-3 / App. J/Acc. to EN 55015:2006 + A1:2007 + A2:2009/Acc. to IEC 61000-3-2/Acc. to IEC 61547
Protection class	I/II

Download Data

File
 Addon Technical Information Frequent switching Quicktronic
 Product Datasheet ECG lifetime - QUICKTRONIC non DIM
 Product Family Datasheet Familiendatenblatt QTP-Optimal
 Certificates ENEC QTP-Optimal
 Certificates EMC QTP-Optimal
 Certificates CE QTP-Optimal
 Certificates QTP-OPTIMAL VDE Certificate
 Certificates EAC certificate for Quicktronics QT
 Operating instructions EAC QTP-OPTIMAL

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321873729	QTP-OPTIMAL 1X54...58	Shipping carton box 20	303 mm x 159 mm x 101 mm	4.87 dm ³	3766.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

QTP-OPTIMAL 1X54...58

QUICKTRONIC PROFESSIONAL OPTIMAL | ECG for FL and CFL, not dimmable

Product name	Lamp group	Nominal current	Nominal wattage + Power loss	Luminous flux at 35 °C	Number of lighting outlets
QTP-OPTIMAL 1x54-58	DULUX L 55 W	0.24 A	50.00 W	4800 lm	1
	DULUX L 55 W CONSTANT		50.00 W	4800 lm	1
	DULUX L 55 W XT		50.00 W	4800 lm	1
	HO 50 W ES	0.26 A	54.00 W	4450 lm	1
	HO 54 W		54.00 W	4450 lm	1
	HO 54 W CONSTANT		54.00 W	4450 lm	1
	HO 54 W XT	0.25 A	54.00 W	4450 lm	1
	L 58 W		54.00 W	5000 lm	1
	L 58 W XT		54.00 W	5000 lm	1
	L 58 W XXT	54.00 W	5000 lm	1	