


## DR 4/8 SF - 5 x 20 mm fuse block

Standard fuse block for 5 x 20 mm or 5 x 25 mm fuses. Can be ganged for multipole operation. Available with indicators, consult Entelec.

Low profile series for height sensitive applications.

Spacing 8 mm (.315")



Standard 8 mm block

Fuses 5 x 20 mm and 5 x 25 mm. Other ratings available, consult Entelec

FU520 HC 5 x 20 - 250 V		
1.6	A	168 831.21
2	A	168 832.22
4	A	168 834.24
6.3	A	168 835.25
FU525 5 x 25 - 250 V		
1.6	A	167 546.22
2	A	167 547.23
2.5	A	167 548.04
4	A	167 549.05
6.3	A	167 550.02

		Type	P/N	
Standard blocks	Grey body	DR 4/8 SF	110 368.12	
Characteristics		DIN-VDE	UL	CSA
Wire size mm <sup>2</sup> /AWG	Solid wire	0 - 4 mm	22-12AWG	20-12AWG
	Stranded wire	0 - 4 mm		
Rated voltage	V AC / =DC	500/600Gr.C	300	300
Rated current	A	6.3	10	6.3
Rated wire size	mm <sup>2</sup> / AWG	4 mm <sup>2</sup>	12 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .37"		
Recommended torque	Nm / lb.in	--		

Accessories		Type		P/N	
	End stop		BADRL	th. 6.5 mm	199 420.21
	End section	grey	FEM8S	th. 1.5	118 624.27
	Comb-type jumper bar Isolating end cap	10 poles	PC81		173 523.11
	IDC jumper		AD2,5		114 205.20
	Assembly rod	2 poles	TGA8		168 672.11
		3 poles	TGA8		168 673.12
		4 poles	TGA8		168 674.13
	Assembly ring		ANT		168 675.14
See markers section		RC810, (RC610 on blade)			