

SAFETY DATA SHEET



CircuitWorks® Silicone Free Heat Sink Grease (UFI)

SECTION 1: Identification of the substance/mixture and of the company/ undertaking

1.1 Product identifier

Product name : CircuitWorks® Silicone Free Heat Sink Grease (UFI)
Product code : CW7270
Product description : grease
Product type : Solid.
Other means of identification : grease CW7270
Industrial/Professional use
UFI: UGD8-FOXX-U007-SH3E

1.2 Relevant identified uses of the substance or mixture and uses advised against

Not applicable.

1.3 Details of the supplier of the safety data sheet

Manufacturer
Chemtronics
8125 Cobb Center Drive
Kennesaw, GA 30152

Tel. 770-424-4888 or toll free 800-645-5244

Distributor

Importer
ITW Contamination Control BV
Saffierlaan 5
VZ-2132 Hoofddorp
The Netherlands

Email: info@itw-cc.com

Tel: +31 88 1307 400
FAX: +31 88 1307 499

e-mail address of person responsible for this SDS : askchemtronics@chemtronics.com

National contact

ITW Contamination Control BV
Saffierlaan 5
VZ-2132 Hoofddorp
The Netherlands

Email: info@itw-cc.com

Tel: +31 88 1307 400
FAX: +31 88 1307 499

1.4 Emergency telephone number

National advisory body/Poison Centre

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- Telephone number** : EMERGENCY HEALTH INFORMATION:
Austria +43 1 31304 5620, Belgium +32022649636, Bulgaria +359 2 9154 409,
Croatia +38514686910,
Cyprus +3572240561, Czech Republic +420267082257, Denmark +45 72 54 40 00,
Estonia +3726943384,
Finland +358 5052 000, France +33 3 85 21 92, Germany +49-30-18412-0, Greece
+302106479250,
Hungary +34 (1) 476 1136, Ireland +35318092566, Italy +390649906140, Latvia
+371 67032600,
Lithuania +370 70662008, Luxembourg +352 24785551, Netherland +31 88 75 585
61,
Norway +47 21 07 70 00, Poland +48 42 2530 400, Portugal +351213303271,
Romania +40213183606,
Slovakia +421 2 5465 2307, Slovenia +38614006039, Spain +34 917689800,
Sweden +46104566750
United Kingdom (England or Wales) 0845 46 47 or Scotland 08454 24 24 24 (UK
only).
- Supplier**
- Telephone number** : Chemtronics Product Information: 800-TECH-401 (800-832-4401)
Chemtronics Customer Service: 800-645-5244
- Hours of operation** : 8:00 AM to 5:00 PM
- Information limitations** : EMERGENCY HEALTH INFORMATION:
EMERGENCY SPILL INFORMATION:
Transport information

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Product definition : Mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Eye Irrit. 2, H319

Aquatic Acute 1, H400

Aquatic Chronic 1, H410

The product is classified as hazardous according to Regulation (EC) 1272/2008 as amended.

Ingredients of unknown toxicity : 100 percent of the mixture consists of component(s) of unknown toxicity

Ingredients of unknown ecotoxicity : Contains 28 % of components with unknown hazards to the aquatic environment

See Section 16 for the full text of the H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

2.2 Label elements

Hazard pictograms :



Signal word : Warning

Hazard statements : Causes serious eye irritation.
Very toxic to aquatic life with long lasting effects.

Precautionary statements

Prevention : Wear eye or face protection. Avoid release to the environment. Wash hands thoroughly after handling.

SECTION 2: Hazards identification

Response	: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
Storage	: Not applicable.
Disposal	: Dispose of contents and container in accordance with all local, regional, national and international regulations.
Hazardous ingredients	: zinc oxide
Supplemental label elements	: FOR INDUSTRIAL USE ONLY
Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles	: Not applicable.
Special packaging requirements	
Containers to be fitted with child-resistant fastenings	: Not applicable.
Tactile warning of danger	: Not applicable.

2.3 Other hazards

Other hazards which do not result in classification	: None known.
--	---------------

SECTION 3: Composition/information on ingredients

3.2 Mixtures : Mixture

Product/ingredient name	Identifiers	%	Regulation (EC) No. 1272/2008 [CLP]	Type
zinc oxide	EC: 215-222-5 CAS: 1314-13-2 Index: 030-013-00-7	≥75 - ≤90	Eye Irrit. 2, H319 Aquatic Acute 1, H400 (M=10) Aquatic Chronic 1, H410 (M=10) See Section 16 for the full text of the H statements declared above.	[1]

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

Type

- [1] Substance classified with a health or environmental hazard
- [2] Substance with a workplace exposure limit
- [3] Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII
- [4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII
- [5] Substance of equivalent concern

Occupational exposure limits, if available, are listed in Section 8.

SECTION 4: First aid measures

4.1 Description of first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Get medical attention.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention if adverse health effects persist or are severe. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.

4.2 Most important symptoms and effects, both acute and delayed

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
irritation
redness
watering
- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:
irritation
- Ingestion** : Adverse symptoms may include the following:
nausea or vomiting
stomach pains
diarrhoea

4.3 Indication of any immediate medical attention and special treatment needed

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

5.2 Special hazards arising from the substance or mixture

SECTION 5: Firefighting measures

Hazards from the substance or mixture : This material is very toxic to aquatic life with long lasting effects. Fire water contaminated with this material must be contained and prevented from being discharged to any waterway, sewer or drain.

Hazardous combustion products : Decomposition products may include the following materials:
metal oxide/oxides

5.3 Advice for firefighters

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.

For emergency responders : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

6.2 Environmental precautions

: Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air). Water polluting material. May be harmful to the environment if released in large quantities. Collect spillage.

6.3 Methods and material for containment and cleaning up

Small spill : Move containers from spill area. Avoid dust generation. Using a vacuum with HEPA filter will reduce dust dispersal. Place spilled material in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor.

Large spill : Move containers from spill area. Approach the release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Avoid dust generation. Do not dry sweep. Vacuum dust with equipment fitted with a HEPA filter and place in a closed, labeled waste container. Dispose of via a licensed waste disposal contractor.

6.4 Reference to other sections

: See Section 1 for emergency contact information.
See Section 8 for information on appropriate personal protective equipment.
See Section 13 for additional waste treatment information.

SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

7.1 Precautions for safe handling

Protective measures : Put on appropriate personal protective equipment (see Section 8). Do not ingest. Avoid contact with eyes, skin and clothing. Avoid release to the environment. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.

SECTION 7: Handling and storage

Advice on general occupational hygiene : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.

Seveso Directive - Reporting thresholds (in tonnes)

Danger criteria

Category	Notification and MAPP threshold	Safety report threshold
E1: Hazardous to the aquatic environment - Acute 1 or Chronic 1	100	200

7.3 Specific end use(s)

Recommendations : Not available.

Industrial sector specific solutions : Not available.

SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker exposure or environmental releases.

8.1 Control parameters

Occupational exposure limits

No exposure limit value known.

Recommended monitoring procedures : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

DNELs/DMELs

No DNELs/DMELs available.

PNECs

No PNECs available

8.2 Exposure controls

Appropriate engineering controls : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

Individual protection measures

SECTION 8: Exposure controls/personal protection

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

- Physical state** : Solid.
- Colour** : White. Off-white. [Light]
- Odour** : Not available.
- Odour threshold** : Not available.
- pH** : Not available.
- Melting point/freezing point** : Not available.
- Initial boiling point and boiling range** : >700°C
- Flash point** : Not available.
- Evaporation rate** : Not available.
- Flammability (solid, gas)** : Not available.
- Upper/lower flammability or explosive limits** : Not available.
- Vapour pressure** : <0.000013 kPa [room temperature]
- Vapour density** : Not available.
- Relative density** : 2.4
- Solubility(ies)** : Not available.
- Partition coefficient: n-octanol/ water** : Not available.

CircuitWorks® Silicone Free Heat Sink Grease (UFI)

SECTION 9: Physical and chemical properties

- Auto-ignition temperature** : Not available.
Decomposition temperature : Not available.
Viscosity : Not available.
Explosive properties : Not available.
Oxidising properties : Not available.

9.2 Other information

- Solubility in water** : Not available.

No additional information.

SECTION 10: Stability and reactivity

- 10.1 Reactivity** : No specific test data related to reactivity available for this product or its ingredients.
- 10.2 Chemical stability** : The product is stable.
- 10.3 Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.
- 10.4 Conditions to avoid** : No specific data.
- 10.5 Incompatible materials** : Reactive or incompatible with the following materials: amines strong alkalis Strong oxidizing materials
- 10.6 Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

- Conclusion/Summary** : Not available.

Acute toxicity estimates

Not available.

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
zinc oxide	Eyes - Mild irritant	Rabbit	-	24 hours 500 milligrams	-
	Skin - Mild irritant	Rabbit	-	24 hours 500 milligrams	-

- Conclusion/Summary** : Not available.

Sensitisation

- Conclusion/Summary** : Not available.

Mutagenicity

- Conclusion/Summary** : Not available.

Carcinogenicity

- Conclusion/Summary** : Not available.

Reproductive toxicity

- Conclusion/Summary** : Not available.

Teratogenicity

- Conclusion/Summary** : Not available.

Specific target organ toxicity (single exposure)

SECTION 11: Toxicological information

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Information on likely routes of exposure : Not available.

Potential acute health effects

Eye contact : Irritating to eyes.
Inhalation : No known significant effects or critical hazards.
Skin contact : May cause skin irritation.
Ingestion : Irritating to mouth, throat and stomach.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact : Adverse symptoms may include the following:
irritation
redness
watering
Inhalation : No specific data.
Skin contact : Adverse symptoms may include the following:
irritation
Ingestion : Adverse symptoms may include the following:
nausea or vomiting
stomach pains
diarrhoea

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Short term exposure

Potential immediate effects : Not available.
Potential delayed effects : Not available.

Long term exposure

Potential immediate effects : Not available.
Potential delayed effects : Not available.

Potential chronic health effects

Not available.

Conclusion/Summary : Not available.
General : No known significant effects or critical hazards.
Carcinogenicity : No known significant effects or critical hazards.
Mutagenicity : No known significant effects or critical hazards.
Teratogenicity : No known significant effects or critical hazards.
Developmental effects : No known significant effects or critical hazards.
Fertility effects : No known significant effects or critical hazards.

Other information : Not available.

SECTION 12: Ecological information

12.1 Toxicity

Product/ingredient name	Result	Species	Exposure
zinc oxide	Acute IC50 1.85 mg/l Marine water	Algae - Skeletonema costatum	96 hours
	Acute IC50 46 µg/l Fresh water	Algae - Pseudokirchneriella subcapitata - Exponential growth phase	72 hours
	Acute LC50 98 µg/l Fresh water	Daphnia - Daphnia magna - Neonate	48 hours
	Acute LC50 1.1 ppm Fresh water	Fish - Oncorhynchus mykiss	96 hours

Conclusion/Summary : Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

12.2 Persistence and degradability

Conclusion/Summary : Not available.

12.3 Bioaccumulative potential

Product/ingredient name	LogP _{ow}	BCF	Potential
zinc oxide	-	60960	high

12.4 Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Mobility : Not available.

12.5 Results of PBT and vPvB assessment

PBT : Not applicable.

vPvB : Not applicable.

12.6 Other adverse effects : No known significant effects or critical hazards.

SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

13.1 Waste treatment methods

Product

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

Hazardous waste : The classification of the product may meet the criteria for a hazardous waste.

Packaging

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

Special precautions : This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: Transport information

	ADR/RID	ADN	IMDG	IATA
14.1 UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name	Adhesives Sealants	Adhesives Sealants	Adhesives Sealants	Adhesives Sealants
14.3 Transport hazard class(es)	-	-	-	-
14.4 Packing group	-	-	-	-
14.5 Environmental hazards	No.	No.	No.	No.
Additional information	-	-	-	The environmentally hazardous substance mark may appear if required by other transportation regulations.

14.6 Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code : Not available.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU Regulation (EC) No. 1907/2006 (REACH)

Annex XIV - List of substances subject to authorisation

Annex XIV

None of the components are listed.

Substances of very high concern

None of the components are listed.

Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles : Not applicable.

Other EU regulations

Europe inventory : Not determined.

Ozone depleting substances (1005/2009/EU)

Not listed.

Prior Informed Consent (PIC) (649/2012/EU)

Not listed.

Seveso Directive

This product is controlled under the Seveso Directive.

Danger criteria

SECTION 15: Regulatory information

Category

E1: Hazardous to the aquatic environment - Acute 1 or Chronic 1

International regulations

Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

Montreal Protocol (Annexes A, B, C, E)

Not listed.

Stockholm Convention on Persistent Organic Pollutants

Not listed.

Rotterdam Convention on Prior Informed Consent (PIC)

Not listed.

UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

International lists

National inventory

Australia	: Not determined.
Canada	: All components are listed or exempted.
China	: All components are listed or exempted.
Japan	: Japan inventory (ENCS) : Not determined. Japan inventory (ISHL) : Not determined.
Malaysia	: Not determined.
New Zealand	: All components are listed or exempted.
Philippines	: Not determined.
Republic of Korea	: All components are listed or exempted.
Taiwan	: All components are listed or exempted.
Turkey	: Not determined.
United States	: Not determined.

15.2 Chemical safety assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

🔍 Indicates information that has changed from previously issued version.

Abbreviations and acronyms : ATE = Acute Toxicity Estimate
CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
DMEL = Derived Minimal Effect Level
DNEL = Derived No Effect Level
EUH statement = CLP-specific Hazard statement
PBT = Persistent, Bioaccumulative and Toxic
PNEC = Predicted No Effect Concentration
RRN = REACH Registration Number
vPvB = Very Persistent and Very Bioaccumulative

Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Eye Irrit. 2, H319 Aquatic Acute 1, H400 Aquatic Chronic 1, H410	Calculation method Calculation method Calculation method

Full text of abbreviated H statements

CircuitWorks® Silicone Free Heat Sink Grease (UFI)

SECTION 16: Other information

H319 H400 H410	Causes serious eye irritation. Very toxic to aquatic life. Very toxic to aquatic life with long lasting effects.
----------------------	--

Full text of classifications [CLP/GHS]

Aquatic Acute 1, H400 Aquatic Chronic 1, H410 Eye Irrit. 2, H319	ACUTE AQUATIC HAZARD - Category 1 LONG-TERM AQUATIC HAZARD - Category 1 SERIOUS EYE DAMAGE/EYE IRRITATION - Category 2
--	--

Date of printing : 10/5/2020
Date of issue/ Date of revision : 10/5/2020
Date of previous issue : No previous validation
Version : 1

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.