

## 1.8 V, Micropower, Zero-Drift, Rail-to-Rail Input/Output Op Amps

#### **Data Sheet**

#### FEATURES


Very low supply current: 13 µA typical Low offset voltage: 15 µV maximum Offset voltage drift: 20 nV/°C Single-supply operation: 1.8 V to 5.5 V High PSRR: 110 dB minimum High CMRR: 110 dB minimum Rail-to-rail input/output Unity-gain stable Extended industrial temperature range

#### **APPLICATIONS**

Pressure and position sensors Temperature measurements Electronic scales Medical instrumentation Battery-powered equipment Handheld test equipment

## ADA4051-1/ADA4051-2

#### **PIN CONFIGURATIONS**



#### **GENERAL DESCRIPTION**

The ADA4051-1/ADA4051-2 are CMOS, micropower, zerodrift operational amplifiers utilizing an innovative chopping technique. These amplifiers feature rail-to-rail input/output swing and extremely low offset voltage while operating from a 1.8 V to 5.5 V power supply. In addition, these amplifiers offer high power supply rejection ratio (PSRR) and common-mode rejection ratio (CMRR) while operating with a typical supply current of 13  $\mu$ A per amplifier. This combination of features makes the ADA4051-1/ADA4051-2 amplifiers ideal choices for battery-powered applications where high precision and low power consumption are important. The ADA4051-1/ADA4051-2 are specified for the extended industrial temperature range of -40°C to +125°C. The ADA4051-1 amplifier is available in 5-lead SOT-23 and 5-lead SC-70 packages. The ADA4051-2 amplifier is available in an 8-lead MSOP and an 8-lead LFCSP.

The ADA4051-1/ADA4051-2 are members of a growing series of zero-drift op amps offered by Analog Devices, Inc. Refer to Table 1 for a list of these devices.

#### Table 1. Op Amps

Supply	Low Power, 5 V	5 V	16 V
Single	AD8538	AD8628	AD8638
Dual	AD8539	AD8629	AD8639
Quad		AD8630	

Rev. C Document Feedback
Information furnished by Analog Devices is believed to be accurate and reliable. However, no

responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A. Tel: 781.329.4700 ©2009-2016 Analog Devices, Inc. All rights reserved. Technical Support www.analog.com

### TABLE OF CONTENTS

Features	1
Applications	1
Pin Configurations	1
General Description	1
Revision History	2
Specifications	3
Electrical Characteristics—1.8 V Operation	3
Electrical Characteristics—5 V Operation	5
Absolute Maximum Ratings	7

#### **REVISION HISTORY**

3/16—Rev. B to Rev. C	
Changed CP-8-2 to CP-8-13 Through	ghout
Changes to Figure 4	1
Changes to Offset Voltage Parameter and Input Resistance	
Parameter, Table 2	3
Changes to Offset Voltage Parameter and Input Resistance	
Parameter, Table 3	5
Changes to Table 5	7
Updated Outline Dimensions	19
Changes to Ordering Guide	20

#### 1/10—Rev. A to Rev. B

Added ADA4051-1, 5-Lead SC-70 Package	Universal
Added Figure 2; Renumbered Sequentially	1
Changes to Figure 4 and General Description Section .	1
Changes to Electrical Characteristics-1.8 V Operation	n Section
and Table 2	3
Changes to Electrical Characteristics—5 V Operation S	Section
and Table 3	4
Changes to Table 5	5
Updated Outline Dimensions	17
Changes to Ordering Guide	18

Thermal Resistance	7
Power Sequencing	7
ESD Caution	7
Typical Performance Characteristics	8
Theory of Operation	17
Input Voltage Range	
Output Phase Reversal	
Outline Dimensions	19
Ordering Guide	20

#### 10/09—Rev. 0 to Rev. A

7/09—Revision 0: Initial Version

### **SPECIFICATIONS**

#### **ELECTRICAL CHARACTERISTICS—1.8 V OPERATION**

 $V_{\text{SY}}$  = 1.8 V,  $V_{\text{CM}}$  =  $V_{\text{SY}}/2$  V,  $T_{\text{A}}$  = 25°C,  $R_{\text{L}}$  = 100 k $\Omega$  to GND, unless otherwise noted.

#### Table 2.

Parameter	Symbol	Test Conditions/Comments	Min	Тур	Мах	Unit
INPUT CHARACTERISTICS						
Offset Voltage	Vos					
ADA4051-2		$0~V \leq V_{\text{CM}} \leq 1.8~V$		2	15	μV
ADA4051-1		$0~V \leq V_{CM} \leq 1.8~V$		2	17	μV
		$-40^{\circ}C \le T_A \le +125^{\circ}C$			27	μV
Offset Voltage Drift	$\Delta V_{os}/\Delta T$	$-40^{\circ}C \le T_A \le +125^{\circ}C$		0.02	0.1	μV/°C
Input Bias Current	IB			5	50	pА
		$-40^{\circ}C \le T_A \le +125^{\circ}C$			200	pА
Input Offset Current	los			10	100	pА
		$-40^{\circ}C \le T_A \le +125^{\circ}C$			150	pА
Input Voltage Range		$-40^{\circ}C \le T_A \le +125^{\circ}C$	0		1.8	V
Common-Mode Rejection Ratio	CMRR	$0~V \leq V_{\text{CM}} \leq 1.8~V$	105	125		dB
		$-40^{\circ}C \le T_A \le +125^{\circ}C$	100			dB
Large-Signal Voltage Gain	A <sub>VO</sub>	$\begin{aligned} R_L &= 10 \ k\Omega \ to \ V_{CM}, \\ 0.1 \ V &\leq V_{OUT} \leq V_{SY} - 0.1 \ V \end{aligned}$	106	130		dB
		$-40^{\circ}C \le T_A \le +125^{\circ}C$	100			dB
Input Resistance						
Differential Mode	RINDM			8		MΩ
Common Mode	RINCM			250		GΩ
Input Capacitance, Differential Mode	CINDM			2		pF
Input Capacitance, Common Mode	CINCM			5		pF
OUTPUT CHARACTERISTICS						
Output Voltage High	Vон	$R_L = 100 \text{ k}\Omega \text{ to } V_{CM}$	1.796	1.799		V
		$-40^{\circ}C \le T_A \le +125^{\circ}C$	1.79			V
		$R_L = 10 \text{ k}\Omega \text{ to } V_{CM}$	1.76	1.796		V
		$-40^{\circ}C \le T_A \le +125^{\circ}C$	1.7			V
Output Voltage Low	Vol	$R_L = 100 \text{ k}\Omega \text{ to } V_{CM}$		1	3	mV
		$-40^{\circ}C \le T_A \le +125^{\circ}C$			9	mV
		$R_L = 10 \text{ k}\Omega \text{ to } V_{CM}$		3	20	mV
		$-40^{\circ}C \le T_A \le +125^{\circ}C$			40	mV
Short-Circuit Current	lsc	$V_{OUT} = V_{SY} \text{ or } GND$		13		mA
Closed-Loop Output Impedance	ZOUT	f = 1 kHz, G = 10		1		Ω
POWER SUPPLY						
Power Supply Rejection Ratio	PSRR	$1.8 V \le V_{SY} \le 5.5 V$	110	135		dB
		$-40^{\circ}C \le T_{A} \le +125^{\circ}C$	106			dB
Supply Current per Amplifier	I <sub>SY</sub>					
ADA4051-2	51	$V_{OUT} = V_{SY}/2$		13	17	μA
ADA4051-1		$V_{\text{OUT}} = V_{\text{SY}}/2$		15	18	μA
		$-40^{\circ}C \le T_A \le +125^{\circ}C$			20	μA
DYNAMIC PERFORMANCE						
Slew Rate	SR+	$R_L = 10 \text{ k}\Omega, C_L = 100 \text{ pF}, G = 1$		0.04		V/µs
	SR-	$R_L = 10 \text{ k}\Omega$ , $C_L = 100 \text{ pF}$ , $G = 1$		0.03		V/μs
Settling Time	ts	To 0.1%, $V_{IN} = 1 V p-p$ , $R_L = 10 k\Omega$ , $C_L = 100 pF$		120		μs
			1			
Gain Bandwidth Product	GBP	$C_{\rm I} = 100  \rm pE, G = 1$		115		kH7
Gain Bandwidth Product Phase Margin	GBP Φ <sub>M</sub>	$C_L = 100 \text{ pF}, G = 1$ $C_L = 100 \text{ pF}, G = 1$		115 40		kHz Degrees

Parameter	Symbol	Test Conditions/Comments	Min	Тур	Мах	Unit
NOISE PERFORMANCE						
Voltage Noise	en p-p	f = 0.1 Hz to 10 Hz		1.96		μV р-р
Voltage Noise Density	en	f = 1 kHz		95		nV/√Hz
Current Noise Density	İn	f = 1 kHz		100		fA/√Hz

#### **ELECTRICAL CHARACTERISTICS—5 V OPERATION**

 $V_{\text{SY}}$  = 5.0 V,  $V_{\text{CM}}$  =  $V_{\text{SY}}/2$  V,  $T_{\text{A}}$  = 25°C,  $R_{\text{L}}$  = 100 k $\Omega$  to GND, unless otherwise noted.

Parameter	Symbol	<b>Test Conditions/Comments</b>	Min	Тур	Max	Unit
INPUT CHARACTERISTICS						
Offset Voltage	Vos					
ADA4051-2		$0 V \leq V_{CM} \leq 5 V$		2	15	μV
ADA4051-1		$0 \text{ V} \leq \text{V}_{CM} \leq 5 \text{ V}$		2	17	μV
		$-40^{\circ}C \leq T_{A} \leq +125^{\circ}C$			27	μV
Offset Voltage Drift	ΔVos/ΔΤ	$-40^{\circ}C \le T_A \le +125^{\circ}C$		0.02	0.1	μV/°C
Input Bias Current	IB			20	70	pА
	-0	$-40^{\circ}C \leq T_{A} \leq +125^{\circ}C$			200	pA
Input Offset Current	los			40	100	pA
	.05	$-40^{\circ}C \le T_A \le +125^{\circ}C$			150	pA
Input Voltage Range		$-40^{\circ}C \le T_A \le +125^{\circ}C$	0		5	V
Common-Mode Rejection Ratio	CMRR	$0 V \le V_{CM} \le 5 V$	110	135	5	dB
common mode nejection hallo	Civilia	$-40^{\circ}C \le T_{A} \le +125^{\circ}C$	106	155		dB
Large-Signal Voltage Gain	Avo	$R_L = 10 \text{ k}\Omega \text{ to } V_{CM}$	115	135		dB
	700	$0.1 V \le V_{OUT} \le V_{SY} - 0.1 V$	115	155		ub
		$-40^{\circ}C \le T_{A} \le +125^{\circ}C$	106			dB
Input Resistance		10 0 = 14 = 1125 0	100			ab
Differential Mode	RINDM			8		MΩ
Common Mode	RINCM			250		GΩ
Input Capacitance, Differential Mode	CINDM			250		pF
Input Capacitance, Common Mode				5		pF
OUTPUT CHARACTERISTICS	CINCM			5		рі
Output Voltage High	V <sub>OH</sub>	$R_{I} = 100 \text{ k}\Omega \text{ to } V_{CM}$	4.996	4.998		v
Output voltage high	V OH	$-40^{\circ}C \leq T_{A} \leq +125^{\circ}C$	4.990	4.990		v
				4.00		v
		$R_L = 10 \text{ k}\Omega \text{ to } V_{CM}$	4.96	4.99		v
		$-40^{\circ}C \le T_A \le +125^{\circ}C$	4.9			-
Output Voltage Low	V <sub>OL</sub>	$R_L = 100 \text{ k}\Omega \text{ to } V_{CM}$		1	4	mV
		$-40^{\circ}C \leq T_{A} \leq +125^{\circ}C$			13	mV
		$R_L = 10 \text{ k}\Omega \text{ to } V_{CM}$		9	30	mV
		$-40^{\circ}C \le T_{A} \le +125^{\circ}C$			90	mV
Short-Circuit Current	I <sub>SC</sub>	$V_{OUT} = V_{SY} \text{ or } GND$		15		mA
Closed-Loop Output Impedance	Zout	f = 1 kHz, G = 10		1		Ω
POWER SUPPLY						
Power Supply Rejection Ratio	PSRR	$1.8~V \leq V_{\text{SY}} \leq 5.5~V$	110	135		dB
		$-40^{\circ}C \le T_A \le +125^{\circ}C$	106			dB
Supply Current per Amplifier	Isy					
ADA4051-2		$V_{OUT} = V_{SY}/2$		13	17	μΑ
ADA4051-1		$V_{OUT} = V_{SY}/2$		15	18	μΑ
		$-40^\circ C \le T_A \le +125^\circ C$			20	μΑ
DYNAMIC PERFORMANCE						
Slew Rate	SR+	$R_L = 10 \text{ k}\Omega$ , $C_L = 100 \text{ pF}$ , $G = 1$		0.06		V/µs
	SR–	$R_L = 10 \text{ k}\Omega$ , $C_L = 100 \text{ pF}$ , $G = 1$		0.04		V/µs
Settling Time	ts	To 0.1%, $V_{IN} = 1 V p - p$ , R <sub>L</sub> = 10 k $\Omega$ , C <sub>L</sub> = 100 pF		110		μs
Gain Bandwidth Product	GBP	$C_{L} = 100 \text{ pF}, \text{G} = 1$		125		kHz
Phase Margin	Фм	$C_{L} = 100 \text{ pF}, \text{G} = 1$		40		Degree
Channel Separation	CS	$V_{IN} = 4.99 V, f = 100 Hz$		140		dB

Data Sheet

Parameter	Symbol	Test Conditions/Comments	Min	Тур	Max	Unit
NOISE PERFORMANCE						
Voltage Noise	e <sub>n</sub> p-p	f = 0.1 Hz to 10 Hz		1.96		μV p-p
Voltage Noise Density	en	f = 1  kHz		95		nV/√Hz
Current Noise Density	İn	f = 1 kHz		100		fA/√Hz

### **ABSOLUTE MAXIMUM RATINGS**

#### Table 4.

Tuble I.	
Parameter	Rating
Supply Voltage	6 V
Input Voltage	$\pm V_{SY} \pm 0.3 V$
Input Current <sup>1</sup>	±10 mA
Differential Input Voltage <sup>2</sup>	±Vsγ
Output Short-Circuit Duration to GND	Indefinite
Storage Temperature Range	–65°C to +150°C
Operating Temperature Range	-40°C to +125°C
Junction Temperature Range	–65°C to +150°C
Lead Temperature (Soldering, 60 sec)	300°C

<sup>1</sup> The input pins have clamp diodes to the power supply pins. Limit the input current to 10 mA or less whenever input signals exceed the power supply rail by 0.3 V.

<sup>2</sup> Inputs are protected against high differential voltages by internal series 1.33 kΩ resistors and back-to-back diode-connected N-MOSFETs (with a typical V<sub>T</sub> of 0.7 V for V<sub>CM</sub> of 0 V).

Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

#### THERMAL RESISTANCE

 $\theta_{JA}$  is specified for the worst-case conditions, that is, a device soldered on a circuit board for surface-mount packages with its exposed paddle soldered to a pad, if applicable. Table 5 shows simulated thermal values for a 4-layer (2S2P) JEDEC standard thermal test board, unless otherwise specified.

#### Table 5. Thermal Resistance

Package Type	θյΑ	Unit
5-Lead SOT-23 (RJ-5)	190	°C/W
5-Lead SC-70 (KS-5)	534	°C/W
8-Lead MSOP (RM-8)	142	°C/W
8-Lead LFCSP (CP-8-13)		
1-Layer JEDEC Board	272	°C/W
2-Layer JEDEC Board	145	°C/W
2-Layer JEDEC Board with $2 \times 2$ Vias	55	°C/W

#### **POWER SEQUENCING**

The op amp supplies must be established simultaneously with or before any input signals are applied. If this is not possible, the input current must be limited to 10 mA.

#### **ESD CAUTION**



**ESD (electrostatic discharge) sensitive device.** Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

### **TYPICAL PERFORMANCE CHARACTERISTICS**

 $T_A = 25^{\circ}C$ , unless otherwise noted.




Figure 5. Input Offset Voltage Distribution




Figure 6. Input Offset Voltage Drift Distribution with Temperature







Figure 7. Input Offset Voltage vs. Input Common-Mode Voltage











Figure 10. Input Offset Voltage vs. Input Common-Mode Voltage

#### **Data Sheet**

### ADA4051-1/ADA4051-2

 $T_A = 25^{\circ}C$ , unless otherwise noted.






Figure 12. Input Bias Current vs. Common-Mode Voltage and Temperature





Figure 13. Output Voltage (V₀+) to Supply Rail vs. Load Current and Temperature






Figure 15. Input Bias Current vs. Common-Mode Voltage and Temperature




Figure 16. Output Voltage (V<sub>OH</sub>) to Supply Rail vs. Load Current and Temperature

 $T_A = 25^{\circ}C$ , unless otherwise noted.





Figure 17. Output Voltage (Vol) to Supply Rail vs. Load Current and Temperature






Figure 19. Output Voltage (Vol) vs. Temperature





Figure 20. Output Voltage ( $V_{\text{OL}}$ ) to Supply Rail vs. Load Current and Temperature








Figure 22. Output Voltage (Vol) vs. Temperature

#### **Data Sheet**

 $T_A = 25^{\circ}C$ , unless otherwise noted.








Figure 24. Open-Loop Gain and Phase vs. Frequency




Figure 25. Closed-Loop Gain vs. Frequency

30  $V_{CM} = V_{SY}/2$ 25 20 15 10 - ADA4051-2, 1.8V ADA4051-2, 5V 5

TEMPERATURE (°C)

Figure 26. Total Supply Current vs. Temperature

TOTAL SUPPLY CURRENT (µA)

0 └─ -40

-25 -10

5 20 35 50 65 80




Figure 27. Open-Loop Gain and Phase vs. Frequency




Figure 28. Closed-Loop Gain vs. Frequency

# ADA4051-1/ADA4051-2

- ADA4051-1, 1.8V

ADA4051-1, 5V

95 110 125

-023

08056

1M 8056-029

- G = -1 - G = -10 - G = -100

 $V_{SY} = 5V$ 1111

100k

100k

1M 8056-030

V<sub>SY</sub> = 5V

1M

08056-031

 $T_A = 25^{\circ}C$ , unless otherwise noted.





Figure 31. PSRR vs. Frequency

Rev. C | Page 12 of 22

### **Data Sheet**

### ADA4051-1/ADA4051-2

 $T_A = 25^{\circ}C$ , unless otherwise noted.






Figure 36. Large-Signal Transient Response






Figure 37. Small-Signal Transient Response








Figure 40. Small-Signal Transient Response

 $T_A = 25^{\circ}C$ , unless otherwise noted.




Figure 46. Positive Overload Recovery


08056-043

#### **Data Sheet**


 $T_A = 25^{\circ}C$ , unless otherwise noted.


# ADA4051-1/ADA4051-2


08056-047




 $T_A = 25^{\circ}C$ , unless otherwise noted.









### THEORY OF OPERATION

The ADA4051-1/ADA4051-2 micropower chopper operational amplifiers feature a novel, patent-pending technique that suppresses offset-related ripple in a chopper amplifier. Instead of filtering the ripple in the ac domain, this technique nulls the initial offset of the amplifier in the dc domain, thus preventing ripple at the overall output.


Auto-zeroing and chopping are two techniques widely used in high precision CMOS amplifiers to achieve low offset, low offset drift, and no 1/f noise. Each of these techniques has pros and cons. Auto-zeroing results in more in-band noise due to aliasing introduced by sampling. On the other hand, chopping produces offset-related ripple because it modulates the initial offset associated with the amplifier up to its chopping frequency.

To accomplish the best noise vs. power trade-off, the chopping technique is the better approach when designing a low offset amplifier because there is no increased in-band noise. It is preferable to suppress the offset-related ripple inside a chopper amplifier because the offset-related ripple would otherwise need to be eliminated by an extra off-chip postfilter.

Figure 59 shows the block diagram design of the ADA4051-1/ ADA4051-2 chopper amplifiers employing a local feedback loop called autocorrection feedback (ACFB). The main signal path contains an input chopping switch network (CHOP1), a first transconductance amplifier (Gm1), an output chopping switch network (CHOP2), a second transconductance amplifier (Gm2), and a third transconductance amplifier (Gm3). CHOP1 and CHOP2 operate at 40 kHz of chopping frequency to modulate the initial offset and 1/f noise from Gm1 up to the chopping frequency. A fourth transconductance amplifier (Gm4) in the ACFB senses the modulated ripple at the output of CHOP2, caused by the initial offset voltage of Gm1. Then, the ripple is demodulated down to a dc domain through a third chopping switch network (CHOP3), operating with the same chopping clock as CHOP1 and CHOP2. Finally, a null transconductance amplifier (Gm5) tries to null any dc component at the output of Gm1 that would otherwise appear in the overall output as ripple.

A switched-capacitor notch filter (NF) functions to selectively suppress the undesired offset-related ripple without disturbing the desired input signal from the overall input. The desired input dc signal appears as a dc signal at the output of CHOP2. Then, the initial offset is modulated up to the chopping frequency by CHOP3 and filtered out by the NF. Therefore, initial offset does not create any feedback and does not disturb the desired input signal. The NF is synchronized with the chopping clock to filter out the modulated component. In the same manner, the offset of Gm5 is filtered out by the combination of CHOP3 and the NF, enabling accurate ripple sensing at the output of CHOP2.

In parallel with the high dc gain path, a feedforward transconductance amplifier (Gm6) is added to bypass the phase shift introduced by the ACFB at the chopping frequency. Gm6 is designed to have the same transconductance as Gm1 to avoid pole-zero doublets. This design prevents any instability introduced by the ACFB in the overall feedback loop.



The voltage noise density, which is equal to the thermal noise floor dominated by the Gm1, is essentially flat from dc to the chopping frequency because CHOP1 and CHOP2 eliminate the 1/f noise generated in Gm1 and the ACFB does not contribute any additional noise. Although the ACFB suppresses the ripple related to the chopping, there is a remaining voltage ripple. To further suppress the remaining ripple down to a desired level, it is recommended to have a postfilter at the output of the amplifier.

The remaining voltage ripple originates from two sources. The first type of ripple is due to the residual ripple associated with the initial offset of the Gm1. It is proportional to the magnitude of the initial offset and creates a spectrum at the chopping frequency ( $f_{CHOP}$ ). When the amplifier is configured as a unitygain buffer, this ripple has a typical value of 4.9  $\mu$ V rms and a maximum of 34.7  $\mu$ V rms. The second type of ripple is due to the intermodulation between the high frequency input signal and the chopping frequency. This ripple depends on the input frequency ( $f_{IN}$ ) and creates a spectrum at frequencies equal to the difference between the chopping frequency and the input frequency ( $f_{CHOP} - f_{IN}$ ), as well as at frequencies equal to the summation of the chopping frequency and the input frequency ( $f_{CHOP} + f_{IN}$ ). The magnitude of the ripple for different input frequencies is shown in Figure 60.




Figure 60. ADA4051-1/ADA4051-2 Modulated Output Ripple vs. Input Frequency

The design architecture of the ADA4051-1/ADA4051-2 specifically targets precision signal conditioning applications requiring accurate and stable performance from dc to 10 Hz bandwidth. In summary, the main features of the ADA4051-1/ ADA4051-2 chopper amplifiers are

- Considerable suppression of the offset-related ripple
- No effect on the desired input signal as long as its frequency is much lower than the chopping frequency shown in Figure 60
- Achievement of low offset similar to a conventional chopper amplifier
- No introduction of excess noise

The ADA4051-1/ADA4051-2 chopper amplifiers provide a railto-rail input range with a 1.8 V to 5.5 V supply voltage range and 20  $\mu$ A supply current consumption over the  $-40^{\circ}$ C to  $+125^{\circ}$ C extended industrial temperature range. The gain bandwidth is 125 kHz as a unity-gain stable amplifier up to 100 pF load capacitance.

#### **INPUT VOLTAGE RANGE**

The ADA4051-1/ADA4051-2 have internal ESD protection diodes. These diodes are connected between the inputs and each supply rail to protect the input MOSFETs from an electrical discharge event and are reversed-biased during normal operation. This protection scheme allows voltages as high as approximately 0.3 V beyond the supplies ( $\pm V_{SY} \pm 0.3$  V) to be applied at the input of either terminal without causing permanent damage.

If either input exceeds one of the supply rails by more than 0.3 V, these ESD diodes become forward-biased and large amounts of current begin to flow through them. Without current limiting, this excessive current would cause permanent damage to the device. If the inputs are expected to be subject to overvoltage conditions, install a resistor in series with each input to limit the input current to 10 mA maximum.

The ADA4051-1/ADA4051-2 also have internal circuitry that protects the input stage from high differential voltages. This circuitry is composed of internal 1.33 k $\Omega$  resistors in series with each input and back-to-back diode-connected N-MOSFET (with a typical V<sub>T</sub> of 0.7 V for a V<sub>CM</sub> of 0 V) after these series resistors. With normal negative feedback operating conditions, the ADA4051-1/ADA4051-2 amplifiers correct their output to ensure that the two inputs are at the same voltage. However, if the device is configured as a comparator or there are unusual operating conditions, the input voltages can be forced to different potentials, which may cause excessive current to flow through the internal diodeconnected N-MOSFETs.

Although the ADA4051-1/ADA4051-2 are rail-to-rail input amplifiers, take care to ensure that the potential difference between the inputs does not exceed  $\pm V_{SY}$  to avert permanent damage to the device.


#### **OUTPUT PHASE REVERSAL**


Although output phase reversal can occur with other amplifiers when the input common-mode voltage range is exceeded, the ADA4051-1/ADA4051-2 amplifiers are designed to prevent any output phase reversal, provided both inputs are maintained approximately within 0.3 V above and below the supply voltages  $(\pm V_{SY} \pm 0.3 \text{ V})$ .

With other amplifiers, the outputs may jump in the opposite direction to the supply rail when a common-mode voltage moves outside the common-mode range. This usually occurs when one of the internal stages of the amplifier no longer has sufficient bias voltage across it and subsequently turns off.

However, with the ADA4051-1/ADA4051-2 amplifiers, if one or both inputs exceed the input voltage range but remain within the  $\pm V_{SY} \pm 0.3$  V range, an internal loop opens and the output remains in saturation mode, without phase reversal, until the input voltage is brought back to within the input voltage range limits as shown in Figure 55 and Figure 58.

### **OUTLINE DIMENSIONS**





#### **ORDERING GUIDE**

Model <sup>1</sup>	Temperature Range	Package Description	Package Option	Branding
ADA4051-1ARJZ-R2	-40°C to +125°C	5-Lead Small Outline Transistor Package [SOT-23]	RJ-5	AOU
ADA4051-1ARJZ-R7	-40°C to +125°C	5-Lead Small Outline Transistor Package [SOT-23]	RJ-5	AOU
ADA4051-1ARJZ-RL	-40°C to +125°C	5-Lead Small Outline Transistor Package [SOT-23]	RJ-5	AOU
ADA4051-1AKSZ-R2	-40°C to +125°C	5-Lead Thin Shrink Small Outline Transistor Package [SC-70]	KS-5	AOU
ADA4051-1AKSZ-R7	-40°C to +125°C	5-Lead Thin Shrink Small Outline Transistor Package [SC-70]	KS-5	AOU
ADA4051-1AKSZ-RL	-40°C to +125°C	5-Lead Thin Shrink Small Outline Transistor Package [SC-70]	KS-5	AOU
ADA4051-2ACPZ-R2	-40°C to +125°C	8-Lead Lead Frame Chip Scale Package [LFCSP]	CP-8-13	A2M
ADA4051-2ACPZ-R7	-40°C to +125°C	8-Lead Lead Frame Chip Scale Package [LFCSP]	CP-8-13	A2M
ADA4051-2ACPZ-RL	-40°C to +125°C	8-Lead Lead Frame Chip Scale Package [LFCSP]	CP-8-13	A2M
ADA4051-2ARMZ	-40°C to +125°C	8-Lead Mini Small Outline Package [MSOP]	RM-8	A2M
ADA4051-2ARMZ-R7	-40°C to +125°C	8-Lead Mini Small Outline Package [MSOP]	RM-8	A2M
ADA4051-2ARMZ-RL	-40°C to +125°C	8-Lead Mini Small Outline Package [MSOP]	RM-8	A2M

<sup>1</sup> Z = RoHS Compliant Part.

### NOTES

### NOTES

©2009–2016 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. D08056-0-3/16(C)



www.analog.com