

LM139, LM239, LM339

Low-power quad voltage comparators

Datasheet - production data



D SO14 (plastic micropackage)



TSSOP14
(thin shrink small outline package)



Q QFN16 3x3 (plastic micropackage)

Features

- Wide single supply voltage range or dual supplies for all devices: +2 to +36 V or ±1 V to ±18 V
- Very low supply current (1.1 mA) independent of supply voltage
- Low input bias current: 25 nA typ
- Low input offset current: ±5 nA typ
- Low input offset voltage: ±1 mV typ
- Input common-mode voltage range includes ground
- Low output saturation voltage: 250 mV typ; (I_{SINK} = 4 mA)
- Differential input voltage range equal to the supply voltage
- TTL, DTL, ECL, MOS, CMOS compatible outputs

Description

This family of devices consists of four independent precision-voltage comparators with an offset voltage specification as low as 2 mV maximum for LM339A, LM239A, and LM139A. Each comparator has been designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible.

These comparators also have a unique characteristic in that the input common mode voltage range includes ground even though operated from a single power supply voltage.

Contents


1	Pin and schematic diagram
2	Absolute maximum ratings and operating conditions 4
3	Electrical characteristics 6
4	Electrical characteristics curves 8
5	Typical applications9
6	Package information
	6.1 SO14 package information
	6.2 TSSOP14 package information
	6.3 QFN16 3x3 package information
7	Ordering information
8	Revision history




1 Pin and schematic diagram

Output2 1 14 Output3 Output1 2 13 Output4 V_{CC}^{+} 3 12 V_{CC} Inverting input1 11 Non-inverting input4 4 Non-inverting input1 10 Inverting input4 Inverting input2 6 Non-inverting input3 Non-inverting input2 Inverting input3 13 VCC-VCC+ 12 IN- 1 11 IN+ 4 2 NC 3 10 NC IN+ 1 4 9 IN-4 IN-2 N+3

Figure 1. Pin connections (top view)





47/

DocID2159 Rev 4

3/19

2 Absolute maximum ratings and operating conditions

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V _{CC}	Supply voltage	±18 or 36	V
V _{ID}	Differential input voltage	±36	V
V _{IN}	Input voltage	-0.3 to +36	V
	Output short-circuit to ground ⁽¹⁾	Infinite	
R _{thja}	Thermal resistance junction to ambient ⁽²⁾ SO14 TSSOP14 QFN16 3x3	105 100 45	°C/W
R _{thjc}	Thermal resistance junction to case ⁽²⁾ SO14 TSSOP14 QFN16 3x3	31 32 14	°C/W
T _{stg}	Storage temperature range	-65 to +150	°C
Tj	Junction temperature	+150	°C
T _{LEAD}	Lead temperature (soldering 10 seconds)	260	°C
	Human body model (HBM) ⁽³⁾	500	
ESD	Machine model (MM) ⁽⁴⁾	100	V
	Charged device model (CDM) ⁽⁵⁾	1500	

Short-circuits from the output to V_{CC}⁺ can cause excessive heating and eventual destruction. The maximum output current is approximately 20 mA independent of the magnitude of V_{CC}⁺.

57

^{2.} Short-circuits can cause excessive heating. These values are typical.

^{3.} Human body model: a 100 pF capacitor is charged to the specified voltage, then discharged through a 1.5 k Ω resistor between two pins of the device. This is done for all couples of connected pin combinations while the other pins are floating.

^{4.} Machine model: a 200 pF capacitor is charged to the specified voltage, then discharged directly between two pins of the device with no external series resistor (internal resistor < 5 Ω). This is done for all couples of connected pin combinations while the other pins are floating.

Charged device model: all pins and the package are charged together to the specified voltage and then discharged directly to the ground through only one pin. This is done for all pins.

Table 2. Operating conditions (T_{amb} = 25 °C)

Symbol	Parameter	Value	Unit
V _{CC}	Supply voltage	2 to 32 ±1 to ±16	V
V _{ICM}	Common mode input voltage range	0 to (V _{CC} ⁺ - 1.5)	V
T _{oper}	Operating free-air temperature range – LM139, LM139A – LM239, LM239A – LM339, LM339A	-55, +125 -40, +105 0, +70	°C



3 Electrical characteristics

Table 3. Electrical characteristics at V_{CC}^+ = +5 V, V_{CC}^- = GND, T_{amb} = +25 °C (unless otherwise specified)

Symbol	Parameter		LM139A - LM239A LM339A			LM139 - LM239 LM339		
			Тур.	Max.	Min	Тур.	Max.	
V _{IO}	Input offset voltage ⁽¹⁾ $T_{min} \leq T_{amb} \leq T_{max}$		1	2 4		1	5 9	mV
I _{IO}	Input offset current T _{min} ≤T _{amb} ≤T _{max}		3	25 100		5	50 150	nA
I _{IB}	Input bias current (I ⁺ or I ⁻) ⁽²⁾ $T_{min} \leq T_{amb} \leq T_{max}$		25	100 300		25	250 400	nA
A _{VD}	Large signal voltage gain V_{CC} = 15 V, R_L = 15 k Ω , V_o = 1 V to 11 V	50	200		50	200		V/mV
I _{CC}	Supply current (all comparators) V _{CC} = +5 V, no load V _{CC} = +30 V, no load		1.1 1.3	2 2.5		1.1 1.3	2 2.5	mA
V _{ICM}	Input common mode voltage range ⁽³⁾ $V_{CC} = 30 \text{ V}$ $T_{min} \leq T_{amb} \leq T_{max}$	0		V _{CC} ⁺ -1.5 V _{CC} ⁺ -2	0		V _{CC} ⁺ -1.5 V _{CC} ⁺ -2	V
V _{ID}	Differential input voltage (4)			V _{CC} ⁺			V _{CC} ⁺	V
V _{OL}	Low level output voltage V_{ID} = -1 V, I_{SINK} = 4 mA $T_{min} \le T_{amb} \le T_{max}$		250	400 700		250	400 700	mV
I _{OH}	High level output current $V_{CC} = V_o = 30 \text{ V}, V_{ID} = 1 \text{ V}$ $T_{min} \le T_{amb} \le T_{max}$		0.1	1		0.1	1	nΑ μΑ
I _{SINK}	Output sink current V _{ID} = 1 V, V _o = 1.5 V	6	16		6	16		mA
t _{re}	Response time $^{(5)}$ R _L = 5.1 k Ω connected to V_{CC}^+		1.3			1.3		μs




Table 3. Electrical characteristics at V_{CC}^+ = +5 V, V_{CC}^- = GND, T_{amb} = +25 °C (unless otherwise specified) (continued)


Symbol	LM139A - LM239A LM339A		LN	M139 - L LM33		Unit		
		Min.	Тур.	Max.	Min	Тур.	Max.	
trel	Large signal response time R_L = 5.1 k Ω connected to V_{CC}^+ , e_l = TTL, $V_{(ref)}$ = +1.4 V		300			300		ns


- 1. At output switch point, $V_0 \approx 1.4 \text{ V}$, V_{CC}^+ from 5 V to 30 V, and over the full common-mode range (0 V to V_{CC}^+ -1.5 V).
- The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output, so no loading charge exists on the reference of input lines.
- The input common-mode voltage of either input signal voltage should not be allowed to go negative by more than 0.3 V.
 The upper end of the common-mode voltage range is V_{CC}⁺ -1.5 V, but either or both inputs can go to +30 V without damage.
- 4. Positive excursions of input voltage may exceed the power supply level. As long as the other voltage remains within the common-mode range, the comparator will provide a proper output state. The low input voltage state must not be less than -0.3 V (or 0.3 V below the negative power supply, if used).
- 5. The response time specified is for a 100 mV input step with 5 mV overdrive. For larger overdrive signals, 300 ns can be obtained.



4 Electrical characteristics curves











Figure 7. Response time for various input overdrives - positive transition



5 Typical applications

Figure 8. Basic comparator

 $V_{CC}^{+} = 5 \text{ V}$ $V_{CC}^{+} = 5 \text{ V}$ $V_{(ref)} \bigcirc V_{(ref)}$ $V_{(ref)} \bigcirc V_{(ref)}$




Figure 10. Driving TTL

+5 V

10 kΩ

-V_(ref)

-V_(ref)

&





Figure 12. Low frequency op amp $(e_o = 0 \text{ V for } e_i = 0 \text{ V})$ $15 \text{ k}\Omega$ $1 \text{ k}\Omega$








Figure 14. Time delay generator







DocID2159 Rev 4

Downloaded from Arrow.com.

10/19





6 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK[®] is an ST trademark.

57/

6.1 SO14 package information

Figure 22. SO14 package mechanical drawing

Table 4. SO14 package mechanical data

Dimensions						
Ref.		Millimeters				
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	1.35		1.75	0.05		0.068
A1	0.10		0.25	0.004		0.009
A2	1.10		1.65	0.04		0.06
В	0.33		0.51	0.01		0.02
С	0.19		0.25	0.007		0.009
D	8.55		8.75	0.33		0.34
E	3.80		4.0	0.15		0.15
е		1.27			0.05	
Н	5.80		6.20	0.22		0.24
h	0.25		0.50	0.009		0.02
L	0.40		1.27	0.015		0.05
k		8° (max.)				
ddd			0.10			0.004

6.2 TSSOP14 package information

Figure 23. TSSOP14 package mechanical drawing

Table 5. TSSOP14 package mechanical data

			Dimer	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α			1.20			0.047
A1	0.05		0.15	0.002	0.004	0.006
A2	0.80	1.00	1.05	0.031	0.039	0.041
b	0.19		0.30	0.007		0.012
С	0.09		0.20	0.004		0.0089
D	4.90	5.00	5.10	0.193	0.197	0.201
E	6.20	6.40	6.60	0.244	0.252	0.260
E1	4.30	4.40	4.50	0.169	0.173	0.176
е		0.65			0.0256	
L	0.45	0.60	0.75	0.018	0.024	0.030
L1		1.00			0.039	
k	0°		8°	0°		8°
aaa			0.10			0.004

577

6.3 QFN16 3x3 package information

BOTTOM VIEW R (OPTIONAL) EXPOSED PAD PIN 1 L 16x **b** 16x (4 LEADS PER SIDE) // 0.1 C A3 SEATING PLANE Ċ 0.08 C LEADS COPLANARITY TOP VIEW

Figure 24. QFN16 3x3 package mechanical drawing

57/


DocID2159 Rev 4

15/19

Table 6. QFN16 3x3 mm package mechanical data (pitch 0.5 mm)

			Dime	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	0.80	0.90	1.00	0.031	0.035	0.039
A1	0		0.05	0		0.002
A3		0.20			0.008	
b	0.18		0.30	0.007		0.012
D	2.90	3.00	3.10	0.114	0.118	0.122
D2	1.50		1.80	0.059		0.071
Е	2.90	3.00	3.10	0.114	0.118	0.122
E2	1.50		1.80	0.059		0.071
е		0.50			0.020	
L	0.30		0.50	0.012		0.020

Figure 25. QFN16 3x3 footprint recommendation



57

7 Ordering information

Table 7. Order codes

Part number	Temperature range	Package	Packing	Marking	
LM139DT LM139ADT	55 °C, +125 °C	SO14		139 139A	
LM139PT LM139APT	-55 C, +125 C	TSSOP14		139 139A	
LM239DT LM239ADT		SO14		239 239A	
LM239PT LM239APT	-40 °C, +105 °C	-40 °C, +105 °C	TSSOP14	Tape and reel	239 239A
LM239QT		QFN16 3x3		K550	
LM339DT LM339ADT		SO14		339 339A	
LM339PT LM339APT	0 °C, +70 °C	TSSOP14		339 339A	
LM339QT		QFN16 3x3		K551	

8 Revision history

Table 8. Document revision history

Date	Revision	Changes
01-Mar-2003	1	Initial release.
28-Apr-2009	2	Updated document format. Removed power dissipation from <i>Table 1: Absolute maximum ratings</i> . Added R _{THJA} , R _{THJC} , ESD and T _{LEAD} values to <i>Table 1</i> . Updated package information in <i>Chapter 6</i> . Added <i>Table 7: Order codes</i> .
13-Jul-2011	3	Added pin connections for QFN16 package in <i>Figure 1 on page 3</i> . Added thermal information for QFN16 package in <i>Table 1 on page 4</i> . Added QFN16 package information in <i>Chapter 6</i> . Added order codes for QFN16 package in <i>Table 7</i> : <i>Order codes</i> .
18-Aug-2014	4	Removed DIP14 package Table 7: Order codes: replaced the marking of the order code LM239QT from K549 to K550; removed all order codes with "tube" packing. Updated disclaimer



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2014 STMicroelectronics – All rights reserved



DocID2159 Rev 4 19/19