

Features

- * 350W peak pulse power (8/20μs)
- * Ultra low capacitance: 1.0 pF typical
- * Ultra low leakage: nA level
- * Low operating :
3.3V ,5V,8V,12V,15V,18V,24V,30V
- * Low clamping voltage
- * Protects one power line or data line
- * Complies with following standards:
- * – IEC 61000-4-2 (ESD) immunity test
Air discharge: ±30kV
Contact discharge: ±30kV
- * – IEC61000-4-4 (EFT) 40A (5/50ns)
- * RoHS Compliant

Ordering Information

Part Number	Qty per Reel	Reel Size
TPGC03C-TPGC30C	3000	7"

Mechanical Characteristics


- * Package: SOD-323
- * Lead Finish: Matte Tin
- * Case Material: "Green" Molding Compound.
- * UL Flammability Classification Rating 94V-0
- * Moisture Sensitivity: Level 3 per J-STD-020
- * Terminal Connections: See Diagram Below



Applications

- * USB Ports
- * Smart Phones
- * Wireless Systems
- * Ethernet 10/100/1000 Base T

Dimensions and Pin Configuration



Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	350	W
Peak Pulse Current (8/20μs)	IPP	22-6	A
ESD per IEC 61000-4-2 (Air)	VESD	±30	kV
ESD per IEC 61000-4-2 (Contact)		±30	
Operating Temperature Range	TJ	-40 to +85	°C
Storage Temperature Range	Tstg	-55 to +150	°C

Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise specified)

TPGC03C

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				3.3	V
Breakdown Voltage	V_{BR}	$I_T = 1\text{mA}$	4		6	V
Reverse Leakage Current	I_R	$V_{RWM} = 3.3\text{ V}$			0.2	μA
Clamping Voltage	V_C	$IPP = 1\text{A}$ (8 x 20μs pulse)			5	V
Clamping Voltage	V_C	$IPP = 22\text{A}$ (8 x 20μs pulse)			16	V
Junction Capacitance	C_J	$VR = 0\text{V}, f = 1\text{MHz}$		1		pF

TPGC05C

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				5.0	V
Breakdown Voltage	V_{BR}	$I_T = 1\text{mA}$	6		8	V
Reverse Leakage Current	I_R	$V_{RWM} = 5.0\text{ V}$			0.2	μA
Clamping Voltage	V_C	$IPP = 1\text{A}$ (8 x 20μs pulse)			9	V
Clamping Voltage	V_C	$IPP = 18\text{A}$ (8 x 20μs pulse)			19	V
Junction Capacitance	C_J	$VR = 0\text{V}, f = 1\text{MHz}$		1		pF

Electrical Characteristics ($T_A=25^\circ C$ unless otherwise specified)
www.sot23.com.tw

TPGC08C

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				8.0	V
Breakdown Voltage	V_{BR}	$I_T = 1mA$	8.5			V
Reverse Leakage Current	I_R	$V_{RWM} = 8 V$			0.2	μA
Clamping Voltage	V_C	$I_{PP} = 1A (8 \times 20\mu s \text{ pulse})$			13	V
Clamping Voltage	V_C	$I_{PP} = 18A (8 \times 20\mu s \text{ pulse})$			19.5	V
Junction Capacitance	C_J	$VR = 0V, f = 1MHz$		1		pF

TPGC12C

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				12.0	V
Breakdown Voltage	V_{BR}	$I_T = 1mA$	13.3			V
Reverse Leakage Current	I_R	$V_{RWM} = 12 V$			0.2	μA
Clamping Voltage	V_C	$I_{PP} = 1A (8 \times 20\mu s \text{ pulse})$			18	V
Clamping Voltage	V_C	$I_{PP} = 12A (8 \times 20\mu s \text{ pulse})$			29	V
Junction Capacitance	C_J	$VR = 0V, f = 1MHz$		1		pF

TPGC15C

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				15.0	V
Breakdown Voltage	V_{BR}	$I_T = 1mA$	16.7			V
Reverse Leakage Current	I_R	$V_{RWM} = 15 V$			0.2	μA
Clamping Voltage	V_C	$I_{PP} = 1A (8 \times 20\mu s \text{ pulse})$			22	V
Clamping Voltage	V_C	$I_{PP} = 10A (8 \times 20\mu s \text{ pulse})$			32	V
Junction Capacitance	C_J	$VR = 0V, f = 1MHz$		1		pF

Electrical Characteristics ($T_A=25^\circ C$ unless otherwise specified)
www.sot23.com.tw

TPGC18C


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				18.0	V
Breakdown Voltage	V_{BR}	$I_T = 1mA$	20			V
Reverse Leakage Current	I_R	$V_{RWM} = 18 V$			0.2	μA
Clamping Voltage	V_C	$I_{PP} = 1A (8 \times 20\mu s \text{ pulse})$			26	V
Clamping Voltage	V_C	$I_{PP} = 10A (8 \times 20\mu s \text{ pulse})$			35	V
Junction Capacitance	C_J	$VR = 0V, f = 1MHz$		1		pF

TPGC24C


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				24.0	V
Breakdown Voltage	V_{BR}	$I_T = 1mA$	26.7			V
Reverse Leakage Current	I_R	$V_{RWM} = 24 V$			0.2	μA
Clamping Voltage	V_C	$I_{PP} = 1A (8 \times 20\mu s \text{ pulse})$			43	V
Clamping Voltage	V_C	$I_{PP} = 8A (8 \times 20\mu s \text{ pulse})$			55	V
Junction Capacitance	C_J	$VR = 0V, f = 1MHz$		1		pF

TPGC30C


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				30.0	V
Breakdown Voltage	V_{BR}	$I_T = 1mA$	33.3			V
Reverse Leakage Current	I_R	$V_{RWM} = 30 V$			0.2	μA
Clamping Voltage	V_C	$I_{PP} = 1A (8 \times 20\mu s \text{ pulse})$			50	V
Clamping Voltage	V_C	$I_{PP} = 6A (8 \times 20\mu s \text{ pulse})$			75	V
Junction Capacitance	C_J	$VR = 0V, f = 1MHz$		1		pF

Typical Performance Characteristics (TA=25°C unless otherwise Specified)


Peak Pulse Power vs. Pulse Time



IEC61000-4-2 Pulse Waveform




Power Derating Curve



8 X 20μs Pulse Waveform




SOD-323 Package Outline Drawing



SYM	DIMENS			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	1.50	1.80	0.060	0.071
B	1.20	1.40	0.045	0.054
C	2.30	2.70	0.090	0.107
D	-	1.10	-	0.043
E	0.30	0.40	0.012	0.016
F	0.10	0.25	0.004	0.010
H	-	0.10	-	0.004

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	
	INCHES	INCHES
A	3.15	0.120
B	0.80	0.031
C	0.80	0.031