

PRODUCT-DETAILS

# SR2-SRN4315K

## SR2-SRN4315K Control and Automation Board



### General Information

Extended Product Type	SR2-SRN4315K
Product ID	SRN4315K
EAN	8015646753212
Catalog Description	SR2-SRN4315K Control and Automation Board
Long Description	Enclosure with blind door + back plate 400x300x150mm (HxWxD)

### Technical

Suitable for Product Class	SR2
Number of Flange Openings	2
Cover Plate Type	Door
Enclosure Type NEMA	Type3R
Mounting Type	Surface mounted (plaster)
Door Type	Single
Surface Finishing	Powder coating
Construction Material	Galvanized steel
Door Surface Finishing	Opaque
Housing Material	Steel
RAL Number	RAL 7035 - Light Grey
Color	Grey
Thickness	Cabinet Plate 1.2 mm Door Plate 1.2 mm

---

## Environmental

Degree of Protection	IP65
Protection Class	Grounded
Environmental Information	1STC804013D0203

---



---

## Dimensions

Product Net Width	300 mm
Product Net Height	400 mm
Product Net Depth / Length	150 mm
Product Net Weight	7.1 kg
Built-In Depth (t <sub>2</sub> )	132 mm

---



---

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	0.315 m
Package Level 1 Height	0.170 m
Package Level 1 Depth / Length	0.425 m
Package Level 1 Gross Weight	7.500 kg
Package Level 1 EAN	8015646753212

---



---

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85381000
Country of Origin	Italy (IT)

---



---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	No declaration needed
Environmental Information	1STC804013D0203
Instructions and Manuals	1STM6041230001
RoHS Information	1STC860027

---



---

## Popular Downloads

Data Sheet, Technical Information	1STC804013D0203
Instructions and Manuals	1STM6041230001

---



---

## Classifications

ETIM 7	EC000058 - Empty cabinet
ETIM 8	EC000058 - Empty cabinet
WEEE Category	Product Not in WEEE Scope

---

Object Classification  
Code

U

---

## Categories

---

Low Voltage Products and Systems → Enclosures → General Purpose Enclosures → Metal Enclosures → SR2

