

**AMPLIMITE**


TE Part # 5-1393738-9

TE Internal #: 5-1393738-9

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



Accessory Type: **Backshell**

Cable Clamp Type: **Two-Piece RFI/EMI Shield**

Number of Positions: **9**

Shell Size: **1**

Shielded: **Yes**

**Features**

**Product Type Features**

Grommets	Without
Slide Latch	Without
Product Type	Backshell/Cable Clamp
Accessory Type	Backshell
Shell Size	1
Shielded	Yes
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Number of Positions	9
---------------------	---

**Body Features**

Shield Plating Material	Nickel over Copper
Cable Clamp Material	Thermoplastic with Shielding Plates
Color	Gray
Shield Plating Finish	Bright
Cable Clamp Type	Two-Piece RFI/EMI Shield



Cable Exit Angle 37.5

**Mechanical Attachment**

Screw & Hole Thread Size 14702

**Dimensions**

Cable Insulation Diameter 4 – 8 mm [.158 – .315 in]

**Packaging Features**

Packaging Quantity 200

Packaging Method Box

**Other**

Comment Knurled screws, cable bushing (grommet) and contact tube must be ordered separately.

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006 Current ECHA Candidate List: JAN 2019 (197)  
 Not Yet Reviewed


Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


## Customers Also Bought




TE Part #5-1393561-1  
V42254A6207L 1=SUB D  
KABELTUE




TE Part #6-1393738-1  
V42254A6004G125=SUB D  
GEHAEUSE



TE Part #6-1393738-0  
V42254A6004G115=SUB D  
GEHAEUSE



TE Part #4-1393561-9  
V42254A6206L 1=SUB D  
KABELTUE



TE Part #3-1393561-4  
V42254A6106L 1=SUB D  
KONTAKTH




TE Part #2120321-1  
SIGNAL HOUSING 5 POS



TE Part #1103427-2  
HC26.Bu.4.C.5,2



TE Part #926887-7  
UNIV.M-N-L.PIN



TE Part #163091-8  
062 SOC.ASS. TYP3+

## Documents

### Product Drawings

V42254A6004G109=SUB D GEHAEUSE

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1393738-9\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1393738-9\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1393738-9\\_B.3d\\_stp.zip](#)

English



---

**Instruction Sheets**

mounting guideline for d-Sub housings

English

**Instruction Sheet (U.S.)**

English