

## SE30AFB, SE30AFD, SE30AFG, SE30AFJ

Vishay General Semiconductor

RoHS COMPLIANT

HALOGEN

**FREE** 

## **Surface Mount ESD Capability Rectifiers**



SlimSMA (DO-221AC)



### **DESIGN SUPPORT TOOLS AVAILABLE**



PRIMARY CHARACTERISTICS					
I <sub>F(AV)</sub>	3.0 A				
$V_{RRM}$	100 V, 200 V, 400 V, 600 V				
I <sub>FSM</sub>	40 A				
$V_F$ at $I_F = 3.0$ A $(T_A = 125  ^{\circ}C)$	0.86 V				
I <sub>R</sub>	10 μA				
T <sub>J</sub> max.	175 °C				
Package	SlimSMA (DO-221AC)				
Circuit configuration	Single				

#### **FEATURES**

- Very low profile typical height of 0.95 mm
- · Ideal for automated placement
- Oxide planar chip junction
- Low forward voltage drop, low leakage current
- ESD capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912">www.vishay.com/doc?99912</a>

#### TYPICAL APPLICATIONS

General purpose, power line polarity protection, in both consumer and automotive applications.

### **MECHANICAL DATA**

Case: SlimSMA (DO-221AC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and

AEC-Q101 qualified **Terminals:** matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102 M3 suffix meets JESD 201 class 2 whisker test, HM3 suffix

meets JESD 201 class 2 whisker test, Hivi3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes the cathode end

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	SE30AFB	SE30AFD	SE30AFG	SE30AFJ	UNIT
Device marking code		S3B	S3D	S3G	S3J	
Maximum repetitive peak reverse voltage	$V_{RRM}$	100	200	400	600	V
Maximum DC forward current	I <sub>F</sub> <sup>(1)</sup>	3.0				А
Waxiiridiii Do Iorward Current	I <sub>F</sub> <sup>(2)</sup>	1.4				
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	40			Α	
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	T <sub>J</sub> , T <sub>STG</sub> -55 to +175			°C	

#### Notes

- (1) Mounted on 15 mm x 15 mm pad areas, 2 oz. FR4 PCB
- (2) Free air, mounted on recommended copper pad area



# SE30AFB, SE30AFD, SE30AFG, SE30AFJ

## Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT
Instantaneous forward voltage	I <sub>F</sub> = 1.5 A	T <sub>A</sub> = 25 °C		0.91	=	V
	$I_F = 3.0 \text{ A}$		V <sub>E</sub> (1)	0.97	1.1	
	I <sub>F</sub> = 1.5 A	- T <sub>A</sub> = 125 °C	v <sub>F</sub> (:/	0.79	-	
	I <sub>F</sub> = 3.0 A			0.86	0.98	
Reverse current	Rated V <sub>R</sub>	$T_A = 25  ^{\circ}\text{C}$ $T_A = 125  ^{\circ}\text{C}$ $I_R^{(2)}$	1 (2)	-	10	
	naieu v <sub>R</sub>		13	100	μA	
Typical reverse recovery time	$I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A}, I_{rr} = 0.25 \text{ A}$		t <sub>rr</sub>	1.5	-	μs
Typical junction capacitance	4.0 V, 1 MHz		CJ	19	=	pF

#### Notes

(1) Pulse test: 300 µs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width  $\leq$  40 ms

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)						
PARAMETER SYMBOL SE30AFB SE30AFG SE30AFJ UN						UNIT
Typical thermal resistance		125				°C/W
Typical triefmal resistance	R <sub>0JM</sub> (2)	12				C/ VV

#### **Notes**

 $^{(1)}$  Free air, mounted on recommended PCB, 1 oz. pad area; thermal resistance  $R_{\theta JA}$  - junction to ambient

(2) Mounted on 15 mm x 15 mm pad areas, 2 oz. FR4 PCB; R<sub>0JM</sub> - junction to mount

IMMUNITY TO ELECTRICAL STATIC DISCHARGE TO THE FOLLOWING STANDARDS (T <sub>A</sub> = 25 $^{\circ}$ C unless otherwise noted)						
STANDARD TEST TYPE TEST CONDITIONS SYMBOL CLASS VALUE						
AEC-Q101-001 Human body model (contact mode) $C = 100 \text{ pF}, R = 1.5 \text{ k}\Omega$ $V_C$ H3B $> 8 \text{ kV}$						

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
SE30AFJ-M3/6A	0.032	6A	3500	7" diameter plastic tape and reel	
SE30AFJ-M3/6B	0.032	6B	14 000	13" diameter plastic tape and reel	
SE30AFJHM3/6A (1)	0.032	6A	3500	7" diameter plastic tape and reel	
SE30AFJHM3/6B (1)	0.032	6B	14 000	13" diameter plastic tape and reel	

### Note

(1) AEC-Q101 qualified

### Vishay General Semiconductor

### **RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25$ °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Typical Junction Capacitance




Fig. 6 - Transient Thermal Impedance

# SE30AFB, SE30AFD, SE30AFG, SE30AFJ

## Vishay General Semiconductor





Fig. 7 - Thermal Resistance Junction to Ambient vs. Copper Pad Areas

### **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

#### SlimSMA (DO-221AC)





### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Vishay:

<u>SE30AFJ-M3/6A</u> <u>SE30AFGHM3/6A</u> <u>SE30AFD-M3/6A</u> <u>SE30AFB-M3/6A</u> <u>SE30AFJHM3/6A</u> <u>SE30AFG-M3/6A</u> <u>SE30AFDHM3/6A</u> <u>SE30AFBHM3/6A</u> <u>SE30AFDHM3/6B</u> <u>SE30AFGHM3/6B</u> <u>SE30AFB-M3/6B</u> <u>SE30AFBHM3/6B</u> <u>SE30AFJ-M3/6B</u> SE30AFJ-M3/6B SE30AFD-M3/6B SE30AFG-M3/6B