


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. (mm)	MAX. (mm)									
BT1M	.06 (1.5)	0.90 (23)	.036 (0.9)	.095 (2.4)	.110 (2.8)	.156 (4.0)	.172 (4.4)	4.0 (102)	18 (80)	MINIATURE	.05 (22)
BT1.5M	.06 (1.5)	1.5 (38)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	6.3 (160)	18 (80)	MINIATURE	.09 (43)
BT2M	.06 (1.5)	2.0 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	7.9 (201)	18 (80)	MINIATURE	.12 (53)
BT4M	.06 (1.5)	4.00 (102)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	14.2 (361)	18 (80)	MINIATURE	.21 (93)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS
 DOME-TOP Barb Ty CABLE TIES
 BT SERIES

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± .10 (2.5) (.XXX) ± .020 (.51)
 (.XX) ± .02 (.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN
 IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
 PMH

MAT'L:

SCALE
 NONE

DATE
 6-24-93

NYLON 6.6

DRAWING NO.
 BT-0037
 SHEET 1 OF 3

DWG
 A
 SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
10	5/2/06	JABO		REMOVED STRAIGHT TIP REFERENCE & TIP STYLE COLUMN	0037	10		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[BT1M-M](#) [BT2M-M0](#) [BT1.5M-M](#) [BT4M-M0](#) [BT4M-M](#) [BT1M-M0](#) [BT2M-M](#) [BT1.5M-M0](#) [BT1M-M1](#) [BT1M-M10](#)
[BT1M-M2](#) [BT1M-M30](#) [BT1.5M-M69](#) [BT1M-M300](#) [BT2M-M5](#) [BT2M-M4Y](#) [BT1M-M5](#) [BT2M-M2](#) [BT2M-M6](#) [BT2M-M3](#)
[BT1M-M69](#) [BT2M-M8](#) [BT1M-M7](#) [BT1M-M4Y](#) [BT1M-M3](#) [BT1M-M8](#) [BT1M-M6](#)