


FEATURES

- ◆ 3 current-limited and short-circuit-proof push-pull drivers
- ◆ Built-in adaption to 75 Ω characteristic impedance
- ◆ High driver current of 300 mA at 24 V typ.
- ◆ Low saturation voltage up to 30 mA load current
- ◆ Short switching times and high slew rates by npn circuitry
- ◆ Wide driver supply range $V_B = 4.5\text{ V to }30\text{ V}$
- ◆ Internal free-wheeling diodes to V_B and GND
- ◆ Schmitt trigger inputs with integrated pull-up current sources
- ◆ Inputs compatible to TTL and CMOS
- ◆ Inverting and non-inverting driver mode
- ◆ Bus capability due to Tri-State switching
- ◆ Compatible to EIA standard RS-422
- ◆ Thermal shutdown with hysteresis
- ◆ Short-circuit-proof OC error output reports thermal shutdown or undervoltage at V_{CC} or V_B
- ◆ Driver disabled in case of fault
- ◆ extended temperature range of up to 130 °C in TSSOP20tp 4.4 mm package


APPLICATIONS

- ◆ 24 V signal transfer
- ◆ Line driver in PLC environment


PACKAGES



SO20




TSSOP20
thermal pad



SO16W

BLOCK DIAGRAM



iC-WE

3-CHANNEL 75 Ω LINE DRIVER



Rev D1, Page 2/10

DESCRIPTION

The iC-WE is a high-speed monolithic line driver circuit for three independent channels with built-in characteristic impedance adaption for 75Ω lines. The push-pull outputs are designed for a high driver power of typ. 300mA at 24V. They are current-limited and short-circuit protected by thermal shut-down at over-temperature. Clamp diodes to VB and to GND protect the IC outputs against echoes of mismatched lines and against damage due to ESD according to MIL-STD-883.


All inputs are Schmitt triggers and contain current sources from the 5V supply VCC which select a defined High Level without external wiring. Clamp diodes to VCC and to GND furnish ESD protection.

Using the INVERT input it is possible to switch all channels to inverting or non-inverting operation. This enables a data transmission with balanced line activation using two iC-WE devices. For bus applications the final stages can be forced to a high impedance state using the TRI-State input.


The circuit monitors supply voltages VB and VCC as well as the chip temperature and switches all final stages to high impedance in the event of a fault. The NER output which is constructed as an open collector and is also short-circuit proof reports the fault via the connected line. The error input TNER can be linked to message outputs of other ICs and allows iC-WE to report a system fault message. If the supply voltage VCC cancels, NER becomes highly resistive.

PACKAGES SO20, SO16W, TSSOP20 to JEDEC Standard

PIN CONFIGURATION, top view




SO20



SO16W

(low power applications only)

(scale 2:1)



TSSOP20tp 4.4 mm

PIN FUNCTIONS

| Name | Function | Name | Function |
|------|------------------------------------|------|-----------------------------------|
| VCC | +5 V (± 10 %) Input Supply Voltage | VB | +4.5..+30 V Driver Supply Voltage |
| E1 | Channel 1 Input | A1 | Channel 1 Output |
| E2 | Channel 2 Input | A2 | Channel 2 Output |
| E3 | Channel 3 Input | A3 | Channel 3 Output |
| TRI | Tristate Input, high active | NER | Error Output, low active |
| INV | Invert Mode Input, high active | GND | Ground |
| TNER | Error Input | | |

To enhance heat removal, the TSSOP20 package offers a large area pad to be soldered (a connection is only permitted to GND).

iC-WE

3-CHANNEL 75 Ω LINE DRIVER



Rev D1, Page 3/10

ABSOLUTE MAXIMUM RATINGS

Values beyond which damage may occur; device operation is not guaranteed.

| Item | Symbol | Parameter | Conditions | Fig. | | | Unit |
|------|--------|--|---|------|------|------|------|
| | | | | | Min. | Max. | |
| G001 | VCC | Supply Voltage | | | 0 | 7 | V |
| G002 | VB | Driver Supply Voltage | | | 0 | 32 | V |
| G003 | I(A) | Output Current in A1..3 | | | -800 | 800 | mA |
| G004 | I(E) | Input Current in E1..3, INV, TRI, TNER | | | -4 | 4 | mA |
| G005 | V(NER) | Voltage at NER | | | | 32 | V |
| G006 | I(NER) | Current in NER | | | | 25 | mA |
| E001 | Vd() | ESD Susceptibility at all pins | MIL-STD-883, Method 3015, HBM 100 pF discharged through 1.5 kΩ | | | 2 | kV |
| TG1 | Tj | Operating Junction Temperature | | | -40 | 165 | °C |
| TG2 | Ts | Storage Temperature Range | | | -40 | 150 | °C |

THERMAL DATA

Operating Conditions: VB = 4.5..30 V, VCC = 5 V ± 10 %

| Item | Symbol | Parameter | Conditions | Fig. | | | | Unit |
|------|--------|--|--|------|------|------|------|------|
| | | | | | Min. | Typ. | Max. | |
| T1 | Ta | Operating Ambient Temperature Range (extended range to -40 °C on request) | iC-WE SO16W | | -25 | | 125 | °C |
| | | | iC-WE SO20, iC-WE TSSOP20 | | -25 | | 130 | °C |
| T2 | Rthja | Thermal Resistance SO20 Chip to Ambient | surface mounted with ca. 2 cm ² heat sink at leads (see Demo Board) | | | 35 | 45 | K/W |
| T3 | Rthja | Thermal Resistance SO16W Chip to Ambient | surface mounted with ca. 2 cm ² heat sink at leads | | | 55 | 75 | K/W |
| T4 | Rthja | Thermal Resistance TSSOP20 Chip to Ambient | surface mounted, thermal pad soldered to ca. 2 cm ² heat sink | | | 30 | 40 | K/W |

All voltages are referenced to ground unless otherwise noted.

All currents into the device pins are positive; all currents out of the device pins are negative.

ELECTRICAL CHARACTERISTICS

Operating Conditions:

VB = 4.5..30 V, VCC = 5 V ± 10 %, Tj = -40..125 °C, unless otherwise noted

| Item | Symbol | Parameter | Conditions | Tj °C | Fig. | | | | Unit |
|-----------------------------|----------|---|---|------------------------|------|------------------|----------------------|-----------------------------|----------------------|
| | | | | | | Min. | Typ. | Max. | |
| Total Device | | | | | | | | | |
| 001 | VCC | Permissible Supply Voltage Range | | | | 4.5 | | 5.5 | V |
| 002 | I(VCC) | Supply Current in VCC | | -40 27 80 125 | | 8 8 8 8 | 15 14 13 12 | 24 23 21 19 | mA mA mA mA |
| 003 | VB | Permissible Driver Supply Voltage Range | | | | 4.5 | | 30 | V |
| 004 | I(VB)lo | Supply Current in VB | A1..3 = lo | -40 27 80 125 | | 8 6 5 4 | 16 14 12 11 | 24 21 18 15 | mA mA mA mA |
| 005 | I(VB)hi | Supply Current in VB | A1..3 = hi, I(A1..3) = 0 | -40 27 80 125 | | 7 6 4 3 | 11 9 7 5 | 14 12 10 8 | mA mA mA mA |
| 006 | I(VB)Tri | Supply Current in VB, Outputs Tri-State | TRI = hi, V(A1..3) = -0.3..VB + 0.3 V | -40 | | | | 1.2 1.4 | mA mA |
| Driver Outputs A1..3 | | | | | | | | | |
| 101 | Vs()lo | Saturation Voltage lo | I(A) = 10 mA | -40 27 80 125 | | | | 1.15 1.05 1.05 1.0 | V V V V |
| 102 | Vs()lo | Saturation Voltage lo | I(A) = 30 mA | -40 27 80 125 | | | | 1.55 1.5 1.5 1.4 | V V V V |
| 103 | Vs()hi | Saturation Voltage hi | Vs()hi = VB - V(A), I(A) = -10 mA | -40 27 80 125 | | | | 1.1 1.0 1.0 0.9 | V V V V |
| 104 | Vs()hi | Saturation Voltage hi | Vs()hi = VB - V(A), I(A) = -30 mA | -40 27 80 125 | | | | 1.45 1.4 1.4 1.3 | V V V V |
| 105 | Isc()hi | Short-Circuit Current hi | VB = 30 V, V(A) = 0 | | | -800 | -500 | -300 | mA |
| 106 | Isc()lo | Short-Circuit Current lo | VB = 30 V, V(A) = VB | | | 300 | 500 | 800 | mA |
| 107 | Rout() | Output Impedance | VB = 30 V, V(A) = 15 V | | | 40 | 75 | 100 | Ω |
| 108 | SR()hi | Slew-Rate hi | VB = 30 V, CL = 100 pF | | | | 250 | | V/μs |
| 109 | SR()lo | Slew-Rate lo | VB = 30 V, CL = 100 pF | | | | 1500 | | V/μs |
| 110 | I0() | Off-State Current | TRI = hi, V(A) = 0..VB | | | -50 | | 50 | μA |
| 111 | Vc()hi | Clamp Voltage hi | Vc()hi = V(A) - VB, TRI = hi, I(A) = 100 mA | | | 0.4 | | 1.5 | V |
| 112 | Vc()lo | Clamp Voltage lo | TRI = hi, I(A) = -100 mA | | | -1.5 | | -0.4 | V |
| Inputs E1..3 | | | | | | | | | |
| 201 | Vt()hi | Threshold Voltage hi | | | | | | 40 | %VCC |
| 202 | Vt()lo | Threshold Voltage lo | | | | 30 | | | %VCC |
| 203 | Vt()hys | Input Hysteresis | Vhys = Vt()hi - Vt()lo | | | 35 | 110 | | mV |

iC-WE

3-CHANNEL 75 Ω LINE DRIVER



Rev D1, Page 5/10

ELECTRICAL CHARACTERISTICS

Operating Conditions:

$V_B = 4.5..30\text{ V}$, $V_{CC} = 5\text{ V} \pm 10\%$, $T_j = -40..125\text{ }^\circ\text{C}$, unless otherwise noted

| Item | Symbol | Parameter | Conditions | Tj °C | Fig. | | | | Unit |
|-----------------------------------|------------------------------------|--|---|-----------|------|------------|------|-------------------|----------------|
| | | | | | | Min. | Typ. | Max. | |
| Inputs E1..3 (continued) | | | | | | | | | |
| 204 | I _{pu} () | Pull-Up Current | $V(E) = 0..V_{CC} - 1\text{ V}$ | | | 40 | | 280 | μA |
| 205 | V _c () _{hi} | Clamp Voltage hi | $V_c(E)_{hi} = V(E) - V_{CC}$, I(E) = 4 mA | | | 0.4 | | 1.25 | V |
| 206 | V _c () _{lo} | Clamp Voltage lo | I(E) = -4 mA | | | -1.25 | | -0.4 | V |
| 207 | t _p (E-A) | Propagation Delay E → A | | 80 125 | | | 200 | 300 330 330 | ns ns ns |
| 208 | Δt _p () _{INV} | Delay Skew E → A for INV = lo vs. INV = hi | | | | | 25 | 150 | ns |
| Error Detection | | | | | | | | | |
| 301 | V _{CCcon} | Turn-on Threshold VCC | | | | 4.0 | | 4.49 | V |
| 302 | V _{CCcoff} | Undervoltage Threshold at VCC | decreasing Supply VCC | | | 3.8 | | 4.30 | V |
| 303 | V _{CChys} | Hysteresis | $V_{CChys} = V_{CCcon} - V_{CCcoff}$ | | | 130 | | | mV |
| 304 | V _{Bon} | Turn-on Threshold VB | | -40 | | 4.0 4.0 | | 4.49 4.6 | V V |
| 305 | V _{Boff} | Undervoltage Threshold at VB | decreasing Supply VB | | | 3.8 | | 4.35 | V |
| 306 | V _{Bhys} | Hysteresis | $V_{bhys} = V_{bon} - V_{boff}$ | | | 130 | | | mV |
| 307 | V _{CC} | Supply Voltage VCC for NER Operation | | | | 2.6 | | 5.5 | V |
| 308 | V _s (NER) | Saturation Voltage lo at NER | I(NER) = 5 mA | | | | | 0.7 | V |
| 309 | I _{sc} (NER) | Short-Circuit Current lo in NER | $V(NER) = 0..30\text{ V}$ | | | 5 | | 30 | mA |
| 310 | I _o (NER) | Collector Off-State Current in NER | $V(NER) = 0..30\text{ V}$, NER = off or $V_{CC} < 0.3\text{ V}$ | | | | | 10 | μA |
| 311 | T _{off} | Thermal Shutdown Threshold | | | | 150 | | 175 | °C |
| 312 | T _{on} | Thermal Lock-on Threshold | decreasing temperature | | | 125 | | 160 | °C |
| 313 | T _{hys} | Thermal Shutdown Hysteresis | $T_{hys} = T_{off} - T_{on}$ | | | | 20 | | °C |
| Mode Select INV, TRI, TNER | | | | | | | | | |
| 401 | V _t () _{hi} | Threshold Voltage hi | | | | | | 40 | %VCC |
| 402 | V _t () _{lo} | Threshold Voltage lo | | | | 30 | | | %VCC |
| 403 | V _t () _{hys} | Input Hysteresis | $V_t(hys) = V_t(hi) - V_t(lo)$ | | | 40 | 90 | | mV |
| 404 | I _{pu} () | Pull-Up Current | $V() = 0..V_{CC} - 0.8\text{ V}$ | | | 35 | 100 | 250 | μA |
| 405 | V _c () _{hi} | Clamp Voltage hi | $V_c(hi) = V() - V_{CC}$, I() = 4 mA | | | 0.4 | | 1.25 | V |
| 406 | V _c () _{lo} | Clamp Voltage lo | I() = -4 mA | | | -1.25 | | -0.4 | V |
| 407 | t _{pz} (TRI-A) | Propagation Delay TRI → A (A: lo, hi → Tri-State) | R _L (A) = 1 kΩ, R _L (V _{CC} , A) = 1 kΩ | | | | | 5 | μs |
| 408 | t _p (INV-A) | Propagation Delay INV → A | | | | | | 5 | μs |
| 409 | t _p (TNER- NER) | Propagation Delay TNER → NER | | | | | | 5 | μs |

APPLICATIONS INFORMATION

Line drivers for automation & control equipment connect digital signals with TTL or CMOS levels to 24 V systems via cables. Due to possible short-circuits, the drivers are current-limited and lock out in the event of over-temperature.

The maximum permissible signal frequency depends on the capacitive load of the outputs (cable length) or the consequential power dissipation in the iC-WE.

Except for saturation voltages, the maximum output voltage corresponds to supply voltage V_B when the output is open. Fig. 1 shows the typical DC output characteristic of a driver as a function of the load. The differential output resistance is about 75 Ω in broad ranges.

Every open-circuited input is set to high level by an internal pull-up current source; an additional inter-connection with VCC enhances the interference immunity. An input can be set to low level in response to a short-circuit or a resistance (<7.5 kΩ) to GND.




Fig. 1: Influence of load on output voltage

LINE EFFECTS

In PLC systems, data transmission with 24 V signals is generally conducted without a line termination with the characteristic impedance. A mismatched line end produces reflections which travel back and forth if there is no line adapter at the driver end either. The transmission is disrupted in case of high-speed pulse trains.

In the iC-WE, signal reflection is prevented by an integrated characteristic impedance adapter, as shown in Fig. 2.




Fig. 2: Reflections due to open line end

During a pulse transmission the amplitude at the output of the iC-WE initially only increases to about one half the level of supply voltage V_B since the internal resistance of the driver and the line characteristic impedance form a voltage divider. A wave with this amplitude is injected into the line and experiences a total reflection at the high impedance end of the line following a delay based on the length of the cable. The open or high impedance terminated end of the line exhibits a voltage maximum with double amplitude since outgoing and reflected wave are superimposed.




Fig. 3: Pulse transmission and transit times

Following a further delay the reflected wave also increases the driver output to twice the amplitude of the wave initially injected, possibly capped by the integrated diode suppressor circuit. The integrated characteristic impedance adaption in the iC-WE prevents another reflection and the voltage achieved is maintained along and at the end of the line.

A mismatch between the iC-WE and the line influences the level of the initially injected wave and produces reflections at the driver end. The output signal may have a number of graduations. Nonetheless, lines with characteristic impedances in the range 40 to 150 Ω permit satisfactory transmissions.

Fig. 3 shows the transmission of a short pulse of 1.5 μs. The signal delay to the end of the cable (here 100 m) is markedly longer than the transit time in the iC-WE driver.

iC-WE

3-CHANNEL 75 Ω LINE DRIVER

EXAMPLE 1: Balanced data transmission over twisted-pair cables

For balanced data transmission two iC-WE devices can be operated in parallel at the inputs with different programming of the individual INVERT input. The OC error outputs NER are linked for the system fault message.




Fig. 4: Balanced data transmission

EXAMPLE 2: Incremental encoder

Fig. 5 shows the iC-WE being used in an optical encoder system together with the iC-Haus incremental encoder iC-WT.

The iC-WT device is an evaluating IC for photodiode arrays used in incremental lengths and angle measuring systems. It preprocesses the sensor signals for transmission with line driver iC-WE. At the receive end the programmable logic controller (PLC) interface can be via optocoupler.

The preprocessed sensor signals are transmitted over cable by the iC-WE with asymmetrical activation. A high interference immunity is achieved as a result of the high output amplitude and the integrated characteristic adaption of the iC-WE.

The 24 V power supply is conducted over the cable from the PLC end. A voltage regulator generates the 5 V supply to the encoder system. It is favourable to use the iC-WD switching regulator device instead of a conventional voltage regulator. This switched-mode power supply IC operates from 8 to 30 V input voltage and contains two 5 V post regulators. Analog and digital devices can thus receive separate supply voltages.

iC-WE

3-CHANNEL 75 Ω LINE DRIVER

The error input TNER on the iC-WE can be utilized to conduct a fault signal from the incremental encoder to the output NER and then to the receiver.

For protection against voltage peaks from the cable, the state input TRI is wired to the RC combination R1, R2 and C5, which can be dimensioned for levels of up to 30 V at the PLC.




Fig. 5: Line driver iC-WE in the incremental encoder

PRINTED CIRCUIT BOARD LAYOUT

The iC-WE's 8 GND terminals (pins 4-7 and 14-17) simultaneously function as thermal conductors and must be soldered to copper tracks with the greatest possible area of the PCB to ensure proper heat dissipation.

Blocking capacitors to smooth the local IC supply voltages must be connected to VCC, V_B and GND pins at the shortest possible intervals. C1 on the regulator in Fig. 3 is only necessary if the voltage regulator is more than about 3 cm away from the other ICs. C3 should not be less than 1 μF in order to block the 24 V supply.

iC-WE

3-CHANNEL 75 Ω LINE DRIVER

DEMO BOARD

The device iC-WE with SO20 package is equipped with a Demo Board for test purposes. Figures 6 to 8 show the wiring as well as the top and bottom layout of the test PCB.




Fig. 6: Schematic diagram of the Demo Board




Fig. 7: Demo Board (components side)




Fig. 8: Demo Board (solder dip side)

This specification is for a newly developed product. iC-Haus therefore reserves the right to modify data without further notice. Please contact us to ascertain the current data. The data specified is intended solely for the purpose of product description and is not to be deemed guaranteed in a legal sense. Any claims for damage against us - regardless of the legal basis - are excluded unless we are guilty of premeditation or gross negligence.

We do not assume any guarantee that the specified circuits or procedures are free of copyrights of third parties.

Copying - even as an excerpt - is only permitted with the approval of the publisher and precise reference to source.

ORDERING INFORMATION

| Type | Package | Order designation |
|---------------|-----------------------------------|--|
| iC-WE | SO20 SO16W TSSOP20tp 4.4 mm | iC-WE SO20 iC-WE SO16W iC-WE TSSOP20 |
| WE Demo Board | | WE DEMO |

For information about prices, terms of delivery, options for other case types, etc., please contact:

iC-Haus GmbH
Am Kuemmerling 18
D-55294 Bodenheim
GERMANY

Tel +49-6135-9292-0
Fax +49-6135-9292-192
<http://www.ichaus.com>