

Data Sheet

Dual-Channel Digital Isolators

ADuM1200/ADuM1201

FEATURES

Narrow body, RoHS-compliant, SOIC 8-lead package Low power operation

- **5 V operation**
 - 1.1 mA per channel maximum at 0 Mbps to 2 Mbps
 - 3.7 mA per channel maximum at 10 Mbps
 - 8.2 mA per channel maximum at 25 Mbps
- 3 V operation
 - 0.8 mA per channel maximum at 0 Mbps to 2 Mbps
 - 2.2 mA per channel maximum at 10 Mbps
 - 4.8 mA per channel maximum at 25 Mbps

Bidirectional communication

3 V/5 V level translation

High temperature operation: 125°C High data rate: dc to 25 Mbps (NRZ) Precise timing characteristics

3 ns maximum pulse width distortion

3 ns maximum channel-to-channel matching High common-mode transient immunity: >25 kV/µs Safety and regulatory approvals

UL recognition

2500 V rms for 1 minute per UL 1577
CSA Component Acceptance Notice 5A
VDE Certificate of Conformity
DIN V VDE V 0884-10 (VDE V 0884-10): 2006-12
V_{IORM} = 560 V peak

Qualified for automotive applications

APPLICATIONS

Size-critical multichannel isolation
SPI interface/data converter isolation
RS-232/RS-422/RS-485 transceiver isolation
Digital field bus isolation
Hybrid electric vehicles, battery monitor, and motor drive

GENERAL DESCRIPTION

The ADuM1200/ADuM1201¹ are dual-channel digital isolators based on the Analog Devices, Inc., *i*Coupler® technology. Combining high speed CMOS and monolithic transformer technologies, these isolation components provide outstanding performance characteristics superior to alternatives, such as optocouplers.

By avoiding the use of LEDs and photodiodes, *i*Coupler devices remove the design difficulties commonly associated with optocouplers.

The typical optocoupler concerns regarding uncertain current transfer ratios, nonlinear transfer functions, and temperature and lifetime effects are eliminated with the simple *i*Coupler digital interfaces and stable performance characteristics. The need for external drivers and other discrete components is eliminated with these *i*Coupler products. Furthermore, *i*Coupler devices consume one-tenth to one-sixth the power of optocouplers at comparable signal data rates.

The ADuM1200/ADuM1201 isolators provide two independent isolation channels in a variety of channel configurations and data rates (see the Ordering Guide). Both devices operate with the supply voltage on either side ranging from 2.7 V to 5.5 V, providing compatibility with lower voltage systems as well as enabling a voltage translation functionality across the isolation barrier. In addition, the ADuM1200/ADuM1201 provide low pulse width distortion (<3 ns for CR grade) and tight channel-to-channel matching (<3 ns for CR grade). Unlike other optocoupler alternatives, the ADuM1200/ADuM1201 isolators have a patented refresh feature that ensures dc correctness in the absence of input logic transitions and during power-up/power-down conditions.

The ADuM1200W and ADuM1201W are automotive grade versions qualified for 125°C operation. See the Automotive Products section for more information.

FUNCTIONAL BLOCK DIAGRAMS




Figure 2. ADuM1201 Functional Block Diagram

 $^{^{\}rm 1}$ Protected by U.S. Patents 5,952,849; 6,873,065; 6,903,578; and 7,075,329.

TABLE OF CONTENTS

Features
Applications1
General Description
Functional Block Diagrams
Revision History
Specifications
Electrical Characteristics—5 V, 105°C Operation
Electrical Characteristics—3 V, 105°C Operation
Electrical Characteristics—Mixed 5 V/3 V or 3 V/5 V, 105°C Operation
Electrical Characteristics—5 V, 125°C Operation 11
Electrical Characteristics—3 V, 125°C Operation 13
Electrical Characteristics—Mixed 5 V/3 V, 125°C Operation
Electrical Characteristics—Mixed 3 V/5 V, 125°C Operation
Package Characteristics
Regulatory Information

insulation and Salety-Related Specifications	15
DIN V VDE V 0884-10 (VDE V 0884-10): 2006-12 Insulation Characteristics	20
Recommended Operating Conditions	20
Absolute Maximum Ratings	21
ESD Caution	21
Pin Configurations and Function Descriptions	22
Typical Performance Characteristics	23
Applications Information	24
PCB Layout	24
Propagation Delay-Related Parameters	24
DC Correctness and Magnetic Field Immunity	24
Power Consumption	25
Insulation Lifetime	25
Outline Dimensions	27
Ordering Guide	27
Automotive Products	26

REVISION HISTORY

9/2016—Rev. J to Rev. K
Changes to Endnote 1 and Endnote 2, Table 919
5/2015—Rev. I to Rev. J
Changes to Table 919
Change to Tracking Resistance (Comparative Tracking Index)
Parameter and Isolation Group Parameter, Table 1020
3/2012—Rev. H to Rev. I
Created Hyperlink for Safety and Regulatory Approvals
Entry in Features Section1
Change to General Description Section1
Change to PCB Layout Section24
Moved Automotive Products Section28
1/2009—Rev. G to Rev. H
Changes to Table 5, Switching Specifications Parameter13
Changes to Table 6, Switching Specifications Parameter15
Changes to Table 7, Switching Specifications Parameter17
9/2008—Rev. F to Rev. G
Changes to Table 919
Changes to Table 1321
Changes to Ordering Guide
3/2008—Rev. E to Rev. F
Changes to Features Section1
Changes to Applications Section1
Added Table 411
Added Table 513
Added Table 615
Added Table 717
Changes to Table 1220
Changes to Table 1321
Added Automotive Products Section26
Changes to Ordering Guide27
11/2007—Rev. D to Rev. E
Changes to Note 11
Added ADuM1200/ADuM1201AR Change vs. Temperature
Parameter3
Added ADuM1200/ADuM1201AR Change vs. Temperature
Parameter5
Added ADuM1200/ADuM1201AR Change vs. Temperature
Parameter8

8/2007—Rev. C to Rev. D
Updated VDE Certification Throughout1
Changes to Features, Note 1, Figure 1, and Figure 21
Changes to Table 3
Changes to Regulatory Information Section10
Added Table 1012
Added Insulation Lifetime Section16
Updated Outline Dimensions
Changes to Ordering Guide18
•
2/2006—Rev. B to Rev. C
Updated Format
Added Note 1
Changes to Absolute Maximum Ratings12
Changes to DC Correctness and Magnetic Field
Immunity Section
9/2004—Rev. A to Rev. B
Changes to Table 510
6/2004—Rev. 0 to Rev. A
Changes to Format
Changes to General Description1
Changes to Electrical Characteristics—5 V Operation3
Changes to Electrical Characteristics—3 V Operation5
Changes to Electrical Characteristics—Mixed 5 V/3 V or
3 V/5 V Operation7

4/2004—Revision 0: Initial Version

SPECIFICATIONS

ELECTRICAL CHARACTERISTICS—5 V, 105°C OPERATION

All voltages are relative to the respective ground; $4.5 \text{ V} \le V_{DD1} \le 5.5 \text{ V}$, $4.5 \text{ V} \le V_{DD2} \le 5.5 \text{ V}$; all minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted; all typical specifications are at $T_A = 25^{\circ}\text{C}$, $V_{DD1} = V_{DD2} = 5 \text{ V}$; this does not apply to the ADuM1200W and ADuM1201W automotive grade products.

Table 1.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
DC SPECIFICATIONS						
Input Supply Current per Channel, Quiescent	I _{DDI (Q)}		0.50	0.60	mA	
Output Supply Current per Channel, Quiescent	I _{DDO (Q)}		0.19	0.25	mA	
ADuM1200 Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		1.1	1.4	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.5	0.8	mA	DC to 1 MHz logic signal freq.
10 Mbps (BR and CR Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		4.3	5.5	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		1.3	2.0	mA	5 MHz logic signal freq.
25 Mbps (CR Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		10	13	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		2.8	3.4	mA	12.5 MHz logic signal freq.
ADuM1201 Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.8	1.1	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.8	1.1	mA	DC to 1 MHz logic signal freq.
10 Mbps (BR and CR Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		2.8	3.5	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		2.8	3.5	mA	5 MHz logic signal freq.
25 Mbps (CR Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		6.3	8.0	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		6.3	8.0	mA	12.5 MHz logic signal freq.
For All Models						
Input Currents	I _{IA} , I _{IB}	-10	+0.01	+10	μΑ	$0 \text{ V} \leq V_{IA}, V_{IB} \leq (V_{DD1} \text{ or } V_{DD2})$
Logic High Input Threshold	V _{IH}	$0.7 (V_{DD1} \text{ or } V_{DD2})$			V	
Logic Low Input Threshold	V _{IL}			0.3 (V _{DD1} or V _{DD2})	V	
Logic High Output Voltages	V _{OAH} , V _{OBH}	$(V_{DD1} \text{ or } V_{DD2}) - 0.1$	5.0		V	$I_{Ox} = -20 \mu A, V_{Ix} = V_{IxH}$
		$(V_{DD1} \text{ or } V_{DD2}) - 0.5$	4.8		V	$I_{Ox} = -4 \text{ mA}, V_{Ix} = V_{IxH}$
Logic Low Output Voltages	V _{OAL} , V _{OBL}		0.0	0.1	V	$I_{Ox} = 20 \mu A$, $V_{Ix} = V_{IxL}$
			0.04	0.1	V	$I_{Ox} = 400 \mu A, V_{Ix} = V_{IxL}$
			0.2	0.4	V	$I_{Ox} = 4 \text{ mA}, V_{Ix} = V_{IxL}$
SWITCHING SPECIFICATIONS						
ADuM1200/ADuM1201AR						C _L = 15 pF, CMOS signal levels
Minimum Pulse Width ²	PW			1000	ns	
Maximum Data Rate ³		1			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	50		150	ns	
Pulse Width Distortion, tplh - tphl 4	PWD			40	ns	
Change vs. Temperature			11		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			100	ns	
Channel-to-Channel Matching ⁶	t _{PSKCD} /t _{PSKOD}			50	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		10		ns	

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
ADuM1200/ADuM1201BR						
Minimum Pulse Width ²	PW			100	ns	
Maximum Data Rate ³		10			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		50	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			15	ns	
Channel-to-Channel Matching				3		
Codirectional Channels ⁶	t _{PSKCD}				ns	
Opposing Directional Channels ⁶	t _{PSKOD}			15	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		2.5		ns	
ADuM1200/ADuM1201CR						
Minimum Pulse Width ²	PW		20	40	ns	
Maximum Data Rate ³		25	50		Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		45	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			15	ns	
Channel-to-Channel Matching				3	ns	
Codirectional Channels ⁶	t _{PSKCD}					
Opposing Directional Channels ⁶	t _{PSKOD}			15	ns	
Output Rise/Fall Time (10% to 90%)	t_R/t_F		2.5		ns	
For All Models						
Common-Mode Transient Immunity						
Logic High Output ⁷	CM _H	25	35		kV/μs	$V_{lx} = V_{DD1}$ or V_{DD2} , $V_{CM} =$
						1000 V, transient magnitude = 800 V
Logic Low Output ⁷	CML	25	35		kV/μs	$V_{lx} = 0 \text{ V}, V_{CM} = 1000 \text{ V},$
Logic Low Output	CIVIL	23	33		Κν/μ3	transient magnitude = 800 V
Refresh Rate	fr		1.2		Mbps	-
Dynamic Supply Current per Channel ⁸						
Input	I _{DDI (D)}		0.19		mA/	
_					Mbps	
Output	I _{DDO (D)}		0.05		mA/ Mbps	

¹ The supply current values are for both channels combined when running at identical data rates. Output supply current values are specified with no output load present. The supply current associated with an individual channel operating at a given data rate can be calculated as described in the Power Consumption section. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See Figure 9 through Figure 11 for total V_{DD1} and V_{DD2} supply currents as a function of data rate for ADuM1200 and ADuM1201 channel configurations.

² The minimum pulse width is the shortest pulse width at which the specified pulse width distortion is guaranteed.

³ The maximum data rate is the fastest data rate at which the specified pulse width distortion is quaranteed.

 $^{^4}$ t_{PHL} propagation delay is measured from the 50% level of the falling edge of the V_{Ix} signal to the 50% level of the falling edge of the V_{Ox} signal. t_{PLH} propagation delay is measured from the 50% level of the rising edge of the V_{Ix} signal to the 50% level of the V_{Ox} signal.

⁵ t_{PSK} is the magnitude of the worst-case difference in t_{PHL} and/or t_{PLH} that is measured between units at the same operating temperature, supply voltages, and output load within the recommended operating conditions.

⁶ Codirectional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on the same side of the isolation barrier. Opposing directional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on opposing sides of the isolation barrier.

 $^{^{7}}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining V₀ > 0.8 V_{DD2}. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining V₀ < 0.8 V. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

⁸ Dynamic supply current is the incremental amount of supply current required for a 1 Mbps increase in the signal data rate. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See the Power Consumption section for guidance on calculating per-channel supply current for a given data rate.

ELECTRICAL CHARACTERISTICS—3 V, 105°C OPERATION

All voltages are relative to the respective ground; $2.7~V \le V_{DD1} \le 3.6~V$, $2.7~V \le V_{DD2} \le 3.6~V$; all minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted; all typical specifications are at $T_A = 25$ °C, $V_{DD1} = V_{DD2} = 3.0~V$; this does not apply to ADuM1200W and ADuM1201W automotive grade products.

Table 2.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
DC SPECIFICATIONS						
Input Supply Current per Channel, Quiescent	I _{DDI (Q)}		0.26	0.35	mA	
Output Supply Current per Channel, Quiescent	I _{DDO (Q)}		0.11	0.20	mA	
ADuM1200 Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.6	1.0	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.2	0.6	mA	DC to 1 MHz logic signal freq.
10 Mbps (BR and CR Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		2.2	3.4	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		0.7	1.1	mA	5 MHz logic signal freq.
25 Mbps (CR Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		5.2	7.7	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		1.5	2.0	mA	12.5 MHz logic signal freq.
ADuM1201 Total Supply Current, Two						
Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.4	0.8	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.4	0.8	mA	DC to 1 MHz logic signal freq.
10 Mbps (BR and CR Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		1.5	2.2	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		1.5	2.2	mA	5 MHz logic signal freq.
25 Mbps (CR Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		3.4	4.8	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		3.4	4.8	mA	12.5 MHz logic signal freq.
For All Models						
Input Currents	I _{IA} , I _{IB}	-10	+0.01	+10	μΑ	$0 \text{ V} \leq V_{IA}, V_{IB} \leq (V_{DD1} \text{ or } V_{DD2})$
Logic High Input Threshold	V _{IH}	0.7 (V _{DD1} or V _{DD2})			V	
Logic Low Input Threshold	V _{IL}			$0.3 (V_{DD1} \text{ or } V_{DD2})$		
Logic High Output Voltages	V _{OAH} , V _{OBH}	$(V_{DD1} \text{ or } V_{DD2}) - 0.1$	3.0		V	$I_{Ox} = -20 \mu A, V_{Ix} = V_{IxH}$
		(V _{DD1} or V _{DD2}) – 0.5	2.8		V	$I_{Ox} = -4 \text{ mA}, V_{Ix} = V_{IxH}$
Logic Low Output Voltages	Voal, Vobl		0.0	0.1	V	$I_{Ox} = 20 \mu A$, $V_{Ix} = V_{IxL}$
			0.04	0.1	V	$I_{Ox} = 400 \ \mu A, \ V_{Ix} = V_{IxL}$
			0.2	0.4	V	$I_{Ox} = 4 \text{ mA}, V_{Ix} = V_{IxL}$
SWITCHING SPECIFICATIONS						
ADuM1200/ADuM1201AR						$C_L = 15 \text{ pF, CMOS signal levels}$
Minimum Pulse Width ²	PW			1000	ns	
Maximum Data Rate ³		1			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	50		150	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			40	ns	
Change vs. Temperature			11		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			100	ns	
Channel-to-Channel Matching ⁶	t _{PSKCD} /t _{PSKOD}			50	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		10		ns	
	1	L			1	<u> </u>

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
ADuM1200/ADuM1201BR						$C_L = 15 \text{ pF, CMOS signal levels}$
Minimum Pulse Width ²	PW			100	ns	
Maximum Data Rate ³		10			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		60	ns	
Pulse Width Distortion, t _{PLH} - t _{PHL} ⁴	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			22	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			22	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3.0		ns	
ADuM1200/ADuM1201CR						
Minimum Pulse Width ²	PW		20	40	ns	
Maximum Data Rate ³		25	50		Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		55	ns	
Pulse Width Distortion, t _{PLH} - t _{PHL} ⁴	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			16	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			16	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3.0		ns	
For All Models						
Common-Mode Transient Immunity						
Logic High Output ⁷	СМн	25	35		kV/μs	$V_{lx} = V_{DD1}$ or V_{DD2} , $V_{CM} = 1000$ V, transient magnitude = 800 V
Logic Low Output ⁷	CM _L	25	35		kV/μs	$V_{lx} = 0 \text{ V}, V_{CM} = 1000 \text{ V},$ transient magnitude = 800 V
Refresh Rate	f _r		1.1		Mbps	
Dynamic Supply Current per Channel ⁸						
Input	I _{DDI} (D)		0.10		mA/ Mbps	
Output	I _{DDO (D)}		0.03		mA/ Mbps	

¹ The supply current values are for both channels combined when running at identical data rates. Output supply current values are specified with no output load present. The supply current associated with an individual channel operating at a given data rate can be calculated as described in the Power Consumption section. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See Figure 9 through Figure 11 for total V_{DD1} and V_{DD2} supply currents as a function of data rate for ADuM1200 and ADuM1201 channel configurations.

² The minimum pulse width is the shortest pulse width at which the specified pulse width distortion is guaranteed.

³ The maximum data rate is the fastest data rate at which the specified pulse width distortion is guaranteed.

⁴ t_{PHL} propagation delay is measured from the 50% level of the falling edge of the V_{Ix} signal to the 50% level of the falling edge of the V_{Ox} signal. t_{PLH} propagation delay is measured from the 50% level of the rising edge of the V_{Ix} signal to the 50% level of the rising edge of the V_{Ox} signal.

⁵ t_{PSK} is the magnitude of the worst-case difference in t_{PHL} and/or t_{PLH} that is measured between units at the same operating temperature, supply voltages, and output load within the recommended operating conditions.

⁶ Codirectional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on the same side of the isolation barrier. Opposing directional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on opposing sides of the isolation barrier.

 $^{^7}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 > 0.8 \, V_{DD2}$. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 < 0.8 \, V$. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

⁸ Dynamic supply current is the incremental amount of supply current required for a 1 Mbps increase in the signal data rate. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See the Power Consumption section for guidance on calculating per-channel supply current for a given data rate.

ELECTRICAL CHARACTERISTICS—MIXED 5 V/3 V OR 3 V/5 V, 105°C OPERATION

All voltages are relative to the respective ground; 5 V/3 V operation: $4.5 \text{ V} \le V_{DD1} \le 5.5 \text{ V}$, $2.7 \text{ V} \le V_{DD2} \le 3.6 \text{ V}$. 3 V/5 V operation: $2.7 \text{ V} \le V_{DD1} \le 3.6 \text{ V}$, $4.5 \text{ V} \le V_{DD2} \le 5.5 \text{ V}$; all minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted; all typical specifications are at $T_A = 25^{\circ}\text{C}$; $V_{DD1} = 3.0 \text{ V}$, $V_{DD2} = 5.0 \text{ V}$; or $V_{DD1} = 5.0 \text{ V}$, $V_{DD2} = 3.0 \text{ V}$; this does not apply to ADuM1200W and ADuM1201W automotive grade products.

Table 3.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions /Comments
DC SPECIFICATIONS						
Input Supply Current per Channel, Quiescent	I _{DDI (Q)}					
5 V/3 V Operation			0.50	0.6	mA	
3 V/5 V Operation			0.26	0.35	mA	
Output Supply Current per Channel, Quiescent	I _{DDO} (Q)					
5 V/3 V Operation			0.11	0.20	mA	
3 V/5 V Operation			0.19	0.25	mA	
ADuM1200 Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}					
5 V/3 V Operation			1.1	1.4	mA	DC to 1 MHz logic signal freq.
3 V/5 V Operation			0.6	1.0	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}					
5 V/3 V Operation			0.2	0.6	mA	DC to 1 MHz logic signal freq.
3 V/5 V Operation			0.5	0.8	mA	DC to 1 MHz logic signal freq.
10 Mbps (BR and CR Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}					
5 V/3 V Operation	, ,		4.3	5.5	mA	5 MHz logic signal freq.
3 V/5 V Operation			2.2	3.4	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}					
5 V/3 V Operation	, ,		0.7	1.1	mA	5 MHz logic signal freq.
3 V/5 V Operation			1.3	2.0	mA	5 MHz logic signal freq.
25 Mbps (CR Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}					
5 V/3 V Operation			10	13	mA	12.5 MHz logic signal freq.
3 V/5 V Operation			5.2	7.7	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}					1
5 V/3 V Operation	1002 (23)		1.5	2.0	mA	12.5 MHz logic signal freq.
3 V/5 V Operation			2.8	3.4	mA	12.5 MHz logic signal freq.
ADuM1201 Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}					
5 V/3 V Operation	IDDI (Q)		0.8	1.1	mA	DC to 1 MHz logic signal freq.
3 V/5 V Operation			0.4	0.8	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	lana (n)		0.4	0.0	IIIA	De to 1 MHz logic signal freq.
5 V/3 V Operation	I _{DD2} (Q)		0.4	0.8	mΛ	DC to 1 MHz logic signal freq.
·					mA mA	,
3 V/5 V Operation			0.8	1.1	mA	DC to 1 MHz logic signal freq.
10 Mbps (BR and CR Grades Only)	lance :					
V _{DD1} Supply Current	I _{DD1} (10)		2.8	3.5	A	5 MHz logic signal freq.
5 V/3 V Operation					mA mA	
3 V/5 V Operation	1,		1.5	2.2	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		1 -	2.2	4	CANILL In significant states of
5 V/3 V Operation			1.5	2.2	mA	5 MHz logic signal freq.
3 V/5 V Operation	İ		2.8	3.5	mA	5 MHz logic signal freq.

ADuM1200/ADuM1201

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions /Comments
25 Mbps (CR Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}					
5 V/3 V Operation			6.3	8.0	mA	12.5 MHz logic signal freq.
3 V/5 V Operation			3.4	4.8	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}					
5 V/3 V Operation			3.4	4.8	mA	12.5 MHz logic signal freq.
3 V/5 V Operation			6.3	8.0	mA	12.5 MHz logic signal freq.
For All Models						
Input Currents	I _{IA} , I _{IB}	-10	+0.01	+10	μΑ	$0 \text{ V} \leq V_{IA}, V_{IB} \leq (V_{DD1} \text{ or } V_{DD2})$
Logic High Input Threshold	V _{IH}	$0.7 (V_{DD1} \text{ or } V_{DD2})$			V	
Logic Low Input Threshold	VIL			0.3 (V_{DD1} or V_{DD2})	V	
Logic High Output Voltages	V _{OAH} , V _{OBH}	$(V_{DD1} \text{ or } V_{DD2}) - 0.1$	V_{DD1} or V_{DD2}		V	$I_{Ox} = -20 \mu A$, $V_{Ix} = V_{IxH}$
		$(V_{DD1} \text{ or } V_{DD2}) - 0.5$	$(V_{DD1} \text{ or } V_{DD2}) - 0.2$		V	$I_{Ox} = -4 \text{ mA}, V_{Ix} = V_{IxH}$
Logic Low Output Voltages	V_{OAL} , V_{OBL}		0.0	0.1	V	$I_{Ox} = 20 \mu A$, $V_{Ix} = V_{IxL}$
			0.04	0.1	V	$I_{Ox} = 400 \ \mu A$, $V_{Ix} = V_{IxL}$
			0.2	0.4	V	$I_{Ox} = 4 \text{ mA}, V_{Ix} = V_{IxL}$
SWITCHING SPECIFICATIONS						
ADuM1200/ADuM1201AR						$C_L = 15 \text{ pF, CMOS signal level}$
Minimum Pulse Width ²	PW			1000	ns	
Maximum Data Rate ³		1			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	50		150	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			40	ns	
Change vs. Temperature			11		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			50	ns	
Channel-to-Channel Matching ⁶	t _{PSKCD} /t _{PSKOD}			50	ns	
Output Rise/Fall Time (10% to 90%)	t_R/t_F		10		ns	
ADuM1200/ADuM1201BR						$C_L = 15 \text{ pF, CMOS signal level}$
Minimum Pulse Width ²	PW			100	ns	
Maximum Data Rate ³		10			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	15		55	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			22	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			22	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F					
5 V/3 V Operation			3.0		ns	
3 V/5 V Operation			2.5		ns	
ADuM1200/ADuM1201CR						C _L = 15 pF, CMOS signal level
Minimum Pulse Width ²	PW		20	40	ns	
Maximum Data Rate ³		25	50		Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20	÷ =	50	ns	
· •	PWD			3		
Pulse Width Distortion, t _{PLH} - t _{PHL} ⁴	FWD		E	J	ns	
Change vs. Temperature	.		5	15	ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			15	ns	
Channel-to-Channel Matching	1.			2		
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			15	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F					
5 V/3 V Operation			3.0		ns	
3 V/5 V Operation	1		2.5		ns	

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions /Comments
For All Models						
Common-Mode Transient Immunity						
Logic High Output ⁷	CM _H	25	35		kV/μs	$V_{lx} = V_{DD1}$ or V_{DD2} , $V_{CM} = 1000$ V, transient magnitude = 800 V
Logic Low Output ⁷	CM _L	25	35		kV/μs	$V_{lx} = 0 \text{ V}, V_{CM} = 1000 \text{ V},$ transient magnitude = 800 V
Refresh Rate	f _r					
5 V/3 V Operation			1.2		Mbps	
3 V/5 V Operation			1.1		Mbps	
Input Dynamic Supply Current per Channel ⁸	I _{DDI (D)}					
5 V/3 V Operation			0.19		mA/ Mbps	
3 V/5 V Operation			0.10		mA/ Mbps	
Output Dynamic Supply Current per Channel ⁸	I _{DDO (D)}					
5 V/3 V Operation			0.03		mA/ Mbps	
3 V/5 V Operation			0.05		mA/ Mbps	

¹ The supply current values are for both channels combined when running at identical data rates. Output supply current values are specified with no output load present. The supply current associated with an individual channel operating at a given data rate can be calculated as described in the Power Consumption section. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See Figure 9 through Figure 11 for total V_{DD1} and V_{DD2} supply currents as a function of data rate for ADuM1200 and ADuM1201 channel configurations.

² The minimum pulse width is the shortest pulse width at which the specified pulse width distortion is guaranteed.

³ The maximum data rate is the fastest data rate at which the specified pulse width distortion is guaranteed.

⁴ t_{PHL} propagation delay is measured from the 50% level of the falling edge of the V_{Ix} signal to the 50% level of the falling edge of the V_{Ox} signal. t_{PLH} propagation delay is measured from the 50% level of the rising edge of the V_{Ix} signal to the 50% level of the V_{Ox} signal.

⁵ t_{PSK} is the magnitude of the worst-case difference in t_{PHL} and/or t_{PLH} that is measured between units at the same operating temperature, supply voltages, and output load within the recommended operating conditions.

⁶ Codirectional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on the same side of the isolation barrier. Opposing directional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on opposing sides of the isolation barrier.

 $^{^{7}}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_{o} > 0.8 \, V_{DD2}$. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_{o} < 0.8 \, V$. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

⁸ Dynamic supply current is the incremental amount of supply current required for a 1 Mbps increase in the signal data rate. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See the Power Consumption section for guidance on calculating per-channel supply current for a given data rate.

ELECTRICAL CHARACTERISTICS—5 V, 125°C OPERATION

All voltages are relative to the respective ground; $4.5~V \le V_{DD1} \le 5.5~V$, $4.5~V \le V_{DD2} \le 5.5~V$; all minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted; all typical specifications are at $T_A = 25^{\circ}C$, $V_{DD1} = V_{DD2} = 5~V$; this applies to ADuM1200W and ADuM1201W automotive grade products.

Table 4.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
DC SPECIFICATIONS						
Input Supply Current per Channel, Quiescent	I _{DDI} (Q)		0.50	0.60	mA	
Output Supply Current per Channel, Quiescent	I _{DDO (Q)}		0.19	0.25	mA	
ADuM1200W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		1.1	1.4	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.5	0.8	mA	DC to 1 MHz logic signal freq.
10 Mbps (TRZ and URZ Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		4.3	5.5	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		1.3	2.0	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		10	13	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		2.8	3.4	mA	12.5 MHz logic signal freq.
ADuM1201W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (O)}		0.8	1.1	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.8	1.1	mA	DC to 1 MHz logic signal freq.
10 Mbps (TRZ and URZ Grades Only)	()					
V _{DD1} Supply Current	I _{DD1 (10)}		2.8	3.5	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		2.8	3.5	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		6.3	8.0	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		6.3	8.0	mA	12.5 MHz logic signal freq.
For All Models						
Input Currents	I _{IA} , I _{IB}	-10	+0.01	+10	μΑ	$0 \text{ V} \leq V_{IA}, V_{IB} \leq (V_{DD1} \text{ or } V_{DD2})$
Logic High Input Threshold	V _{IH}	0.7 (V _{DD1} or V _{DD2})			V	
Logic Low Input Threshold	VIL			0.3 (V_{DD1} or V_{DD2})	V	
Logic High Output Voltages	V _{OAH} , V _{OBH}	$(V_{DD1} \text{ or } V_{DD2}) - 0.1$	5.0		V	$I_{Ox} = -20 \mu A$, $V_{Ix} = V_{IxH}$
		$(V_{DD1} \text{ or } V_{DD2}) - 0.5$	4.8		V	$I_{Ox} = -4 \text{ mA}, V_{Ix} = V_{IxH}$
Logic Low Output Voltages	V _{OAL} , V _{OBL}		0.0	0.1	V	$I_{Ox} = 20 \mu A$, $V_{Ix} = V_{IxL}$
			0.04	0.1	V	$I_{Ox}=400~\mu\text{A, }V_{Ix}=V_{IxL}$
			0.2	0.4	V	$I_{Ox} = 4 \text{ mA}, V_{Ix} = V_{IxL}$
SWITCHING SPECIFICATIONS						
ADuM1200/ADuM1201WSRZ						$C_L = 15 \text{ pF}$, CMOS signal levels
Minimum Pulse Width ²	PW			1000	ns	
Maximum Data Rate ³		1			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		150	ns	
Pulse Width Distortion, t _{PLH} - t _{PHL} ⁴	PWD			40	ns	
Propagation Delay Skew⁵	t _{PSK}			100	ns	
Channel-to-Channel Matching ⁶	t _{PSKCD} /t _{PSKOD}			50	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		2.5		ns	

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
ADuM1200/ADuM1201WTRZ						C _L = 15 pF, CMOS signal levels
Minimum Pulse Width ²	PW			100	ns	
Maximum Data Rate ³		10			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		50	ns	
Pulse Width Distortion, tplh - tphl 4	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			15	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			15	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		2.5		ns	
ADuM1200/ADuM1201WURZ						$C_L = 15 \text{ pF, CMOS signal levels}$
Minimum Pulse Width ²	PW		20	40	ns	
Maximum Data Rate ³		25	50		Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		45	ns	
Pulse Width Distortion, tplh - tphl 4	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			15	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			15	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		2.5		ns	
For All Models						
Common-Mode Transient Immunity						
Logic High Output ⁷	CM _H	25	35		kV/μs	$V_{lx} = V_{DD1}$, V_{DD2} , $V_{CM} = 1000 \text{ V}$, transient magnitude = 800 V
Logic Low Output ⁷	CM _L	25	35		kV/μs	$V_{lx} = 0 \text{ V}, V_{CM} = 1000 \text{ V},$
Refresh Rate	f _r		1.2		Mbps	transient magnitude = 800 V
Dynamic Supply Current per Channel ⁸						
Input	I _{DDI (D)}		0.19		mA/ Mbps	
Output	I _{DDO (D)}		0.05		mA/ Mbps	

¹ The supply current values are for both channels combined when running at identical data rates. Output supply current values are specified with no output load present. The supply current associated with an individual channel operating at a given data rate can be calculated as described in the Power Consumption section. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See Figure 9 through Figure 11 for total l_{DD1} and l_{DD2} supply currents as a function of data rate for ADuM1200W and ADuM1201W channel configurations. ² The minimum pulse width is the shortest pulse width at which the specified pulse width distortion is guaranteed.

³ The maximum data rate is the fastest data rate at which the specified pulse width distortion is guaranteed.

⁴ tp-HL propagation delay is measured from the 50% level of the falling edge of the VIx signal to the 50% level of the falling edge of the VOx signal. tp-H propagation delay is measured from the 50% level of the rising edge of the V_{lx} signal to the 50% level of the rising edge of the V_{0x} signal.

⁵ track is the magnitude of the worst-case difference in terl. and/or tell that is measured between units at the same operating temperature, supply voltages, and output load within the recommended operating conditions.

⁶ Codirectional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on the same side of the isolation barrier. Opposing directional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on opposing sides of the isolation barrier.

 $^{^{7}}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining V₀ > 0.8 V_{DD2}. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 < 0.8 \text{ V}$. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

[®] Dynamic supply current is the incremental amount of supply current required for a 1 Mbps increase in the signal data rate. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See the Power Consumption section for guidance on calculating per-channel supply current for a given data rate.

ELECTRICAL CHARACTERISTICS—3 V, 125°C OPERATION

All voltages are relative to the respective ground; $3.0~V \le V_{DD1} \le 3.6~V$, $3.0~V \le V_{DD2} \le 3.6~V$. All minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted; all typical specifications are at $T_A = 25^{\circ}C$, $V_{DD1} = V_{DD2} = 3.0~V$; this applies to ADuM1200W and ADuM1201W automotive grade products.

Table 5.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
DC SPECIFICATIONS						
Input Supply Current per Channel, Quiescent	I _{DDI (Q)}		0.26	0.35	mA	
Output Supply Current per Channel, Quiescent	I _{DDO (Q)}		0.11	0.20	mA	
ADuM1200W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.6	1.0	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.2	0.6	mA	DC to 1 MHz logic signal freq.
10 Mbps (TRZ and URZ Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		2.2	3.4	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		0.7	1.1	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		5.2	7.7	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		1.5	2.0	mA	12.5 MHz logic signal freq.
ADuM1201W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.4	0.8	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.4	0.8	mA	DC to 1 MHz logic signal freq.
10 Mbps (TRZ and URZ Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		1.5	2.2	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		1.5	2.2	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		3.4	4.8	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		3.4	4.8	mA	12.5 MHz logic signal freq.
For All Models						
Input Currents	I _{IA} , I _{IB}	-10	+0.01	+10	μΑ	$0 \text{ V} \leq V_{IA}, V_{IB} \leq (V_{DD1} \text{ or } V_{DD2})$
Logic High Input Threshold	V _{IH}	0.7 (V _{DD1} or V _{DD2})			V	
Logic Low Input Threshold	V _{IL}			0.3 (V_{DD1} or V_{DD2})		
Logic High Output Voltages	V _{OAH} , V _{OBH}	$(V_{DD1} \text{ or } V_{DD2}) - 0.1$	3.0		V	$I_{Ox} = -20 \mu A, V_{Ix} = V_{IxH}$
		$(V_{DD1} \text{ or } V_{DD2}) - 0.5$	2.8		V	$I_{Ox} = -4 \text{ mA}, V_{Ix} = V_{IxH}$
Logic Low Output Voltages	V _{OAL} , V _{OBL}		0.0	0.1	V	$I_{Ox} = 20 \mu A$, $V_{Ix} = V_{IxL}$
			0.04	0.1	V	$I_{Ox}=400~\mu\text{A},V_{Ix}=V_{IxL}$
			0.2	0.4	V	$I_{Ox} = 4 \text{ mA}, V_{Ix} = V_{IxL}$
SWITCHING SPECIFICATIONS						
ADuM1200/ADuM1201WSRZ						$C_L = 15 pF$, CMOS signal levels
Minimum Pulse Width ²	PW			1000	ns	
Maximum Data Rate ³		1			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		150	ns	
Pulse Width Distortion, tplh - tphl 4	PWD			40	ns	
Propagation Delay Skew⁵	t _{PSK}			100	ns	
Channel-to-Channel Matching ⁶	t _{PSKCD} /t _{PSKOD}			50	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3		ns	

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
ADuM1200/ADuM1201WTRZ						C _L = 15 pF, CMOS signal levels
Minimum Pulse Width ²	PW			100	ns	
Maximum Data Rate ³		10			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		60	ns	
Pulse Width Distortion, t _{PLH} - t _{PHL} ⁴	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			22	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			22	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3.0		ns	
ADuM1200/ADuM1201WCR						$C_L = 15 \text{ pF, CMOS signal levels}$
Minimum Pulse Width ²	PW		20	40	ns	
Maximum Data Rate ³		25	50		Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		55	ns	
Pulse Width Distortion, tplh - tphl 4	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			16	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			16	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3.0		ns	
For All Models						
Common-Mode Transient Immunity						
Logic High Output ⁷	CM _H	25	35		kV/μs	$V_{lx} = V_{DD1}$, V_{DD2} , $V_{CM} = 1000 \text{ V}$, transient magnitude = 800 V
Logic Low Output ⁷	CM _L	25	35		kV/μs	$V_{lx} = 0 \text{ V}, V_{CM} = 1000 \text{ V},$ transient magnitude = 800 V
Refresh Rate	fr		1.1		Mbps	addistant magnitude – 000 V
Dynamic Supply Current per Channel ⁸						
Input	I _{DDI (D)}		0.10		mA/ Mbps	
Output	I _{DDO (D)}		0.03		mA/ Mbps	

¹ The supply current values are for both channels combined when running at identical data rates. Output supply current values are specified with no output load present. The supply current associated with an individual channel operating at a given data rate can be calculated as described in the Power Consumption section. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See Figure 9 through Figure 11 for total I_{DD1} and I_{DD2} supply currents as a function of data rate for ADuM1200W and ADuM1201W channel configurations.

² The minimum pulse width is the shortest pulse width at which the specified pulse width distortion is guaranteed.

³ The maximum data rate is the fastest data rate at which the specified pulse width distortion is guaranteed.

 $^{^4}$ t_{PHL} propagation delay is measured from the 50% level of the falling edge of the V_{Ix} signal to the 50% level of the falling edge of the V_{Ox} signal. t_{PLH} propagation delay is measured from the 50% level of the rising edge of the V_{Ix} signal to the 50% level of the rising edge of the V_{Ox} signal.

⁵ t_{PSK} is the magnitude of the worst-case difference in t_{PHL} and/or t_{PLH} that is measured between units at the same operating temperature, supply voltages, and output load within the recommended operating conditions.

⁶ Codirectional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on the same side of the isolation barrier. Opposing directional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on opposing sides of the isolation barrier.

 $^{^7}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 > 0.8 \, V_{DD2}$. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 < 0.8 \, V$. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

⁸ Dynamic supply current is the incremental amount of supply current required for a 1 Mbps increase in the signal data rate. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See the Power Consumption section for guidance on calculating per-channel supply current for a given data rate.

ELECTRICAL CHARACTERISTICS—MIXED 5 V/3 V, 125°C OPERATION

All voltages are relative to the respective ground; 5 V/3 V operation: $4.5 \text{ V} \le V_{DD1} \le 5.5 \text{ V}$, $3.0 \text{ V} \le V_{DD2} \le 3.6 \text{ V}$. 3 V/5 V operation; all minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted; all typical specifications are at $T_A = 25^{\circ}\text{C}$; $V_{DD1} = 5.0 \text{ V}$, $V_{DD2} = 3.0 \text{ V}$; this applies to ADuM1200W and ADuM1201W automotive grade products.

Table 6.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
DC SPECIFICATIONS						
Input Supply Current per Channel, Quiescent	I _{DDI} (Q)		0.50	0.6	mA	
Output Supply Current per Channel, Quiescent	I _{DDO} (Q)		0.11	0.20	mA	
ADuM1200W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		1.1	1.4	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current 10 Mbps (TRZ and URZ Grades Only)	I _{DD2} (Q)		0.2	0.6	mA	DC to 1 MHz logic signal freq.
V _{DD1} Supply Current	I _{DD1 (10)}		4.3	5.5	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		0.7	1.1	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		10	13	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		1.5	2.0	mA	12.5 MHz logic signal freq.
ADuM1201W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.8	1.1	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current 10 Mbps (TRZ and URZ Grades Only)	I _{DD2} (Q)		0.4	0.8	mA	DC to 1 MHz logic signal freq.
V _{DD1} Supply Current	I _{DD1 (10)}		2.8	3.5	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		1.5	2.2	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		6.3	8.0	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		3.4	4.8	mA	12.5 MHz logic signal freq.
For All Models						
Input Currents	I _{IA} , I _{IB}	-10	+0.01	+10	μΑ	$0 \text{ V} \leq V_{IA}, V_{IB} \leq (V_{DD1} \text{ or } V_{DD2})$
Logic High Input Threshold	V _{IH}	0.7 (V _{DD1} or V _{DD2})			V	
Logic Low Input Threshold	V _{IL}			$0.3(V_{DD1}orV_{DD2})$	V	
Logic High Output Voltages	V_{OAH} , V_{OBH}	$(V_{DD1} \text{ or } V_{DD2}) - 0.1$	V_{DD1} or V_{DD2}		V	$I_{Ox} = -20 \mu A, V_{Ix} = V_{IxH}$
		$(V_{DD1} \text{ or } V_{DD2}) - 0.5$	$(V_{DD1} \text{ or } V_{DD2}) - 0.2$		V	$I_{Ox} = -4 \text{ mA}, V_{Ix} = V_{IxH}$
Logic Low Output Voltages	V _{OAL} , V _{OBL}		0.0	0.1	V	$I_{Ox}=20~\mu\text{A},V_{Ix}=V_{IxL}$
			0.04	0.1	V	$I_{Ox} = 400 \mu A$, $V_{Ix} = V_{IxL}$
			0.2	0.4	V	$I_{Ox} = 4 \text{ mA}, V_{Ix} = V_{IxL}$
SWITCHING SPECIFICATIONS						
ADuM1200/ADuM1201WSRZ						$C_L = 15 \text{ pF, CMOS signal levels}$
Minimum Pulse Width ²	PW			1000	ns	
Maximum Data Rate ³		1			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	15		150	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			40	ns	
Propagation Delay Skew⁵	t _{PSK}			50	ns	
Channel-to-Channel Matching ⁶	t _{PSKCD} / t _{PSKOD}			50	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3		ns	

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
ADuM1200/ADuM1201WTRZ			•			C _L = 15 pF, CMOS signal levels
Minimum Pulse Width ²	PW			100	ns	
Maximum Data Rate ³		10			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	15		55	ns	
Pulse Width Distortion, tplh - tphl 4	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew ⁵	t _{PSK}			22	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			22	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3.0		ns	
ADuM1200/ADuM1201WURZ						$C_L = 15 \text{ pF}$, CMOS signal levels
Minimum Pulse Width ²	PW		20	40	ns	
Maximum Data Rate ³		25	50		Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		50	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			15	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			15	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3.0		ns	
For All Models						
Common-Mode Transient Immunity						
Logic High Output ⁷	CM _H	25	35		kV/μs	$V_{lx} = V_{DD1}$, V_{DD2} , $V_{CM} = 1000 \text{ V}$, transient magnitude = 800 V
Logic Low Output ⁷	CM _L	25	35		kV/μs	$V_{lx} = V_{DD1}$, V_{DD2} , $V_{CM} = 1000 \text{ V}$, transient magnitude = 800 V
Refresh Rate	f _r		1.2		Mbps	transient magnitude = 800 v
Dynamic Supply Current per Channel ⁸						
Input	I _{DDI (D)}		0.19		mA/ Mbps	
Output	I _{DDO (D)}		0.03		mA/ Mbps	

¹ The supply current values are for both channels combined when running at identical data rates. Output supply current values are specified with no output load present. The supply current associated with an individual channel operating at a given data rate can be calculated as described in the Power Consumption section. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See Figure 9 through Figure 11 for total I_{DD1} and I_{DD2} supply currents as a function of data rate for ADuM1200W and ADuM1201W channel configurations.

² The minimum pulse width is the shortest pulse width at which the specified pulse width distortion is guaranteed.

³ The maximum data rate is the fastest data rate at which the specified pulse width distortion is guaranteed.

 $^{^4}$ t_{PHL} propagation delay is measured from the 50% level of the falling edge of the V_{Ix} signal to the 50% level of the falling edge of the V_{Ox} signal. t_{PLH} propagation delay is measured from the 50% level of the rising edge of the V_{Ix} signal to the 50% level of the V_{Ox} signal.

 $^{^{5}}$ t_{PSK} is the magnitude of the worst-case difference in t_{PHL} and/or t_{PLH} that is measured between units at the same operating temperature, supply voltages, and output load within the recommended operating conditions.

⁶ Codirectional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on the same side of the isolation barrier. Opposing directional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on opposing sides of the isolation barrier.

 $^{^7}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 > 0.8 \, V_{DD2}$. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 < 0.8 \, V$. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

⁸ Dynamic supply current is the incremental amount of supply current required for a 1 Mbps increase in the signal data rate. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See the Power Consumption section for guidance on calculating per-channel supply current for a given data rate.

ELECTRICAL CHARACTERISTICS—MIXED 3 V/5 V, 125°C OPERATION

All voltages are relative to the respective ground; $3.0 \text{ V} \le V_{DD1} \le 3.6 \text{ V}$, $4.5 \text{ V} \le V_{DD2} \le 5.5 \text{ V}$; all minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted; all typical specifications are at $T_A = 25^{\circ}\text{C}$; $V_{DD1} = 3.0 \text{ V}$, $V_{DD2} = 5.0 \text{ V}$; this applies to ADuM1200W and ADuM1201W automotive grade products.

Table 7.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
DC SPECIFICATIONS						
Input Supply Current per Channel, Quiescent	I _{DDI} (Q)		0.26	0.35	mA	
Output Supply Current per Channel, Quiescent	I _{DDO} (Q)		0.19	0.25	mA	
ADuM1200W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.6	1.0	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.5	0.8	mA	DC to 1 MHz logic signal freq.
10 Mbps (TRZ and URZ Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		2.2	3.4	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		1.3	2.0	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		5.2	7.7	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		2.8	3.4	mA	12.5 MHz logic signal freq.
ADuM1201W, Total Supply Current, Two Channels ¹						
DC to 2 Mbps						
V _{DD1} Supply Current	I _{DD1 (Q)}		0.4	0.8	mA	DC to 1 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (Q)}		0.8	1.1	mA	DC to 1 MHz logic signal freq.
10 Mbps (TRZ and URZ Grades Only)						
V _{DD1} Supply Current	I _{DD1 (10)}		1.5	2.2	mA	5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (10)}		2.8	3.5	mA	5 MHz logic signal freq.
25 Mbps (URZ Grade Only)						
V _{DD1} Supply Current	I _{DD1 (25)}		3.4	4.8	mA	12.5 MHz logic signal freq.
V _{DD2} Supply Current	I _{DD2 (25)}		6.3	8.0	mA	12.5 MHz logic signal freq.
For All Models						
Input Currents	I _{IA} , I _{IB}	-10	+0.01	+10	μΑ	$0 \text{ V} \leq V_{IA}$, $V_{IB} \leq (V_{DD1} \text{ or } V_{DD2})$
Logic High Input Threshold	V _{IH}	0.7 (V _{DD1} or V _{DD2})			V	
Logic Low Input Threshold	VIL			$0.3(V_{DD1}orV_{DD2})$	V	
Logic High Output Voltages	V_{OAH} , V_{OBH}	$(V_{DD1} \text{ or } V_{DD2}) - 0.1$	V_{DD1} or V_{DD2}		V	$I_{Ox} = -20 \mu A, V_{Ix} = V_{IxH}$
		$(V_{DD1} \text{ or } V_{DD2}) - 0.5$	$(V_{DD1} \text{ or } V_{DD2}) - 0.2$		V	$I_{Ox} = -4 \text{ mA}, V_{Ix} = V_{IxH}$
Logic Low Output Voltages	V_{OAL} , V_{OBL}		0.0	0.1	V	$I_{Ox}=20~\mu\text{A},V_{lx}=V_{lxL}$
			0.04	0.1	V	$I_{Ox}=400~\mu\text{A, }V_{lx}=V_{lxL}$
			0.2	0.4	V	$I_{Ox} = 4 \text{ mA}, V_{Ix} = V_{IxL}$
SWITCHING SPECIFICATIONS						
ADuM1200/ADuM1201WSRZ						$C_L = 15 \text{ pF, CMOS signal levels}$
Minimum Pulse Width ²	PW			1000	ns	
Maximum Data Rate ³		1			Mbps	
Propagation Delay⁴	t _{PHL} , t _{PLH}	15		150	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			40	ns	
Propagation Delay Skew ⁵	t _{PSK}			50	ns	
Channel-to-Channel Matching ⁶	t _{PSKCD/} t _{PSKOD}			50	ns	
Output Rise/Fall Time (10% to 90%)	t _R /t _F		3		ns	

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
ADuM1200/ADuM1201WTRZ			•			C _L = 15 pF, CMOS signal levels
Minimum Pulse Width ²	PW			100	ns	
Maximum Data Rate ³		10			Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	15		55	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			22	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			22	ns	
Output Rise/Fall Time (10% to 90%)	t_R/t_F		2.5		ns	
ADuM1200/ADuM1201WURZ						$C_L = 15 \text{ pF}$, CMOS signal levels
Minimum Pulse Width ²	PW		20	40	ns	
Maximum Data Rate ³		25	50		Mbps	
Propagation Delay ⁴	t _{PHL} , t _{PLH}	20		50	ns	
Pulse Width Distortion, $ t_{PLH} - t_{PHL} ^4$	PWD			3	ns	
Change vs. Temperature			5		ps/°C	
Propagation Delay Skew⁵	t _{PSK}			15	ns	
Channel-to-Channel Matching						
Codirectional Channels ⁶	t _{PSKCD}			3	ns	
Opposing Directional Channels ⁶	t _{PSKOD}			15	ns	
Output Rise/Fall Time (10% to 90%)	t_R/t_F		2.5		ns	
For All Models						
Common-Mode Transient Immunity						
Logic High Output ⁷	СМн	25	35		kV/μs	$V_{lx} = V_{DD1}$, V_{DD2} , $V_{CM} = 1000 \text{ V}$, transient magnitude = 800 V
Logic Low Output ⁷	CM _L	25	35		kV/μs	$V_{lx} = 0 \text{ V}, V_{CM} = 1000 \text{ V},$ transient magnitude = 800 V
Refresh Rate	fr		1.1		Mbps	
Input Dynamic Supply Current per Channel ⁸	I _{DDI (D)}		0.10		mA/ Mbps	
Output Dynamic Supply Current per Channel ⁸	I _{DDO (D)}		0.05		mA/ Mbps	

¹ The supply current values are for both channels combined when running at identical data rates. Output supply current values are specified with no output load present. The supply current associated with an individual channel operating at a given data rate can be calculated as described in the Power Consumption section. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See Figure 9 through Figure 11 for total I_{DD1} and I_{DD2} supply currents as a function of data rate for ADuM1200W and ADuM1201W channel configurations.

² The minimum pulse width is the shortest pulse width at which the specified pulse width distortion is guaranteed.

³ The maximum data rate is the fastest data rate at which the specified pulse width distortion is guaranteed.

⁴ tp-HL propagation delay is measured from the 50% level of the falling edge of the VIx signal to the 50% level of the falling edge of the VOx signal. tp-H propagation delay is measured from the 50% level of the rising edge of the VIX signal to the 50% level of the VOX signal.

⁵ t_{PSK} is the magnitude of the worst-case difference in t_{PHL} and/or t_{PLH} that is measured between units at the same operating temperature, supply voltages, and output load within the recommended operating conditions.

⁶ Codirectional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on the same side of the isolation barrier. Opposing directional channel-to-channel matching is the absolute value of the difference in propagation delays between any two channels with inputs on opposing sides of the isolation barrier.

 $^{^7}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 > 0.8 \, V_{\text{DD2}}$. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining $V_0 < 0.8 \, V$. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

⁸ Dynamic supply current is the incremental amount of supply current required for a 1 Mbps increase in the signal data rate. See Figure 6 through Figure 8 for information on per-channel supply current as a function of data rate for unloaded and loaded conditions. See the Power Consumption section for guidance on calculating per-channel supply current for a given data rate.

PACKAGE CHARACTERISTICS

Table 8.

Parameter	Symbol	Min Typ Max	Unit	Test Conditions/Comments
Resistance (Input-to-Output) ¹	R _{I-O}	10 ¹²	Ω	
Capacitance (Input-to-Output) ¹	C _{I-O}	1.0	pF	f = 1 MHz
Input Capacitance	Cı	4.0	pF	
IC Junction-to-Case Thermal Resistance, Side 1	θ_{JCI}	46	°C/W	Thermocouple located at center of package underside
IC Junction-to-Case Thermal Resistance, Side 2	θ_{JCO}	41	°C/W	

¹ The device is considered a 2-terminal device; Pin 1, Pin, 2, Pin 3, and Pin 4 are shorted together, and Pin 5, Pin 6, Pin 7, and Pin 8 are shorted together.

REGULATORY INFORMATION

The ADuM1200/ADuM1201 and ADuM1200W/ADuM1201W are approved by the organizations listed in Table 9; refer to Table 14 and the Insulation Lifetime section for details regarding recommended maximum working voltages for specific cross-isolation waveforms and insulation levels.

Table 9.

UL	CSA	CQC	VDE
Recognized Under 1577 Component Recognition Program ¹	Approved under CSA Component Acceptance Notice 5A	Approved under CQC11-471543-2012	Certified according to DIN V VDE V 0884-10 (VDE V 0884-10): 2006-12 ²
Single/Basic 2500 V rms Isolation Voltage	Basic insulation per CSA 60950-1-03 and IEC 60950-1, 400 V rms (566 peak) maximum working voltage	Basic insulation per GB4943.1-2011	Reinforced insulation, 560 V peak
	Functional insulation per CSA 60950-1-03 and IEC 60950-1, 800 V rms (1131 V peak) maximum working voltage	Basic insulation, 400 V rms (588 V peak) maximum working voltage, tropical climate, altitude ≤ 5000 m	
File E214100	File 205078	File CQC14001114901	File 2471900-4880-0001

¹ In accordance with UL 1577, each ADuM1200, ADuM1201, ADuM1200W, and ADuM1201W is proof tested by applying an insulation test voltage ≥ 3000 V rms for 1 sec (current leakage detection limit = 5 μA).

INSULATION AND SAFETY-RELATED SPECIFICATIONS

Table 10.

Parameter	Symbol	Value	Unit	Conditions
Rated Dielectric Insulation Voltage		2500	V rms	1 minute duration
Minimum External Air Gap (Clearance)	L(I01)	4.90 min	mm	Measured from input terminals to output terminals, shortest distance through air
Minimum External Tracking (Creepage)	L(102)	4.01 min	mm	Measured from input terminals to output terminals, shortest distance path along body
Minimum Internal Gap (Internal Clearance)		0.017 min	mm	Insulation distance through insulation
Tracking Resistance (Comparative Tracking Index)	CTI	>400	V	DIN IEC 112/VDE 0303 Part 1
Isolation Group		II		Material Group (DIN VDE 0110, 1/89, Table 1)

² In accordance with DIN V VDE V 0884-10, each ADuM1200, ADuM1201, ADuM1200W, and ADuM1201W is proof tested by applying an insulation test voltage ≥ 1050 V peak for 1 sec (partial discharge detection limit = 5 pC). The * and/or & marking branded on the component designates DIN V VDE V 0884-10 approval.

DIN V VDE V 0884-10 (VDE V 0884-10): 2006-12 INSULATION CHARACTERISTICS

This isolator is suitable for reinforced isolation only within the safety limit data. Maintenance of the safety data is ensured by protective circuits. Note that the asterisk (*) marking on the package denotes DIN V VDE V 0884-10 approval for a 560 V peak working voltage.

Table 11.

Description	Conditions	Symbol	Characteristic	Unit
Installation Classification per DIN VDE 0110				
For Rated Mains Voltage ≤ 150 V rms			I to IV	
For Rated Mains Voltage ≤ 300 V rms			l to III	
For Rated Mains Voltage ≤ 400 V rms			l to II	
Climatic Classification			40/105/21	
Pollution Degree per DIN VDE 0110, Table 1			2	
Maximum Working Insulation Voltage		V _{IORM}	560	V peak
Input-to-Output Test Voltage, Method B1	$V_{IORM} \times 1.875 = V_{PR}$, 100% production test, $t_m = 1$ second, partial discharge < 5 pC	V_{PR}	1050	V peak
Input-to-Output Test Voltage, Method A	$V_{IORM} \times 1.6 = V_{PR}$, $t_m = 60$ seconds, partial discharge < 5 pC	V_{PR}		
After Environmental Tests Subgroup 1			896	V peak
After Input and/or Safety Test Subgroup 2 and Subgroup 3	$V_{IORM} \times 1.2 = V_{PR}$, $t_m = 60$ seconds, partial discharge < 5 pC		672	V peak
Highest Allowable Overvoltage	Transient overvoltage, $t_{TR} = 10$ seconds	V_{TR}	4000	V peak
Safety-Limiting Values	Maximum value allowed in the event of a failure (see Figure 3)			
Case Temperature		Ts	150	°C
Side 1 Current		I _{S1}	160	mA
Side 2 Current		I _{S2}	170	mA
Insulation Resistance at T _S	$V_{IO} = 500 V$	R_{S}	>109	Ω




Figure 3. Thermal Derating Curve, Dependence of Safety-Limiting Values on Case Temperature per DIN V VDE V 0884-10

RECOMMENDED OPERATING CONDITIONS

Table 12.

Parameter	Rating
Operating Temperature (T _A) ¹	-40°C to +105°C
Operating Temperature (T _A) ²	−40°C to +125°C
Supply Voltages (V _{DD1} , V _{DD2}) ^{1, 3}	2.7 V to 5.5 V
Supply Voltages (V _{DD1} , V _{DD2}) ^{2, 3}	3.0 V to 5.5 V
Input Signal Rise and Fall Times	1.0 ms

¹ Does not apply to ADuM1200W and ADuM1201W automotive grade

products. ² Applies to ADuM1200W and ADuM1201W automotive grade products.

³ All voltages are relative to the respective ground. See the DC Correctness and Magnetic Field Immunity section for information on immunity to external magnetic fields.

ABSOLUTE MAXIMUM RATINGS

Ambient temperature = 25°C, unless otherwise noted.

Table 13.

Parameter	Rating
Storage Temperature (T _{ST})	−55°C to +150°C
Ambient Operating Temperature $(T_A)^1$	−40°C to +105°C
Ambient Operating Temperature $(T_A)^2$	-40°C to +125°C
Supply Voltages (V _{DD1} , V _{DD2}) ³	−0.5 V to +7.0 V
Input Voltages (V _{IA} , V _{IB}) ^{3, 4}	-0.5V to $ \text{V}_{\text{DDI}} + 0.5 \text{V}$
Output Voltages (V _{OA} , V _{OB}) ^{3, 4}	$-0.5 \text{ V to V}_{DDO} + 0.5 \text{ V}$
Average Output Current per Pin (I ₀) ⁵	−11 mA to +11 mA
Common-Mode Transients (CM _L , CM _H) ⁶	–100 kV/μs to +100 kV/μs

¹ Does not apply to ADuM1200W and ADuM1201W automotive grade products.

Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

Table 14. Maximum Continuous Working Voltage¹

	U	O		
Parameter	Max	Unit	Constraint	
AC Voltage, Bipolar Waveform	565	V peak	50-year minimum lifetime	
AC Voltage, Unipolar Waveform				
Functional Insulation	1131	V peak	Maximum approved working voltage per IEC 60950-1	
Basic Insulation	560	V peak	Maximum approved working voltage per IEC 60950-1 and VDE V 0884-10	
DC Voltage				
Functional Insulation	1131	V peak	Maximum approved working voltage per IEC 60950-1	
Basic Insulation	560	V peak	Maximum approved working voltage per IEC 60950-1 and VDE V 0884-10	

¹ Refers to continuous voltage magnitude imposed across the isolation barrier. See the Insulation Lifetime section for more details.

² Applies to ADuM1200W and ADuM1201W automotive grade products.


³ All voltages are relative to the respective ground.

 $^{^4\,}V_{DDI}$ and V_{DDO} refer to the supply voltages on the input and output sides of a given channel, respectively.

⁵ See Figure 3 for maximum rated current values for various temperatures.

⁶ Refers to common-mode transients across the insulation barrier. Common-mode transients exceeding the absolute maximum ratings can cause latch-up or permanent damage.

PIN CONFIGURATIONS AND FUNCTION DESCRIPTIONS








Figure 5. ADuM1201 Pin Configuration

Table 15. ADuM1200 Pin Function Descriptions

Pin No.	Mnemonic	Description
1	V _{DD1}	Supply Voltage for Isolator Side 1.
2	V _{IA}	Logic Input A.
3	V _{IB}	Logic Input B.
4	GND₁	Ground 1. Ground Reference for Isolator Side 1.
5	GND₂	Ground 2. Ground Reference for Isolator Side 2.
6	V _{OB}	Logic Output B.
7	Voa	Logic Output A.
8	V_{DD2}	Supply Voltage for Isolator Side 2.

Table 16. ADuM1201 Pin Function Descriptions

Pin No.	Mnemonic	Description
1	V _{DD1}	Supply Voltage for Isolator Side 1.
2	V _{OA}	Logic Output A.
3	V _{IB}	Logic Input B.
4	GND₁	Ground 1. Ground Reference for Isolator Side 1.
5	GND ₂	Ground 2. Ground Reference for Isolator Side 2.
6	V _{OB}	Logic Output B.
7	VIA	Logic Input A.
8	V_{DD2}	Supply Voltage for Isolator Side 2.

Table 17. ADuM1200 Truth Table (Positive Logic)

V _{IA} Input	V _{IB} Input	V _{DD1} State	V _{DD2} State	V _{OA} Output	V _{OB} Output	Notes
Н	Н	Powered	Powered	Н	Н	
L	L	Powered	Powered	L	L	
Н	L	Powered	Powered	Н	L	
L	Н	Powered	Powered	L	Н	
X	X	Unpowered	Powered	Н	Н	Outputs return to the input state within 1 μ s of V_{DDI} power restoration.
X	Х	Powered	Unpowered	Indeterminate	Indeterminate	Outputs return to the input state within 1 μ s of V_{DDO} power restoration.

Table 18. ADuM1201 Truth Table (Positive Logic)

V _{IA} Input	V _{IB} Input	V _{DD1} State	V _{DD2} State	V _{OA} Output	V _{OB} Output	Notes
Н	Н	Powered	Powered	Н	Н	
L	L	Powered	Powered	L	L	
Н	L	Powered	Powered	Н	L	
L	Н	Powered	Powered	L	Н	
Χ	X	Unpowered	Powered	Indeterminate	Н	Outputs return to the input state within 1 μ s of V_{DDI} power restoration.
Χ	X	Powered	Unpowered	Н	Indeterminate	Outputs return to the input state within 1 μ s of V_{DDO} power restoration.

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 6. Typical Input Supply Current per Channel vs. Data Rate for 5 V and 3 V Operation




Figure 7. Typical Output Supply Current per Channel vs. Data Rate for 5 V and 3 V Operation (No Output Load)




Figure 8. Typical Output Supply Current per Channel vs. Data Rate for 5 V and 3 V Operation (15 pF Output Load)




Figure 9. Typical ADuM1200 $V_{\rm DD1}$ Supply Current vs. Data Rate for 5 V and 3 V Operation




Figure 10. Typical ADuM1200 V_{DD2} Supply Current vs. Data Rate for 5 V and 3 V Operation




Figure 11. Typical ADuM1201 $V_{\rm DD1}$ or $V_{\rm DD2}$ Supply Current vs. Data Rate for 5 V and 3 V Operation

APPLICATIONS INFORMATION PCB LAYOUT

The ADuM1200/ADuM1201 digital isolators require no external interface circuitry for the logic interfaces. Power supply bypassing is strongly recommended at the input and output supply pins.

The capacitor value must be between 0.01 μF and 0.1 μF . The total lead length between both ends of the capacitor and the input power supply pin must not exceed 20 mm.

See the AN-1109 Application Note for board layout guidelines.

PROPAGATION DELAY-RELATED PARAMETERS

Propagation delay is a parameter that describes the time it takes a logic signal to propagate through a component. The propagation delay to a logic low output can differ from the propagation delay to a logic high output.




Figure 12. Propagation Delay Parameters

Pulse width distortion is the maximum difference between these two propagation delay values and is an indication of how accurately the timing of the input signal is preserved.

Channel-to-channel matching refers to the maximum amount that the propagation delay differs between channels within a single ADuM1200/ADuM1201 component.

Propagation delay skew refers to the maximum amount that the propagation delay differs between multiple ADuM1200/ADuM1201 components operating under the same conditions.

DC CORRECTNESS AND MAGNETIC FIELD IMMUNITY

Positive and negative logic transitions at the isolator input send narrow ($\sim\!1$ ns) pulses to the decoder via the transformer. The decoder is bistable and is therefore either set or reset by the pulses, indicating input logic transitions. In the absence of logic transitions of more than $\sim\!1$ µs at the input, a periodic set of refresh pulses indicative of the correct input state is sent to ensure dc correctness at the output. If the decoder receives no internal pulses for more than about 5 µs, the input side is assumed to be unpowered or nonfunctional, in which case the isolator output is forced to a default state (see Table 17 and Table 18) by the watchdog timer circuit.

The ADuM1200/ADuM1201 are extremely immune to external magnetic fields. The limitation on the magnetic field immunity of the ADuM1200/ADuM1201 is set by the condition in which induced voltage in the receiving coil of the transformer is sufficiently large enough to either falsely set or reset the decoder. The following analysis defines the conditions under which this can occur.

The 3 V operating condition of the ADuM1200/ADuM1201 is examined because it represents the most susceptible mode of operation.

The pulses at the transformer output have an amplitude greater than $1.0~\rm V$. The decoder has a sensing threshold at about $0.5~\rm V$, therefore establishing a $0.5~\rm V$ margin in which induced voltages can be tolerated. The voltage induced across the receiving coil is given by

$$V = (-d\beta/dt) \sum \prod r_n^2; n = 1, 2, \dots, N$$

where

 β is the magnetic flux density (gauss).

N is the number of turns in the receiving coil.

 r_n is the radius of the nth turn in the receiving coil (cm).

Given the geometry of the receiving coil in the ADuM1200/ADuM1201 and an imposed requirement that the induced voltage be 50% at most of the 0.5 V margin at the decoder, a maximum allowable magnetic field is calculated, as shown in Figure 13.




Figure 13. Maximum Allowable External Magnetic Flux Density

For example, at a magnetic field frequency of 1 MHz, the maximum allowable magnetic field of 0.2 kgauss induces a voltage of 0.25 V at the receiving coil. This is about 50% of the sensing threshold and does not cause a faulty output transition. Similarly, if such an event occurs during a transmitted pulse (and has the worst-case polarity), it reduces the received pulse from $>1.0~\rm V$ to 0.75 V—still well above the 0.5 V sensing threshold of the decoder.

The preceding magnetic flux density values correspond to specific current magnitudes at given distances away from the ADuM1200/ADuM1201 transformers. Figure 14 expresses these allowable current magnitudes as a function of frequency for selected distances. As seen, the ADuM1200/ADuM1201 are extremely immune and can be affected only by extremely large currents operating very close to the component at a high frequency. For the 1 MHz example, place a 0.5 kA current 5 mm away from the ADuM1200/ADuM1201 to affect the operation of the component.




Figure 14. Maximum Allowable Current for Various Current-to-ADuM1200/ADuM1201 Spacings

Note that, at combinations of strong magnetic fields and high frequencies, any loops formed by PCB traces can induce sufficiently large error voltages to trigger the threshold of succeeding circuitry. Take care in the layout of such traces to avoid this possibility.

POWER CONSUMPTION

The supply current at a given channel of the ADuM1200/ ADuM1201 isolator is a function of the supply voltage, the data rate of the channel, and the output load of the channel.

For each input channel, the supply current is given by

$$I_{DDI} = I_{DDI(Q)}$$
 $f \le 0.5 f_r$

$$I_{DDI} = I_{DDI(D)} \times (2f - f_r) + I_{DDI(Q)}$$
 $f > 0.5 f_r$

For each output channel, the supply current is given by

$$I_{DDO} = I_{DDO(Q)}$$
 $f \le 0.5f_r$
 $I_{DDO} = (I_{DDO(D)} + (0.5 \times 10^{-3}) \times C_L V_{DDO}) \times (2f - f_r) + I_{DDO(Q)}$
 $f > 0.5f_r$

where:

 $I_{DDI(D)}$, $I_{DDO(D)}$ are the input and output dynamic supply currents per channel (mA/Mbps).

 C_L is the output load capacitance (pF).

 V_{DDO} is the output supply voltage (V).

f is the input logic signal frequency (MHz, half of the input data rate, NRZ signaling).

 f_r is the input stage refresh rate (Mbps).

 $I_{DDI\,(Q)},\,I_{DDO\,(Q)}$ are the specified input and output quiescent supply currents (mA).

To calculate the total $I_{\rm DD1}$ and $I_{\rm DD2}$ supply currents, the supply currents for each input and output channel corresponding to $I_{\rm DD1}$ and $I_{\rm DD2}$ are calculated and totaled. Figure 6 and Figure 7 provide per-channel supply currents as a function of data rate for an unloaded output condition. Figure 8 provides per-channel supply current as a function of data rate for a 15 pF output condition. Figure 9 through Figure 11 provide total $V_{\rm DD1}$ and $V_{\rm DD2}$ supply current as a function of data rate for ADuM1200 and ADuM1201 channel configurations.

INSULATION LIFETIME

All insulation structures eventually break down when subjected to voltage stress over a sufficiently long period. The rate of insulation degradation is dependent on the characteristics of the voltage waveform applied across the insulation. In addition to the testing performed by the regulatory agencies, Analog Devices carries out an extensive set of evaluations to determine the lifetime of the insulation structure within the ADuM1200/ADuM1201.


Analog Devices performs accelerated life testing using voltage levels higher than the rated continuous working voltage. Acceleration factors for several operating conditions are determined. These factors allow calculation of the time to failure at the actual working voltage. The values shown in Table 14 summarize the peak voltage for 50 years of service life for a bipolar ac operating condition and the maximum CSA/VDE approved working voltages. In many cases, the approved working voltage is higher than the 50-year service life voltage. Operation at these high working voltages can lead to shortened insulation life in some cases.

The insulation lifetime of the ADuM1200/ADuM1201 depends on the voltage waveform type imposed across the isolation barrier. The *i*Coupler insulation structure degrades at different rates depending on whether the waveform is bipolar ac, unipolar ac, or dc. Figure 15, Figure 16, and Figure 17 illustrate these different isolation voltage waveforms, respectively.

Bipolar ac voltage is the most stringent environment. The goal of a 50-year operating lifetime under the ac bipolar condition determines the Analog Devices recommended maximum working voltage.

In the case of unipolar ac or dc voltage, the stress on the insulation is significantly lower, which allows operation at higher working voltages yet still achieves a 50-year service life. The working voltages listed in Table 14 can be applied while maintaining the 50-year minimum lifetime provided the voltage conforms to either the unipolar ac or dc voltage cases. Any crossinsulation voltage waveform that does not conform to Figure 16 or Figure 17 is to be treated as a bipolar ac waveform, and the peak voltage is to be limited to the 50-year lifetime voltage value listed in Table 14.

Note that the voltage presented in Figure 16 is shown as sinusoidal for illustration purposes only. It is meant to represent any voltage waveform varying between 0 V and some limiting value. The limiting value can be positive or negative, but the voltage cannot cross 0 V.



RATED PEAK VOLTAGE


Figure 16. Unipolar AC Waveform

RATED PEAK VOLTAGE

OV ------

Figure 17. DC Waveform

OUTLINE DIMENSIONS



COMPLIANT TO JEDEC STANDARDS MS-012-AA

CONTROLLING DIMENSIONS ARE IN MILLIMETERS; INCH DIMENSIONS (IN PARENTHESES) ARE ROUNDED-OFF MILLIMETER EQUIVALENTS FOR REFERENCE ONLY AND ARE NOT APPROPRIATE FOR USE IN DESIGN.

Figure 18. 8-Lead Standard Small Outline Package [SOIC_N] Narrow Body (R-8) Dimensions shown in millimeters and (inches)

ORDERING GUIDE

Model ^{1, 2}	Number of Inputs, V _{DD1} Side	Number of Inputs, V _{DD2} Side	Maximum Data Rate (Mbps)	Maximum Propagation Delay, 5 V (ns)	Maximum Pulse Width Distortion (ns)	Temperature Range	Package Option ³
ADuM1200AR	2	0	1	150	40	−40°C to +105°C	R-8
ADuM1200ARZ	2	0	1	150	40	-40°C to +105°C	R-8
ADuM1200ARZ-RL7	2	0	1	150	40	-40°C to +105°C	R-8
ADuM1200BR	2	0	10	50	3	-40°C to +105°C	R-8
ADuM1200BRZ	2	0	10	50	3	−40°C to +105°C	R-8
ADuM1200BRZ-RL7	2	0	10	50	3	−40°C to +105°C	R-8
ADuM1200CR	2	0	25	45	3	-40°C to +105°C	R-8
ADuM1200CRZ	2	0	25	45	3	−40°C to +105°C	R-8
ADuM1200CRZ-RL7	2	0	25	45	3	-40°C to +105°C	R-8
ADuM1200WSRZ	2	0	1	150	40	−40°C to +125°C	R-8
ADuM1200WSRZ-RL7	2	0	1	150	40	−40°C to +125°C	R-8
ADuM1200WTRZ	2	0	10	50	3	−40°C to +125°C	R-8
ADuM1200WTRZ-RL7	2	0	10	50	3	-40°C to +125°C	R-8
ADuM1200WURZ	2	0	25	45	3	-40°C to +125°C	R-8
ADuM1200WURZ-RL7	2	0	25	45	3	-40°C to +125°C	R-8
ADuM1201AR	1	1	1	150	40	-40°C to +105°C	R-8
ADuM1201AR-RL7	1	1	1	150	40	-40°C to +105°C	R-8
ADuM1201ARZ	1	1	1	150	40	-40°C to +105°C	R-8
ADuM1201ARZ-RL7	1	1	1	150	40	−40°C to +105°C	R-8
ADuM1201BR	1	1	10	50	3	−40°C to +105°C	R-8
ADuM1201BR-RL7	1	1	10	50	3	−40°C to +105°C	R-8
ADuM1201BRZ	1	1	10	50	3	−40°C to +105°C	R-8
ADuM1201BRZ-RL7	1	1	10	50	3	-40°C to +105°C	R-8
ADuM1201CR	1	1	25	45	3	−40°C to +105°C	R-8
ADuM1201CRZ	1	1	25	45	3	-40°C to +105°C	R-8
ADuM1201CRZ-RL7	1	1	25	45	3	-40°C to +105°C	R-8

Model ^{1, 2}	Number of Inputs, V _{DD1} Side	Number of Inputs, V _{DD2} Side	Maximum Data Rate (Mbps)	Maximum Propagation Delay, 5 V (ns)	Maximum Pulse Width Distortion (ns)	Temperature Range	Package Option ³
ADuM1201WSRZ	1	1	1	150	40	-40°C to +125°C	R-8
ADuM1201WSRZ-RL7	1	1	1	150	40	−40°C to +125°C	R-8
ADuM1201WTRZ	1	1	10	50	3	−40°C to +125°C	R-8
ADuM1201WTRZ-RL7	1	1	10	50	3	−40°C to +125°C	R-8
ADuM1201WURZ	1	1	25	45	3	-40°C to +125°C	R-8
ADuM1201WURZ-RL7	1	1	25	45	3	-40°C to +125°C	R-8

¹ Z = RoHS Compliant Part.

AUTOMOTIVE PRODUCTS

The ADuM1200W/ADuM1201W models are available with controlled manufacturing to support the quality and reliability requirements of automotive applications. Note that these automotive models may have specifications that differ from the commercial models; therefore, designers should review the Specifications section of this data sheet carefully. Only the automotive grade products shown are available for use in automotive applications. Contact your local Analog Devices account representative for specific product ordering information and to obtain the specific Automotive Reliability reports for these models.

 $^{^{2}}$ W = Qualified for Automotive Applications.

³ R-8 = 8-lead narrow-body SOIC_N.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Analog Devices Inc.:

ADUM1200BRZ ADUM1200BRZ-RL7 ADUM1200CRZ-RL7 ADUM1200ARZ-RL7 ADUM1200CRZ ADUM1200ARZ

ADUM1200WSRZ ADUM1200WTRZ-RL7 ADUM1200WURZ-RL7 ADUM1200WSRZ-RL7 ADUM1200WURZ

ADUM1200WTRZ