## **Complementary Silicon Plastic Power Transistors**

These devices are designed for use as high-frequency drivers in audio amplifiers.

#### **Features**

- High Current Gain Bandwidth Product
- TO-220 Compact Package
- These Devices are Pb-Free and are RoHS Compliant\*

#### **MAXIMUM RATINGS**

Rating	Symbol	Value	Unit
Collector–Emitter Voltage MJE15028G, MJE15029G MJE15030G, MJE15031G	V <sub>CEO</sub>	120 150	Vdc
Collector-Base Voltage MJE15028G, MJE15029G MJE15030G, MJE15031G	V <sub>CB</sub>	120 150	Vdc
Emitter-Base Voltage	V <sub>EB</sub>	5.0	Vdc
Collector Current – Continuous	Ic	8.0	Adc
Collector Current – Peak	I <sub>CM</sub>	16	Adc
Base Current	Ι <sub>Β</sub>	2.0	Adc
Total Device Dissipation @ T <sub>C</sub> = 25°C Derate above 25°C	P <sub>D</sub>	50 0.40	W W/°C
Total Device Dissipation @ T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	2.0 0.016	W W/°C
Operating and Storage Junction Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-65 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

### THERMAL CHARACTERISTICS


Characteristics	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	2.5	°C/W
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	62.5	°C/W



## ON Semiconductor®


http://onsemi.com

## 8 AMPERE POWER TRANSISTORS COMPLEMENTARY SILICON 120-150 VOLTS, 50 WATTS





#### **MARKING DIAGRAM**



MJE150xx = Device Code x = 28, 29, 30, or 31

A = Assembly Location

Y = Year
WW = Work Week
G = Pb-Free Package

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

<sup>\*</sup>For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

## **ELECTRICAL CHARACTERISTICS** (T<sub>C</sub> = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS	·			
Collector–Emitter Sustaining Voltage (Note 1) ( $I_C = 10 \text{ mAdc}$ , $I_B = 0$ ) MJE15028, MJE15029 MJE15030, MJE15031	V <sub>CEO(sus)</sub>	120 150	- -	Vdc
Collector Cutoff Current $(V_{CE} = 120 \text{ Vdc}, I_B = 0)$ MJE15028, MJE15029 $(V_{CE} = 150 \text{ Vdc}, I_B = 0)$ MJE15030, MJE15031	I <sub>CEO</sub>	-	0.1 0.1	mAdc
Collector Cutoff Current $(V_{CB} = 120 \text{ Vdc}, I_E = 0)$ $MJE15028, MJE15029$ $(V_{CB} = 150 \text{ Vdc}, I_E = 0)$ $MJE15030, MJE15031$	I <sub>CBO</sub>	-	10 10	μAdc
Emitter Cutoff Current (V <sub>BE</sub> = 5.0 Vdc, I <sub>C</sub> = 0)	I <sub>EBO</sub>	-	10	μAdc
ON CHARACTERISTICS (Note 1)				
DC Current Gain ( $I_C = 0.1 \text{ Adc}$ , $V_{CE} = 2.0 \text{ Vdc}$ ) ( $I_C = 2.0 \text{ Adc}$ , $V_{CE} = 2.0 \text{ Vdc}$ ) ( $I_C = 3.0 \text{ Adc}$ , $V_{CE} = 2.0 \text{ Vdc}$ ) ( $I_C = 4.0 \text{ Adc}$ , $V_{CE} = 2.0 \text{ Vdc}$ )	h <sub>FE</sub>	40 40 40 20	- - - -	_
DC Current Gain Linearity (V <sub>CE</sub> From 2.0 V to 20 V, I <sub>C</sub> From 0.1 A to 3 A) (NPN to PNP)	h <sub>FE</sub>	<b>Typ</b> 2 3		
Collector–Emitter Saturation Voltage (I <sub>C</sub> = 1.0 Adc, I <sub>B</sub> = 0.1 Adc)	V <sub>CE(sat)</sub>	-	0.5	Vdc
Base–Emitter On Voltage (I <sub>C</sub> = 1.0 Adc, V <sub>CE</sub> = 2.0 Vdc)	V <sub>BE(on)</sub>	-	1.0	Vdc
DYNAMIC CHARACTERISTICS	<u> </u>			
Current Gain – Bandwidth Product (Note 2) (I <sub>C</sub> = 500 mAdc, V <sub>CE</sub> = 10 Vdc, f <sub>test</sub> = 10 MHz)	f⊤	30	-	MHz

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Pulse Test: Pulse Width  $\leq$  300  $\mu$ s, Duty Cycle  $\leq$  2.0%.

<sup>2.</sup>  $f_T = |h_{fe}| \cdot f_{test}$ .




Figure 1. Power Derating




Figure 2. Thermal Response




Figure 3. Forward Bias Safe Operating Area

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate  $I_C - V_{CE}$  limits of the transistor that must be observed for reliable operation, i.e., the transistor must not be subjected to greater dissipation then the curves indicate.

The data of Figures 3 and 4 is based on  $T_{J(pk)} = 150^{\circ} C$ ;  $T_C$  is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided  $T_{J(pk)} < 150^{\circ} C$ .  $T_{J(pk)}$  may be calculated from the data in Figure 2. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.




Figure 4. Reverse–Bias Switching Safe Operating Area





Figure 5. Capacitances





100 f<sub>T</sub>, CURRENT GAIN-BANDWIDTH PRODUCT (MHz) 90 (PNP) (NPN) 60 50 20 10 0 L 0.1 0.2 0.5 2.0 5.0 1.0 10 IC, COLLECTOR CURRENT (AMP)

Figure 6. Small-Signal Current Gain

NPN — MJE15028 MJE15030

Figure 7. Current Gain-Bandwidth Product





#### PNP — MJE15029 MJE15031






Figure 8. DC Current Gain



NPN



**PNP** 

Figure 9. "On" Voltage




Figure 10. Turn-On Times


Figure 11. Turn-Off Times


### **ORDERING INFORMATION**

Device	Package	Shipping
MJE15028G	TO-220 (Pb-Free)	50 Units / Rail
MJE15029G	TO-220 (Pb-Free)	50 Units / Rail
MJE15030G	TO-220 (Pb-Free)	50 Units / Rail
MJE15031G	TO-220 (Pb-Free)	50 Units / Rail

#### PACKAGE DIMENSIONS

TO-220 CASE 221A-09 **ISSUE AH** 





#### NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- CONTROLLING DIMENSION: INCH.
  DIMENSION Z DEFINES A ZONE WHERE ALL **BODY AND LEAD IRREGULARITIES ARE** ALLOWED

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.570	0.620	14.48	15.75
В	0.380	0.415	9.66	10.53
С	0.160	0.190	4.07	4.83
D	0.025	0.038	0.64	0.96
F	0.142	0.161	3.61	4.09
G	0.095	0.105	2.42	2.66
Н	0.110	0.161	2.80	4.10
J	0.014	0.024	0.36	0.61
K	0.500	0.562	12.70	14.27
٦	0.045	0.060	1.15	1.52
N	0.190	0.210	4.83	5.33
Q	0.100	0.120	2.54	3.04
R	0.080	0.110	2.04	2.79
S	0.045	0.055	1.15	1.39
T	0.235	0.255	5.97	6.47
U	0.000	0.050	0.00	1.27
٧	0.045		1.15	
Z		0.080		2.04

## STYLE 1:

PIN 1. BASE

- COLLECTOR
- EMITTER
- COLLECTOR

ON Semiconductor and iii) are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**ON Semiconductor:** 

MJE15028G MJE15029G MJE15030G MJE15031G