

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2170630087](#)
Status: **Active**
Overview: [Micro-One Wire-to-Board Connector System](#)
Description: [Micro-One Wire-to-Board Header, Vertical, 2.00mm Pitch, Single Row, Glow-Wire Capable, 8 Circuits, Tin-Bismuth Plating, Black, with Cover Tape](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 2170639200-SPK-200 \(PDF\)](#)
[Product Specification 2059790000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 2059790000-AS-000 \(PDF\)](#)

General

Product Family	PCB Headers
Series	217063
Application	Power, Wire-to-Board
Overview	Micro-One Wire-to-Board Connector System
Product Name	Micro-One
UPC	195842005242

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	1316.286/mg
Number of Rows	1
Orientation	Vertical
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount


Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	2059790000-AS-000
Packaging Specification	2170639200-SPK-200
Product Specification	2059790000-PS-000
Sales Drawing	2170630000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[217063 Series](#)

Mates With

Micro-One Receptacle Housing [205979](#)