

1462039-9 ✓ ACTIVE

Axicom | Axicom IM

TE Internal #: 1462039-9

Axicom IM, Signal Relays, 220 VDC Contact Voltage, 250 VAC


Contact Voltage, 100 mW Coil Power (DC), Printed Circuit Board,

PCB-SMT

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Signal Relays



Contact Voltage Rating: 220 VDC

Signal Relay Coil Power Rating (DC): 100 mW

Isolation (HF Parameter): -18.8dB @ 900MHz, -37dB @ 100MHz

Insertion Loss (HF Parameter): -.03dB @ 100MHz, -.33dB @ 900MHz

## Features

### Product Type Features

Relay Type	IM Relay
Product Type	Relay

### Electrical Characteristics

Coil Power Rating Class	50 – 300 mW
Actuating System	DC
Insulation Initial Dielectric Between Open Contacts	750 Vrms
Contact Limiting Short-Time Current	5 A
Insulation Initial Dielectric Between Contacts and Coil	1500 Vrms
Insulation Initial Dielectric Between Coil/Contact Class	1500 V – 2500 VA
Voltage Standing Wave Ratio (HF Parameter)	1.06 @ 100MHz, 1.49 @ 900Mhz
Insulation Initial Dielectric Between Adjacent Contacts	750 Vrms
Insulation Initial Resistance	1000000 MΩ
Contact Limiting Making Current	5 A
Coil Resistance	58 Ω
Contact Limiting Continuous Current	5 A



Coil Type	Bistable
Contact Limiting Breaking Current	5 A
Contact Switching Load (Min)	.1mA @ .0001V
Contact Voltage Rating	220 VDC
Signal Relay Coil Power Rating (DC)	100 mW
Signal Relay Coil Voltage Rating	2.4 VDC
Signal Relay Contact Switching Voltage (Max)	220 VDC
Signal Relay Coil Magnetic System	Bistable, 1 Coil

### Signal Characteristics

Isolation (HF Parameter)	-18.8dB @ 900MHz, -37dB @ 100MHz
Insertion Loss (HF Parameter)	-.03dB @ 100MHz, -.33dB @ 900MHz

### Body Features

Insulation Special Features	2000V Initial Surge Withstand Voltage Between Contacts & Coil
Weight	.75 g[.026 oz]

### Contact Features

Contact Plating Material	Gold
Contact Current Class	0 – 5 A
Contact Special Features	Bifurcated/Twin Contacts
Signal Relay Terminal Type	PCB-SMT
Signal Relay Contact Current Rating	5 A
Signal Relay Contact Arrangement	2 Form C (2 CO)
Contact Material	AgNi+Au
Contact Number of Poles	2

### Termination Features

Termination Type	Surface Mount
------------------	---------------

### Mechanical Attachment

Signal Relay Mounting Type	Printed Circuit Board
----------------------------	-----------------------

### Dimensions

Width Class (Mechanical)	0 – 6 mm
Width	6 mm[.236 in]
Height	5.65 mm[.222 in]



Length Class (Mechanical)	0 – 10 mm
Length	10 mm[.393 in]
Height Class (Mechanical)	0 – 6 mm
Dimensions (L x W x H) (Approximate)	10 x 6 x 5.65 mm[.393 x .236 x .222 in]

### Usage Conditions

Environmental Ambient Temperature (Max)	85 °C[185 °F]
Environmental Ambient Temperature Class	70 – 85°C
Operating Temperature Range	-40 – 85 °C

### Operation/Application

Performance Type	High Current
------------------	--------------

### Packaging Features

Packaging Method	Reel
------------------	------

### Other

Additional Features	Gull Wing
---------------------	-----------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # CAT-AX41-IM11B  
Standard Signal Relay 2 Form C,2 CO Cont

## Also in the Series | Axicom IM



RJ45 Connectors(2)



Signal Relays(124)


## Customers Also Bought



TE Part #1676285-2  
RN 0805 2K21 0.1% 10PPM 1KRL



TE Part #647402-6  
06P SL156 HSG W/RMP&TABS,OVSZ



TE Part #1474654-2  
FSN-11A-20




TE Part #1-86479-5  
06 MODII HDR DRRA UNSHRD .100



TE Part #1734366-4  
Std USB Type A, VT, T/H




TE Part #5569380-1  
STK MJ,8POS,2X1,SHLD,CAT5



TE Part #1658525-2  
622-3453LF, PCB IDC, LEAD FREE



TE Part #1825002-9  
ADF0604=DIP SWT,FLUSH,THRU/HL



## Documents

### Product Drawings

[IM48DGR=IM RELAY 100 MW 2.4 V](#)

English

[IM48DGR=IM RELAY 100 MW 2.4 V](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1462037-2\\_A.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1462037-2\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1462037-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[Axicom Signal and High Frequency Relays \(RF Switches\) APPLICATION NOTE #2](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

[IM\\_Datasheet PCN P-20-019002](#)

English

### Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English

1462039-9

Axicom IM, Signal Relays, 220 VDC Contact Voltage, 250 VAC Contact Voltage, 100 mW Coil Power (DC), Printed Circuit Board, PCB-SMT

