



**BIPOLAR TRANSISTOR (PNP)**
**FEATURES**

- Complementary to BC848
- Ideally suited for automatic insertion
- For switching and AF amplifier applications
- Surface Mount device


**SOT-23**

**MECHANICAL DATA**

- Case: SOT-23
- Case Material: Molded Plastic. UL flammability
- Classification Rating: 94V-0
- Weight: 0.008 grams (approximate)

**MAXIMUM RATINGS (T<sub>A</sub> = 25°C unless otherwise noted)**

| Parameter                                   | Symbol           | Value     | Unit |
|---------------------------------------------|------------------|-----------|------|
| Collector-Base Voltage                      | V <sub>CB0</sub> | -30       | V    |
| Collector-Emitter Voltage                   | V <sub>CEO</sub> | -30       | V    |
| Emitter-Base Voltage                        | V <sub>EBO</sub> | -5        | V    |
| Collector Current                           | I <sub>C</sub>   | -100      | mA   |
| Collector Power Dissipation                 | P <sub>C</sub>   | 200       | mW   |
| Thermal Resistance From Junction To Ambient | R <sub>θJA</sub> | 625       | °C/W |
| Junction Temperature                        | T <sub>J</sub>   | 150       | °C   |
| Storage Temperature                         | T <sub>STG</sub> | -55 ~+150 | °C   |

**ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise specified)**


| Parameter                            | Symbol               | Min | Typ | Max  | Unit | Conditions                                            |
|--------------------------------------|----------------------|-----|-----|------|------|-------------------------------------------------------|
| Collector-base breakdown voltage     | V <sub>(BR)CBO</sub> | -30 |     |      | V    | I <sub>C</sub> =-10uA, I <sub>E</sub> =0              |
| Collector-emitter breakdown voltage  | V <sub>(BR)CEO</sub> | -30 |     |      | V    | I <sub>C</sub> =-10mA, I <sub>B</sub> =0              |
| Emitter-base breakdown voltage       | V <sub>(BR)EBO</sub> | -5  |     |      | V    | I <sub>E</sub> =-1uA, I <sub>C</sub> =0               |
| Collector cut-off current            | I <sub>CBO</sub>     |     |     | -0.1 | uA   | V <sub>CB</sub> =-30V, I <sub>E</sub> =0              |
| Emitter cut-off current              | I <sub>EBO</sub>     |     |     | -0.1 | uA   | V <sub>EB</sub> =-5V, I <sub>C</sub> =0               |
| DC current gain                      | h <sub>FE1</sub>     | 110 |     | 800  |      | V <sub>CE</sub> =-5V, I <sub>C</sub> =-2mA            |
| Collector-emitter saturation voltage | V <sub>CE(sat)</sub> |     |     | -0.5 | V    | I <sub>C</sub> =-100mA, I <sub>B</sub> =-5mA          |
| Base-emitter saturation voltage      | V <sub>BE(sat)</sub> |     |     | -1.1 | V    | I <sub>C</sub> =-100mA, I <sub>B</sub> =-5mA          |
| Transition frequency                 | f <sub>T</sub>       | 100 |     |      | MHz  | V <sub>CE</sub> =-5V, I <sub>C</sub> =-10mA, f=100MHz |
| Collector output capacitance         | C <sub>ob</sub>      |     |     | 4.5  | pF   | V <sub>CE</sub> =-10V, I <sub>E</sub> =0, f=1MHz      |

**CLASSIFICATION OF h<sub>FE</sub>**

| Rank    | BC858A  | BC858B  | BC858C  |
|---------|---------|---------|---------|
| Range   | 125-250 | 220-475 | 420-800 |
| Marking | 3J      | 3K      | 3L      |

**BIPOLAR TRANSISTOR (PNP)**

**Typical Characteristics**




**BIPOLAR TRANSISTOR (PNP)**

**SOT-23 Package Outline Dimensions**



| Symbol | Dimensions In Millimeters |       | Dimensions In Inches |       |
|--------|---------------------------|-------|----------------------|-------|
|        | Min.                      | Max.  | Min.                 | Max.  |
| A      | 0.900                     | 1.150 | 0.035                | 0.045 |
| A1     | 0.000                     | 0.100 | 0.000                | 0.004 |
| A2     | 0.900                     | 1.050 | 0.035                | 0.041 |
| b      | 0.300                     | 0.500 | 0.012                | 0.020 |
| c      | 0.080                     | 0.150 | 0.003                | 0.006 |
| D      | 2.800                     | 3.000 | 0.110                | 0.118 |
| E      | 1.200                     | 1.400 | 0.047                | 0.055 |
| E1     | 2.250                     | 2.550 | 0.089                | 0.100 |
| e      | 0.950 TYP                 |       | 0.037 TYP            |       |
| e1     | 1.800                     | 2.000 | 0.071                | 0.079 |
| L      | 0.550 REF                 |       | 0.022 REF            |       |
| L1     | 0.300                     | 0.500 | 0.012                | 0.020 |
| θ      | 0°                        | 8°    | 0°                   | 8°    |

**SOT-23 Suggested Pad Layout**




**Note:**

1. Controlling dimension: in millimeters
2. General tolerance:  $\pm 0.05\text{mm}$
3. The pad layout is for reference purposes only

**BIPOLAR TRANSISTOR (PNP)**


**SOT-23 Tape and Reel**

**SOT-23 Embossed Carrier Tape**




| DIMENSIONS ARE IN MILLIMETER |      |      |      |       |      |      |      |      |      |      |
|------------------------------|------|------|------|-------|------|------|------|------|------|------|
| TYPE                         | A    | B    | C    | d     | E    | F    | P0   | P    | P1   | W    |
| SOT-23                       | 3.15 | 2.77 | 1.22 | Ø1.50 | 1.75 | 3.50 | 4.00 | 4.00 | 2.00 | 8.00 |
| TOLERANCE                    | ±0.1 | ±0.1 | ±0.1 | ±0.1  | ±0.1 | ±0.1 | ±0.1 | ±0.1 | ±0.1 | ±0.1 |

**SOT-23 Tape Leader and Trailer**



**SOT-23 Reel**



| DIMENSIONS ARE IN MILLIMETER |      |       |       |     |        |       |      |       |
|------------------------------|------|-------|-------|-----|--------|-------|------|-------|
| REEL OPTION                  | D    | D1    | D2    | G   | H      | I     | W1   | W2    |
| 7" DIA                       | Ø178 | 54.40 | 13.00 | R78 | R25.60 | R6.50 | 9.50 | 12.30 |
| TOLERANCE                    | ±2   | ±1    | ±1    | ±1  | ±1     | ±1    | ±1   | ±1    |