Wire Wound Magnetically Shielded SMD Power Inductor

ASPI-4030S





> FEATURES:

- · Shielded magnetics, low radiation
- · Large Terminal surface for good PCB bonding
- Low DCR, High Energy storage, suitable for large currents
- Ideal for a variety of DC-DC converter inductor applications

> APPLICATIONS:

- Partable communication equipment
- OA equipment
- LCD, DVD, modem, set-top box
- DC/DC converters

ELECTRICAL SPECIFICATIONS:

Abracon P/N:	ASPI-4030S Series				
Operating Temperature :	-40°C to +125°C				
Storage Temperature :	-10°C to +40°C and 70% R.H. max				

Part Number	Inductance	L Tolerance	DC Resistance (±30%)	Saturation Current	Temperature Rise Current	Self resonant frequency	Inductance Code Marking	
Units	μН	-	Ω	A Max	A Max	MHz Min		
Symbol	L	N, M	DCR	Isat	Irms	SRF		
ASPI-4030S-R91	0.91	N	0.013	6.25	4.15	100	R91	
ASPI-4030S-1R0	1.0	N	0.014	5.26	4.15	70	1R0	
ASPI-4030S-1R2	1.2	N	0.015	5.80	3.82	80	1R2	
ASPI-4030S-1R5	1.5	N	0.020	4.84	3.34	62	1R5	
ASPI-4030S-1R8	1.8	N	0.025	5.40	3.20	60	1R8	
ASPI-4030S-2R2	2.2	N	0.030	4.90	2.95	52	2R2	
ASPI-4030S-3R3	3.3	M	0.040	3.30	2.40	38	3R3	
ASPI-4030S-4R3	4.3	M	0.055	2.95	2.10	37	4R3	
ASPI-4030S-4R7	4.7	M	0.060	2.90	2.00	31	4R7	
ASPI-4030S-5R6	5.6	M	0.065	2.60	1.95	30	5R6	
ASPI-4030S-6R8	6.8	M	0.090	2.75	1.60	24	6R8	
ASPI-4030S-7R5	7.5	M	0.085	2.20	1.65	26	7R5	
ASPI-4030S-8R2	8.2	M	0.090	2.10	1.60	26	8R2	
ASPI-4030S-100	10	M	0.100	1.95	1.50	21	100	
ASPI-4030S-120	12	M	0.135	1.70	1.30	18	120	
ASPI-4030S-150	15	M	0.190	1.65	1.11	16	150	
ASPI-4030S-180	18	M	0.200	1.40	1.10	10	180	
ASPI-4030S-220	22	M	0.225	1.30	1.00	10	220	
ASPI-4030S-330	33	M	0.330	1.10	0.84	10	330	
ASPI-4030S-360	36	M	0.335	1.05	0.83	9.8	360	
ASPI-4030S-390	39	M	0.435	1.03	0.73	10	390	
ASPI-4030S-470	47	M	0.445	0.95	0.72	8.4	470	
ASPI-4030S-510	51	M	0.470	0.90	0.70	8.4	510	
ASPI-4030S-560	56	M	0.555	0.85	0.65	8.4	560	
ASPI-4030S-620	62	M	0.585	0.80	0.63	7.0	620	
ASPI-4030S-680	68	M	0.868	0.72	0.52	7.0	680	
ASPI-4030S-750	75	M	1.020	0.70	0.48	6.3	750	
ASPI-4030S-820	82	M	1.060	0.66	0.47	5.6	820	
ASPI-4030S-910	91	M	1.100	0.65	0.46	5.6	910	
ASPI-4030S-101	100	M	1.150	0.60	0.45	5.6	101	
ASPI-4030S-121	120	M	1.350	0.55	0.42	5.4	121	

Test Conditions:

a. Ambient Temperature: 20±15°C

b. Relative Humidity: 65%±20%

c. Air Pressure: 86KPa to 106KPa

Inductance (L): WK3260B LCR meter or equivalent, 100kHz, 1Vrms

Direct Current Resistance (DCR): HIOKI 3540 or equivalent

Saturation Current (Isat): WK3260B LCR meter or equivalent

Isat: Based on inductance change ($\Delta L/Lo :\leq -30\%$)

Temperature rise current (Irms): Electric Power, Electric current meter, Thermometer

Irms: Based on temperature rise ($\Delta T : 40^{\circ}C \text{ TYP.}$)




Wire Wound Magnetically Shielded SMD Power Inductor

ASPI-4030S







ELECTRICAL CHARACTERISTICS CURVES



> PART IDENTIFICATION:



OUTLINE DIMENSIONS:



Dimensions: mm






Wire Wound Magnetically Shielded SMD Power Inductor

ASPI-4030S

RoHS/RoHS II Compliant


4.0 x 4.0 x 3.0 mm

Materials



No	Components	Material				
1	Ferrite Core	Ni-Zn Ferrite				
2	Wire	Polyurethane System enameled copper wire				
3	Magnetic Glue	Epoxy resin and magnetic powder				
4	Plating Electrodes	Plating: Ag/Ni/Sn				
5	Outer Electrodes	Top surface solder coating: Sn96.5%/Ag3%/Cu0.5%				


REFLOW PROFILE:



- Δ Preheat condition: 150 ~200°C /60~120sec.
- Δ Allowed time above 217°C: 60~90sec.
- Δ Max temp: 260°C
- Δ Max time at max temp: 5sec. Δ Solder paste: Sn/3.0Ag/0.5Cu
- Δ Allowed Reflow time: 2x max

> TAPE & REEL:

T: 2,000pcs / reel



A0	В0	W	E	F	P0	P1	P2	D0	T	K
4.3±0.1	4.3±0.1	12.0±0.3	1.75±0.1	5.5±0.1	4.0±0.1	8.0±0.1	2.0±0.1	1.5+0.1/-0.0	0.4±0.03	3.2±0.1

Storage Conditions

- a. To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled.
- b. Recommended conditions: -10° C $\sim +40^{\circ}$ C, 70% RH (Max.)
- c. Even under ideal storage conditions, solderability of products electrodes may decrease as time passes. For this reason, product should be used with one year from the time of delivery.
- d. In case of storage over 12 months, solderability shall be checked before actual usage.

Dimensions: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

ASPI-4030S-510M-T ASPI-4030S-560M-T ASPI-4030S-2R2N-T ASPI-4030S-3R3M-T ASPI-4030S-7R5M-T ASPI-4030S-1R5N-T ASPI-4030S-100M-T ASPI-4030S-150M-T ASPI-4030S-390M-T ASPI-4030S-6R8M-T ASPI-4030S-180M-T ASPI-4030S-121M-T ASPI-4030S-120M-T ASPI-4030S-1R0N-T ASPI-4030S-8R2M-T ASPI-4030S-180M-T ASPI-4030S-1R8N-T ASPI-4030S-220M-T ASPI-4030S-750M-T ASPI-4030S-820M-T ASPI-4030S-5R6M-T ASPI-4030S-1R2N-T ASPI-4030S-620M-T ASPI-4030S-680M-T ASPI-4030S-101M-T ASPI-4030S-330M-T ASPI-4030S-910M-T ASPI-4030S-R91N-T ASPI-4030S-4R3M-T ASPI-4030S-330M-T