





REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	FIRST RELEASE	Oct.22.2015	Drack	Tommy



P type, Normal Key

Item	Part number	Cable OD Range
1	MASCAP1600-S1	4.5-7.5 mm
2	MASCAP1600-S2	7.5-11.0 mm
3	MASCAP1600-S3	11.0-15.0 mm

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

INSULATION INSERT: PA66, UL94 V0
 SEAL: VITON, EPDM
 HOUSING BODY: ZINC DIE CAST, NICKEL PLATED
 COUPLING NUT: ZINC DIE CAST, NICKEL PLATED

2. SPECIFICATIONS:

- 2.1 CURRENT RATING: 9 AMPS
- 2.2 VOLTAGE RATING: 125 V AC/DC
- 2.3 OPERATING TEMPERATURE: -20°C TO +130°C
- 2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 2500 VOLTS AC.
- 2.5 DEGREE OF PROTECTION: IP67 (MATED CONDITION)
- 2.6 DEGREE OF POLLUTION: 3 PER UL840
- 2.7 OVERVOLTAGE CATEGORY: III PER UL840
- 2.8 MATING CYCLE DURABILITY: >500 CYCLES
- 2.9 ROHS COMPLIANT

3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

QUANTITY	SEE PART NUMBER CHART	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST

Amphenol

Site Systems - www.amphenol-site.com
 44724 Morley Drive
 Clinton Township, MI 48036

M23A PLUG, STR, 16P, P TYPE, CHECKMATE

UNLESS OTHERWISE SPECIFIED	SIGNATURES	DATE	SIZE	TYPE	DWG NO.	REVISION
1) All dimensions are in millimeters. 2) Tolerances are as follows: a) Holes: ±.104 b) Radii: ±.014 c) Flat DEC: ±0.15 d) Flat DEC: ±.015 3) Note reference = 	DRAWN: Dax CHECKED: [Signature] ENGINEER: [Signature] APPROVAL: [Signature]	04/22/05	B	C-	MASCAP1600-Sx	A1
PROCESS SPECIFICATIONS: THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA ARE THE PROPERTY OF AMPHENOL CORPORATION. NO RIGHTS OR PERMISSIONS ARE GRANTED FOR REPRODUCTION OR MANUFACTURING VARIATIONS.	CUSTOMER:		SCALE: NONE			
NEXT ASSY:						