



# **PI3WVR13412**

### DisplayPort 1.3/1.4, HDMI 2.0 Video Switch

### **Description**

The PI3WVR13412 is a multi-standard video switch with wide voltage range capability. It supports DisplayPort 1.3/1.4, HDMI 2.0, and emerging and proprietary standard.

The PI3WVR13412 can pass high-speed signals up to 1.2 V peak-to-peak differential with a common-mode voltage from 0 to 3.4V for TMDS signal.


The wide voltage range allow DC-coupled multi-standard operation. Eliminating AC coupling capacitors saves board space and improves signal integrity for dense PCB design.

In addition to four high-speed lanes, PI3WVR13412 also switches the DDC and HPD signals or AUX and HPD signals using the DDC/ AUX and HPD channel mux/demux.

### **Applications**

- → Routing of DisplayPort video signals with low signal attenuation between source and sink for PC and monitor.
- → Routing of HDMI 2.0 video signals with low signal attenuation between source and sink for 4K2K ultra high definition video display and broadcast video equipment.

## **Block Diagram**



#### **Features**

- → DisplayPort 1.3/1.4, HDMI 2.0 Electrical standard compatible
- → 4-lane, 1:2 and 2:1 switches that support RBR, HBR1, HBR2 and HBR3
- → Data rate: 8.1 Gbps for high-speed channels
- → Supports DDC with HPD channel mux/demux @ HDMI
- → Supports 720 Mbps high-speed DP AUX @ DP
- → -1.6 dB Insertion Loss for high-speed channels @ 4.05 GHz
- → -3 dB Bandwidth for high-speed channels: 7 GHz
- → Return loss for high-speed channels @ 4.05 GHz: -11 dB
- → Low Crosstalk for high-speed channels: -35 dB@4.05 GHz
- → Low Off Isolation for high-speed channels: -20 dB@4.05 GHz
- → Low channel-to-channel skew, 35ps max
- → Low Bit-to-Bit Skew, 5ps typ (between '+' and '-' bits)
- → VDD Operating Range: 3.3V +/-10%
- → ESD Tolerance: 1.5kV HBM
- → Packaging (Pb-free & Green): 42 TQFN (ZHE)

### Ordering Information

Part Number	Package	Description
PI3WVR13412ZHEX	l ZH	42-contact, Very Thin Quad Flat No- Lead (TQFN)

#### Notes:

- EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/ EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- See http://www.diodes.com/quality/lead-free/for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free. Thermal characteristics can be found on the company web site at www.diodes.com/design/support/packaging/
- 3. E = Pb-free and Green
- 4. X suffix = Tape/Reel