

# DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-5007Y** 



# Release | Revision: A/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker.

#### Page 1

Speaker Specification

#### Page 2

Measuring Circuit

Typical Frequency Response Curve

## Page 3

Dimensions

Speaker Specification		
Item	Specification	Testing Condition
Dimensions	Ø50.0 x H7.0 mm	
Voice Coil Impedance	8Ω±15%	At 1.2KHz 1V
Resonant Frequency	580±20%Hz	At 1.0V
Output S.P.L.	87±2dB at 0.8, 1.0, 1.2, 1.5 KHz in average	At 0.5m/1.0W
Frequency Response	f0~10KHz	-10dB
Rated Input Power	2.0 W	
Max Input Power	3.0 W	
Operation	Must be normal	Program source 2.0 W
Noise	Must be normal	Sine wave 4.0 V
Heat Test	Meet items 8 & 9 after test	55±2°C 16 hours
Humidity Test	Meet items 8 & 9 after test	40±2°C 90∼95%RH 48 hours
Load Test	Meet items 8 & 9 after test	2.0 W 100 hours
Magnet	Ф12.5 x 1.5mm NdFeB	
Net Weight	12.8g	
Polarity	When a positive DC current is applied to the terminal marked(+), the diaphragm moves forward.	





# DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-5007Y** 



Release | Revision: A/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker.

#### Page 1

Speaker Specification


## Page 2


Measuring Circuit

Typical Frequency Response Curve

#### Page 3


Dimensions





MEASUREMENT

# **Typical Frequency Response Curve**





Tolerance:±0.2mm



# DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-5007Y** 



Release | Revision: A/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker.

#### Page 1

Speaker Specification

# Page 2

Measuring Circuit

Typical Frequency Response Curve

## Page 3

Dimensions

