



light source

- work equipment
- connected load
- Power consumption
- luminous flux
- luminous efficacy
- colour temperature
- color rendering index (CRI)
- chromaticity tolerance LED

System of protection

- class of protection
- technology
- operation
- luminaire body
- lamp cover
- tubular sections

balance of articulation joints

- weight (net)
- mains lead

Fastening

- lens; dimensions
- lens material
- lens; diopters
- special features

LED

- Energy efficiency category A/A+/A++
- electronic plug-in ballast
- 100-240 V; 50/60 Hz
- approx. 13 W
- approx. 750 lm
- approx. 57 lm/W
- neutral white, approx. 4000 K
- >= 90 (R9>50)
- 3 SDCM
- IP20
- II
- multi-stage switchable, continuously dimmable
- multi-function switch
- plastic, untreated, black
- screen, milky, Polyamide
- tubular aluminium section, anodized, aluminium coloured
- anodised
- spring
- approx. 3.0 kg
- approx. 3.4 m; mains plug
- BS 1363
- CEE 7/XVI
- NEMA 1-15P
- screw-down flange
- Ø 160 mm
- glass
- 3,5
- long arms, light characteristic can be adjusted with a three-way switch



BS 1363



CEE 7/XVI



NEMA 1-15P

illuminance

distance: 15 cm

Em: 4099 lx
Emax: 5537 lx
Emin: 1894 lx

